

Product Name: 3-[3-(Benzyloxy)phenyl]propionic acid, 96%
Catalog Number: H33899.03

CAS Number: 57668-34-5
IUPAC Name: 3-[3-(benzyloxy)phenyl]propanoic acid
Molecular Formula: C₁₆H₁₆O₃
Molecular Weight: 256.30
InChI Key: HVXOYUOKPLHWN-UHFFFAOYSA-N
SMILES: OC(=O)CCC1=CC(OCC2=CC=CC=C2)=CC=C1
Synonym: 3-[3-(benzyloxy)phenyl]propanoic acid

Product Specification

Appearance (Color): White
Form: Crystals or powder or crystalline powder
Assay (Silylated GC): ≥95.0%
Assay (Aqueous acid-base Titration): ≥95.0 to ≤105.0%
Melting Point (clear melt): 79.5-88.5°C

Date Of Print: 06/05/2025

Product Specifications are subject to amendment and may change over time. Data contained is accurate as of the date printed.