

Product Name: 2,5-Norbornadiene, 97%, stab with 250 ppm BHT
Catalog Number: L13935.AE

CAS Number: 121-46-0
IUPAC Name: bicyclo[2.2.1]hepta-2,5-diene
Molecular Formula: C7H8
Molecular Weight: 92.14
MDL Number: MFCD00082301
InChI Key: SJYNFBVQFBRSIB-UHFFFAOYSA-N
SMILES: C1C2C=CC1C=C2
Synonym: norbornadiene1,2,5-norbornadiene

Product Specification

Appearance (Color): Clear colourless
Form: Liquid
Assay (GC): ≥96.0% (non-U.S. sourced material)
Comment: Material sourced in the U.S. and in other countries
Assay from Supplier's CofA: ≥96.0% (U.S. sourced material)
Refractive Index: 1.4685-1.4735 @ 20°C (non-U.S. sourced material)

Date Of Print: 04/26/2025

Product Specifications are subject to amendment and may change over time. Data contained is accurate as of the date printed.