

#TOP100antibodies

You've made these our Bestsellers!



PROMOTION

Free Nalgene Antibodies Bottle

When you purchase 3 Primary and/or Flow Cytometry Antibodies

Valid till 30th June 2018



Bestsellers

Alexa Fluor™ Secondary Antibodies

Ordering Information

Cat No	Products	Unit Size
A21206	Donkey anti-Rabbit IgG (H+L) Highly Cross-Adsorbed Secondary Antibody, Alexa Fluor 488	500 ul
A21207	Donkey anti-Rabbit IgG (H+L) Highly Cross-Adsorbed Secondary Antibody, Alexa Fluor 594	500 ul
A21202	Donkey anti-Mouse IgG (H+L) Highly Cross-Adsorbed Secondary Antibody, Alexa Fluor 488	500 ul
A11029	Goat anti-Mouse IgG (H+L) Highly Cross-Adsorbed Secondary Antibody, Alexa Fluor 488	500 ul
A-11004	Goat anti-Mouse IgG (H+L) Cross-Adsorbed Secondary Antibody, Alexa Fluor 568	500 ul
A11005	Goat anti-Mouse IgG (H+L) Cross-Adsorbed Secondary Antibody, Alexa Fluor 594	500 ul
A11034	Goat anti-Rabbit IgG (H+L) Highly Cross-Adsorbed Secondary Antibody, Alexa Fluor 488	500 ul
A32732	Goat anti-Rabbit IgG (H+L) Highly Cross-Adsorbed Secondary Antibody, Alexa Fluor Plus 555	1 mg
A11013	Goat anti-Human IgG (H+L) Cross-Adsorbed Secondary Antibody, Alexa Fluor 488	500 ul
A21445	Goat anti-Human IgG (H+L) Cross-Adsorbed Secondary Antibody, Alexa Fluor 647	500 ul
A11017	F(ab') ₂ -Goat anti-Mouse IgG (H+L) Cross-Adsorbed Secondary Antibody, Alexa Fluor 488	250 ul
A11070	F(ab') ₂ -Goat anti-Rabbit IgG (H+L) Cross-Adsorbed Secondary Antibody, Alexa Fluor 488	250 ul




No.2 Bestsellers
 Invitrogen™ and eBioscience™
 Primary Antibodies

Ordering Information

Cat No	Products	Unit Size
MA1-80218	6x-His Tag Monoclonal Antibody (AD1.1.10), HRP	100 ug
322588	alpha Tubulin Monoclonal Antibody (B-5-1-2), Alexa Fluor 488	100 ug
374200	beta Amyloid (N-terminal) Monoclonal Antibody (NAB228)	100 ug
PA129662	beta-2 Microglobulin Polyclonal Antibody, HRP	200 ug
322600	beta Tubulin Monoclonal Antibody (2 28 33)	100 ug
HAH 002-01-02	Butyrylcholinesterase Monoclonal Antibody (3E8)	100 ug
MA5-12960	Cardiac Troponin T Monoclonal Antibody (13-11)	500 ul
131900	E-cadherin Monoclonal Antibody (ECCD-2)	100 ug
MA1-24226	EGFR Monoclonal Antibody (F4)	100 ug
136200	ERK1/ERK2 Monoclonal Antibody (ERK-7D8)	200 ug
396500	FAK Monoclonal Antibody (ZF002)	100 ug
MA5-15738	GAPDH Loading Control Monoclonal Antibody (GA1R)	100 ug
G10362	GFP Tag Antibody, ABfinity™ Rabbit Monoclonal	100 ug
MA5-15256	GFP Tag Monoclonal Antibody (GF28R)	100 ug
A21311	GFP Tag Polyclonal Antibody, Alexa Fluor 488	100 ul
A21270	Golgin-97 Monoclonal Antibody (CDF4)	100 ug
715500	HA Tag Polyclonal Antibody	100 ug
PA5-35290	HLA-DQB1 Polyclonal Antibody	400 ul
MA1-080	Hepatitis C Virus Core Antigen Monoclonal Antibody (C7-50)	100 ul
A-21271	HuC/HuD Monoclonal Antibody (16A11)	100 ug
R95025	Myc Tag Monoclonal Antibody	50 ul
71-1500	Occludin Polyclonal Antibody	100 ug
PA534805	p21 Polyclonal Antibody	100 ul
MA1-412	Progesterone Receptor Monoclonal Antibody (alpha PR-22)	100 ug
PA5-27802	SHP-1 Polyclonal Antibody	100 ug
131600	Ubiquitin Monoclonal Antibody (Ubi-1)	100 ug
R96025	V5 Tag Monoclonal Antibody	50 ul
339100	ZO-1 Monoclonal Antibody (ZO1-1A12)	100 ug



No. 3 Bestsellers

**Invitrogen™ and eBioscience™
Flow Cytometry Antibodies & Reagents**

Ordering Information (eBioscience™ Flow Cytometry Antibodies)

Cat No	Products	Unit Size
16-0037-81	CD3 Monoclonal Antibody (OKT3), Functional Grade, eBioscience™	50 ug
17-0079-42	CD7 Monoclonal Antibody (eBio124-1D1 (124-1D1)), APC, eBioscience™	100 tests
16-0111-85	CD11a (LFA-1alpha) Monoclonal Antibody (M17/4), Functional Grade, eBioscience™	500 ug
16-0492-85	CD49d (Integrin alpha 4) Monoclonal Antibody (R1-2), Functional Grade, eBioscience™	500 ug
14-5982-85	CD274 (PD-L1, B7-H1) Monoclonal Antibody (MIH5), eBioscience™	500 ug
14-2799-80	CD279 (PD-1) Monoclonal Antibody (eBioJ105 (J105)), eBioscience™	25 ug
14-4877-82	EOMES Monoclonal Antibody (WD1928), eBioscience™	100 ug
14-4776-82	FOXP3 Monoclonal Antibody (PCH101), eBioscience™	100 ug
14-9966-82	Gata-3 Monoclonal Antibody (TWAJ), eBioscience™	100 ug
12-8899-41	Granzyme B Monoclonal Antibody (GB11), PE, eBioscience™	25 tests
14-5698-82	Ki-67 Monoclonal Antibody (SolA15), eBioscience™	100 ug
53-0443-82	LYVE1 Monoclonal Antibody (ALY7), Alexa Fluor 488, eBioscience™	100 ug
56-5321-82	MHC Class II (I-A/I-E) Monoclonal Antibody (M5/114.15.2), Alexa Fluor 700, eBioscience™	100 ug
53-6503-82	Myosin 4 Monoclonal Antibody (MF20), Alexa Fluor 488, eBioscience™	100 ug
62-0199-42	CD19 Monoclonal Antibody (HIB19), Super Bright 436, eBioscience™	100 tests
62-0279-42	CD27 Monoclonal Antibody (O323), Super Bright 436, eBioscience™	100 tests
63-0081-82	CD8a Monoclonal Antibody (53-6.7), Super Bright 600, eBioscience™	100 ug
63-0566-42	CD56 (NCAM) Monoclonal Antibody (TULY56), Super Bright 600, eBioscience™	100 tests
64-0081-82	CD8a Monoclonal Antibody (53-6.7), Super Bright 645, eBioscience™	100 ug
64-0451-82	CD45 Monoclonal Antibody (30-F11), Super Bright 645, eBioscience™	100 ug
67-9488-42	KLRG1 Monoclonal Antibody (13F12F2), Super Bright 702, eBioscience™	100 tests
67-0451-80	CD45 Monoclonal Antibody (30-F11), Super Bright 702, eBioscience™	25 ug
78-0042-80	CD4 Monoclonal Antibody (RM4-5), Super Bright 780, eBioscience™	25 ug
78-0198-41	CD19 Monoclonal Antibody (SJ25C1), Super Bright 780, eBioscience™	25 tests
16-4321-85	Rat IgG2a kappa Isotype Control, Functional Grade, eBioscience™	500 ug

Ordering Information (eBioscience™ Flow Cytometry Reagents⁺)

Cat No	Products	Unit Size
00-4333-57	1X RBC Lysis Buffer, eBioscience™	200 ml
00-4555-56	Accutase - Enzyme Cell Detachment Medium	100 ml
00-5223-56	Fixation/Permeabilization Diluent, eBioscience™	100 ml
00-5523-00	Foxp3 / Transcription Factor Staining Buffer Set, eBioscience™	1 Kit
00-4958-02	Fluoromount-G™	25 ml
SB-4400-42	Super Bright Staining Buffer, eBioscience™	100 tests
01-2222-42	UltraComp eBeads™ Compensation Beads	100 tests

Ordering Information (Invitrogen™ Flow Cytometry Antibodies)

Cat No	Products	Unit Size
A15764	Bcl-2 Monoclonal Antibody (Bcl2/100), FITC	100 tests
MHCD0418	CD4 Monoclonal Antibody (S3.5), PE-Cyanine5.5	500 ul
Q10009	CD8 Monoclonal Antibody (3B5), Qdot 605	100 ul
Q10064	CD14 Monoclonal Antibody (TüK4), Qdot 800	100 ul
Q10379	CD19 Monoclonal Antibody (6D5), Qdot 655	100 ul
Q22139	CD19 Monoclonal Antibody (SJ25-C1), Qdot 800	25 ul
A15724	CD36 Monoclonal Antibody (NL07), APC	100 tests
MHCD4520	CD45 Monoclonal Antibody (HI30), Alexa Fluor 488	500 ul
MHCD5617	CD56 Monoclonal Antibody (MEM-188), PE-Texas Red	500 ul
17-0909-41	CD90 (Thy-1) Monoclonal Antibody (eBio5E10 (5E10)), APC, eBioscience™	25 tests
MHFH01	Fetal Hemoglobin Monoclonal Antibody (HBF-1), FITC	500 ul
GRB05	Granzyme B Monoclonal Antibody (GB11), APC	500 ul
Q22159	HLA-DR Monoclonal Antibody (Tü36), Qdot 705	25 ul
MA523662	IL1R2 Monoclonal Antibody (34141), FITC	100 tests
MH1013	Mouse anti-Human IgG1 Secondary Antibody	500 ul
MH1722	Mouse anti-Human IgG2 Secondary Antibody, HRP	500 ul
MH1715	Mouse anti-Human IgG1 Fc Secondary Antibody, HRP	500 ul
MH1732	Mouse anti-Human IgG3 Secondary Antibody, HRP	500 ul
MHGD01	TCR gamma/delta Monoclonal Antibody (5A6.E9), FITC	500 ul
02-6202	Goat IgG Isotype Control	10 mg
02-7102	Human IgG Isotype Control	10 mg
02-6100	Mouse IgG1 Isotype Control	1 mg
10000C	Normal Goat Serum Control	25 ml
10510	Normal Rabbit Serum Control	10 ml
02-6102	Rabbit IgG Isotype Control	10 mg

Ordering Information (Invitrogen™ Flow Cytometry Reagents⁺)

Cat No	Products	Unit Size
A10389	AbC™ Anti-Rat/Hamster Bead Kit	1 kit
A35110	Annexin V, APC conjugate	250 ul
C34554	CellTrace™ CFSE Cell Proliferation Kit	1 kit
C34557	CellTrace™ Violet Cell Proliferation Kit	180 assays
C36950	CountBright™ Absolute Counting Beads	5 ml
V13241	Dead Cell Apoptosis Kit with Annexin V Alexa Fluor™ 488 & Propidium Iodide (PI)	250 ul
GAS004	FIX & PERM™ Cell Permeabilization Kit	200 Tests
L7012	LIVE/DEAD™ BacLight™ Bacterial Viability Kit	1 kit
L34957	LIVE/DEAD™ Fixable Aqua Dead Cell Stain Kit	1 kit
L23105	LIVE/DEAD™ Fixable Blue Dead Cell Stain Kit	200 assays
GAS001S100	Permeabilization Medium (Medium A)	100 ml
GAS002S100	Permeabilization Medium (Medium B)	100 ml
P3566	Propidium Iodide - 1.0 mg/mL Solution in Water	10 ml



No.4 Bestsellers

HRP Secondary Antibodies

Ordering Information

Cat No	Products	Unit Size
31430	Goat anti-Mouse IgG (H+L) Secondary Antibody, HRP	2 ml
31460	Goat anti-Rabbit IgG (H+L) Secondary Antibody, HRP	2 ml
31470	Goat anti-Rat IgG (H+L) Secondary Antibody, HRP	2 ml
32430	Goat anti-Mouse IgG (H+L) Secondary Antibody, HRP	2 ml
31439	Goat anti-Mouse IgG Fc Cross-Adsorbed Secondary Antibody, HRP	1.5 ml
31660	Goat anti-Mouse IgG (H+L) Secondary Antibody, Rhodamine	2 mg
SA119255	Mouse anti-Human IgG Fab Secondary Antibody	100 ug
31584	Mouse anti-Rabbit IgG (H+L) Cross-Adsorbed Secondary Antibody, FITC	1 mg
31402	Rabbit anti-Goat IgG (H+L) Secondary Antibody, HRP	1.5 ml
31433	Rabbit anti-Goat IgG Fc Secondary Antibody, HRP	1.5 ml
31450	Rabbit anti-Mouse IgG (H+L) Secondary Antibody, HRP	1.5 ml
31456	Rabbit anti-Mouse IgM Secondary Antibody, HRP	1.5 ml

Start your search at thermofisher.com/top100antibodies



Terms and conditions apply; for complete details go to thermofisher.com/antibody-performance-guarantee

*This promotion is available only to customers in Singapore only. Discount is valid for purchase of 5 antibodies from Jan 1 to March 31 2018. The 3 free antibodies must be of the same or lower value than the purchased antibodies. Discount applies to the list price in effect at the time the order is received by Thermo Fisher Scientific. Cannot be combined with other discounts or promotions. +The eBioscience and Invitrogen Flow Cytometry reagents are not applicable for any form of discount. The list of reagents are listed for reference only. Offer void where prohibited, licensed, or restricted by federal, state, provincial, Or local laws or regulation or agency/ institutional policy. Other restrictions may apply.

ThermoFisher
SCIENTIFIC

For Research Use Only. Not for use in diagnostic procedures. © 2018 Thermo Fisher Scientific Inc. All rights reserved. All trademarks are the property of Thermo Fisher Scientific and its subsidiaries unless otherwise specified.