

thermoscientific



SAVE UP TO
40%

2019 赛默飞质谱奖励计划

• 节省经费 • 体验新产品 • 优化样品制备和定量

ThermoFisher
SCIENTIFIC

通过2019赛默飞质谱奖励计划，拥有赛默飞质谱仪的客户单个订单可享低至6折折扣。如果您在2019年新购置一台或多台赛默飞质谱仪，还能省得更多！

奖励方式

参与条件	促销编码	选购上限	优惠价
曾购买过赛默飞质谱仪	MSReward1	目录价 ¥30,000	6折
2019年，购买赛默飞质谱仪1台	MSReward2	目录价 ¥45,000	6折
2019年，购买赛默飞质谱仪2台及以上	MSReward3	每多购买1台质谱仪，选购上限在 ¥45,000基础上增加 ¥5,000； ¥60,000封顶	6折

如果您对参与此奖励计划有任何问题，请与当地销售联系。此奖励计划每个实验室每自然年限参与一次。活动有效期至2019年12月31日。

校准液	货号	包装规格
Pierce™ Peptide Retention Time Calibration Mixture, 0.5pmol/μL	88320	50μL
Pierce™ Peptide Retention Time Calibration Mixture, 5pmol/μL	88321	200μL
Pierce™ LTQ ESI Positive Ion Calibration Solution	88322	10mL
Pierce™ LTQ Velos ESI Positive Ion Calibration Solution	88323	10mL
Pierce™ ESI Negative Ion Calibration Solution	88324	10mL
Pierce™ Triple Quadrupole Calibration Solution	88325	10mL
Pierce™ Triple Quadrupole Calibration Solution, Extended Mass Range	88340	10mL
Reserpine Standard for LC-MS	88326	5 x 1mL
Digestion Indicator for Mass Spectrometry	84841	10μg
Pierce™ HeLa Protein Digest Standard	88328	20μg
Pierce™ HeLa Protein Digest Standard	88329	5 x 20μg
Pierce Intact Protein Standard Mix	A33526	1 x 76 μg
Pierce Intact Protein Standard Mix	A33527	5 x 76 μg
NEW Pierce™ FlexMix™ Calibration Solution, 10mL	A39239	10mL
NEW Pierce™ LC-MS/MS System Suitability Standard (7 x 5 Mix)	A40010	25ul, 25 injections
NEW Pierce™ TMT11plex Yeast Digest Standard, 20mg	A40938	20ug
NEW Pierce™ TMT11plex Yeast Digest Standard, 5 x 20mg	A40939	5 x 20ug
蛋白定量试剂 – SILAC	货号	包装规格
L-Arginine-HCl	89989	50mg
L-Arginine-HCl	88427	500mg
¹³ C ₆ L-Arginine-HCl	88210	50mg
¹³ C ₆ L-Arginine-HCl	88433	500mg
¹³ C ₆ ¹⁵ N ₄ L-Arginine-HCl	89990	50mg
¹³ C ₆ ¹⁵ N ₄ L-Arginine-HCl	88434	500mg
L-Lysine-2HCl	89987	50mg
L-Lysine-2HCl	88429	500mg
¹³ C ₆ L-Lysine-2HCl	89988	50mg
¹³ C ₆ L-Lysine-2HCl	88431	500mg
¹³ C ₆ 15N ₂ L-Lysine-2HCl	88209	50mg
¹³ C ₆ 15N ₂ L-Lysine-2HCl	88432	500mg
L-Lysine-2HCl (4,4,5,5-D ₄)	88437	50mg
L-Lysine-2HCl (4,4,5,5-D ₄)	88438	500mg
NeuCode Lysine-080(3,3,4,4,5,5,6,6-D ₈ L-Lysine-2HCl)	A36750	25 mg
NeuCode Lysine-080(3,3,4,4,5,5,6,6-D ₈ L-Lysine-2HCl)	A33613	50 mg
NeuCode Lysine-080(3,3,4,4,5,5,6,6-D ₈ L-Lysine-2HCl)	A33614	500 mg
NeuCode Lysine-440(L-Lysine: 2HCL (3,4,5,6-13C ₄ , 5,5,6,6-D ₄ , 98%))	A36752	25 mg
NeuCode Lysine-521 (L-Lysine:2HCL)	A36753	25 mg
NeuCode Lysine-341(13C ₃ 2H ₄ 15N ₁ L-Lysine-2HCl)	A36851	25 mg
NeuCode Lysine-202 (13C ₂ 15N ₂ L-Lysine-2HCl)	A36754	25 mg

蛋白定量试剂 – SILAC (续)	货号	包装规格
NeuCode 4-plex Lysine Bundle(NeuCode Lysine-080, NeuCode Lysine-602, NeuCode Lysine-440, NeuCode Lysine-521)	A36755	1 bundle
L-Leucine	88428	500mg
¹³ C ₆ L-Leucine	88435	50mg
¹³ C ₆ L-Leucine	88436	500mg
L-Proline	88211	115mg
L-Proline	88430	500mg
RPMI Media for SILAC	88365	500mL
RPMI Media for SILAC	A33823	6 x 500mL
DMEM Media for SILAC	88364	500mL
DMEM Media for SILAC	A33822	6 x 500mL
DMEM:F12 (1:1) Media for SILAC	88370	500mL
MEM for SILAC	88368	500mL
IMDM for SILAC	88367	500mL
Ham's F12 for SILAC	88424	500mL
Powdered DMEM Media for SILAC, sufficient to prepare 10L of medium	88425	135g
Powdered RPMI Media for SILAC, sufficient to prepare 10L of medium	88426	104g
McCoy's 5A Media for SILAC	88441	500mL
蛋白定量试剂 - 氨基反应性串联质谱标记试剂 (TMT)	货号	包装规格
TMTsixplex™ Isobaric Mass Tagging Kit	90064CH	35-rxn kit
TMTduplex™ Isobaric Label Reagent Set	90065	10-rxn set
TMTsixplex™ Isobaric Label Reagent Set	90066	30-rxn set
TMTzero™ Label Reagent	90067	5 x 0.8mg
TMTduplex™ Isotopic Label Reagent Set	90060	10-rxn set
TMTsixplex™ Isobaric Label Reagent Set	90061	6-rxn set
TMTsixplex™ Isobaric Label Reagent Set	90062	12-rxn set
TMTsixplex™ Isobaric Label Reagent Set	90068	72-rxn set
TMT10plex™ Label Reagent Set	90110	10-rxn set
TMT10plex™ Label Reagent Set	90111	30-rxn set
TMT10plex™ Isobaric Mass Tag Labeling Kit	90113CH	30-rxn kit
TMT10plex™ Isobaric Label Reagent Set	90406	60-rxn set
TMTsixplex™ Isobaric Label Reagent Set, 16 x 0.2 mg	90308	96 rxn set
TMT10plex™ Isobaric Label Reagent Set, 8 x 0.2 mg	90309	80-rxn set
TMT11-131C Label Reagent, 1 x 5mg	A34807	1 x 5mg
TMT10plex Isobaric Label Reagent Set plus TMT11-131C Label Reagent, 1 x 5mg	A34808	1 x 5mg
蛋白定量试剂 - 半胱氨酸反应性串联质谱标记试剂 (iodo TMT)	货号	包装规格
iodoTMTzero™ Label Reagent, 5 x 0.2mg	90100	5-rxn set
iodoTMTsixplex™ Label Reagent Set	90101	6-rxn set
iodoTMTsixplex™ Label Reagent Set	90102	30-rxn set
iodoTMTsixplex™ Isobaric Mass Tag Labeling Kit	90103CH	30-rxn kit

蛋白定量试剂 - 巯基反应性串联质谱标记试剂 (aminoxyl TMT)	货号	包装规格
aminoxylTMTsixplex™ Label Reagent Set	90401	1 x 0.2mg
aminoxylTMTsixplex™ Label Reagent Set	90402	5 x 0.2mg
TMT™ 相关试剂	货号	包装规格
Anti-TMT™ Antibody	90075	0.1mL
Immobilized Anti-TMT™ Antibody Resin	90076	6mL
TMT™ Elution Buffer	90104	20mL
1M Triethylammonium Bicarbonate (TEAB)	90114	50mL
50% Hydroxylamine	90115	5mL
蛋白富集 - 免疫沉淀	货号	包装规格
Pierce™ MS-Compatible Magnetic IP Kit (Streptavidin)	90408	40-rxn kit
Pierce™ MS-Compatible Magnetic IP Kit (Protein A/G)	90409	40-rxn kit
Pierce™ Antibody Biotinylation Kit for IP	90407	8-rxn kit
Low Protein Binding Microcentrifuge Tubes, 1.5mL	90410	250 tubes
Low Protein Binding Microcentrifuge Tubes, 1.5mL	90411	10 x 250 tubes
高丰度蛋白去除	货号	包装规格
Albumin Depletion Kit	85160	24-rxn kit
High-Select HSA/ Immunoglobulin Depletion Mini Spin Columns	A36365	6 columns
High-Select HSA/ Immunoglobulin Depletion Mini Spin Columns	A36366	24 columns
High-Select HSA/Immunoglobulin Depletion Midi Spin Columns	A36367	10 columns
High-Select HSA/Immunoglobulin Depletion Resin	A36368	50 mL
High-Select Top14 Abundant Protein Depletion Mini Spin Columns	A36369	6 columns
High-Select Top14 Abundant Protein Depletion Mini Spin Columns	A36370	12 columns
High-Select Top14 Abundant Protein Depletion Midi Spin Columns	A36371	10 columns
High-Select Top14 Abundant Protein Depletion Resin	A36372	50 mL
蛋白脱盐和浓缩	货号	包装规格
Zeba™ Micro Spin Desalting Columns, 7K MWCO, 75µL	89877	25 columns
Zeba™ Spin Desalting Columns, 7K MWCO, 0.5mL	89882	25 columns
Zeba™ Spin Desalting Columns, 7K MWCO, 2mL	89890	25 columns
Zeba™ Spin Desalting Columns, 7K MWCO, 5mL	89892	25 columns
Zeba™ Spin Desalting Columns, 7K MWCO, 10mL	89894	25 columns
Zeba™ 96-well Spin Desalting Plates, 7K MWCO	89807	2 plates
Zeba™ Micro Spin Desalting Columns, 40K MWCO, 75µL	87764	25 columns
Zeba™ Spin Desalting Columns, 40K MWCO, 0.5mL	87766	25 columns
Zeba™ Spin Desalting Columns, 40K MWCO, 2mL	87769	25 columns
Zeba™ Spin Desalting Columns, 40K MWCO, 5mL	87771	25 columns
Zeba™ Spin Desalting Columns, 40K MWCO, 10mL	87773	25 columns
Zeba™ 96-well Spin Desalting Plates, 40K MWCO	87774	2 plates
Pierce Protein Concentrators PES, 30K MWCO, 0.5 mL	88502	25 columns
Pierce Protein Concentrators PES, 100K MWCO, 0.5 mL	88503	25 columns
Pierce Protein Concentrators PES, 3K MWCO, 0.5 mL	88512	25 columns
Pierce Protein Concentrators PES, 10K MWCO, 0.5 mL	88513	25 columns
蛋白酶解 - 质谱级蛋白酶, 试剂与试剂盒	货号	包装规格
Trypsin Protease, MS Grade	90057	5 x 20µg
Trypsin Protease, MS Grade	90058	5 x 100µg
Trypsin Protease, MS Grade	90059	1mg
Trypsin Protease, MS Grade, Frozen Liquid	90305	100µg
LysN Protease, MS Grade	90300	20µg
LysN Protease, MS Grade	90301	5 x 20µg
LysC Protease, MS Grade	90051	20µg
AspN Protease, MS Grade	90053	2µg
GluC Protease, MS Grade	90054	5 x 10µg
Chymotrypsin (TLCK treated), MS Grade	90056	4 x 25µg

肽段定量分析	货号	包装规格
Pierce Quantitative Colorimetric Peptide Assay	23275	500 assay kit
Pierce Quantitative Fluorometric Peptide Assay	23290	500 assay kit
Peptide Digest Assay Standard (1mg/mL)	23295	1.5mL
96-well Black Plates	88378	25 pack
磷酸化肽段的富集与纯化	货号	包装规格
High Select™ Fe-NTA Phosphopeptide Enrichment Kit	A32992	30-rxn kit
High Select™ TiO2 Phosphopeptide Enrichment Kit	A32993	24-rxn kit
Pierce™ Magnetic TiO2 Phosphopeptide Enrichment Kit	88811	96-rxn kit
Pierce Magnetic TiO2 Phosphopeptide Enrichment Kit	88812	24-rxn kit
Pierce™ Graphite Spin Columns, 0.5mL	88302	30 columns
肽段分离	货号	包装规格
Pierce High pH Reversed-Phase Peptide Fractionation Kit	84868	12 column kit
Low Protein Binding Microfuge Tubes, 2mL	88379	250 tubes
Low Protein Binding Microfuge Tubes, 2mL	88380	10 x 250 tubes
活性位点的标记与富集	货号	包装规格
Pierce™ Kinase Enrichment Kit with ATP Probe	88310	16-rxn kit
ActivX™ Desthiobiotin-ATP Probe	88311	16 x 12.6µg
Pierce™ Kinase Enrichment Kit with ADP Probe	88312	16-rxn kit
ActivX™ Desthiobiotin-ADP Probe	88313	16 x 9.9µg
Pierce™ GTPase Enrichment Kit with GTP Probe	88314	16-rxn kit
ActivX™ Desthiobiotin-GTP Probe	88315	16 x 12.9µg
ActivX™ Azido-FP Serine Hydrolase Probe	88316	3.5µg
ActivX™ Desthiobiotin-FP Serine Hydrolase Probe	88317	4.6µg
ActivX™ TAMRA-FP Serine Hydrolase Probe	88318	6.8µg
质谱可碎裂交联剂	货号	包装规格
DSSO (disuccinimidyl sulfoxide)	A33545	10 x 1 mg
DSBU (disuccinimidyl dibutyric urea)	A35459	10 x 1 mg
肽段纯化	货号	包装规格
Pierce™ Detergent Removal Spin Column, 125µL	87776	25 columns
Pierce™ Detergent Removal Spin Column, 0.5mL	87777	25 columns
Pierce™ Detergent Removal Spin Column, 2mL	87778	5 columns
Pierce™ Detergent Removal Spin Column, 4mL	87779	5 columns
Pierce™ Detergent Removal Resin	87780	10mL
Pierce™ Detergent Removal Spin Plates	88304	2 plates
HiPPR™ Detergent Removal Spin Column Kit (Resin + Columns)	88305	5mL kit
HiPPR™ Detergent Removal Spin Columns, .1mL	88306	24 columns
HiPPR™ Detergent Removal 96-well Spin Plates	88307	2 plates
Pierce Peptide Desalting Spin Columns	89852	25 columns
Pierce Peptide Desalting Spin Columns	89853	50 columns
Pierce™ C18 Spin Columns	89870	25 columns
Pierce™ C18 Spin Columns	89873	50 columns
Pierce™ C18 Tips, 10µL bed	87782	96 tips
Pierce™ C18 Tips, 100µL bed	87784	96 tips
Pierce™ C18 Spin Tips	84850	96 tips
辅助试剂	货号	包装规格
Trifluoroacetic Acid	28901	500mL
Trifluoroacetic Acid	28902	10 x 1g
Trifluoroacetic Acid	28903	100g
Trifluoroacetic Acid	28904	10 x 1mL
Heptafluorobutyric Acid, Sequanal Grade	25003	100mL
Heptafluorobutyric Acid, HPLC Grade	53104	10 x 1mL
Water, LC/MS Grade	51140	1L
CHCA MALDI Matrix, Single-Use	90031	24 x 1mg
SA MALDI Matrix, Single-Use	90032	24 x 1mg
DHB MALDI Matrix, Single-Use	90033	24 x 4mg
MALDI Matrix Sample Pack, Single-Use	90035	Kit

辅助试剂(续)	货号	包装规格	靶向定量-绝对、相对定量	货号	包装规格
Trifluoroacetic Acid (TFA), LC-MS Grade	85183	50mL	NEW SureQuant AKT Pathway Multiplex Panel (Absolute Quantitation)	A40011	10 reactions
Bond-Breaker™ TCEP Solution, Neutral pH	77720	5mL	NEW SureQuant AKT Pathway Multiplex Panel (Relative Quantitation)	A40080	10 reactions
No-Weigh™ Dithiothreitol (DTT)	20291	48 tubes	NEW SureQuant AKT Pathway IP and MS Sample Preparation Module	A40081	10 reactions
Iodoacetamide (IAM), Single Use	90034	24 x 9.3mg	NEW SureQuant AKT Pathway Relative Quantitation Module	A40082	10 reactions
Iodoacetic Acid (IAA)	35603	500mg	NEW SureQuant AKT Pathway Absolute Quantitation Module	A40083	10 reactions
Methyl methanethiosulfonate (MMTS)	23011	200mg	NEW SureQuant AKT Pathway (Phospho) Multiplex Panel (Absolute Quantitation)	A40084	10 reactions
N-Ethylmaleimide (NEM)	23030	25g	NEW SureQuant AKT Pathway (Phospho) Multiplex Panel (Relative Quantitation)	A40085	10 reactions
Formic Acid, LC-MS Grade	85178	50mL	NEW SureQuant AKT Pathway (Phospho) IP and MS Sample Preparation Module	A40086	10 reactions
Acetonitrile, LC/MS Grade 51101 1L	51101	1L	NEW SureQuant AKT Pathway (Phospho) Relative Quantitation Module	A40087	10 reactions
Water, LC/MS Grade	85189	4 x 1L	NEW SureQuant AKT Pathway (Phospho) Absolute Quantitation Module	A40088	10 reactions
0.1% Formic Acid (v/v) in Water, LC-MS Grade	85170	1L	NEW SureQuant RAS Isoform Panel (Absolute Quantitation)	A40094	10 reactions
0.1% Formic Acid (v/v) in Water, LC-MS Grade	85171	4 x 1L	NEW SureQuant RAS Isoform Panel (Relative Quantitation)	A40095	10 reactions
0.1% Formic Acid (v/v) in Acetonitrile, LC-MS Grade	85174	1L	NEW SureQuant RAS Isoform IP and MS Sample Preparation Module	A40096	10 reactions
0.1% Formic Acid (v/v) in Acetonitrile, LC-MS Grade	85175	4 x 1L	NEW SureQuant RAS Isoform Relative Quantitation Module	A40097	10 reactions
0.1% Trifluoroacetic Acid (v/v) in Acetonitrile, LC-MS Grade	85176	1L	NEW SureQuant RAS Isoform Absolute Quantitation Module	A40098	10 reactions
0.1% Trifluoroacetic Acid (v/v) in Acetonitrile, LC-MS Grade	85177	4 x 1L	NEW SureQuant AKT Isoform Panel (Absolute Quantitation)	A40089	10 reactions
DHB MALDI Matrix, Single-Use	90033	24 x 4mg	NEW SureQuant AKT Isoform Panel (Relative Quantitation)	A40090	10 reactions
样本制备试剂	货号	包装规格	NEW SureQuant AKT Isoform IP and MS Sample Preparation Module	A40091	10 reactions
NEW Thermo Scientific™ EasyPep™ Mini MS Sample Prep Kit	A40006	20 reactions	NEW SureQuant AKT Isoform Relative Quantitation Module	A40092	10 reactions
NEW Pierce Trypsin/Lys-C Protease Mix, MS-Grade, 20mg	A40007	20ug	NEW SureQuant AKT Isoform Absolute Quantitation Module	A40093	10 reactions
NEW Pierce Trypsin/Lys-C Protease Mix, MS-Grade, 100mg	A40009	100ug	NEW SureQuant TP53 Panel (Absolute Quantitation)	A40099	10 reactions
NEW Pierce Trypsin/Lys-C Protease Mix, MS-Grade, 5 x 20mg	A41007	5 x 20ug	NEW SureQuant TP53 Panel (Relative Quantitation)	A40100	10 reactions
NEW MCF7 (+hIGF-1) Control Lysate, 0.5mg (1mg/mL)	A37959	0.5mg	NEW SureQuant TP53 Panel IP and MS Sample Preparation Module	A40101	10 reactions
NEW A549 (+hIGF-1) Control Lysate, 0.5mg (1mg/mL)	A37960	0.5mg	NEW SureQuant TP53 Panel Relative Quantitation Module	A40102	10 reactions
NEW HCT 116 (+hIGF-1) Control Lysate, 0.5mg (1mg/mL)	A37961	0.5mg	NEW SureQuant TP53 Panel Absolute Quantitation Module	A40103	10 reactions
NEW BT-549 Positive Lysate, 0.5mg (1mg/mL)	A37962	0.5mg			

了解更多关于 Thermo Scientific 蛋白质组学产品的信息, 请浏览:

<http://thermofisher.com/msreagents>

获取更多关于2019质谱奖励计划信息, 请浏览: thermofisher.com/ms-rewards

获取更多质谱数字资源, 请浏览: thermofisher.com/msresources

*仅限在2019年12月31日前通过英潍捷基 (Life Technologies) 订购的有效订单享受此优惠。每个客户仅能享用一次, 限单个订单使用。折扣基于英潍捷基当时发布的有效目录价。不与其他活动共享。



赛默飞
官方微信



赛默飞
生命科学官方微信

免费服务电话: 800 820 8982/400 820 8982
销售服务信箱: sales.china@thermofisher.com
技术咨询信箱: LifeScience-CNTS@thermofisher.com

Thermo Fisher
SCIENTIFIC