

SPARE PART KIT RECOMMENDATIONS

Thermo Scientific™ Model 42i-LS Low Source NO-NO₂-NO_x Analyzer

To keep your system running and properly collecting data, it's important to have spare parts on hand to avoid costly downtime. We developed Spare Parts Kits to ensure maximum uptime of your Thermo Scientific Instrument during its life cycle.

Spare Parts Kit # 111842-03	
Part Numbers	Description
4119	1 x Capillary, 08 mil (Red)
4121	1 x Capillary, 10 MIL L. (BLACK)
4800	1 x O-RING VITON (PK/10) (FOR CAPILLARIES)
4806	2 x O ring , (Base End & Chamber /quartz)
4808	1 x O ring, (Between chamber halves)
4821	1 x O Ring, (PMT end)
4822	1 x O Ring, (Inside Cooler)
6556	1 x Filter Kit, Optical (w/quartz)
9212	1 x O ring Capillary Holder (pk/5)
11290	1 x Receptacle Fuse Drawer, 110V
101016-00	1 x Silica Scrubber Assy.
101680-00	1 x NH3 Scrubber
101905-00	2 x Fuse, 4 amp slo blow
107751-00	1 x 42i pump rebuild kit

Extended Maintenance Kit # 105087-00	
Part Numbers	Description
9367	1 x PMT
9973	1 x Ozonator
9995	1 x cooler
100907-00	1 x Fan, 24VDC, i-series
101011-01	1 x pump assy
101023-00	1 x pressure transducer
101024-00	1 x HV power supply
101390-00	1 x solenoid assy (i-series)
101419-00	1 x ozonator transformer
101681-00	1 x power supply w/o cables

USA

27 Forge Parkway
Franklin, MA 02038
Ph: (866) 282-0430
orders.aqi@thermofisher.com

India

C/327, TTC Industrial Area
MIDC Pawane
New Mumbai 400 705, India
Ph: +91 22 4157 8800
india@thermofisher.com

China

+Units 702-715, 7th Floor
Tower West, Yonghe
Beijing, China 100007
+86 10 84193588
info.eid.china@thermofisher.com

Europe

Ion Path Road Three
Winsford, Cheshire CW7 3GA
Ph: +44 (0) 1606 548700
orders.epm.uk@thermofisher.com

Find out more at thermofisher.com/EMservice

ThermoFisher
SCIENTIFIC