

Specifications

Product Description :Acetic Acid Glacial ExcelsaR-ACS 50KG
Product Code :Q1100E

Sr.No	Description	Unit	Standards
1	Description : Clear colorless liquid (< 10 Hazen) (characteristic Odor)		Should Comply
2	Dilution test : Passes test		Should Comply
3	Water insoluble matter : Passes test		Should Comply
4	Identification : Comply to the test for acetates		Should Comply
5	Identification : Solution is strongly acid		Should Comply
6	Acetic Anhydride [(CH ₃ CO) ₂ O]	%	0.01 Max
7	Arsenic (As)	%	0.00005 Max
8	Assay	%	99.8 Min
9	Chloride (Cl)	%	0.0001 Max
10	Copper (Cu)	%	0.00001 Max
11	Formate (H.COO)	%	0.05 Max
12	Freezing point (In °C)		16.2 Min
13	Iron (Fe)	%	0.00002 Max
14	Lead (Pb)	%	0.00001 Max
15	Non-volatile matter	%	0.001 Max
16	Substances reducing dichromate (O)	%	0.003 Max
17	Sulphate (SO ₄)	%	0.0001 Max
18	Titration base (In meq/g)		0.0004 Max
19	Water (by K.F.)	%	0.2 Max
20	Weight per ml (at 20°C) (In gm/ml)		1.048 - 1.05

Specifications

Product Description :Acetic Acid Glacial ExcelaR-ACS 50KG
Product Code :Q1100E

Quality Assurance

The document has been produced electronically and is valid without signature.

Registered Office : Thermo Fisher Scientific India Pvt. Ltd. 403-404,B-wing, Delphi, Hiranandani Business Park, Powai, Mumbai-400076, INDIA.
Tel : +91-22-67162200/66803000, CIN-U73100MH2000PTC126872.