

New Acros Organics Screening Tools

Screening Tools			
SKU#	Product Name	Pack size	CAS No.
458860010	Abacavir sulfate, 99%	1GR	188062-50-2
458860050		5GR	
459080010	Acarbose, 95%	1GR	56180-94-0
459080050		5GR	
455190050	Amikacin disulfate salt	5GR	39831-55-5
455190250		25GR	
457980010	Amiodarone hydrochloride	1GR	19774-82-4
457980050		5GR	
457980250		25GR	
459910010	1,5-Anhydro-D-glucitol, 97%	1GR	154-58-5
459912500		250MG	
459070010	Betamethasone, 97%	1GR	378-44-9
459070050		5GR	
459070250		25GR	
458620010	Bifonazole, 98%	1GR	60628-96-8
458620050		5GR	
458620250		25GR	
460620010	Budesonide, 97%	1GR	51333-22-3
460620050		5GR	

Screening Tools

SKU#	Product Name	Pack size	CAS No.
458610050	Carbimazole, 98%	5GR	22232-54-8
458610250		25GR	
459470010	Cefadroxil, 95-105%	1GR	66592-87-8
459470050		5GR	
459480010	Cefixime, 98%	1GR	79350-37-1
459480050		5GR	
459490010	Cefotetan, 95-103%	1GR	69712-56-7
459492500		250MG	
458870010	Chelidamic acid hydrate, 97%	1GR	138-60-3
458870050		5GR	
458870250		25GR	
459530050	Chloramphenicol sodium succinate, 98 - 102%	5GR	982-57-0
459530250		25GR	
456060250	1,4-Cineole, 85%	25GR	470-67-7
456061000		100GR	
456065000		500GR	
457780010	Citicoline, 98%	1GR	987-78-0
457780050		5GR	
457780250		25GR	
455460050	Clotrimazole	5GR	23593-75-1
455460250		25GR	
455461000		100GR	
460520010	Cortisone, 98%	1GR	53-06-5
460522500		250MG	

Screening Tools			
SKU#	Product Name	Pack size	CAS No.
458850010	Cytisine, 98%	1GR	485-35-8
458852500		250MG	
460420010	Daidzin, 98%	1GR	552-66-9
460421000		100MG	
460470010	11-Deoxycorticosterone acetate, 97%	1GR	56-47-3
460470050		5GR	
459220050	3,3'-Diindolylmethane, 96%	5GR	1968-05-4
459220250		25GR	
329080010	Diltiazem hydrochloride, 98%	1GR	33286-22-5
329080050		5GR	
329080250		25GR	
458050010	Donepezil hydrochloride	1GR	120011-70-3
458050050		5GR	
446060050	Doxycycline hyclate, 98%	5GR	24390-14-5
446060250		25GR	
446061000		100GR	
458890050	Doxycycline monohydrate, 97%	5GR	17086-28-1
458890250		25GR	
458630050	Econazole, 99%	5GR	27220-47-9
458630250		25GR	
460490010	Estriol, 97%	1GR	50-27-1
460490050		5GR	
459090010	7-Ethyl-10-hydroxycamptothecin, 98%	1GR	86639-52-3
459091000		100MG	

Screening Tools			
SKU#	Product Name	Pack size	CAS No.
458000010	Finasteride	1GR	98319-26-7
458000050		5GR	
101910010	Flubendazole	1GR	31430-15-6
101910050		5GR	
101910250		25GR	
460200010	Fluorometholone, 97%	1GR	426-13-1
458010010	Fluvastatin sodium salt	1GR	93957-55-2
458010050		5GR	
458460010	Fusidic acid, 98%	1GR	6990-06-3
458460050		5GR	
460230010	Gatifloxacin, 98%	1GR	112811-59-3
460230050		5GR	
460230250		25GR	
458030050	Indomethacin	5GR	53-86-1
458030250		25GR	
458031000		100GR	
458880010	Indoxyl-beta-D-glucoside, 98%	1GR	487-60-5
458882500		250MG	
458640010	Isoconazole nitrate, 99%	1GR	24168-96-5
458640050		5GR	
458640250		25GR	
460590010	Linezolid, 98%	1GR	165800-03-3
460592500		250MG	

Screening Tools			
SKU#	Product Name	Pack size	CAS No.
458830050		5GR	
458830250	Lovastatin, 98%	25GR	75330-75-5
458831000		100GR	
459550050		5GR	
459550250	Meloxicam, 99-101%	25GR	71125-38-7
458650010		1GR	
458650050	Melphalan, 94%	5GR	148-82-3
460660010		1GR	
460660050	5-Methoxypsoralen, 98%	5GR	484-20-8
460660250		25GR	
226810010		1GR	
226810050	Methyl behenate, 99%, analytical standard for GC	5GR	929-77-1
414420010		1GR	
414420050	Methyl hexanoate, 99%, analytical standard for GC	5GR	106-70-7
460360010		1GR	
460360050	Methyl myristate, 99%, analytical standard for GC	5GR	124-10-7
460371000		100MG	
460375000	Methyl nervonate, 99%, analytical standard for GC	500MG	2733-88-2
460350010		1GR	
460350050	Methyl octanoate, 99%, analytical standard for GC	5GR	111-11-5
460380010		1GR	
460380050	Methyl oleate, 99%, analytical standard for GC	5GR	112-62-9
460390010		1GR	
460390050	Methyl palmitate, 99%, analytical standard for GC	5GR	112-39-0

Screening Tools

SKU#	Product Name	Pack size	CAS No.
460400010	Methyl palmitoleate, 99%, analytical standard for GC	1GR	1120-25-8
459560010	Mezlocillin sodium, 97%	1GR	42057-22-7
459562500		250MG	
291830010	(±)-Miconazole nitrate salt	1GR	22832-87-7
291830050		5GR	
291830250		25GR	
459980010	Mifepristone, 98%	1GR	84371-65-3
459980050		5GR	
459982500		250MG	
459370010	Mycophenolate mofetil, 98%	1GR	128794-94-5
459370050		5GR	
459370250		25GR	
459380010	Mycophenolic acid, 98%	1GR	24280-93-1
459380050		5GR	
459380250		25GR	
458660010	Naftifine hydrochloride, 99%	1GR	65473-14-5
458660050		5GR	
458660250		25GR	
458520010	Omeprazole, 98+%	1GR	73590-58-6
458520050		5GR	
458520250		25GR	
459640010	Perfluorooctanesulfonamide, 95%	1GR	754-91-6
459640050		5GR	

Screening Tools			
SKU#	Product Name	Pack size	CAS No.
457880010	Proadifen hydrochloride, 95%	1GR	62-68-0
457880050		5GR	
460480010	Ribavirin, 98%	1GR	36791-04-5
460480050		5GR	
460480250		25GR	
459360010	Riluzole, 98%	1GR	1744-22-5
459360050		5GR	
459360100		10GR	
459390010	Risperidone, 99%	1GR	106266-06-2
459390050		5GR	
459400010	Robenidine hydrochloride, 98%	1GR	25875-50-7
459400050		5GR	
459400250		25GR	
459570050	Roxithromycin, 96%	5GR	80214-83-1
459570250		25GR	
459650050	Silver sulfadiazine, 98%	5GR	22199-08-2
459650250		25GR	
458840010	Simvastatin, 98%	1GR	79902-63-9
458840050		5GR	
458840250		25GR	
458060010	Sulfachloropyridazine sodium, 97%	1GR	23282-55-5
458060050		5GR	
442850250	Sulfapyridine, 95%	25GR	144-83-2
442851000		100GR	

Screening Tools

SKU#	Product Name	Pack size	CAS No.
459250250		25GR	
459251000	Theophylline-7-acetic acid, 98%	100GR	652-37-9
459255000		500GR	
459580010	Ticarcillin disodium salt, 80%	1GR	4697-14-7
458670010	Voriconazole, 98%	1GR	137234-62-9

To place an order, contact your local distributor.



©2016 Thermo Fisher Scientific Inc. All rights reserved.
All other trademarks are the property of Thermo Fisher Scientific Inc. and its subsidiaries.

Thermo Fisher Scientific
ENA 23, Zone 1, nr 1350
Janssen Pharmaceuticaaan 3a
2440 Geel
Belgium
www.acros.com