



## Compatible racks for the Thermo Scientific ID Scribe Labware Identifier



Clearly identify your laboratory samples.

Rack PN	Rack Description	Writing Area	Tubes/Rack	Compatible PN	Description
3300	Thermo Scientific ID Scribe Rack: 1.0-2.0 mL Nunc CryoTubes including Cryobank	Side	21	374221	2.0 mL Cryobank 2D code racked Sterile
				374223	2.0 mL Cryobank non coded racked sterile
				351934	Nunc CryoTube Vial, 1.8 mL, int thread, round bottom, PP tube w/ writing area and w/o caps, clear, NS, 5 packs of 500/cs
				347597	Nunc CryoTube Vial, 1.0 mL, ext thread, conical bottom, self standing, anti-rotation, PP tube, PE screw cap, clear, S, 4 packs of 500/cs
				375353	Nunc CryoTube Vial, 1.0 mL, ext thread, conical bottom, self standing, anti-rotation, PP tube w/ printed area, PE screw cap, clear, S, 4 packs 500/cs
				375299	Nunc CryoTube Vial, 1.0 mL, ext thread, round bottom , PP narrow-neck tube w/ printed area, PE screw cap, clear, S, 4 packs of 500/cs
				375418	Nunc CryoTube Vial, 1.8 mL, ext thread, round bottom , self-standing, anti-rotation, PP tube w/ printed area, PE screw cap, clear, S, 4 packs of 450/cs
				340711	Nunc CryoTube Vial, 1.8 mL, ext thread, round bottom , PP narrow-neck tube w/ printed area, PE screw cap, clear, S, 4 packs of 500/cs
				347627	Nunc CryoTube Vial, 1.8 mL, ext thread, round bottom, self standing, anti-rotation, PP tube, PE screw cap, clear, S, 4 packs of 450/cs
				377224	Nunc CryoTube Vial, 1.0 mL, int thread, conical bottom , self standing, anti-rotation, PP tube w/ writing area and screw cap w/ silicone gasket, clear, S, 4 packs of 500/cs
				366656	Nunc CryoTube Vial, 1.0 mL, int thread, conical bottom , self standing, PP tube w/ writing area and screw cap w/ silicone gasket, clear, S, 4 packs of 500/cs
				377267	Nunc CryoTube Vial, 1.8 mL, int thread, round bottom, self-standing, anti-rotation, PP tube and writing area and screw cap w/ silicone gasket, clear, S, 4 packs of 500/cs
				368632	Nunc CryoTube Vial, 1.8 mL, int thread, round bottom, self-standing, PP tube w/ writing area and screw cap, clear, S, 4 packs of 450/cs
				363401	Nunc CryoTube Vial, 1.8 mL, int thread, round bottom, PP tube w/ writing area and screw cap w/ silicone gasket, clear, S, 4 packs of 500/cs
3301	Thermo Scientific ID Scribe Rack: 1.0-1.4 mL 96-Way Tubes	Side	36	4140	Matrix 1.4 mL blank, polypropylene, round bottom tubes, bulk, 1000/case
				4245	Matrix 1.4 mL blank, polypropylene, round bottom tubes, 10 Snap Racks of 96 tubes/case
				4246	Matrix 1.4 mL blank, polypropylene, round bottom tubes, Sterile, 10 Snap Racks of 96 tubes/case
				4247	Matrix 1.4 mL blank, polypropylene, round bottom tubes, 10 Latch Racks of 96 tubes/case
				4248	Matrix 1.4 mL blank, polypropylene, round bottom tubes, Sterile, 10 Latch Racks of 96 tubes/case
				4249	Matrix 1.4 mL blank, polypropylene, round bottom tubes, 10 Refill packs of 96 tubes/case
				4250	Matrix 1.4 mL blank, polypropylene, round bottom tubes, Sterile, 10 Refill packs of 96 tubes/case
				4147	Matrix 1.4 mL alphanumeric, polypropylene, round bottom tubes, 10 Snap Racks of 96 tubes/case
				4148	Matrix 1.4 mL alphanumeric, polypropylene, round bottom tubes, Sterile, 10 Snap Racks of 96 tubes/case
				4251	Matrix 1.4 mL alphanumeric, polypropylene, round bottom tubes, 10 Latch Racks of 96 tubes/case
				4252	Matrix 1.4 mL alphanumeric, polypropylene, round bottom tubes, Sterile, 10 Latch Racks of 96 tubes/case
				4253	Matrix 1.4 mL alphanumeric, polypropylene, round bottom tubes, 10 Refill packs of 96 tubes/case
				4254	Matrix 1.4 mL alphanumeric, polypropylene, round bottom tubes, Sterile, 10 Refill packs of 96 tubes/case
				3790	Matrix 1.4 mL 2D, polypropylene, V bottom tubes, bulk, 1000/case
				3791	Matrix 1.4 mL 2D, polypropylene, V bottom tubes, 10 Latch Racks of 96 tubes/case
				3792	Matrix 1.4 mL 2D, polypropylene, V bottom tubes, Sterile, 10 Latch Racks of 96 tubes/case
				3794	Matrix 1.4 mL 2D, polypropylene, V bottom tubes, 10 Snap Racks of 96 tubes/case
				3801	Matrix 1.4 mL 2D, polypropylene, V bottom tubes with DuraSeal septum installed, 10 Latch Racks of 96 tubes/case
				3710	Matrix 1.4 mL 2D with human readable text, polypropylene, flat bottom tubes, bulk, 1000/case
				3711	Matrix 1.4 mL 2D with human readable text, polypropylene, flat bottom tubes, 10 Latch Racks of 96 tubes/case
3712	Matrix 1.4 mL 2D with human readable text, polypropylene, flat bottom tubes, Sterile, 10 Latch Racks of 96 tubes/case				
3713	Matrix 1.4 mL 2D with human readable text, polypropylene, flat bottom tubes, 10 Snap Racks of 96 tubes/case				
3714	Matrix 1.4 mL 2D with human readable text, polypropylene, flat bottom tubes, Sterile, 10 Snap Racks of 96 tubes/case				

Rack PN	Rack Description	Writing Area	Tubes/Rack	Compatible PN	Description
3301	Thermo Scientific ID Scribe Rack: 1.0-1.4 mL 96-Way Tubes	Side	36	3715	Matrix 1.4 mL 2D with human readable text, polypropylene, flat bottom tubes, 10 Refill packs of 96 tubes/case
				3719	Matrix 1.4 mL 2D TTP comPOUND code (small print) polypropylene, flat bottom tubes, 10 Latch Racks of 96 tubes/case
				3850	Matrix 1.0 mL 2D, glass, V bottom tubes, 5 Latch Racks of 96 tubes/case
				3740	Matrix 1.0 mL 2D, polypropylene, V bottom ScrewCap tubes with caps, Sterile, bulk, 10 bags of 48 tubes/case
				3740RED	Matrix 1.0 mL 2D, polypropylene, V bottom ScrewCap tubes with red caps, Sterile, bulk, 10 bags of 48 tubes/case
				3740YEL	Matrix 1.0 mL 2D, polypropylene, V bottom ScrewCap tubes with yellow caps, Sterile, bulk, 10 bags of 48 tubes/case
				3740BLU	Matrix 1.0 mL 2D, polypropylene, V bottom ScrewCap tubes with blue caps, Sterile, bulk, 10 bags of 48 tubes/case
				3740GRE	Matrix 1.0 mL 2D, polypropylene, V bottom ScrewCap tubes with green caps, Sterile, bulk, 10 bags of 48 tubes/case
				3740WHI	Matrix 1.0 mL 2D, polypropylene, V bottom ScrewCap tubes with white caps, Sterile, bulk, 10 bags of 48 tubes/case
				3740PUR	Matrix 1.0 mL 2D, polypropylene, V bottom ScrewCap tubes with purple caps, Sterile, bulk, 10 bags of 48 tubes/case
				3741	Matrix 1.0 mL 2D, polypropylene, V bottom ScrewCap tubes with caps, Sterile, 5 Latch Racks of 96 tubes/case
				3741RED	Matrix 1.0 mL 2D, polypropylene, V bottom ScrewCap tubes with red caps, Sterile, 5 Latch Racks of 96 tubes/case
				3741YEL	Matrix 1.0 mL 2D, polypropylene, V bottom ScrewCap tubes with yellow caps, Sterile, 5 Latch Racks of 96 tubes/case
				3741BLU	Matrix 1.0 mL 2D, polypropylene, V bottom ScrewCap tubes with blue caps, Sterile, 5 Latch Racks of 96 tubes/case
				3741GRE	Matrix 1.0 mL 2D, polypropylene, V bottom ScrewCap tubes with green caps, Sterile, 5 Latch Racks of 96 tubes/case
				3741WHI	Matrix 1.0 mL 2D, polypropylene, V bottom ScrewCap tubes with white caps, Sterile, 5 Latch Racks of 96 tubes/case
				3741PUR	Matrix 1.0 mL 2D, polypropylene, V bottom ScrewCap tubes with purple caps, Sterile, 5 Latch Racks of 96 tubes/case
3742	Matrix 1.0 mL 2D, polypropylene, V bottom ScrewCap tubes without caps, Sterile, 5 Latch Racks of 96 tubes/case				
3302	Thermo Scientific ID Scribe Rack: 1.5-2.0 mL Microcentrifuge Tubes, Side Writing	Side	20-32	3448	Molecular BioProducts 1.5mL Snap Cap microcentrifuge tube, graduated, flat cap, NS
				3451	Molecular BioProducts 1.5mL Snap Cap microcentrifuge tube, graduated, flat cap, S
				3434	Molecular BioProducts 2.0mL Snap Cap microcentrifuge tube, graduated, flat cap, NS
				3453	Molecular BioProducts 2.0mL Snap Cap microcentrifuge tube, graduated, flat cap, S
				3456	Molecular BioProducts 1.5mL Safelock Cap microcentrifuge tube, graduated, flat cap, NS
				3457	Molecular BioProducts 1.5mL Safelock Cap microcentrifuge tube, graduated, flat cap, S
				3457/W	Molecular BioProducts 1.5mL Safelock Cap microcentrifuge tube, graduated, individually wrapped, flat cap, S
				3458	Molecular BioProducts 2.0mL Safelock Cap microcentrifuge tube, graduated, flat cap, NS
				3459	Molecular BioProducts 2.0mL Safelock Cap microcentrifuge tube, graduated, flat cap, S
				3459/W	Molecular BioProducts 2.0mL Safelock Cap microcentrifuge tube, graduated, individually wrapped, flat cap, S
				3464	Molecular BioProducts 1.5mL unattached Screw Cap Conical microcentrifuge tube, flat cap, NS
				3464A	Molecular BioProducts 1.5mL unattached Screw Cap Conical Amber microcentrifuge tube, flat cap, NS
				3461	Molecular BioProducts 1.5mL attached Screw Cap Conical microcentrifuge tube, flat cap, S
				3461A	Molecular BioProducts 1.5mL attached Screw Cap Conical Amber microcentrifuge tube, flat cap, S
				3466	Molecular BioProducts 1.5mL Screw Cap Conical microcentrifuge tube, caps not included, S
				3468	Molecular BioProducts 2.0mL unattached Screw Cap Conical microcentrifuge tube, flat cap, NS
				3468A	Molecular BioProducts 2.0mL unattached Screw Cap Conical Amber microcentrifuge tube, flat cap, NS
3463	Molecular BioProducts 2.0mL attached Screw Cap Conical microcentrifuge tube, flat cap, S				

Rack PN	Rack Description	Writing Area	Tubes/Rack	Compatible PN	Description
3302	Thermo Scientific ID Scribe Rack: 1.5-2.0 mL Microcentrifuge Tubes, Side Writing	Side	20-32	3463A	Molecular BioProducts 2.0mL attached Screw Cap Conical Amber microcentrifuge tube, flat cap, S
				3470	Molecular BioProducts 2.0mL Screw Cap Conical microcentrifuge tube, caps not included, S
				3474	Molecular BioProducts 1.5mL unattached Screw Cap Free Standing microcentrifuge tube, flat cap, NS
				3474A	Molecular BioProducts 1.5mL unattached Screw Cap Free Standing Amber microcentrifuge tube, flat cap, NS
				3467	Molecular BioProducts 1.5mL attached Screw Cap Free Standing microcentrifuge tube, flat cap, S
				3467A	Molecular BioProducts 1.5mL attached Screw Cap Free Standing Amber microcentrifuge tube, flat cap, S
				3478	Molecular BioProducts 1.5mL Screw Cap Free Standing microcentrifuge tube, caps not included, S
				3488	Molecular BioProducts 2.0mL unattached Screw Cap Free Standing microcentrifuge tube, graduated, flat cap, NS
				3488A	Molecular BioProducts 2.0mL unattached Screw Cap Free Standing Amber microcentrifuge tube, graduated, flat cap, NS
				3469	Molecular BioProducts 2.0mL attached Screw Cap Free Standing microcentrifuge tube, graduated, flat cap, S
				3469A	Molecular BioProducts 2.0mL attached Screw Cap Free Standing Amber microcentrifuge tube, graduated, flat cap, S
				3490	Molecular BioProducts 2.0mL Screw Cap Free Standing microcentrifuge tube, graduated, caps not included, S
3303	Thermo Scientific ID Scribe Rack: 1.5-2.0 mL Microcentrifuge Tubes, Top Writing	Top	42	3448	Molecular BioProducts 1.5mL Snap Cap microcentrifuge tube, graduated, flat cap, NS
				3451	Molecular BioProducts 1.5mL Snap Cap microcentrifuge tube, graduated, flat cap, S
				3434	Molecular BioProducts 2.0mL Snap Cap microcentrifuge tube, graduated, flat cap, NS
				3453	Molecular BioProducts 2.0mL Snap Cap microcentrifuge tube, graduated, flat cap, S
				3456	Molecular BioProducts 1.5mL Safelock Cap microcentrifuge tube, graduated, flat cap, NS
				3457	Molecular BioProducts 1.5mL Safelock Cap microcentrifuge tube, graduated, flat cap, S
				3457/W	Molecular BioProducts 1.5mL Safelock Cap microcentrifuge tube, graduated, individually wrapped, flat cap, S
				3458	Molecular BioProducts 2.0mL Safelock Cap microcentrifuge tube, graduated, flat cap, NS
				3459	Molecular BioProducts 2.0mL Safelock Cap microcentrifuge tube, graduated, flat cap, S
				3459/W	Molecular BioProducts 2.0mL Safelock Cap microcentrifuge tube, graduated, individually wrapped, flat cap, S
				3464	Molecular BioProducts 1.5mL unattached Screw Cap Conical microcentrifuge tube, flat cap, NS
				3464A	Molecular BioProducts 1.5mL unattached Screw Cap Conical Amber microcentrifuge tube, flat cap, NS
				3461	Molecular BioProducts 1.5mL attached Screw Cap Conical microcentrifuge tube, flat cap, S
				3461A	Molecular BioProducts 1.5mL attached Screw Cap Conical Amber microcentrifuge tube, flat cap, S
				3468	Molecular BioProducts 2.0mL unattached Screw Cap Conical microcentrifuge tube, flat cap, NS
				3468A	Molecular BioProducts 2.0mL unattached Screw Cap Conical Amber microcentrifuge tube, flat cap, NS
				3463	Molecular BioProducts 2.0mL attached Screw Cap Conical microcentrifuge tube, flat cap, S
				3463A	Molecular BioProducts 2.0mL attached Screw Cap Conical Amber microcentrifuge tube, flat cap, S
				3474	Molecular BioProducts 1.5mL unattached Screw Cap Free Standing microcentrifuge tube, flat cap, NS
				3474A	Molecular BioProducts 1.5mL unattached Screw Cap Free Standing Amber microcentrifuge tube, flat cap, NS
				3467	Molecular BioProducts 1.5mL attached Screw Cap Free Standing microcentrifuge tube, flat cap, S
				3467A	Molecular BioProducts 1.5mL attached Screw Cap Free Standing Amber microcentrifuge tube, flat cap, S
				3488	Molecular BioProducts 2.0mL unattached Screw Cap Free Standing microcentrifuge tube, graduated, flat cap, NS
				3488A	Molecular BioProducts 2.0mL unattached Screw Cap Free Standing Amber microcentrifuge tube, graduated, flat cap, NS
3469	Molecular BioProducts 2.0mL attached Screw Cap Free Standing microcentrifuge tube, graduated, flat cap, S				
3469A	Molecular BioProducts 2.0mL attached Screw Cap Free Standing Amber microcentrifuge tube, graduated, flat cap, S				

Rack PN	Rack Description	Writing Area	Tubes/Rack	Compatible PN	Description
3304	Thermo Scientific ID Scribe Rack: 15 mL Centrifuge Tubes, Side Writing	Side	10	366052	Nunc 15 mL Screw Top Centrifuge Tubes, PBS, S, racked 500/case
				366036	Nunc 15 mL Screw Top Centrifuge Tubes, PP, S, racked 500/case
				366079	Nunc 15 mL Screw Top Centrifuge Tubes, PBS, S, bulk 500/case
				366060	Nunc 15 mL Screw Top Centrifuge Tubes, PP, S, bulk 500/case
				362694	Nunc 15 mL EZ Flip Centrifuge Tubes, PP, S, bulk 500/case
				362695	Nunc 15 mL EZ Flip Centrifuge Tubes, PP, S, racked 500/case
3305	Thermo Scientific ID Scribe Rack: Micropackaging Vials and Closures, Side Writing	Side	24	362800-0005	Nalgene Micropackaging Vials, 0.5 mL, natural PP, 1000/case
				362800-0015	Nalgene Micropackaging Vials, 1.5 mL, natural PP, 1000/case
				362800-0020	Nalgene Micropackaging Vials, 2.0 mL, natural PP, 1000/case
				362805-0005	Nalgene Micropackaging Vials, 0.5 mL, amber PP, 1000/case
				362805-0020	Nalgene Micropackaging Vials, 2.0 mL, amber PP, 1000/case
3306	Thermo Scientific ID Scribe Rack: 3.6-5.0 mL Nunc and Nalgene CryoTubes including Cryobank, Side Writing	Side	12	5000-0050	Nalgene Cryogenic Vial, 5.0 mL, ext thread, conical bottom, self-standing, anti-rotation, PP tube w/ writing area, PE screw cap, clear, S, 25 packs of 10/cs
				5001-0050	Nalgene Linear Barcoded (ink-jet, Code 128) Cryogenic Vial, 5.0 mL, ext thread, conical bottom, self-standing, anti-rotation, PP tube w/ writing area, PE screw cap, clear, S, 25 packs of 10/cs (base 5000-0050)
				337516	Nunc CryoTube Vial, 4.5 mL, ext thread, round bottom, self-standing, anti-rotation, PP tube w/ printed area, PE screw cap, clear, S, 4 packs of 300/cs
				374220	5 ml Cryobank 2D code racked Sterile
				374222	5 ml Cryobank non coded racked sterile
				379189	Nunc CryoTube Vial, 3.6 mL, int thread, conical bottom, self standing, anti-rotation, PP tube w/ writing area and screw cap w/ silicone gasket, clear, S, 4 packs of 400/cs
				366524	Nunc CryoTube Vial, 3.6 mL, int thread, round bottom, PP tube w/ writing area and screw cap w/ silicone gasket, clear, S, 4 packs of 400/cs
				367997	Nunc CryoTube Vial, 3.6 mL, int thread, round bottom, PP tube w/ writing area and w/o caps, clear, NS, 6 packs of 250/cs
				379146	Nunc CryoTube Vial, 4.5 mL, int thread, conical bottom, self standing, anti-rotation, PP tube w/ writing area and screw cap w/ silicone gasket, clear, S, 4 packs of 300/cs
				361247	Nunc CryoTube Vial, 4.5 mL, int thread, round bottom, PP tube w/ writing area and w/o caps, clear, NS, 6 packs of 250/cs
				347643	Nunc CryoTube Vial, 4.5 mL, ext thread, round bottom, self-standing, anti-rotation, PP tube, PE screw cap, clear, S, 4 packs of 300/cs
				363452	Nunc CryoTube Vial, 4.5 mL, int thread, round bottom, PP tube w/ writing area and screw cap w/ silicone gasket, clear, S, 4 packs of 300/cs
3311	Thermo Scientific ID Scribe Rack: 1.2 mL Nalgene Cryogenic Tubes, Side Writing	Side	32	5000-0012	Nalgene Cryogenic Vial, 1.2 mL, ext thread, conical bottom, self-standing, anti-rotation, PP tube w/ writing area, PE screw cap, clear, S, 20 packs of 25/cs
				5001-0012	Nalgene Linear Barcoded (ink-jet, Code 128) Cryogenic Vial, 1.2 mL, ext thread, conical bottom, self-standing, anti-rotation, PP tube w/ writing area, PE screw cap, clear, S, 20 packs of 25/cs (base 5000-0012)
				5011-0012	Nalgene Cryogenic Vial, 1.2 mL, ext thread, conical bottom, self-standing, anti-rotation, PP tube, PE screw cap, clear, NS, bulk 1000/cs
				5012-0012	Nalgene Cryogenic Vial, 1.2 mL, ext thread, conical bottom, self-standing, anti-rotation, PP tube w/ writing area, PE screw cap, clear, S, bulk 1000/cs
3312	Thermo Scientific ID Scribe Rack: 2.0 mL Nalgene Cryogenic Tubes, Side Writing	Side	24	5000-0020	Nalgene Cryogenic Vial, 2.0 mL, ext thread, conical bottom, self-standing, anti-rotation, PP tube w/ writing area, PE screw cap, clear, S, 20 packs of 25/cs
				5001-0020	Nalgene Linear Barcoded (ink-jet, Code 128) Cryogenic Vial, 2.0 mL, ext thread, conical bottom, self-standing, anti-rotation, PP tube w/ writing area, PE screw cap, clear, S, 20 packs of 25/cs (base 5000-0020)
				5011-0020	Nalgene Cryogenic Vial, 2.0 mL, ext thread, conical bottom, self-standing, anti-rotation, PP tube, PE screw cap, clear, NS, bulk 1000/cs
				5012-0020	Nalgene Cryogenic Vial, 2.0 mL, ext thread, conical bottom, self-standing, anti-rotation, PP tube w/ writing area, PE screw cap, clear, S, bulk 1000/cs

Rack PN	Rack Description	Writing Area	Tubes/Rack	Compatible PN	Description
3313	Thermo Scientific ID Scribe Rack: 2 mL HPLC Vials, Side Writing	Side	24	C4000 Series	National Scientific 12x32 mm chromatography vials, screw thread
				C4010 Series	National Scientific 12x32 mm chromatography vials, screw thread
				C4011 Series	National Scientific 12x32 mm chromatography vials, crimp top and snap cap
				C4012 Series	National Scientific 12x32 mm chromatography vials, standard opening
				C4013 Series	National Scientific 12x32 mm chromatography vials, screw thread
				60180-502	Thermo Scientific 2.0 mL autosampler vials, 1000/Pk.
				60180-503	Thermo Scientific 2.5 mL autosampler vials, 1000/Pk.
				60180-593	Thermo Scientific 2.0 mL autosampler vials with caps, 1000/Pk.
60180-597	Thermo Scientific 2.0 mL autosampler vials with caps, 100/Pk.				
3350	Thermo Scientific ID Scribe Rack: 0.5 mL Cryobank Tubes, Side Writing	Side	48	374025	0.5 ml cryobank vials, 2D coded, racked, blue cap
				374026	0.5 ml cryobank vials, 2D coded, racked, red cap
				374027	0.5 ml cryobank vials, 2D coded, racked, green cap
				374066	0.5 ml Bank-It 2D
				374067	0.5 ml Bank-It NC
				374074	0.5 ml Bank-It 2D
				374075	0.5 ml Bank-It NC
				374080	0.5 ml CryoBank Bulk Sterile NC
				374082	0.5 ml CryoBank 2D Sterile
				374083	0.5 ml CryoBank NC Sterile
				374086	0.5 ml CryoBank 2D Sterile
				374087	0.5 ml CryoBank NC Sterile
				374097	0.5 ml cryobank vials, alphacode, racked
				374099	0.5 ml cryobank vials, uncoded, racked, red cap
374100	0.5 ml cryobank vials, uncoded, racked, blue cap				
3351	Thermo Scientific ID Scribe Rack: 0.5-0.75 mL 96-Way Tubes, Side Writing	Side	48	3750	Matrix 0.5 mL 2D, polypropylene, V bottom tubes, bulk, 1000/case
				3734	Matrix 0.5 mL 2D, polypropylene, V bottom tubes, 10 Latch Racks of 96 tubes/case
				3735	Matrix 0.5 mL 2D, polypropylene, V bottom tubes, Sterile, 10 Latch Racks of 96 tubes/case
				3725	Matrix 0.5 mL 2D, polypropylene, V bottom tubes, Sterile, 10 Latch Racks (with DuraSeal tall Lid) of 96 tubes/case
				3736	Matrix 0.5 mL 2D, polypropylene, V bottom tubes with DuraSeal septum installed, 10 Latch Racks of 96 tubes/case
				3737	Matrix 0.5 mL 2D, polypropylene, V bottom tubes with DuraSeal septum installed, Sterile, 10 Latch Racks of 96 tubes/case
				4170	Matrix 0.75 mL blank, polypropylene, round bottom tubes, bulk, 1000/case
				4271	Matrix 0.75 mL blank, polypropylene, round bottom tubes, 10 Latch Racks of 96 tubes/case
				4272	Matrix 0.75 mL blank, polypropylene, round bottom tubes, Sterile, 10 Latch Racks of 96 tubes/case
				4273	Matrix 0.75 mL alphanumeric, polypropylene, round bottom tubes, 10 Latch Racks of 96 tubes/case
				4274	Matrix 0.75 mL alphanumeric, polypropylene, round bottom tubes, Sterile, 10 Latch Racks of 96 tubes/case
				3730	Matrix 0.75 mL 2D, polypropylene, V bottom tubes, bulk, 1000/case
				3731	Matrix 0.75 mL 2D, polypropylene, V bottom tubes, 10 Latch Racks of 96 tubes/case
				3732	Matrix 0.75 mL 2D, polypropylene, V bottom tubes, Sterile, 10 Latch Racks of 96 tubes/case
				3729	Matrix 0.75 mL 2D, polypropylene, V bottom tubes with DuraSeal septum installed, 10 Latch Racks of 96 tubes/case
				3743	Matrix 0.5 mL 2D, polypropylene, V bottom ScrewCap tubes with caps, Sterile, bulk, 10 bags of 48 tubes/case

Rack PN	Rack Description	Writing Area	Tubes/Rack	Compatible PN	Description
3351	Thermo Scientific ID Scribe Rack: 0.5-0.75 mL 96-Way Tubes, Side Writing	Side	48	3743RED	Matrix 0.5 mL 2D, polypropylene, V bottom ScrewCap tubes with red caps, Sterile, bulk, 10 bags of 48 tubes/case
				3743YEL	Matrix 0.5 mL 2D, polypropylene, V bottom ScrewCap tubes with yellow caps, Sterile, bulk, 10 bags of 48 tubes/case
				3743BLU	Matrix 0.5 mL 2D, polypropylene, V bottom ScrewCap tubes with blue caps, Sterile, bulk, 10 bags of 48 tubes/case
				3743GRE	Matrix 0.5 mL 2D, polypropylene, V bottom ScrewCap tubes with green caps, Sterile, bulk, 10 bags of 48 tubes/case
				3743WHI	Matrix 0.5 mL 2D, polypropylene, V bottom ScrewCap tubes with white caps, Sterile, bulk, 10 bags of 48 tubes/case
				3743PUR	Matrix 0.5 mL 2D, polypropylene, V bottom ScrewCap tubes with purple caps, Sterile, bulk, 10 bags of 48 tubes/case
				3744	Matrix 0.5 mL 2D, polypropylene, V bottom ScrewCap tubes with caps, Sterile, 5 Latch Racks of 96 tubes/case
				3744RED	Matrix 0.5 mL 2D, polypropylene, V bottom ScrewCap tubes with red caps, Sterile, 5 Latch Racks of 96 tubes/case
				3744YEL	Matrix 0.5 mL 2D, polypropylene, V bottom ScrewCap tubes with yellow caps, Sterile, 5 Latch Racks of 96 tubes/case
				3744BLU	Matrix 0.5 mL 2D, polypropylene, V bottom ScrewCap tubes with blue caps, Sterile, 5 Latch Racks of 96 tubes/case
				3744GRE	Matrix 0.5 mL 2D, polypropylene, V bottom ScrewCap tubes with green caps, Sterile, 5 Latch Racks of 96 tubes/case
				3744WHI	Matrix 0.5 mL 2D, polypropylene, V bottom ScrewCap tubes with white caps, Sterile, 5 Latch Racks of 96 tubes/case
				3744PUR	Matrix 0.5 mL 2D, polypropylene, V bottom ScrewCap tubes with purple caps, Sterile, 5 Latch Racks of 96 tubes/case
				3745	Matrix 0.5 mL 2D, polypropylene, V bottom ScrewCap tubes without caps, Sterile, 5 Latch Racks of 96 tubes/case
3746	Matrix 0.5 mL 2D, polypropylene, V bottom ScrewCap tubes without caps, Sterile, bulk, 10 bags of 48 tubes/case				
3352	Thermo Scientific ID Scribe Rack: 0.5 mL Microcentrifuge Tubes, Side Writing	Side	30	3446	Molecular BioProducts 0.6mL Snap Cap microcentrifuge tube, graduated, flat cap, NS
				3449	Molecular BioProducts 0.6mL Snap Cap microcentrifuge tube, graduated, flat cap, S
				3454	Molecular BioProducts 0.6mL Safelock Cap microcentrifuge tube, graduated, flat cap, NS
				3455	Molecular BioProducts 0.6mL Safelock Cap microcentrifuge tube, graduated, flat cap, S
				3455/W	Molecular BioProducts 0.6mL Safelock Cap microcentrifuge tube, graduated, individually wrapped, flat cap, S
				3460	Molecular BioProducts 0.5mL unattached Screw Cap Conical microcentrifuge tube, flat cap, NS
				3460A	Molecular BioProducts 0.5mL unattached Screw Cap Conical Amber microcentrifuge tube, flat cap, NS
				3431	Molecular BioProducts 0.5mL attached Screw Cap Conical microcentrifuge tube, flat cap, S
				3431A	Molecular BioProducts 0.5mL attached Screw Cap Conical Amber microcentrifuge tube, flat cap, S
				3462	Molecular BioProducts 0.5mL Screw Cap Conical microcentrifuge tube, caps not included, S
				3472	Molecular BioProducts 0.5mL unattached Screw Cap Free Standing microcentrifuge tube, flat cap, NS
				3472A	Molecular BioProducts 0.5mL unattached Screw Cap Free Standing Amber microcentrifuge tube, flat cap, NS
				3465	Molecular BioProducts 0.5mL attached Screw Cap Free Standing microcentrifuge tube, flat cap, S
				3465A	Molecular BioProducts 0.5mL attached Screw Cap Free Standing Amber microcentrifuge tube, flat cap, S
				3422	Molecular BioProducts 0.5mL Screw Cap Free Standing microcentrifuge tube, caps not included, S
				3430	Molecular BioProducts 0.5mL frosted cap thin walled, natural, PCR tubes, flat cap, NS
				3430A	Molecular BioProducts 0.5mL frosted cap thin walled, assorted colors, PCR tubes, flat cap, NS
3432	Molecular BioProducts 0.5mL domed cap thin walled, natural, PCR tubes, NS				
3432A	Molecular BioProducts 0.5mL domed cap thin walled, assorted colors, PCR tubes, NS				

Rack PN	Rack Description	Writing Area	Tubes/Rack	Compatible PN	Description
3353	Thermo Scientific ID Scribe Rack: 0.5 mL Microcentrifuge Tubes, Top Writing	Top	48	3446	Molecular BioProducts 0.6mL Snap Cap microcentrifuge tube, graduated, flat cap, NS
				3449	Molecular BioProducts 0.6mL Snap Cap microcentrifuge tube, graduated, flat cap, S
				3454	Molecular BioProducts 0.6mL Safelock Cap microcentrifuge tube, graduated, flat cap, NS
				3455	Molecular BioProducts 0.6mL Safelock Cap microcentrifuge tube, graduated, flat cap, S
				3455/W	Molecular BioProducts 0.6mL Safelock Cap microcentrifuge tube, graduated, individually wrapped, flat cap, S
				3460	Molecular BioProducts 0.5mL unattached Screw Cap Conical microcentrifuge tube, flat cap, NS
				3460A	Molecular BioProducts 0.5mL unattached Screw Cap Conical Amber microcentrifuge tube, flat cap, NS
				3431	Molecular BioProducts 0.5mL attached Screw Cap Conical microcentrifuge tube, flat cap, S
				3431A	Molecular BioProducts 0.5mL attached Screw Cap Conical Amber microcentrifuge tube, flat cap, S
				3472	Molecular BioProducts 0.5mL unattached Screw Cap Free Standing microcentrifuge tube, flat cap, NS
				3472A	Molecular BioProducts 0.5mL unattached Screw Cap Free Standing Amber microcentrifuge tube, flat cap, NS
				3465	Molecular BioProducts 0.5mL attached Screw Cap Free Standing microcentrifuge tube, flat cap, S
				3465A	Molecular BioProducts 0.5mL attached Screw Cap Free Standing Amber microcentrifuge tube, flat cap, S
				3430	Molecular BioProducts 0.5mL frosted cap thin walled, natural, PCR tubes, flat cap, NS
3430A	Molecular BioProducts 0.5mL frosted cap thin walled, assorted colors, PCR tubes, flat cap, NS				
3354	Thermo Scientific ID Scribe Rack: 50 mL Centrifuge Tubes, Side Writing	Side	6	334959	Nunc 50 mL Centrifuge Tubes, PP, racked, S, 300/case
				334940	Nunc 50 mL Centrifuge Tubes, PP, bulk, S, 300/case
				362696	Nunc EZ Flip 50 mL Conical Centrifuge Tubes, PP, loose, S, 20 packs of 25/case
				362697	Nunc EZ Flip 50 mL Conical Centrifuge Tubes, PP, racked, S, 20 racks of 25/case
3355*	Thermo Scientific ID Scribe Rack: 1.8-2.0 mL Nalgene and Nunc CryoTube Caps With Inserts, Top Writing	Top	35	351934	Nunc CryoTube Vial, 1.8 mL, int thread, round bottom, PP tube w/ writing area and w/o caps, clear, NS, 5 packs of 500/cs
				375418	Nunc CryoTube Vial, 1.8 mL, ext thread, round bottom, self-standing, anti-rotation, PP tube w/ printed area, PE screw cap, clear, S, 4 packs of 450/cs
				340711	Nunc CryoTube Vial, 1.8 mL, ext thread, round bottom, PP narrow-neck tube w/ printed area, PE screw cap, clear, S, 4 packs of 500/cs
				347627	Nunc CryoTube Vial, 1.8 mL, ext thread, round bottom, self standing, anti-rotation, PP tube, PE screw cap, clear, S, 4 packs of 450/cs
				377267	Nunc CryoTube Vial, 1.8 mL, int thread, round bottom, self-standing, anti-rotation, PP tube and writing area and screw cap w/ silicone gasket, clear, S, 4 packs of 500/cs
				368632	Nunc CryoTube Vial, 1.8 mL, int thread, round bottom, self-standing, PP tube w/ writing area and screw cap, clear, S, 4 packs of 450/cs
				363401	Nunc CryoTube Vial, 1.8 mL, int thread, round bottom, PP tube w/ writing area and screw cap w/ silicone gasket, clear, S, 4 packs of 500/cs
				5000-0020	Nalgene Cryogenic Vial, 2.0 mL, ext thread, conical bottom, self-standing, anti-rotation, PP tube w/ writing area, PE screw cap, clear, S, 20 packs of 25/cs
				5001-0020	Nalgene Linear Barcoded (ink-jet, Code 128) Cryogenic Vial, 2.0 mL, ext thread, conical bottom, self-standing, anti-rotation, PP tube w/ writing area, PE screw cap, clear, S, 20 packs of 25/cs (base 5000-0020)
				5011-0020	Nalgene Cryogenic Vial, 2.0 mL, ext thread, conical bottom, self-standing, anti-rotation, PP tube, PE screw cap, clear, NS, bulk 1000/cs
				5012-0020	Nalgene Cryogenic Vial, 2.0 mL, ext thread, conical bottom, self-standing, anti-rotation, PP tube w/ writing area, PE screw cap, clear, S, bulk 1000/cs
3356	Thermo Scientific ID Scribe Rack: 0.2 mL PCR Tubes, Side Writing	Side	48	3430	Molecular BioProducts 0.2mL frosted cap thin walled, natural, PCR tubes, flat cap, NS
				3430A	Molecular BioProducts 0.2mL frosted cap thin walled, assorted colors, PCR tubes, flat cap, NS
				3432	Molecular BioProducts 0.2mL domed cap thin walled, natural, PCR tubes, flat cap, NS
				3432A	Molecular BioProducts 0.2mL domed cap thin walled, assorted colors, PCR tubes, flat cap, NS
3357	Thermo Scientific ID Scribe Rack: 0.2 mL PCR Tubes, Top Writing	Top	48	3430	Molecular BioProducts 0.2mL frosted cap thin walled, natural, PCR tubes, flat cap, NS
				3430A	Molecular BioProducts 0.2mL frosted cap thin walled, assorted colors, PCR tubes, flat cap, NS

\*indicated parts would need cap inserts in place to write on



Rack PN	Rack Description	Writing Area	Tubes/Rack	Compatible PN	Description
3358*	Thermo Scientific ID Scribe Rack: Micropackaging Vials and Closures, PPCO, Top Writing	Top	42	362800-0005	Nalgene Micropackaging Vials, 0.5 mL, natural PP, 1000/case
				362800-0015	Nalgene Micropackaging Vials, 1.5 mL, natural PP, 1000/case
				362800-0020	Nalgene Micropackaging Vials, 2.0 mL, natural PP, 1000/case
				362805-0005	Nalgene Micropackaging Vials, 0.5 mL, amber PP, 1000/case
				362805-0020	Nalgene Micropackaging Vials, 2.0 mL, amber PP, 1000/case
3359	Thermo Scientific ID Scribe Rack: PCR Strips, Top Writing	Top	48	3418	Molecular BioProducts 0.2mL domed cap thin walled, natural, PCR 8-strips, NS
				3418A	Molecular BioProducts 0.2mL domed cap thin walled, assorted colors, 8-strips tubes, NS
3360	Thermo Scientific ID Scribe Rack: ~25 x 75 mm Slides, Top Writing	Top	6	Various	Any ~25x75mm slide
3361	Thermo Scientific ID Scribe Rack: 1.0 mL Cryobank Tubes, Side Writing	Side	36	374070	1.0 ml Bank-It 2D
				374078	1.0 ml Bank-It 2D
				374079	1.0 ml Bank-It NC
				374081	1.0 ml CryoBank Bulk Sterile NC
				374084	1.0 ml CryoBank 2D Sterile
				374085	1.0 ml CryoBank NC Sterile
				374088	1.0 ml CryoBank 2D Sterile
				374089	1.0 ml CryoBank NC Sterile
				374090	1.0 ml Bank-It NC
				374094	1.0 ml cryobank vials, alphacode, racked
				374110	1.0mL CryoBank 2D Coded Green - NEW!
				374120	1.0mL CryoBank 2D Coded Red - NEW!
				374130	1.0mL CryoBank 2D Coded Blue - NEW!
3362	Thermo Scientific ID Scribe Rack: 1.0 mL Nalgene System 100 Cryogenic Tubes, Side Writing	Side	32	5000-1012	Nalgene System 100 Cryogenic Vial, 1.0 mL, ext thread, conical bottom , self-standing, anti-rotation, PP tube w/ writing area, PP screw cap w/ silicone gasket, clear, S, 20 packs of 25/cs
3363	Thermo Scientific ID Scribe Rack: 1.5 mL Nalgene System 100 Cryogenic Tubes, Side Writing	Side	32	5000-1020	Nalgene System 100 Cryogenic Vial, 1.5 mL, ext thread, conical bottom , self-standing, anti-rotation, PP tube w/ writing area, PP screw cap w/ silicone gasket, clear, S, 20 packs of 25/cs
				5001-1020	Nalgene System 100 Linear Barcoded (ink-jet, Code 128) Cryogenic Vial, 1.5 mL, ext thread, conical bottom , self-standing, anti-rotation, PP tube w/ writing area, PP screw cap w/ silicone gasket, clear, S, 20 packs of 25/cs (base 5000-1012)
3364	Thermo Scientific ID Scribe Rack: 0.5" Microplate, Top Writing	Top	1	Various	Any Nunc, Matrix, Thermo Scientific Microplate ~0.5" high (standard height)
3365	Thermo Scientific ID Scribe Rack: IVF Straws, Side Writing	Side	10	Various	IVF Straws, Side Writing
3366*	Thermo Scientific ID Scribe Rack: 1.0-1.2 mL Nalgene and Nunc CryoTube Caps With Inserts, Top Writing	Top	35	347597	Nunc CryoTube Vial, 1.0 mL, ext thread, conical bottom, self standing, anti-rotation, PP tube, PE screw cap, clear, S, 4 packs of 500/cs
				375353	Nunc CryoTube Vial, 1.0 mL, ext thread, conical bottom, self standing, anti-rotation, PP tube w/ printed area, PE screw cap, clear, S, 4 packs 500/cs
				375299	Nunc CryoTube Vial, 1.0 mL, ext thread, round bottom , PP narrow-neck tube w/ printed area, PE screw cap, clear, S, 4 packs of 500/cs
				377224	Nunc CryoTube Vial, 1.0 mL, int thread, conical bottom , self standing, anti-rotation, PP tube w/ writing area and screw cap w/ silicone gasket, clear, S, 4 packs of 500/cs
				366656	Nunc CryoTube Vial, 1.0 mL, int thread, conical bottom , self standing, PP tube w/ writing area and screw cap w/ silicone gasket, clear, S, 4 packs of 500/cs
				5000-0012	Nalgene Cryogenic Vial, 1.2 mL, ext thread, conical bottom , self-standing, anti-rotation, PP tube w/ writing area, PE screw cap, clear, S, 20 packs of 25/cs
				5001-0012	Nalgene Linear Barcoded (ink-jet, Code 128) Cryogenic Vial, 1.2 mL, ext thread, conical bottom , self-standing, anti-rotation, PP tube w/ writing area, PE screw cap, clear, S, 20 packs of 25/cs (base 5000-0012)
				5011-0012	Nalgene Cryogenic Vial, 1.2 mL, ext thread, conical bottom , self-standing, anti-rotation, PP tube, PE screw cap,clear, NS, bulk 1000/cs
				5012-0012	Nalgene Cryogenic Vial, 1.2 mL, ext thread, conical bottom , self-standing, anti-rotation, PP tube w/ writing area, PE screw cap , clear, S, bulk 1000/cs

\*indicated parts would need cap inserts in place to write on



Visit [www.thermoscientific.com/IDscribe](http://www.thermoscientific.com/IDscribe)  
for more information and to see the video!

© 2011 Thermo Fisher Scientific Inc. All rights reserved. All other trademarks are the property of Thermo Fisher Scientific Inc. and its subsidiaries.

North America: Tel: 800.345.0206 | email: [matrix.info@thermofisher.com](mailto:matrix.info@thermofisher.com)  
Europe: Tel: +44 (0) 161 486 2110 | email: [matrix.eu.info@thermofisher.com](mailto:matrix.eu.info@thermofisher.com)  
Asia: email: [matrix.ap.info@thermofisher.com](mailto:matrix.ap.info@thermofisher.com)

[www.thermoscientific.com](http://www.thermoscientific.com)

Rev A

**Thermo**  
SCIENTIFIC