


CATALOG NO.....:		002124-0005
NOM. CAP, (L/GAL).....:		1/2
MATERIALS	BOTTLE	HDPE
	CLOSURE	PP
SIZE (NOM VOL L/GAL)....:		2/ 1/2
NOM. BRIM CAP. (mL).....:		2200
NECK FINISH (mm).....:		100-415
THREAD (T.P.I.).....:		5
NOM. WEIGHT W/CLOSURE (gms).....:		205
	INCH	MM
A (NECK I.D.).....:	3.51 ±0.08	89.2 ±2.0
B (HEIGHT W/CLOSURE)....:	9.60 ±.12	243.8 ±3.0
C (HEIGHT W/O CLOSURE)..:	9.26 ±.12	235.2 ±3.0
D (DIA).....:	4.73 ±0.09	120.1 ±2.3
W.T. (NOM. WALL THK)....:	0.080	2.03
T (MAJOR THD DIA.).....:	3.90 ±0.03	99.1 ±0.8
E (MINOR THD DIA.).....:	3.74 ±0.02	95.0 ±0.5
F (THREAD FACE).....:	0.25	6.4
G (THREAD PITCH).....:	0.20	5.1
ANGLE X.....:	45°	
ANGLE Y.....:	7°	



SPECS ON BACK

NOT TO SCALE

NOTES:

1. ALL DIMENSIONS ARE NOMINAL AND IN INCHES AND MILLIMETERS UNLESS OTHERWISE NOTED.
2. THIS IS NOT A PRODUCTION DRAWING, BUT IS FOR INFORMATIONAL PURPOSES ONLY, AND IS SUBJECT TO CHANGE WITHOUT NOTICE.

CONFIDENTIAL

THIS PRODUCT SPECIFICATION SHEET CONTAINS CONFIDENTIAL AND/OR PROPRIETARY INFORMATION AND IS TO BE USED ONLY FOR THE EXPRESSED PURPOSES AGREED UPON BY AN AUTHORIZED OFFICER OF THERMO FISHER SCIENTIFIC.

ThermoFisher
SCIENTIFIC

Thermo Fisher Scientific
75 Panorama Creek Drive
Rochester, NY 14625-2385, USA

MADE	PB	APP'D	JMC	PSS 00-2124-0005	REV.	1108
CK'D			11/3/08			

DESCRIPTION: FLUORINATED WIDE MOUTH BOTTLE