

Exclusive Thermo Scientific offer!

Fast Shipping - In seven business days or less!

12/02/2015

Purchase an eligible Thermo Scientific product and we will ship your order from our factory in seven business days or less from the date of your order.

Bench Top Centrifuges and Bench Top Centrifuge Packages	Part Number
Sorvall ST 40 120v Tabletop w/	75004510
Sorvall ST40Cent120V BT108/84	75101923
Sorvall ST40Cent120V BT196/144	75107271
SorvallST40RCent120V TC28/56	75253839
Sorvall ST40Cent120V TC28/56	75103839
Sorvall Legend XT 120v Tabletop	75004506
SorLegendXTCent120V TC28/56	75063839
SorLegendXTCent120V mp	75060817
SorLegendXTRCentPKG TC40/88	75217473
Sorvall Legend X1, 120v	75004221
SorLegendX1RCentPKG TC16/36	75618382
Sorvall ST 16, 120v	75004241
Sorvall ST16CentPKG BT56/76	75418180
Sorvall ST 16R, 120v	75004381
Microfuges	
SORVALL LEGEND MICRO 17 120V 60HZ W/CLICK SEAL ROTOR 24X1.5/2ML	75002431
SORVALL LEGEND MICRO 21 120V 60HZ W/CLICK SEAL ROTOR 24X1.5/2ML & DUAL ROW ROTOR	75002488
Micro21 It Takes Two Promo	75772488
SORVALL LEGEND MICRO 21R 120V 60HZ W/CLICK SEAL ROTOR 24X1.5/2ML & DUAL ROW ROTOR	75002480
Micro21R It Takes Two Promo	75772490
Heraeus Pico 21 Best of Both Whirls promo	75772477
Heraeus Fresco 21R Best of Both Whirls Promo	75772478
HERAEUS FRESCO 17R 120V 60HZ W/CLICK SEAL ROTOR 24X1.5/2ML	75002421
HERAEUS PICO 21 120V 60HZ W/CLICK SEAL ROTOR 24X1.5/2ML	75002416
CO2 Incubators	
Forma Series 3 Water Jacket CO2 Incubator with TC Sensor, 120V	204110
HERAccl 150i Copper CO2 Incubator	51026283
HERAccl 150i CU Dual Stack	50115060
HERAccl 150i Stainless Steel CO2 Incubator	51026282
HERAccl 150i SST Dual Stack	50116048
Modular Water Jacket Roller Base	190647
Ultra Low Temperature Freezers	
Forma 88000 Ultra Low Temperature Freezer w/500 box capacity 115V 60 Hz	88500A
Forma 88000 Ultra Low Temperature Freezer w/500 box capacity 208V 60 Hz	88500D
Forma 88000 Ultra Low Temperature Freezer w/600 box capacity 115V 60 Hz	88600A
Forma 88000 Ultra Low Temperature Freezer w/600 box capacity 208V 60 Hz	88600D
Forma 88000 Ultra Low Temperature Freezer w/700 box capacity 208V 60 Hz	88700D
VWR 23 cu ft 400 2" box capacity Upright Single Door 115V 60Hz	VWR40086A
VWR 23 cu ft 400 2" box capacity Upright Single Door 208-230V 60Hz	VWR40086D
Revco UxF Ultra Low Temperature Freezer w/500 box capacity 115V 60 Hz	UxF50086A
Revco UxF Ultra Low Temperature Freezer w/500 box capacity 208V 60 Hz	UxF50086D
Revco UxF Ultra Low Temperature Freezer w/600 box capacity 115V 60 Hz	UxF60086A
Revco UxF Ultra Low Temperature Freezer w/600 box capacity 208V 60 Hz	UxF60086D
Revco UxF Ultra Low Temperature Freezer w/700 box capacity 208V 60 Hz	UxF70086D
Revco EvF Ultra Low Temperature Freezer 23 cu ft 400 2" box capacity Upright Single Door 115 V 60 Hz	EvF 40086A
Revco EvF Ultra Low Temperature Freezer 23 cu ft 400 2" box capacity Upright Single Door 208 V 60 Hz	EvF 40086D
Lab Refrigerators and Freezers	
JEWETT +4°C, 5.4 cu. ft., 120 V 60 HZ UNDERCOUNTER BLOOD BANK REFRIGERATOR	CT1-1B
JEWETT +4°C, 23 cu ft, 120 V 60 HZ UPRIGHT GENERAL PURPOSE REFRIGERATOR WITH GLASS DOOR	JRG2304A
REVCO -20°C, 23 cu.ft., MANUAL DEFROST, 120 V 60 HZ UPRIGHT GENERAL-PURPOSE LAB FREEZER	UGL 2320 A
REVCO +4°C, 4.9 cu ft., 120V 60 HZ Undercounter General Purpose Lab Refrigerator	REL 404A
REVCO +4°C, 23 cu. ft., 120V 60 HZ UPRIGHT GENERAL-PURPOSE LAB REFRIGERATOR	REL 2304 A
REVCO +4°C, 23 cu. ft., 120V 60 HZ UPRIGHT GENERAL-PURPOSE LAB REFRIGERATOR WITH GLASS DOOR	RGL 2304 A
REVCO +4°C, 30 cu. ft., 120 V 60 HZ UPRIGHT GENERAL-PURPOSE LAB REFRIGERATOR	REL 3004 A
REVCO +4°C, 45 cu. ft., 120 V 60 HZ UPRIGHT CHROMATOGRAPHY REFRIGERATOR	REC 4504 A
REVCO +4°C, 50 cu. ft., 120 V 60 HZ UPRIGHT GENERAL-PURPOSE LAB REFRIGERATOR WITH GLASS DOORS	RGL 5004A
REVCO -20°C, 23 cu. ft., 120 V 60 HZ UPRIGHT GENERAL-PURPOSE LAB FREEZER	ULF 2320 A
REVCO -30°C, 30 cu. ft., 120 V 60 HZ UPRIGHT GENERAL-PURPOSE LAB FREEZER	ULT 3030 A
VWR +4C, 45 cu ft 120V 60 Hz Chromatography Refrigerator	MH48PA-GAEE-VW
VWR +4C, 49 cu ft 120V 60 Hz Chromatography Refrigerator	MH49PA-GAEE-VW
Microbiological Incubators	
Heratherm 18L Compact Incubator Temperature range 17-40C, Model JMC18 120-230V, US style Plug	50125590
Heratherm GP 100L Gravity Convection Incubator - OGS100 120V/60Hz	51028064
Heratherm GP 180L Gravity Convection Incubator - OGS180 120V/60Hz	51028065
Heratherm AP 60L Dual Convection Incubator - IMH60 120V/60Hz	51028066
Heratherm AP 100L Dual Convection Incubator - IMH100 120V/60Hz	51028067
General Purpose Ovens	
Heratherm GP 60L Gravity Convection Oven, Temp Range 50-250°C - OGS60 120V/60Hz	51028112
Heratherm GP 180L Gravity Convection Oven, Temp Range 50-250°C - OGS180 120VAC 60Hz	51028074
Heratherm GP 60L Mechanical Convection Oven, Temp Range 50-250°C - OMS60 120V/60Hz	51028121
Heratherm GP 100L Mechanical Convection Oven, Temp Range 50-250°C - OMS100 120VAC 60Hz	51028073
Heratherm AP 60L Gravity Oven Temp Range 50-330°C - OGH60 120V/60Hz	51028115
Heratherm AP 100L Gravity Oven Temp Range 50-330°C - OGH100 208-240V/50/60Hz	51028116
Heratherm AP 60L Mechanical Oven Temp Range 50-330°C - OMH60 120V/60Hz	51028124
Heratherm AP 180L Mechanical Oven Temp Range 50-330°C - OMH180 208-240V/50/60Hz	51028126
Rockers, Rotators, Mixers	
MAXI-MIX 120V UL	M167150
VARI-MIX 120V	M487250
SPECT-MIX HALF SIZE 120V	M710150
Hot Plates and Stirrers	
CIMAREC STIRRER 120V 4X4	S1308150
CIMAREC STIRRER 120V 7X7	S1311250
CIMAREC STIRRER 120V 10X10	S1314350
STIRRER STUDENT 120V	S1685150
CIMAREC STIR PLATE 120V 4X4	SP1310150
CIMAREC STIR PLATE 120V 7X7	SP1313250
CIMAREC STIR PLATE 120V 10X10	SP1316350
SUPER NUOVA SP 120V 7X7 CER	SP1318250
SUPER NUOVA SP 120V 10X10 CER	SP1338350
SUPER NUOVA SP 4POS 120V	SP1359350
STIRRING HOT PLATE 4X4 120V	SP194715
STIRRING HOT PLATE 7X7 120V	SP195025
MULTIPOINT 15 100-240V	S0093538
CIMAREC HOT PLATE 120V 4X4	HP1309150
CIMAREC HOT PLATE 120V 7X7	HP1312250
CIMAREC HOT PLATE 120V 10X10	HP1315350
HOT PLATE 7X7 120V	HP194825
HOT PLATE 12 X 12 120V UL/CSA	HPA2235MQ
HOT PLATE 12 X 24 120V UL/CSA	HPA2245MQ
Furnaces	
Thermo Scientific Thermolyne Furnace - 1.3 cu ft unit, 120V, with Digital single set point control furnace	FB1315M
Thermo Scientific Thermolyne Furnace - 2.1 cu ft unit, 120V, with Digital single set point control furnace	FB1415M
Thermo Scientific Lindberg/BlueM Mini Mite Tube Furnace - 12in heating zone, 120V, with Digital single set point control	TF55035A-1
Thermo Scientific Lindberg/BlueM Mini Mite Tube Furnace - 12in heating zone, 120V, with Digital multi set point control	TF55035A-1
Biological Safety Cabinets	
1300 Series Class II, Type A2 Biological Safety Cabinet Package, 4 ft. Cabinet Width Package. Includes Cabinet, Manual Adjustable Height Stand, Factory installed UV Light, 1 set of armrests	1375
1300 Series Class II, Type A2 Biological Safety Cabinet Package, 6 ft. Cabinet Width Package. Includes Cabinet, Manual Adjustable Height Stand, Factory installed UV Light, 1 set of armrests	1377
SpeedVacs	
Thermo Scientific Savant DNA120 Vacuum Concentrator with timer 115VAC 60HZ	DNA120-115
Thermo Scientific Savant DNA120 Vacuum Concentrator with timer for Oligo Prep 115VAC 60 HZ	DNA120CP-115
Thermo Scientific Savant ISS110 Integrated Vacuum Concentrator with 50 cold trap 115VAC 60HZ	ISS110P1-115

Terms & Conditions: The menu of eligible products listed and dated may be modified from time to time by Thermo Fisher Scientific.

© 2015 Thermo Fisher Scientific Inc. All rights reserved. All trademarks are the property of Thermo Fisher Scientific Inc. and its subsidiaries. Specification, terms and prices are subject to change. Not all products are available in all countries. Please consult your local sales representative for details.

