

Thermo Scientific IQCP Product Listing

CLSI-exempt Culture Media

We have created a risk assessment template and other resources to support your laboratory's IQCP for the following Thermo Scientific™ Remel™ CLSI-exempt culture media. Please refer to CLSI M22-A3 Table 1B for list of CLSI-exempt media.

General Bacteriological Media

Blood Agar

Description	Item Number
Blood Agar, 5% Sheep Blood 150/PK	R01198
Blood Agar, 5% Sheep Blood 10/PK	R01200
Blood Agar, 5% Sheep Blood 15/PK	R01201
Blood Agar, 5% Sheep Blood 100/PK	R01202
Blood Agar, 5% Sheep Blood (25ml) 100/PK	R01209
Blood/Blood Biplate 100/PK	R02019
Blood/Blood Biplate 10/PK	R02020
Blood/Chocolate Biplate 100/PK	R02029
Blood/Chocolate Biplate 10/PK	R02030
Blood/EMB, Levine Biplate 10/PK	R02040
Blood/EMB, Levine Biplate 100/PK	R02041
Blood/MacConkey Biplate 100/PK	R02049
Blood/MacConkey Biplate 10/PK	R02050
Blood/SXT Biplate 10/PK	R02053
Blood Agar Quad 10/PK	R02420
Blood Agar, 5% Sheep Blood (slant) 100/PK	R060310
Blood Agar, 5% Sheep Blood (slant) 20/PK	R060312
Blood Agar, 5% Sheep Blood (slant) 20/PK	R07013

Chocolate Agar*

Description	Item Number
Chocolate Agar* 150/PK	R01293
Chocolate Agar* 10/PK	R01300
Chocolate Agar* 15/PK	R01301
Chocolate Agar* 100/PK	R01302
Chocolate Agar* 20/PK	R060482
Chocolate Agar* 100/PK	R060480
Chocolate Agar* 20/PK	R08240

*Quality control exempt media used for fastidious organisms (in particular exempt media for recovery of *N. gonorrhoeae*, *H. influenzae*, *Campylobacter* sp., *Legionella* sp., and *B. cepacia* among others) strongly recommended to ensure optimum recovery of organisms.

General Bacteriological Media Cont'd

Thioglycolate Broth

Description	Item Number
Thio Med w/Dex, Hem, Vit, K (7ml) 100/PK	R05152
Thio Med w/Dex, Hem, Vit K (7ml) 20/PK	R05153
Thio Med w/o Ind, w/Dex (9ml) 100/PK	R064700
Thio Med w/o Ind, w/Dex (9ml) 20/PK	R064702
Thio Med w/o Ind, w/o Dex (5ml) 100/PK	R064710
Thio Med w/o Ind, w/o Dex (5ml) 20/PK	R064712
Thio Med w/o Ind, w/o Dex (9ml) 20/PK	R064716
Thio Med w/Dex, Hem, Vit K (9ml) 100/PK	R064720
Thio Med w/Dex, Hem, Vit K (9ml) 20/PK	R064722
Thio Med w/Dex, Hem, Vit K (5ml) 100/PK	R064730
Thio Med w/Dex, Hemin, Vit K (5ml) 20/PK	R064732
Thio Med w/o Ind, w/Dex (10ml) 100/PK	R07176
Thio Med w/o Ind, w/Dex (10ml) 20/PK	R07178
Thio Med w/Dex, Hem, Vit K (10ml) 100/PK	R07180
Thio Med w/Dex, Hem, Vit K (10ml) 20/PK	R07182
Thio Med w/Ind, Dex, Vit K, Hem (10ml) 20/PK	R07900
Thio Med w/o Ind, w/Dex (10ml) 100/PK	R08850
Thio Med w/o Ind, w/Dex (10ml) 20/PK	R08852
Thio Med w/o Ind, w/Dex (18ml) 100/PK	R08856
Thio Med w/o Ind, w/Dex (18ml) 20/PK	R08858

Urease Agar

Description	Item Number
Urea Agar (slant) 100/PK	R065210
Urea Agar (slant) 20/PK	R065212

Blood Culture Media

Thiol Blood Culture Broth

Description	Item Number
Thermo Scientific™ VersaTREK™ REDOX™ 2, 80 mL	7103-44
VersaTREK REDOX 2, 40mL EZ Draw™	7107-44
VersaTREK REDOX 2, 40mL (NM)	7110-44

Trypticase Soy Blood Culture Broth

Description	Item Number
VersaTREK REDOX 1, 80mL	7102-44
VersaTREK REDOX 1, 40mL EZ Draw	7106-44
Thermo Scientific™ SIGNAL™ Blood Culture System	BC0100M

Media for Gram-Positive Bacteria

Columbia (CNA) Agar

Description	Item Number
CNA w/Blood (25ml) 100/PK	R01318
CNA w/Blood 10/PK	R01320
CNA w/Blood 15/PK	R01321
CNA w/Blood 100/PK	R01322
CNA w/Blood 150/PK	R01323
CNA/Bile Esculin Azide Biplate 100/PK	R02061

Selective Media for Enterococci with Azide

Description	Item Number
Bile Esculin Azide Agar 100/PK	R01189
Bile Esculin Azide Agar 10/PK	R01194
Bile Esculin Azide Agar 15/PK	R01195

Media for Gram-Positive Bacteria Cont'd

LIM Broth

Description	Item Number
Todd Hewitt Broth w/CNA (LIM) (3ml) 100/PK	R064810
Todd Hewitt Broth w/CNA (LIM) (3ml) 20/PK	R064812
Todd Hewitt Broth w/CNA (LIM) (5ml) 100/PK	R064814

Mannitol Salt Agar

Description	Item Number
Mannitol Salt Agar 10/PK	R01580
Mannitol Salt Agar 15/PK	R01581
Mannitol Salt Agar 100/PK	R01587

Phenylethyl Alcohol (PEA) Agar

Description	Item Number
PEA w/5% Sheep Blood 10/PK	R01660
PEA w/5% Sheep Blood 15/PK	R01661
PEA w/5% Sheep Blood 100/PK	R01662
MacConkey/PEA w/SB BiPlate 10/PK	R02096

Selective Agar for Group A Streptococcus

Description	Item Number
Strep A Isolation Agar 100/PK	R01855
Strep A Isolation Agar 10/PK	R01856
Strep Selective Agar 10/PK	R01857
Strep Selective Agar 100/PK	R01864
Strep Selective Agar 15/PK	R01867
Strep Selective II Agar 10/PK	R01858
Strep Selective II Agar 100/PK	R01859
Strep A Isol/Strep A Isol Biplate 10/PK	R02162

Sheep Blood Agar with Sulfamethoxazole/Trimethoprim (SXT)

Description	Item Number
SXT Blood Agar 10/PK	R01860
SXT Blood Agar 15/PK	R01861
SXT Blood Agar 100/PK	R01862
Blood/SXT Biplate 10/PK	R02053
SXT Blood/SXT Blood Biplate 10/PK	R02142

Media for Gram-Negative Bacteria

Cefsulodin Irgasan Novobiocin (CIN) Agar

Description	Item Number
Yersinia Sel (CIN) Agar 10/PK	R01998
Yersinia Sel (CIN) (deep, add R45050) 20/PK	R09999

Citrate Agar

Description	Item Number
Simmons Citrate Agar (slant) 100/PK	R060494
Simmons Citrate Agar (slant) 20/PK	R060496

Cystine Lactose Electrolyte Deficient (CLED) Agar

Description	Item Number
CLED Agar 10/PK	R01312

Eosin Methylene Blue (EMB) Agar

Description	Item Number
EMB Agar, Levine 10/PK	R01400
EMB Agar, Levine 15/PK	R01401
EMB Agar, Levine 100/PK	R01402
EMB Agar, Levine 150/PK	R01403

Gram-Negative (GN) Broth

Description	Item Number
GN Broth (4ml) skirt 100/PK	R060988
GN Broth (5ml) 100/PK	R060990
GN Broth (5ml) 20/PK	R060992
GN Broth (10ml) 100/PK	R08380
GN Broth (10ml) 20/PK	R08382
GN Broth (8ml) 100/PK	R08383
GN Broth (8ml) 20/PK	R08393

Hektoen (HE) Agar

Description	Item Number
HE Agar (Hektoen Enteric) 10/PK	R01480
HE Agar (Hektoen Enteric) Agar 15/PK	R01481
HE Agar (Hektoen Enteric) 100/PK	R01483
HE (Hektoen Enteric)/SS Biplate 10/PK	R02082
HE (Hektoen Enteric)/XLD Biplate 10/PK	R02086

Media for Gram-Negative Bacteria Cont'd

MacConkey Agar

Description	Item Number
MacConkey Agar 10/PK	R01550
MacConkey Agar 15/PK	R01551
MacConkey Agar 100/PK	R01552
MacConkey Agar (25ml) 100/PK	R01557
MacConkey Agar 150/PK	R01562
Blood/MacConkey Biplate 100/PK	R02049
Blood/MacConkey Biplate 10/PK	R02050
EMB Agar, Levine/MacConkey Biplate 10/PK	R02068
MacConkey/Mannitol Salt Biplate 10/PK	R02092
MacConkey/PEA w/SB Biplate 10/PK	R02096
MacConkey Agar (slant) 20/PK	R061322

Salmonella-Shigella Agar (SS)

Description	Item Number
Salmonella Shigella Agar 10/PK	R01840
Salmonella Shigella Agar 15/PK	R01841
Salmonella Shigella Agar 100/PK	R01842
Salmonella Shigella/XLD Biplate 10/PK	R02140
Salmonella Shigella Agar (slant) 20/PK	R064582

Selenite Broth

Description	Item Number
Selenite Broth (9ml) 100/PK	R064500
Selenite Broth (9ml) 20/PK	R064502

Thiosulfate Citrate Bile Salts Sucrose Agar (TCBS)

Description	Item Number
TCBS Agar 10/PK	R01865
TCBS Agar (deep) 20/PK	R09832

Media for Gram-Negative Bacteria Cont'd

Triple Sugar Iron (TSI) Agar

Description	Item Number
Triple Sugar Iron Agar (slant) 100/PK	R064850
Triple Sugar Iron Agar (slant) 20/PK	R064852
Triple Sugar Iron Agar (slant) 100/PK	R07200
Triple Sugar Iron Agar (slant) 20/PK	R07202

Trypticase Soy Agar with Sheep Blood with Ampicillin

Description	Item Number
Blood Agar w/Amp (10mcg) 10/PK	R01226

Xylose Lysine Desoxycholate (XLD) Agar

Description	Item Number
XLD Agar 10/PK	R01980
XLD Agar 15/PK	R01981
XLD Agar 100/PK	R01982
HE (Hektoen Enteric)/XLD Biplate 10/PK	R02086
Salmonella Shigella/XLD Biplate 10/PK	R02140

Neisseria gonorrhoeae Media

Thayer-Martin Agar (Modified)*

Description	Item Number
Thayer Martin, Modified (JEMBEC)* 10/pk	R10310
Thayer Martin Modified* 10/pk	R01880
Thayer Martin Modified* 15/pk	R01881
Thayer Martin Modified* 100/pk	R01882

*Quality control exempt media used for fastidious organisms (in particular exempt media for recovery of *N. gonorrhoeae*, *H. influenzae*, *Campylobacter* sp., *Legionella* sp., and *B. cepacia* among others) strongly recommended to ensure optimum recovery of organisms.

Legionella Media

Legionella Selective (CYE/BCYE) Agar*

Description	Item Number
Buffered CYE Agar* 10/PK	R01342
Buffered CYE Agar* 20/PK	R07092
Buffered CYE Agar* 20/PK	R09300

*Quality control exempt media used for fastidious organisms (in particular exempt media for recovery of *N. gonorrhoeae*, *H. influenzae*, *Campylobacter* sp., *Legionella* sp., and *B. cepacia* among others) strongly recommended to ensure optimum recovery of organisms.

Burkholderia (PC) Media

Pseudomonas cepacia (PC) Agar*

Description	Item Number
Burkholderia cepacia Agar* 10/PK	R01709

*Quality control exempt media used for fastidious organisms (in particular exempt media for recovery of *N. gonorrhoeae*, *H. influenzae*, *Campylobacter* sp., *Legionella* sp., and *B. cepacia* among others) strongly recommended to ensure optimum recovery of organisms.

Campylobacter Media

Charcoal Selective Agar with CVC

Description	Item Number
Charcoal Selective Medium 10/PK	R01294

Anaerobic Media

Anaerobic Blood Agar

Description	Item Number
Anaer Reducible Blood Agar 100/PK	R01059
Anaer Reducible Blood Agar 10/PK	R01060
Anaer Reducible Blood Agar 15/PK	R01061

Anaerobic Phenylethyl Alcohol (PEA) Agar

Description	Item Number
Anaer Reducible Bld/PEA w/SB, Vit K 10/PK	R02124
Anaer Reducible LKV/PEA w/Vit K Biplate 10/PK	R02126

Bacteroides Bile Esculin (BBE) Agar

Description	Item Number
Anaer Reducible LKV/B Frag (BBE) Biplate 10/PK	R02006
CDC Blood/B Frag (BBE) Biplate 100/PK	R02176
B Frag Isolation Agar 10/PK	R01104

Anaerobic Media Cont'd

Brucella Agar

Description	Item Number
Brucella Agar w/5% SB 10/PK	R01252
Brucella Agar w/5% SB 100/PK	R01253

Brucella Agar w/ Hemin/Vit K

Description	Item Number
Brucella w/5% SB, Hem, Vit K 10/PK	R01254
Brucella w/5% SB, Hem, Vit K 100/PK	R01255
Brucella w/5% SB, Hem, Vit K (150mm) 10/PK	R04011
Brucella w/Lkd Bld, Hem, Vit K (150mm) 10/PK	R04012

Brucella Laked Blood Agar with KV

Description	Item Number
Brucella Agar, LKV 10/PK	R01262
Brucella KV Agar 10/PK	R01264

CDC Anaerobe Laked Blood Agar with KV

Description	Item Number
Anaer (CDC) LKV Blood Agar 10/PK	R01044
Anaer (CDC) LKV Blood Agar 100/PK	R01045

CDC Anaerobic 5% Sheep Blood with KV

Description	Item Number
Anaer (CDC) KV Blood Agar 10/PK	R01042
Anaer (CDC) KV Blood Agar 100/PK	R01043

Egg Yolk (Modified) Agar

Description	Item Number
Anaer Egg Yolk Agar 10/PK	R01057

Mycobacteria (AFB) Media

Middlebrook 7H9 Broth

Description	Item Number
Middlebrook 7H9 Broth w/Glyc (2ml) 100/PK	R061344
Middlebrook 7H9 Broth w/Glyc (2ml) 20/PK	R061346
Middlebrook 7H9 w/Glyc (4.5ml) 20/PK	R061347
Middlebrook 7H9 w/Glyc (4ml) 20/PK	R07117
Middlebrook 7H9 w/Glyc, glass bead 20/PK	R07330

Lowenstein-Jensen Media

Description	Item Number
LJ Med (1oz BTL)100/PK	R10100
LJ Medium (1oz BTL) 10/PK	R10101
LJ Medium (slant 20x113) 100/PK	R08500
LJ Medium (slant) 20/PK	R08502
LJ Medium (slant 20x150) 100/PK	R09504
LJ Medium (slant) 20/PK	R09506
LJ Medium (5ml) 20/PK	R09512

Automated AFB Bottle Broths

Description	Item Number
VersaTREK Myco Broth	7111-42
VersaTREK Myco Broth, Modified Cap	7111-42M

Fungal Media

Cornmeal Agar

Description	Item Number
Cornmeal Agar 10/PK	R01326
Cornmeal Agar (22ml deep) 20/PK	R09282

Inhibitory Mold Agar

Description	Item Number
Inhibitory Mold Agar 10/PK	R01505
Inhibitory Mold Agar 100/PK	R01507
Inhibitory Mold Agar (35ml) 10/PK	R01508
Inhibitory Mold Agar (slant) 100/PK	R08410
Inhibitory Mold Agar (slant) 20/PK	R08412

Inhibitory Mold Agar w/Gentamicin

Description	Item Number
Inhibitory Mold Agar w/Gent (26ml) 100/PK	R01502
Inhibitory Mold Agar w/Gent (26ml) 10/PK	R01506

Soy Peptone Agar with CC, without pH Indicators

Description	Item Number
Mycobiotic Agar (Mycocel) (25ml) 10/PK	R01630
Mycobiotic Agar (35ml) 10/PK	R01645
Mycobiotic Agar (Mycocel) 100/PK	R01646
Mycobiotic Agar (slant) 100/PK	R08600
Mycobiotic Agar (Mycocel) (slant) 20/PK	R08602
Mycobiotic Agar (Mycocel) (slant) 100/PK	R09600
Mycobiotic Agar (1oz. bottle) 100/PK	R10130
Mycobiotic Agar (1oz. bottle) 10/PK	R10131
Mycobiotic Agar (Bactiflask) 20/PK	R10264
Mycobiotic Agar (Mycotube) 10/PK	R241055

Potato Dextrose Agar

Description	Item Number
Potato Dextrose Agar, pH 5.6 (26ml) 100/PK	R01693
Potato Dextrose Agar, pH 5.6 (26ml) 10/PK	R01695
Potato Dextrose Agar, pH 3.5 (26ml) 10/PK	R01697
Potato Dextrose Agar (slant) 100/PK	R08650
Potato Dextrose Agar (slant) 20/PK	R08652
Potato Dextrose Agar (deep) 100/PK	R09654
Potato Dextrose Agar (deep) 20/PK	R09656

Fungal Media Cont'd

Brain Heart Infusion with 5% Sheep Blood/CG Agar

Description	Item Number
BHI Agar w/SB, Chlor, Gent (35ml) 10/PK	R01123
BHI Agar w/SB, Chlor, Gent (slant) 100/PK	R08070
BHI Agar w/SB, Chlor, Gent (slant) 20/PK	R08072
BHI Agar w/SB, Chlor, Gent (1oz BTL) 100/PK	R10044
BHI Agar w/SB, Chlor, Gent (1oz BTL) 10/PK	R10045
BHI w/SB, Chlor, Gent (Bactiflask) 20/PK	R10248
BHI Agar w/SB, Chlor, Gent (26mL) 10/PK	R01144

Sabouraud Dextrose Agar

Description	Item Number
Sab Dex Emmons (35ml) 10/PK	R01728
Sab Dex Agar, Emmons (26ml) 10/PK	R01760
Sab Dex Emmons Agar 15/PK	R01761
Sab Dex Agar, Emmons (26ml) 100/PK	R01763
Sab Dex Agar pH 5.6 (26ml) 100/PK	R01766
Sab Dex Agar pH 5.6 (26ml) 10/PK	R01768
Sab Dex Agar, Emmons (slant) 100/PK	R054420
Sab Dex Agar, Emmons (slant) 20/PK	R064422
Sab Dex Agar pH 5.6 20/PK	R07810
Sab Dex Agar pH 5.6 100/PK	R08716
Sab Dex Agar, Emmons (slant) 100/PK	R08720
Sab Dex Agar, Emmons (slant) 20/PK	R08722
Sab Dex Agar pH 5.6 (slant) 100/PK	R09746
Sab Dex Agar pH 5.6 (slant) 20/PK	R09747
Sab Dex Agar, Emmons (1 oz BTL) 100/PK	R10150
Sab Dex Agar, Emmons (1 oz BTL) 10/PK	R10151
Sab Dex Agar, pH 5.6 (1 oz BTL) 100/PK	R10155
Sab Dex Agar, pH 5.6 (1 oz BTL) 10/PK	R10156
Sab Dex Agar pH 5.6 (Bactiflask) 20/PK	R10268
Sab Dex Agar, Emmons (Bactiflask) 20/PK	R10270

Sabouraud Dextrose Agar CG

Description	Item Number
Sab Dex, Emmons w/Chlor, Gent (26ml) 10/PK	R01772
Sab Dex, Emmons w/Chlor, Gent (slant) 20/PK	R08742

thermoscientific.com/microIQCP

© 2016 Thermo Fisher Scientific Inc. All rights reserved. All trademarks are the property of Thermo Fisher Scientific and its subsidiaries.

Contact Information:

microbiology@thermofisher.com
USA +1 800 255 6730

Thermo
S C I E N T I F I C

A Thermo Fisher Scientific Brand