

SENSITITRE™ GRAM NEGATIVE PLATE FORMAT

Plate Code: **DKMGN**

Plate Type: **MIC**

	1	2	3	4	5	6	7	8	9	10	11	12
A	MERO 0.12	MERO 0.25	MERO 0.5	MERO 1	MERO 2	MERO 4	MERO 8	MERO 16	AMI 4	AMI 8	AMI 16	AMI 32
B	GEN 0.5	GEN 1	GEN 2	GEN 4	GEN 8	AZT 0.5	AZT 1	AZT 2	AZT 4	AZT 8	AZT 16	AZT 32
C	CIP 0.06	CIP 0.12	CIP 0.25	CIP 0.5	CIP 1	CIP 2	P/T4 1/4	P/T4 2/4	P/T4 4/4	P/T4 8/4	P/T4 16/4	P/T4 32/4
D	AUGC 4/2	AUGC 8/2	AUGC 16/2	AUGC 32/2	AUGC 64/2	C/T 0.5/4	C/T 1/4	C/T 2/4	C/T 4/4	C/T 8/4	C/T 16/4	C/T 32/4
E	COL 0.25	COL 0.5	COL 1	COL 2	COL 4	COL 8	FOT 0.5	FOT 1	FOT 2	FOT 4	FOT 8	TOB 1
F	TGC 0.25	TGC 0.5	TGC 1	TGC 2	TGC 4	SXT 1/19	SXT 2/38	SXT 4/76	SXT 8/152	TOB 2	TOB 4	TOB 8
G	TAZ 0.5	TAZ 1	TAZ 2	TAZ 4	TAZ 8	TAZ 16	CZA 0.5/4	CZA 1/4	CZA 2/4	CZA 4/4	CZA 8/4	CZA 16/4
H	IMI 0.5	IMI 1	IMI 2	IMI 4	IMI 8	IMI 16	ETP 0.12	ETP 0.25	ETP 0.5	ETP 1	ETP 2	POS

ANTIMICROBICS

AMI	Amikacin
AUGC	Amoxicillin / clavulanic acid constant 2
AZT	Aztreonam
FOT	Cefotaxime
TAZ	Ceftazidime
CZA	Ceftazidime/avibactam
C/T	Ceftolozane/tazobactam 4
CIP	Ciprofloxacin
COL	Colistin
ETP	Ertapenem
GEN	Gentamicin
IMI	Imipenem
MERO	Meropenem
P/T4	Piperacillin / tazobactam constant 4
POS	Positive Control
TGC	Tigecycline
TOB	Tobramycin
SXT	Trimethoprim / sulfamethoxazole