

**SENSITITRE™ GRAM NEGATIVE PLATE FORMAT**

Plate Code: **GNX3F**

	1	2	3	4	5	6	7	8	9	10	11	12
<b>A</b>	AMI 4	GEN 1	TOB 1	CIP 0.06	SXT 0.5/9.5	AZT 2	FEP 2	COL 0.25	COL 0.5	COL 1	COL 2	COL 4
<b>B</b>	AMI 8	GEN 2	TOB 2	CIP 0.12	SXT 1/19	AZT 4	FEP 4	POL 0.25	POL 0.5	POL 1	POL 2	POL 4
<b>C</b>	AMI 16	GEN 4	TOB 4	CIP 0.25	SXT 2/38	AZT 8	FEP 8	TAZ 1	TAZ 2	TAZ 4	TAZ 8	TAZ 16
<b>D</b>	AMI 32	GEN 8	TOB 8	CIP 0.5	SXT 4/76	AZT 16	FEP 16	FOT 2	FOT 4	FOT 8	FOT 16	FOT 32
<b>E</b>	DOX 2	MIN 2	TGC 0.25	CIP 1	LEVO 1	IMI 1	MERO 1	A/S2 4/2	A/S2 8/4	A/S2 16/8	A/S2 32/16	A/S2 64/32
<b>F</b>	DOX 4	MIN 4	TGC 0.5	CIP 2	LEVO 2	IMI 2	MERO 2	DOR 0.5	DOR 1	DOR 2	DOR 4	POS
<b>G</b>	DOX 8	MIN 8	TGC 1	TGC 4	LEVO 4	IMI 4	MERO 4	P/T4 8/4	P/T4 16/4	P/T4 32/4	P/T4 64/4	POS
<b>H</b>	DOX 16	MIN 16	TGC 2	TGC 8	LEVO 8	IMI 8	MERO 8	TIM2 16/2	TIM2 32/2	TIM2 64/2	TIM2 128/2	POS

**ANTIMICROBICS**

AMI	Amikacin
DOX	Doxycycline
GEN	Gentamicin
MIN	Minocycline
TOB	Tobramycin
TGC	Tigecycline
CIP	Ciprofloxacin
SXT	Trimethoprim / sulfamethoxazole
LEVO	Levofloxacin
AZT	Aztreonam
IMI	Imipenem
FEP	Cefepime
MERO	Meropenem
COL	Colistin
POL	Polymixin B
TAZ	Ceftazidime
FOT	Cefotaxime
A/S2	Ampicillin / sulbactam 2:1 ratio
DOR	Doripenem
P/T4	Piperacillin / tazobactam constant 4
TIM2	Ticarcillin / clavulanic acid constant 2
POS	Positive Control