



Comprehensive testing for *Mycobacterium tuberculosis*

Thermo Scientific Sensititre *Mycobacterium tuberculosis* MIC Plate*: the first dry microbroth dilution plate to test first and second-line antimicrobics for *Mycobacterium tuberculosis*

- Test 12 antimicrobics on a single MIC plate for cost-effective results
- Comprehensive MIC format includes first and second-line antimicrobics for complete formulary options
- Inclusive on-scale QC ranges provide immediate quality assurance of testing methodology
- Easy set-up procedures and incubation requirements provide MIC results in only 7-21 days
- Individual packaging allows laboratory to test one plate at a time with no waste
- Extended 18-24 month shelf life and room-temperature storage eliminate inventory control concerns
- Convenient microbroth dilution format provides accurate endpoint determination with manual read or Thermo Scientific Sensititre Vizion System options

*CE-marked. For research use only in the U.S. Not for use in diagnostic procedures.

Thermo
SCIENTIFIC

Sensititre® *Mycobacterium tuberculosis* MIC Plates:

Antimicrobial:	Part #: MYCOTB*,**	Dilution Range (µg/mL):	MYCOTBI***
Amikacin	0.12-16		0.12-16
Cycloserine	2-256		2-256
Ethambutol	0.5-32		0.5-32
Ethionamide	0.3-40		0.3-40
Isoniazid	0.03-4		0.03-4
Kanamycin	0.6-40		0.6-40
Moxifloxacin	0.06-8		0.06-8
Ofloxacin	0.25-32		0.25-32
Para-aminosalicylic acid	0.5-64		0.5-64
Rifabutin	0.12-16		0.12-16
Rifampin	0.12-16		0.12-16
Streptomycin	0.25-32		0.25-32

Related products:

Middlebrook 7H9 w/ OADC; 10/box
 Middlebrook 7H9 w/ OADC; 10/box
 Saline Tween w/ Glass Beads; 10/box
 Saline Tween w/ Glass Beads; 10/box


Part #:

T3440*,**
 T3441***
 T3490*,**
 T3491***

*CE-marked. For research use only in the U.S. Not for use in diagnostic procedures.

**Available in the U.S. only.

***Not available in the U.S.



Sensititre *Mycobacterium tuberculosis* plate image on the Sensititre Vizion® Digital MIC Viewing System.

© 2012 Thermo Fisher Scientific Inc. All rights reserved. All trademarks are the property of Thermo Fisher Scientific Inc. and its subsidiaries. Specifications, terms and pricing are subject to change. Not all products are available in all countries. Please consult your local sales representative for details.

USA and Canada +1 800 871 8909
All Other Inquiries +44 1256 841144

Technical Support
USA and Canada +1 800 642 7029
All Other Inquiries +44 1342 318777

Thermo
 S C I E N T I F I C

Part of Thermo Fisher Scientific

LT2025A/CS/02/12