

Consumables to meet your needs

A selection of commonly used consumables.



ThermoFisher
SCIENTIFIC

Product	Product Code	Description
Gas Detectors & Analysers		
Impact Pro Multi Gas Monitor		
Test/Calibration Gas ¹	ALQ004030	Four gas mix for use with Enforcer
PID/VOC Monitors (MiniRAE 3000, MiniRAE Lite, MiniRAE 2000)		
Test/Calibration Gas ¹	ALE004032	CalGaz Isobutylene 100 ppm/air 34 L
Other	ACE002-3022-100	MiniRae water trap filter
Soil Vapour Monitoring - Soil Vapour Probe Kit		
Vapour Implants	DPSSVPT96-6	Stainless Steel permanent implant 152 mm
	DPSSVPT97	Expendable vapour point for SS implant 28 mm
	DPS33.7-50	Teflon tubing 0.187 in ID 0.25 in OD 15.2 m roll
Single & Multi-Parameter WQM		
Aquaread GPS Aquameter & TPS 90FL		
RapidCal	AQRRC-300	300mL RAPIDCAL solution in wide neck bottle RapidCal calibrates EC at 2570 µS/cm, the pH7.00 point and the Zero NTU Turbidity point simultaneously
ORP Calibration ²	EEQ231MV-ZOBELL-A-250ML	231 mV Zobell Part A 250 mL
	EEQ231MV-ZOBELL-B-250ML	231 mV Zobell Part B 250 mL
Turbidity Calibration	EEQ0800-1000NTU-1L	Turbidity formazin standard 1000 NTU
Dissolved Oxygen Zero	TPS123302	Sodium Sulphite for Zero Dissolved Oxygen cal 50 g
pH	EEQ0114-7PH-500ML	pH 7 buffer 500 mL
	EEQ0113-4PH-500ML	pH 4 buffer 500 mL
Conductivity	EEQ0442-2760US-500ML	Conductivity std 2760 us/cm 500 mL
TDS	EEQ1347-36PPK-500ML	TDS Std 36 ppk 500 mL
ORP	HANHI7021L	ORP Test Solution 240 mV 500 mL
Dissolved Oxygen Zero	TPS 123302	Sodium Sulphite for Zero Dissolved Oxygen cal 50 g
Turbidity Standard	EEQ360NTU-1L	Turbidity standard 360 NTU 1000 mL
	EEQ0800-0NTU-500ML	Turbidity standard 0 NTU 1000 mL
Groundwater Sampling Systems		
Micropurge Kits		
Bladders	QED38360	Sample Pro polyethylene bladder
Tubing – Aqua Twin Tube	EEQMPAW-100	LDPE bonded air 6 mm OD water 9.5 mm OD 100 m roll
Tubing Single Lines – Air Line	EEQMPTA-100	LDPE tubing 6 mm OD tubing 100 m Roll
Tubing Single Lines – Water Line	EEQMPTW-100	LDPE tubing 9.5 mm OD tubing 100 m Roll

¹ A regulator is also required for Test/Calibration Gas - please ask if required

² Both part A & B are required

Product	Product Code	Description
Geotech Peristaltic Pump		
	JHS48953	Tubing silastic 4.8 mm ID x 9.53 mm OD 15 m roll
	EEQMPTA-100	LDPE tubing 6 mm OD tubing 100 m Roll
Waterra Pumps		
Standard Flow	WTPD25	Waterra Standard Flow Footvalve D25
	WTPWSBD25	Waterra surge block for D25
	EEQLDPE16	LDPE tubing 15.9 mm OD 100 m roll
	EEQHIGHDPE16	HDPE tubing 15.9 mm OD 100 m roll
High Flow	WTPD32	Waterra footvalve D32
	WTPWSB32	Waterra surge block for D32
	WTPSS32	Waterra footvalve SS32
	EEQLDPE25	LDPE tubing 25.4 mm, 19 mm ID 100 m Roll
	WTPWTCT	Waterra tubing cutter
QED AP2 Pump		
Tubing - Triple Tube	EEQTRITUBE	LDPE bonded triple tube 6 mm, 9.5 mm, 12.7 mm OD 100 m
Tubing 3 x Single Lines:		
Air Supply	EEQMPTA-100	LDPE tubing 6 mm OD tubing 100 m Roll
Air Exhaust Line	EEQMPTW-100	LDPE tubing 9.5 mm OD tubing 100 m Roll
Water Discharge Line	EEQLDPE12	LDPE tubing 12.7 mm OD 100 m Roll
QED AP4 Pump / Bennett Pump³		
Tubing 3 x Single Lines:		
Air Supply	EEQMPTW-100	LDPE tubing 9.5 mm OD tubing 100 m Roll
Air Exhaust Line	EEQMPTW-100	LDPE tubing 9.5 mm OD tubing 100 m Roll
Water Discharge Line	EEQLDPE16	LDPE tubing 15.9 mm OD tubing 50 m Roll
General Field Supplies Checklist for Groundwater Sampling & Contaminated Site Monitoring		
Wildco Hand Corer Sediment Sampler		
Core Catcher	WLS2449-B13	Eggshell core catcher 3 pcs
Liners	WLS2447-C21	Liner tube for 20 in with end caps
PPE - promed Nitrile Disposable Gloves		
	PMD172070-E	promed Nitrile p/free long cuff Small 100/pk
	PMD172080-E	promed Nitrile p/free long cuff Med 100/pk
	PMD172090-E	promed Nitrile p/free long cuff Large 100/pk
	PMD172095-E	promed Nitrile p/free long cuff X-Large 100/pk
PPE - Tyvek Suits		
	SAFTVK-M	Protective suit disposable Tyvek Suit white medium

³Please contact your local Thermo Fisher Scientific rental office to discuss your specific requirements

Product	Product Code	Description
	SAFTVK-L	Protective suit disposable Tyvek Suit white large
	SAFTVK-XL	Protective suit disposable Tyvek Suit white X large
Decontamination Liquid		
	DEC90-5L-E	Decon 90 liquid concentrate 5 L
	DECNEUTRACON-5L-E	Neutracon liquid concentrate 5 L
Filtration		
Filters	WTPWAT45	Waterra WAT45 filter GW 0.45 micron 600 cm ²
	QEDFF8200T	Filter GW 045 micron 600 cm ² 3.2 mm thread
	QEDFF8100	Filter GW 045 micron 30 cm ² 3.2 mm thread
	MILSCHVU01RE-E	Stericup HV 0.45 um 150 mL PVDF 12 pcs
	MILSCHVU02RE-E	Stericup HV 0.45 um 250 mL PVDF 12 pcs
	NAL125-0045-E	Filter unit PS 150 mL 0.45 um
Groundwater Samplers / Accessories		
	ESPCV153	Clear View PVC Disposable Bailer 38 x 914 mm
	ESPBB-153	Biobailer - Clear View PVC Biodegradable Bailer 38 x 914 mm
	VOS91946SWR	Voss polyethylene disposable bailer 38 x 914 mm
	VOSTW100R	Bailer cord 1.52 mm disposable Voss nylon 30 m
	VOSTW300R	Bailer cord 1.52 mm disposable Voss nylon 90 m
	Hydrasleeve No Purge Samplers	
	EONGSH110	Hydrasleeve sampler 44.5 x 711.2 mm 500 mL
	EONGSW311	Stainless steel weight for Hydrasleeve
	EONFSF135	Snap connectors

This is only a selection of consumable items available from Thermo Fisher Scientific. Please contact us for your specific requirements.

Authorised distributor

In Australia:

For customer service, call 1300-735-292
 To email an order, ordersau@thermofisher.com
 To order online: thermofisher.com

In New Zealand:

For customer service, call 0800-933-966
 To email an order, ordersnz@thermofisher.com
 To order online: thermofisher.com

ThermoFisher
 SCIENTIFIC