

Frequently Asked Questions



Common questions for the AutoFLEX instrument



Will the AutoFLEX flow computer work with AutoCONFIG software?

Yes, AutoCONFIG interface will support AutoFLEX, AutoPILOT Pro, AutoEXEC, and AutoXP.

Do I connect to the AutoFLEX with the same CHIT cable?

The AutoFLEX can be connected to via Bluetooth, Ethernet, and USB; also available is the legacy CHIT connector.

Can configurations from AutoPILOT Pro and AutoEXEC be used with AutoFLEX?

Yes, previous Auto series configurations can be installed in AutoFLEX systems.

Will AutoFLEX be hazardous location certified?

The system is certified Class I, Div. 2

How much faster is the processor in the AutoFLEX?

Using the AGA8 Detailed calculation as a gauge the AutoFLEX can process it 4X faster than the AutoEXEC.

Does AutoFLEX support software selectable I/O?

Yes, combination inputs can be configured via AutoCONFIG interface software. The AutoFLEX supports DO/DI/PI, DO/DI, and DO/DI,FO software selectable inputs

Can additional chassis be plugged into base chassis?

The AutoFLEX7 will accept up to 9 additional chassis.

Can I/O modules be interchanged between chassis?

All I/O modules for the AutoFLEX series including the CPU can be interchanged between chassis.

What communication ports are included on the CPU module?

(2) Ethernet, (1) USB, (1) Serial host, and (1) Serial local port. Ethernet port speeds 1 @ 100 Mbps and 1 @ 1000Mbps

How many meter runs will the AutoFLEX handle?

The limitation of meter runs is based on limitation of hardware. AutoCONFIG SW is capable of handling 32+ run configurations.

Does the AutoFLEX offer wireless communication?

Yes, AutoFLEX comes with standard with Bluetooth that can be turned on/off via AutoCONFIG interface.

Does the AutoFLEX meet API 21.1 and 21.2 custody transfer standards?

Yes.

USA

27 Forge Parkway
Franklin, MA 02038
Ph: (713) 272-0404
Fax: (713) 272-2273
orders.process.us@thermofisher.com

India

Industrial Unit No.101+130,
Plot No.C-56/1, TTC Industrial
area, MIDC-Turbhe,
New Mumbai 400 703, India
Ph: +91 82 9199 0337
INinfo@thermofisher.com

China

8/F Bldg C of Global Trade Ctr,
No.36, North 3rd Ring Road,
Dong Cheng District
Beijing, China 100013
Ph: +86 10 84193588
info.eid.china@thermofisher.com

Europe

Ion Path, Road Three,
Winsford, Cheshire CW73GA UK
Ph: +44 1606 548700
Fax: +44 1606 548711
sales.epm.uk@thermofisher.com

Find out more at thermofisher.com/autoflex