

## Urine Toxicology Cups and Dip Cards

# Rapid drugs of abuse testing

## Supporting hospital patients when rapid results matter

### Simple and easy to use urine drug screening dip card and cups

- CLIA-Waived
- Simple to Use – Easy to Read
- Toxicology results available in minutes
- Up to 99% agreement with GC/MS or LC/MS
- Low cross reactivity

### Test results available quickly

- Drug test results available in 5 minutes
- Specimen Validity Test results available in 2 minutes

### Flexibility for your test needs – choose the panel product best suited to your needs

- Single Methamphetamine dip card
- 5 Test panel with or without specimen validity tests
- 6 Test panel
- 10 Test panel
- 12 Test panel with or without specimen validity tests



## Cups Test Panel Configurations

Test	Drug Confirm - 5 Panel Clicker Cup Test (ng/mL)	5 Panel Clicker Cup Test(ng/mL)	Drug Confirm - 10 Panel Clicker Cup Test (ng/mL)	10 Panel Clicker Cup Test (ng/mL)	Drug Confirm - 12 Panel Clicker Cup Test (ng/mL)	12 Panel Clicker Cup Test with Vacu Confirm Lid & Collection kit * (ng/mL)	Drug Confirm - 12 Panel Clicker Cup Test (ng/mL)
Product PN	HE-Cup-254pr	HE-Cup-254A3	HE-Cup-3104pr	HE-Cup-8104pr	HE-Cup-6125A3pr	HE-Cup-6125pr-VAC	HE-Cup-6125pr
CLIA-waived	✓	✓	✓	✓	✓	✓	✓
Amphetamine	1000	1000	1000	1000	1000	1000	1000
Barbiturate			300		300	300	300
Benzodiazepine			300	300	300	300	300
Buprenorphine				10	10	10	10
Cocaine	300	300	300	300	300	300	300
Ecstasy (MDMA)			500	500	500	500	500
Marijuana (THC)	50	50	50	50	50	50	50
Methamphetamine	1000	1000	1000	1000	1000	1000	1000
Methadone			300	300	300	300	300
Morphine	2000	2000	2000	2000	300	300	300
Oxycodone				100	100	100	100
Phencyclidine			25		25	25	25
<b>Specimen Validity</b>							
Creatinine					X		
Oxidants		X			X		
pH		X					
Specific Gravity		X			X		

\* Collection Kit includes: x1 Sleeves X1 Specimen Bag x1 Soap Wipe per cup

## Dip Card Test Panel Configurations

Test	1 Panel Dip Test: mAMP (ng/mL)	Drug Confirm - 5 Panel Dip Test (ng/mL)	Drug Confirm - 6 Panel Dip Test (ng/mL)	Drug Confirm - 12 Panel Dip Test (ng/mL)	Drug Confirm - 12 Panel Dip Test (ng/mL)	90 mL (3oz)/53mm sterile container with label
Product PN	HE-Dip-MAMP	HE-Dip-254pr	HE-Dip-564pr	HE-Dip-6124pr	HE-Dip-6125pr	BM-Collection-Cup
CLIA-waived	✓	✓	✓	✓	✓	N/A
Amphetamine		1000		1000	1000	
Barbiturate				300	300	
Benzodiazepine			300	300	300	
Buprenorphine				10	10	
Cocaine		300	300	300	300	
Ecstasy (MDMA)				500	500	
Marijuana (THC)		50	50	50	50	
Methamphetamine	1000	1000	1000	1000	1000	
Methadone				300	300	
Morphine		2000	2000	2000	300	
Oxycodone			100	100	100	
Phencyclidine				25	25	

### Limitations of the test:

Drug Tests (Strip/Card/Device/Cup) are for professional in vitro diagnostic use, and should be only used for the qualitative detection of drugs of abuse. This assay provides a preliminary analytical test result only. A more specific alternative chemical method such as LC-MS/MS or GC/MS must be used in order to obtain a confirmed analytical result. Clinical consideration and professional judgment should be applied to any test result, particularly when preliminary positive results are indicated. There is a possibility that technical or procedural errors as well as other substances and factors may interfere with the test and cause false results.