

SPARE PART KIT RECOMMENDATIONS

# Thermo Scientific™ Model 42i-Y NO<sub>y</sub> Analyzer

To keep your system running and properly collecting data, it's important to have spare parts on hand to avoid costly downtime. We developed Spare Parts Kits to ensure maximum uptime of your Thermo Scientific Instrument during its life cycle.

Spare Parts Kit # 111842-05	
Part Numbers	Description
4119	1 x Capillary, 08 mil (Red)
4126	1 x Capillary, 20 mil (Blue)
4800	1 x O-RING VITON (PK/10) (FOR CAPILLARIES)
4806	2 x O ring , (Base End & Chamber /quartz)
4808	1 x O ring, (Between chamber halves)
4821	1 x O Ring, (PMT end)
4822	1 x O Ring, (Inside Cooler)
6556	1 x Filter Kit, Optical (w/quartz)
9212	1 x O ring Capillary Holder (pk/5)
9464	2 x Pump Repair Kit
11290	1 x Receptacle Fuse Drawer, 110V
101905-00	2 x Fuse, 4 amp slo blow
108002-00	1 x PUMP REPAIR KIT, KNF

Extended Maintenance Kit # 105292-00	
Part Numbers	Description
9269	1 x Moly Converter Cartridge w/fittings
9973	1 x Ozonator
9995	1 x cooler
100907-00	1 x Fan, 24VDC, i-series
101021-00	1 x flow transducer
101023-00	1 x pressure transducer
101024-00	1 x HV power supply
101390-00	1 x solenoid assy (i-series)
101419-00	1 x ozonator transformer
101681-00	1 x power supply w/o cables
109604-00	1 x Heater 120V / 60 Watts
114064-00	1 x assy, spare pmt 42iTL,42iY, 17i

**USA**  
27 Forge Parkway  
Franklin, MA 02038  
Ph: (866) 282-0430  
orders.aqi@thermofisher.com

**India**  
C/327, TTC Industrial Area  
MIDC Pawane  
New Mumbai 400 705, India  
Ph: +91 22 4157 8800  
india@thermofisher.com

**China**  
+Units 702-715, 7th Floor  
Tower West, Yonghe  
Beijing, China 100007  
+86 10 84193588  
info.eid.china@thermofisher.com

**Europe**  
Ion Path Road Three  
Winsford, Cheshire CW7 3GA  
Ph: +44 (0) 1606 548700  
orders.epm.uk@thermofisher.com

Find out more at [thermofisher.com/EMservice](http://thermofisher.com/EMservice)

**ThermoFisher**  
SCIENTIFIC