


CATALOG NUMBER	NOMINAL CAPACITY (mL)					MATERIAL
4103	50	125	250	500	1000	PC

SIZE CODE.....:	-0050		-0125		-0250	
SIZE (NOM VOL mL).....:	50		125		250	
NOM. WT. (gms).....:	15		40		55	
	INCH	MM	INCH	MM	INCH	MM
A (NECK I.D. NEAR TOP).....:	0.62	15.7	0.85	21.6	1.1	28
B (LIP O.D. AT TOP).....:	0.97	24.6	1.31	33.3	1.60	40.6
C (BODY O.D.).....:	2.00	50.8	2.62	66.5	3.25	82.6
D (HEIGHT).....:	3.1	79	4.3	109	5.3	135
W.T. (NOM. WALL THK).....:	0.05	1.3	0.05	1.3	0.05	1.3

SIZE CODE.....:	-0500		-1000	
NOM. CAP.....:	500		1000	
NOM. WT. (gms).....:	75		150	
	INCH	MM	INCH	MM
A (NECK I.D. NEAR TOP).....:	1.3	33	1.5	38
B (LIP O.D. AT TOP).....:	1.68	42.7	1.96	49.8
C (BODY O.D.).....:	4.00	101.6	5.12	130.0
D (HEIGHT).....:	6.9	175	8.5	216
W.T. (NOM. WALL THK).....:	0.04	1.0	0.04	1.0

1. ALL DIMENSIONS ARE NOMINAL AND IN INCHES AND MILLIMETERS UNLESS OTHERWISE NOTED.
2. THIS IS NOT A PRODUCTION DRAWING, BUT IS FOR INFORMATIONAL PURPOSES ONLY, AND IS SUBJECT TO CHANGE WITHOUT NOTICE.



SPECS ON BACK

NOT TO SCALE

CONFIDENTIAL

THIS PRODUCT SPECIFICATION SHEET CONTAINS CONFIDENTIAL AND/OR PROPRIETARY INFORMATION AND IS TO BE USED ONLY FOR THE EXPRESSED PURPOSES AGREED UPON BY AN AUTHORIZED OFFICER OF THERMO FISHER SCIENTIFIC.

ThermoFisher
SCIENTIFIC

Thermo Fisher Scientific
75 Panorama Creek Drive
Rochester, NY 14625-2385, USA

MADE MCC	APP'D PVC	PSS 00-4103-XXXX	REV. 0303
CK'D PVC	3/26/03		

DESCRIPTION:

ERLENMEYER FLASKS