



## ROTOR SPECIFICATIONS

Type	Fixed Angle
Material	Titanium
Capacity	8 x 5.1 mL
Maximum Speed	100,000 rpm
Tube Dimensions Ø x L	13 x 63 mm
Angle	30°
K Factor	17.7
Net Weight	1.13 kg /2.5 lbs
Warranty	5 years

	RCF	RADIUS
Maximum	603,180 xg	54.0 mm
Average	452,385 xg	40.5 mm
Minimum	300,473 xg	26.9 mm

## ROTOR AND ACCESSORIES ORDERING INFORMATION

## S100-AT6 Rotor Package includes:

Description	Cat. No.
S100-AT6 Rotor	45588
4.0 mL PC Thick-Walled Tubes (qty. 2 pkg. of 50)	45239
Large O-ring for Cover (qty. 2)	45703
Small O-ring for Cover (qty. 2)	45294
Rotor Holding Fixture	45266
Lubricant	61556
Vacuum Grease	65937
Instruction Manual	45735

## Accessories:

Description	Cat. No.
Starter Kit for use with 13 mm Re-Seal Tubes {Includes 1 Crown (45321), 10 Plugs (45307), Wrench (45308) and Removal Tool (45309)}	45320
13 mm x 51 mm Tube Vise	45534
Rotor Stand	45357
Cover Opener	45173

## LABWARE ORDERING INFORMATION

Tube Vol. (mL)	Vol. Fill (mL)	Description	Cat. No.	Qty. /Pkg.	Tubes /Rotor	Max. Speed (rpm)	Max. RCF (xg)	Dims ØxL (mm)	REQUIRED TUBE CLOSURES, ADAPTERS, TOOLS & ACCESSORIES			
									Type	Cat. No.	Qty. /Pkg.	Description
5.0	5.1	PA Re-Seal Tube	45248	50	8	100,000	603,180	13 x 51	Closure	45321	1	13 mm Al Crown <sup>1</sup>
									Closure	45307	10	Stainless Steel Plug
									Tool	45308	1	Wrench
									Tool	45309	1	Tube Removal Tool
									Tool	45534	1	Tube Vise
5.0	5.0	PA Easy-Seal Tube	75000508	50	8	80,000	386,035	13 x 51	Closure	75000511	1	13 mm Al Crown <sup>1</sup>
									Tool	75000505	1	Crown Clamp
									Tool	75000506	1	Hex Driver
									Tool	75000507	1	Tube Removal Tool
									Tool	75000481	1	Easy-Seal Tube Vise
4.0	3.4	PC Thick-Walled Tube	45239	50	8	100,000	603,180	13 x 63	—	—	—	—
3.5	3.5	PA Easy-Seal Tube	75000509	50	8	80,000	386,035	13 x 45	Closure	75000511	1	13 mm Al Crown <sup>1</sup>
									Tool	75000505	1	Crown Clamp
									Tool	75000506	1	Hex Driver
									Tool	75000507	1	Tube Removal Tool
									Tool	75000481	1	Easy-Seal Tube Vise
3.5	3.5	PET Easy-Seal Tube	75000510	50	8	80,000	—	13 x 45	Closure	75000511	1	13 mm Al Crown <sup>1</sup>
									Tool	75000505	1	Crown Clamp
									Tool	75000506	1	Hex Driver
									Tool	75000507	1	Tube Removal Tool
									Tool	75000481	1	Easy-Seal Tube Vise
1.5	1.5	PA Easy-Seal Tube	75000512	50	8	80,000	—	13 x 29	Closure	75000511	1	13 mm Al Crown <sup>1</sup>
									Tool	75000505	1	Crown Clamp
									Tool	75000506	1	Hex Driver
									Tool	75000507	1	Tube Removal Tool
									Tool	75000481	1	Easy-Seal Tube Vise
1.5	1.5	High Performance Microtube	314352H01	100	8	55,000	—	11 x 42	Adapter	45587	1	Adapter for Microtube

<sup>1</sup> Must order one crown for each place in the rotor.

© 2014 Thermo Fisher Scientific Inc. All rights reserved. All trademarks are the property of Thermo Fisher Scientific Inc. and its subsidiaries. Specifications, terms and pricing are subject to change. Not all products are available in all countries. Please consult your local sales representative for details.

For more information, please visit  
[www.thermoscientific.com/rotors](http://www.thermoscientific.com/rotors).