

- 
- Natural High Density Polyethylene
 - Fits Nalgene PET and PETG Media Bottles with 38-430 neck finish (*except 125ml PETG Media Bottles)
 - Leak Proof Guarantee when used with Nalgene PET and PETG Media Bottles
 - One piece linerless closure with integrally molded seal ring
 - Easy application and breaking of the tamper evident seal ring
 - Removes requirement for heat shrink band
 - Gamma irradiated to provide 10⁻⁶ Sterility Assurance Level (SAL)
 - Flat top surface for possible printing or labeling
 - High quality non-cytotoxic, non-hemolytic and non-pyrogenic material
 - Meets latest biological testing standards including
 - USP Class VI
 - USP <661>
 - European Pharmacopeia for Abnormal Toxicity
 - Made from ADCF (Animal Derived Component Free) materials
 - Manufactured in compliance with ISO 13485-2003 quality requirements
 - Unique, robust design prevents breaking of the tamper evident ring during capping

Thermo Scientific Nalgene

HDPE Tamper Evident Closure, Sterile, Bulk Pack

Tamper Evident Closures Enhanced Product Integrity

We are proud to introduce a new generation of Nalgene HDPE closures for use with PET and PETG Nalgene Square Media Bottles, sterile and bulk packed.

Thermo
SCIENTIFIC

Thermo Scientific™ Nalgene™ HDPE Tamper Evident Closures, Sterile, Bulk Pack

Featuring a tamper evident break ring design which combines the unique leak proof nature of the Nalgene bottles/closure system with the possibility to ensure proof of content integrity.

Improper use or intentional opening of the media bottle can be easily identified by the detachment of the seal ring.

The easy application and breaking of the tamper evident seal ring eliminates the need for shrink bands and provides in one single, cost effective step, a tamper evident and leakproof guaranteed system.



Order Information			
Description	Qty	Closure Size, mm	Cat. No.
Tamper Evident HDPE Closure, Sterile, Bulk Pack	240	38-430	342141-0384

Closures are sterile and bulk packed . Order Nalgene PET or PETG Media Bottles with 38-430 neck finish without closures separately as described below.

Thermo Scientific™ Nalgene™ Nalgene Square PET/PETG Media Bottles

Nalgene Square Media Bottles are the leading media, buffer and reagent storage and shipping containers in today's pharmaceutical, diagnostic and biotech markets.

Nalgene Square Media Bottles are designed and manufactured to meet the most stringent requirements of safe and leak proof guaranteed containers.

The unique Nalgene closure and bottle design requires no liner or gasket to provide repeatable leak proof performance, and now it features a tamper evident closure system to prove content integrity.



Order Information	
Description	Order Number
PET Media Bottles without closures, Sterile	
125 ml	342044-0125
650 ml	342044-0650
1000 ml	342044-1000
PETG Media Bottles without closures, Sterile	
250 ml	342024-0250
500 ml	342024-0500
1000 ml	342024-1000

To learn more about our complete product offering, visit www.thermoscientific.com/packagingbottles

thermoscientific.com/packagingbottles

© 2014 Thermo Fisher Scientific Inc. All rights reserved. All (other) trademarks are the property of Thermo Fisher Scientific Inc. and its subsidiaries.

ANZ: Australia: 1300 735 292, New Zealand: 0800 933 966; **Asia:** China Toll-free: 800-810-5118 or 400-650-5118; India: +91 22 6716 2200, India Toll-free: 1 800 22 8374; Japan: +81-3-5826-1616; Other Asian countries: 65 68729717
Europe: Austria: +43 1 801 40 0; Belgium: +32 2 482 30 30; Denmark: +45 4631 2000; France: +33 2 2803 2180; Germany: +49 6184 90 6000, Germany Toll-free: 0800 1-536 376; Italy: +39 02 95059 554; Netherlands: +31 76 571 4440; Nordic/Baltic countries: +358 9 329 10200; Russia/CIS: +7 (812) 703 42 15; Spain/Portugal: +34 93 223 09 18; Switzerland: +41 44 454 12 22; UK/Ireland: +44 870 609 9203
North America: USA/Canada +1 585 586 8800; USA Toll-free: 800 625 4327
South America: USA sales support: +1 585 586 8800 **Countries not listed:** +49 6184 90 6000 or +33 2 2803 2000

Thermo
SCIENTIFIC
Part of Thermo Fisher Scientific