

# Won't float, won't fade

Test tube racks that withstand chemicals and temperatures up to 121°C

Rely on Thermo Scientific™ Nalgene™ Unwire™ Test Tube Racks to securely hold your tubes while withstanding most chemicals and temperatures up to 121°C. Made of durable and brightly colored plastic, Nalgene Unwire racks won't float in water baths and their color won't fade over time or with use. They are molded in a single piece for exceptional strength, and there are no welds to break and no sharp edges.

- Strong enough to securely hold a full load of test tubes
- No welds to break, no sharp edges, no rust or corrosion, and no assembly required
- Withstands most lab chemicals and temperatures up to 121°C
- Half racks are space efficient and fit easily in water or ice baths
- Available in six bright colors that won't fade
- Higher specific gravity than water—won't float



## Ordering information

Color	Tube size	Qty per pack/case	Cat. No.
<b>Nalgene Unwire Half-Rack</b>			
White	13 mm	1/8	5972-0013
White	16 mm	1/8	5972-0016
White	20 mm	1/8	5972-0020
White	25 mm	1/8	5972-0025
White	30 mm	1/8	5972-0030
Blue	13 mm	1/8	5972-0313
Blue	16 mm	1/8	5972-0316
Blue	20 mm	1/8	5972-0320
Blue	25 mm	1/8	5972-0325
Blue	30 mm	1/8	5972-0330
Green	13 mm	1/8	5972-0413
Green	16 mm	1/8	5972-0416
Green	20 mm	1/8	5972-0420
Green	30 mm	1/8	5972-0430
Red	13 mm	1/8	5972-0513
Red	16 mm	1/8	5972-0516
Red	20 mm	1/8	5972-0520
Red	30 mm	1/8	5972-0530

Color	Tube size	Qty per pack/case	Cat. No.
<b>Nalgene Unwire Test Tube Rack</b>			
White	13 mm	1/8	5970-0013
White	16 mm	1/8	5970-0016
White	20 mm	1/8	5970-0020
White	25 mm	1/8	5970-0025
White	30 mm	1/8	5970-0030
Orange	13 mm	1/8	5970-0113
Orange	16 mm	1/8	5970-0116
Orange	20 mm	1/8	5970-0120
Orange	25 mm	1/8	5970-0125
Orange	30 mm	1/8	5970-0130
Yellow	13 mm	1/8	5970-0213
Yellow	16 mm	1/8	5970-0216
Yellow	20 mm	1/8	5970-0220
Yellow	25 mm	1/8	5970-0225
Yellow	30 mm	1/8	5970-0230
Blue	13 mm	1/8	5970-0313
Blue	16 mm	1/8	5970-0316
Blue	20 mm	1/8	5970-0320
Blue	25 mm	1/8	5970-0325
Blue	30 mm	1/8	5970-0330
Green	13 mm	1/8	5970-0413
Green	16 mm	1/8	5970-0416
Green	20 mm	1/8	5970-0420
Green	25 mm	1/8	5970-0425
Green	30 mm	1/8	5970-0430
Red	13 mm	1/8	5970-0513
Red	16 mm	1/8	5970-0516
Red	20 mm	1/8	5970-0520
Red	25 mm	1/8	5970-0525
Red	30 mm	1/8	5970-0530

16 mm racks are a perfect fit  
for 12 mL tubes



50 mL tubes work great  
with our 30 mm racks

Find out more at [thermofisher.com/test-tube-racks-holders](https://thermofisher.com/test-tube-racks-holders)

**ThermoFisher**  
SCIENTIFIC