


Thermo Scientific Versi-Dry Surface Protectors

Protect laboratory surfaces
from damage and
contamination

Thermo Scientific™ Versi-Dry™ Surface Protectors can help make your lab a safer place by quickly absorbing spills and cushioning breakable labware. Use Versi-Dry material as a bench protector, shelf liner, cabinet liner or for wiping up isolated spills. The skid-resistant polyethylene backing protects your benchtop and other lab surfaces from damage and contamination caused by liquid drips and spills. The cloth-like top layer is long-lasting and will not fall apart, even when wet.



Thermo Scientific Versi-Dry Surface Protectors

- Thousands of Thirsty-Cells™ quilted into the surface quickly absorb spills. Available in white regular absorbency (750ml/m²) or blue super absorbency (1,050 ml/m²)
- Cushioned surface minimizes breakage of fragile glassware when dropped or tipped over
- Low-pile sheets lie flat and are skid-resistant helping to stabilize labware and prevent tipping
- Remains flat and won't curl up or warp with repeated wetting and drying
- Polyethylene backing prevents chemicals from breaking through to protected surfaces beneath

Versi-Dry resists the following chemical spills:

Acetone	Hydrofluoric Acid, 10%*	Potassium Hydroxide, 30%*
Ammonium Hydroxide, 30%*	Methylene Chloride	Sulfuric Acid, 10%
Chlorine Bleach	Methyl Ethyl Ketone (MEK)	Sodium Hydroxide, 10N*
Chlorobenzene	Methyl Iso Butyl Ketone (MIBK)	Toluene
Chloroform	Mineral Spirits	Xylene
Ethanolamine	Nitric Acid, 10%*	
Hydrochloric Acid, 10%*	Phosphoric Acid, 10%*	

*Highest concentration tested

Regular Versi-Dry Surface Protectors-absorbs 750ml/m²

Catalog No.		Color	No. per case
Mat		L x W	
62080-00	46 x 51 cm (18 x 20 in)	white	350
Dispenser Rolls		W x L	
62050-00	51 cm x 91 m (20 in x 300 ft)	white	1
62070-00	51 cm x 30 m (20 in x 100 ft)	white	4
Rolls		W x L	
62060-00	51 cm x 91 m (20 in x 300 ft)	white	2
62065-00	51 cm x 46 m (20 in x 150 ft)	white	2

Super Versi-Dry Surface Protectors – absorbs 1,050ml/m²

Catalog No.	Description	Dimensions	Color	No. per case
Mats		L x W		
74018-00	Small Mat	46 x 51 cm (18 x 20 in)	blue	350
74040-00	Large Mat	46 x 102 cm (18 x 40 in)	blue	175
74043-00	Table Mat	51 x 110 cm (20 x 43 in)	blue	150
74218-00	Fume Hood Mat	46 x 51 cm (18 x 20 in)	blue	100
74240-00	Floor Mat	46 x 102 cm (18 x 40 in)	blue	50
Rolls		L x W	Color	
74000-00	Benchtop Roll	51 cm x 76 m (20 in x 250 ft)	blue	1
74050-00	Benchtop Roll	51 cm x 30 m (20 in x 100 ft)	blue	4
74200-00	Floor Mat Roll	102 cm x 61 m (40 in x 200 ft)	blue	1

Get a free sample of Super Versi-Dry.

Go to www.thermofisher.com/versidry for details.



Enable the Smart Lab

Find out more at thermofisher.com/breaktheglasshabit

ThermoFisher
SCIENTIFIC