

Looking to replace your tired labware?



Thermo Scientific Nalgene Labware Value Pack

**not all labware**  
is created equal

The Nalgene® Labware Value Pack is an assortment of popular labware items used every day in every lab; bundled in a convenient pack and ready for your research right out of the box! Nalgene Labware sets the standard for quality and superior performance for your valuable research:

- with the highest quality materials for dependable performance
- safer alternative to glass - won't shatter or break
- so trusted, millions are used in laboratories world wide

This labware value pack makes a convenient and economical new lab starter kit or is a great refresher pack for established labs.

**Thermo**  
SCIENTIFIC



## Thermo Scientific Nalgene Labware Value Pack

- **Convenient** - receive 20 items with one catalog number
- **Cost effective** - variety of everyday lab items at one low price
- **Safe alternative to glass** - won't shatter or break!

Cat. No. 1350-0001 includes:				
Qty	Product	Size	Material*	Autoclavable
6	Straight-Sided Jars,	500mL	PPCO	Yes
4	Unitary wash bottles	500mL	LDPE	No
2	Graduated cylinders	100mL	PPCO	Yes
1	Graduated cylinders	500mL	PPCO	Yes
1	Graduated cylinders	1L	PPCO	Yes
1	Griffin Low Form Beaker	50mL	PPCO	Yes
1	Griffin Low Form Beaker	100mL	PPCO	Yes
1	Griffin Low Form Beaker	250mL	PPCO	Yes
1	Griffin Low Form Beaker	600mL	PPCO	Yes
1	Griffin Low Form Beaker	1000mL	PPCO	Yes
1	Unwire™ Half-Rack, Blue	for 30mm tubes	RMT	Yes

\*PPCO = Polypropylene Copolymer; LDPE = Low Density Polyethylene;  
RMT = Resmer Manufacturing Technology

### Details:

All items in the labware value pack are chemically compatible with a wide range of common laboratory reagents; especially acids, bases and alcohols.

### Compliance:

Graduated Cylinders Meet CFR 21, Part 177.1520 and ASTM\* E 1272 Class B accuracy requirements as well as ISO Standard 6706. Beakers meet ISO/DIN 7056 International Standards for Laboratory Plasticware Accuracy.

Remove jar closure and autoclave separately.

© 2012 Thermo Fisher Scientific Inc. All rights reserved. All trademarks are the property of ThermoFisher Scientific Inc. and its subsidiaries.

[www.thermoscientific.com/labware](http://www.thermoscientific.com/labware)

**ANZ:** Australia: 1300 735 292; New Zealand: 0800 933 966; **Asia:** China Toll-free: 800-810-5118 or 400-650-5118; India: +91 22 6716 2200, India Toll-free: 1 800 22 8374; Japan: +81-3-5826-1616; Other Asian countries: 65 68729717  
**Europe:** Austria: +43 1 801 40 0; Belgium: +32 2 482 30 30; Denmark: +45 4631 2000; France: +33 2 2803 2180; Germany: +49 6184 90 6000, Germany Toll-free: 0800 1 536 376; Italy: +39 02 95059 554 or 434-254-375; Netherlands: +31 76 571 4440; Nordic/Baltic countries: +358 9 329 10200; Russia/CIS: +7 (812) 703 42 15; Spain/Portugal: +34 93 223 09 18; Switzerland: +41 44 454 12 22; UK/Ireland: +44 870 609 9203  
**North America:** USA/Canada +1 585 586 8800; USA Toll-free: 800 625 4327  
**South America:** USA sales support: +1 585 899 7198 **Countries not listed:** +49 6184 90 6900 or +33 2 2803 2000