ppliedbiosystem

Routine PCR, elevated

Introducing MiniAmp Plus and MiniAmp Thermal Cyclers

The proven reliability of Applied Biosystems thermal cyclers for routine PCR at every lab bench

Applied Biosystems[™] thermal cyclers have a reputation for reliability, accuracy, and user-friendly interfaces. Our MiniAmp[™] Thermal Cyclers offer all this but with only the features you need for routine PCR. With their small size and entry-level price, MiniAmp Thermal Cyclers are perfect for every lab bench.

Compact to fit on every benchtop

Applied Biosystems[™] technology reconfigured into a minimal footprint, just 7.5 in. (19 cm) wide, helps save valuable lab space.

Cloud-enabled for secure remote access

Conveniently access your instrument anytime, anywhere with Thermo Fisher Connect. You can design a protocol, start a run, and more from any mobile device or desktop computer.

VeriFlex Block or isothermal block option

The MiniAmp[™] Plus Thermal Cycler features an Applied Biosystems[™] VeriFlex[™] Block with 3 independent temperature zones for easy PCR optimization.

If optimization is not part of your routine PCR, the MiniAmp Thermal Cycler has an isothermal block for basic PCR.



Need a larger touch screen, a faster ramp rate, or higher throughput? Go to thermofisher.com/thermalcyclers





Award-winning service and support

• Help reduce downtime with rapid exchange support

• Have our engineers perform temperature qualification at your site

MiniAmp Plus Thermal Cycler	MiniAmp Thermal Cycler	
96-well, 0.2 mL 3-zone VeriFlex Block	96-well, 0.2 mL isothermal block	
3.5°C/sec	3.0°C/sec	
2.7°C/sec	2.2°C/sec	
±0.25°C (35–99.9°C)		
0–100.0°C		
<0.5°C (30 sec after reaching 95°C)		
Calibrated to standards traceable to the National Institute of Standards and Technology		
20 x 19 x 39 cm (7.9 x 7.5 x 15.4 in.)		
5.9 kg (13.0 lb)		
10–100 µL		
2,000 MB onboard memory (capacity for >1,000 protocols); USB port for additional external storage		
5-inch color TFT LCD		
100–240 V, 50–60 Hz, max. 500 W		
3 temperature zones, 20°C range (10°C zone-to-zone)	Not available	
Cloud or mobile via Ethernet or Wi-Fi		
	96-well, 0.2 mL 3-zone VeriFlex Block 3.5°C/sec 2.7°C/sec ±0.25°C (3 0-100 <0.5°C (30 sec aft Calibrated to standards traceable to the Nat 20 x 19 x 39 cm (7 5.9 kg (7 10-10 2,000 MB onboard memory (capacity for >1,000 p 5-inch colo 100–240 V, 50–60 3 temperature zones, 20°C range (10°C zone-to-zone)	

* At reaction volume of 1 µL. ** The Instrument Connect app, available on the Apple[™] and Google[™] app stores, can be used to monitor your instrument. Thermo Fisher Connect can be used to create and share protocols, schedule an instrument, and start and monitor runs remotely.

Ordering information

Product	Quantity	Cat. No.
MiniAmp Plus Thermal Cycler	1 instrument	A37835
MiniAmp Thermal Cycler	1 instrument	A37834
Recommended plastics		
MicroAmp EnduraPlate Optical 96-Well Clear Reaction Plates with Barcode	20 plates	4483354
MicroAmp Clear Adhesive Film	100 films	4306311
MicroAmp TriFlex 3 x 32-Well PCR Reaction Plate (20 plates/pack)	20 plates	A32811
MicroAmp 32-Well Clear Adhesive Film	100 films	A32812
MicroAmp 8-Tube Strip with Attached Domed Caps, 0.2 mL	125 strips	A30589
Recommended reagents		
Platinum II Hot-Start PCR Master Mix (2X)	200 reactions	14000013
Platinum II Green Hot-Start PCR Master Mix (2X)	200 reactions	14001013
Platinum SuperFi PCR Master Mix	100 reactions	12358010
Platinum SuperFi Green PCR Master Mix	100 reactions	12359010

Did you know?

VeriFlex Blocks have separate temperature zones, each with a heating/ cooling element, enabling precise temperature control in each zone for PCR optimization and incubation.



Find out more at **thermofisher.com/miniamp**

For Research Use Only. Not for use in diagnostic procedures. © 2018 Thermo Fisher Scientific Inc. All rights reserved. All trademarks are the property of Thermo Fisher Scientific and its subsidiaries unless otherwise specified. Apple is a trademark of Apple Inc. Google is a trademark of Google Inc. The content provided herein may relate to products that have not been officially released and is subject to change without notice. COL15589 0118