

SECTION 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

1.1. Product identifier

Product Description:	Acethydrazide
Cat No. :	102350000; 102350250; 102351000
Synonyms	Acetic acid hydrazide
CAS No	1068-57-1
EC No	213-948-7
Molecular Formula	C ₂ H ₆ N ₂ O

1.2. Relevant identified uses of the substance or mixture and uses advised against

Recommended Use	Laboratory chemicals.
Uses advised against	No Information available

1.3. Details of the supplier of the safety data sheet

Company

EU entity/business name
Thermo Fisher Scientific
Janssen Pharmaceuticaaan 3a, 2440 Geel, Belgium

UK entity/business name
Fisher Scientific UK
Bishop Meadow Road,
Loughborough, Leicestershire LE11 5RG, United Kingdom

Swiss distributor - Fisher Scientific AG
Neuhofstrasse 11, CH 4153 Reinach
Tel: +41 (0) 56 618 41 11
e-mail - infoch@thermofisher.com

E-mail address begel.sdsdesk@thermofisher.com

1.4. Emergency telephone number

For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11
Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99
CHEMTREC Tel. No.**US**:001-800-424-9300 / **Europe**:001-703-527-3887

customers in Switzerland:
Tox Info Suisse Emergency Number: **145 (24hr)**
Tox Info Suisse: +41-44 251 51 51 (Emergency number from abroad)
Chemtrec (24h) Toll-Free: 0800 564 402
Chemtrec Local: +41-43 508 20 11 (Zurich)

SECTION 2: HAZARDS IDENTIFICATION

2.1. Classification of the substance or mixture

SAFETY DATA SHEET

Acethydrazide

Revision Date 22-Sep-2023

CLP Classification - Regulation (EC) No 1272/2008

Physical hazards

Based on available data, the classification criteria are not met

Health hazards

Acute oral toxicity	Category 3 (H301)
Skin Corrosion/Irritation	Category 2 (H315)
Serious Eye Damage/Eye Irritation	Category 2 (H319)
Germ Cell Mutagenicity	Category 2 (H341)
Carcinogenicity	Category 2 (H351)

Environmental hazards

Based on available data, the classification criteria are not met

Full text of Hazard Statements: see section 16

2.2. Label elements



Signal Word

Danger

Hazard Statements

H301 - Toxic if swallowed
H315 - Causes skin irritation
H319 - Causes serious eye irritation
H341 - Suspected of causing genetic defects
H351 - Suspected of causing cancer

Precautionary Statements

P301 + P330 + P331 - IF SWALLOWED: rinse mouth. Do NOT induce vomiting
P302 + P352 - IF ON SKIN: Wash with plenty of soap and water
P332 + P313 - If skin irritation occurs: Get medical advice/attention
P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing
P280 - Wear protective gloves/protective clothing/eye protection/face protection
P308 + P313 - IF exposed or concerned: Get medical advice/attention

2.3. Other hazards

No information available
This product does not contain any known or suspected endocrine disruptors

SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS

SAFETY DATA SHEET

Acethydrazide

Revision Date 22-Sep-2023

3.1. Substances

Component	CAS No	EC No	Weight %	CLP Classification - Regulation (EC) No 1272/2008
Acetic acid, hydrazide	1068-57-1	EEC No. 213-948-7	<=100	Acute Tox. 3 (H301) Skin Irrit. 2 (H315) Eye Irrit. 2 (H319) Muta. 2 (H341) Carc. 2 (H351)

Full text of Hazard Statements: see section 16

SECTION 4: FIRST AID MEASURES

4.1. Description of first aid measures

General Advice	Show this safety data sheet to the doctor in attendance. Immediate medical attention is required.
Eye Contact	In the case of contact with eyes, rinse immediately with plenty of water and seek medical advice.
Skin Contact	Wash off immediately with plenty of water for at least 15 minutes. Immediate medical attention is required.
Ingestion	Do NOT induce vomiting. Call a physician or poison control center immediately.
Inhalation	Remove to fresh air. If not breathing, give artificial respiration. Do not use mouth-to-mouth method if victim ingested or inhaled the substance; give artificial respiration with the aid of a pocket mask equipped with a one-way valve or other proper respiratory medical device. Immediate medical attention is required.
Self-Protection of the First Aider	Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

4.2. Most important symptoms and effects, both acute and delayed

None reasonably foreseeable.

4.3. Indication of any immediate medical attention and special treatment needed

Notes to Physician	Treat symptomatically.
---------------------------	------------------------

SECTION 5: FIREFIGHTING MEASURES

5.1. Extinguishing media

Suitable Extinguishing Media

Water spray. Carbon dioxide (CO₂). Dry chemical. Chemical foam.

Extinguishing media which must not be used for safety reasons

No information available.

SAFETY DATA SHEET

Acethydrazide

Revision Date 22-Sep-2023

5.2. Special hazards arising from the substance or mixture

Thermal decomposition can lead to release of irritating gases and vapors.

Hazardous Combustion Products

Nitrogen oxides (NO_x), Carbon monoxide (CO), Carbon dioxide (CO₂).

5.3. Advice for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear. Thermal decomposition can lead to release of irritating gases and vapors.

SECTION 6: ACCIDENTAL RELEASE MEASURES

6.1. Personal precautions, protective equipment and emergency procedures

Ensure adequate ventilation. Use personal protective equipment as required. Avoid dust formation. Keep people away from and upwind of spill/leak. Evacuate personnel to safe areas.

6.2. Environmental precautions

Should not be released into the environment.

6.3. Methods and material for containment and cleaning up

Sweep up and shovel into suitable containers for disposal. Avoid dust formation.

6.4. Reference to other sections

Refer to protective measures listed in Sections 8 and 13.

SECTION 7: HANDLING AND STORAGE

7.1. Precautions for safe handling

Wear personal protective equipment/face protection. Do not get in eyes, on skin, or on clothing. Avoid dust formation. Use only under a chemical fume hood. Do not breathe (dust, vapor, mist, gas). Do not ingest. If swallowed then seek immediate medical assistance.

Hygiene Measures

Handle in accordance with good industrial hygiene and safety practice. Keep away from food, drink and animal feeding stuffs. Do not eat, drink or smoke when using this product. Remove and wash contaminated clothing and gloves, including the inside, before re-use. Wash hands before breaks and after work.

7.2. Conditions for safe storage, including any incompatibilities

Keep containers tightly closed in a dry, cool and well-ventilated place. Keep under nitrogen. Store under an inert atmosphere. Protect from moisture.

Technical Rules for Hazardous Substances (TRGS) 510
Storage Class (LGK) (Germany)

Storage Class/LGK 6.1C

Switzerland - Storage of hazardous substances

Storage class - SC 6.1
<https://www.kvu.ch/de/themen/stoffe-und-produkte>
<https://www.kvu.ch/fr/themes/substances-et-produits>
<https://www.kvu.ch/it/temi/sostanze-e-prodotti>

7.3. Specific end use(s)

ACR10235

SAFETY DATA SHEET

Acethydrazide

Revision Date 22-Sep-2023

Use in laboratories

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1. Control parameters

Exposure limits

This product, as supplied, does not contain any hazardous materials with occupational exposure limits established by the region specific regulatory bodies

Biological limit values

This product, as supplied, does not contain any hazardous materials with biological limits established by the region specific regulatory bodies

Monitoring methods

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents.

MDHS14/3 General methods for sampling and gravimetric analysis of respirable and inhalable dust

Derived No Effect Level (DNEL) / Derived Minimum Effect Level (DMEL)

No information available

Predicted No Effect Concentration (PNEC)

No information available.

8.2. Exposure controls

Engineering Measures

Use explosion-proof electrical/ventilating/lighting/equipment. Ensure that eyewash stations and safety showers are close to the workstation location.

Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source

Personal protective equipment

Eye Protection

Goggles (European standard - EN 166)

Hand Protection

Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Natural rubber	See manufacturers	-		(minimum requirement)

SAFETY DATA SHEET

Acethydrazide

Revision Date 22-Sep-2023

Nitrile rubber Neoprene PVC	recommendations	EN 374
-----------------------------------	-----------------	--------

Skin and body protection Wear appropriate protective gloves and clothing to prevent skin exposure.

Inspect gloves before use. observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information) gloves are suitable for the task: Chemical compatability, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion. gloves with care avoiding skin contamination.

Respiratory Protection When workers are facing concentrations above the exposure limit they must use appropriate certified respirators.
To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly

Large scale/emergency use Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced
Recommended Filter type: Particulates filter conforming to EN 143

Small scale/Laboratory use Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.
Recommended half mask:- Valve filtering: EN405; or; Half mask: EN140; plus filter, EN 141
When RPE is used a face piece Fit Test should be conducted

Environmental exposure controls No information available.

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

9.1. Information on basic physical and chemical properties

Physical State	Solid	
Appearance	White	
Odor	No information available	
Odor Threshold	No data available	
Melting Point/Range	57 - 60 °C / 134.6 - 140 °F	
Softening Point	No data available	
Boiling Point/Range	129 °C / 264.2 °F	@ 18 mmHg
Flammability (liquid)	Not applicable	Solid
Flammability (solid,gas)	No information available	
Explosion Limits	No data available	
Flash Point	> 110 °C / > 230 °F	Method - No information available
Autoignition Temperature	No data available	
Decomposition Temperature	100 °C	
pH	Not applicable	
Viscosity	Not applicable	Solid
Water Solubility	Soluble	
Solubility in other solvents	No information available	
Partition Coefficient (n-octanol/water)		
Component	log Pow	
Acetic acid, hydrazide	-1.58	
Vapor Pressure	No information available	
Density / Specific Gravity	No data available	
Bulk Density	No data available	
Vapor Density	Not applicable	Solid
Particle characteristics	No data available	

SAFETY DATA SHEET

Acethydrazide

Revision Date 22-Sep-2023

9.2. Other information

Molecular Formula	C2 H6 N2 O
Molecular Weight	74.08
Evaporation Rate	Not applicable - Solid

SECTION 10: STABILITY AND REACTIVITY

10.1. Reactivity

Yes

10.2. Chemical stability

Hygroscopic.

10.3. Possibility of hazardous reactions

Hazardous Polymerization	No information available.
Hazardous Reactions	None under normal processing.

10.4. Conditions to avoid

Incompatible products. Exposure to moist air or water.

10.5. Incompatible materials

Strong oxidizing agents. Strong bases.

10.6. Hazardous decomposition products

Nitrogen oxides (NOx). Carbon monoxide (CO). Carbon dioxide (CO₂).

SECTION 11: TOXICOLOGICAL INFORMATION

11.1. Information on hazard classes as defined in Regulation (EC) No 1272/2008

Product Information

(a) acute toxicity;

Oral	Category 3
Dermal	No data available
Inhalation	No data available

(b) skin corrosion/irritation; Category 2

(c) serious eye damage/irritation; Category 2

(d) respiratory or skin sensitization;

Respiratory	No data available
Skin	No data available

(e) germ cell mutagenicity; Category 2

(f) carcinogenicity; Category 2

There are no known carcinogenic chemicals in this product

SAFETY DATA SHEET

Acethydrazide

Revision Date 22-Sep-2023

(g) reproductive toxicity; No data available

(h) STOT-single exposure; No data available

(i) STOT-repeated exposure; No data available

Target Organs None known.

(j) aspiration hazard; Not applicable
Solid

Other Adverse Effects The toxicological properties have not been fully investigated.

Symptoms / effects, both acute and delayed No information available.

11.2. Information on other hazards

Endocrine Disrupting Properties Assess endocrine disrupting properties for human health. This product does not contain any known or suspected endocrine disruptors.

SECTION 12: ECOLOGICAL INFORMATION

12.1. Toxicity

Ecotoxicity effects .

12.2. Persistence and degradability

Persistence Persistence is unlikely.

12.3. Bioaccumulative potential Bioaccumulation is unlikely

Component	log Pow	Bioconcentration factor (BCF)
Acetic acid, hydrazide	-1.58	No data available

12.4. Mobility in soil The product is water soluble, and may spread in water systems Will likely be mobile in the environment due to its water solubility. Highly mobile in soils

12.5. Results of PBT and vPvB assessment No data available for assessment.

12.6. Endocrine disrupting properties

Endocrine Disruptor Information This product does not contain any known or suspected endocrine disruptors

12.7. Other adverse effects
Persistent Organic Pollutant
Ozone Depletion Potential

This product does not contain any known or suspected substance
This product does not contain any known or suspected substance

SAFETY DATA SHEET

Acethydrazide

Revision Date 22-Sep-2023

SECTION 13: DISPOSAL CONSIDERATIONS

13.1. Waste treatment methods

Waste from Residues/Unused Products	Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.
Contaminated Packaging	Empty containers retain product residue, (liquid and/or vapor), and can be dangerous. Keep product and empty container away from heat and sources of ignition. Dispose of this container to hazardous or special waste collection point.
European Waste Catalogue (EWC)	According to the European Waste Catalog, Waste Codes are not product specific, but application specific.
Other Information	Do not flush to sewer. Can be landfilled or incinerated, when in compliance with local regulations. Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains.
Switzerland - Waste Ordinance	Disposal should be in accordance with applicable regional, national and local laws and regulations. Ordinance on the Avoidance and the Disposal of Waste (Waste Ordinance, ADWO) SR 814.600 https://www.fedlex.admin.ch/eli/cc/2015/891/en

SECTION 14: TRANSPORT INFORMATION

IMDG/IMO

14.1. UN number	UN2811
14.2. UN proper shipping name	TOXIC SOLID, ORGANIC, N.O.S.
Technical Shipping Name	Acethydrazide
14.3. Transport hazard class(es)	6.1
14.4. Packing group	III

ADR

14.1. UN number	UN2811
14.2. UN proper shipping name	TOXIC SOLID, ORGANIC, N.O.S.
Technical Shipping Name	Acethydrazide
14.3. Transport hazard class(es)	6.1
14.4. Packing group	III

IATA

14.1. UN number	UN2811
14.2. UN proper shipping name	TOXIC SOLID, ORGANIC, N.O.S.
Technical Shipping Name	Acethydrazide
14.3. Transport hazard class(es)	6.1
14.4. Packing group	III

14.5. Environmental hazards	No hazards identified
14.6. Special precautions for user	No special precautions required.
14.7. Maritime transport in bulk according to IMO instruments	Not applicable, packaged goods

SECTION 15: REGULATORY INFORMATION

SAFETY DATA SHEET

Acethydrazide

Revision Date 22-Sep-2023

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

International Inventories

Europe (EINECS/ELINCS/NLP), China (IECSC), Taiwan (TCSI), Korea (KECL), Japan (ENCS), Japan (ISHL), Canada (DSL/NDSL), Australia (AICS), New Zealand (NZIoC), Philippines (PICCS). US EPA (TSCA) - Toxic Substances Control Act, (40 CFR Part 710)

Component	CAS No	EINECS	ELINCS	NLP	IECSC	TCSI	KECL	ENCS	ISHL
Acetic acid, hydrazide	1068-57-1	213-948-7	-	-	-	X	-	-	X

Component	CAS No	TSCA	TSCA Inventory notification - Active-Inactive	DSL	NDSL	AICS	NZIoC	PICCS
Acetic acid, hydrazide	1068-57-1	X	ACTIVE	-	X	-	X	X

Legend: X - Listed '-' - Not Listed

KECL - NIER number or KE number (<http://ncis.nier.go.kr/en/main.do>)

Authorisation/Restrictions according to EU REACH

Not applicable

Component	CAS No	REACH (1907/2006) - Annex XIV - Substances Subject to Authorization	REACH (1907/2006) - Annex XVII - Restrictions on Certain Dangerous Substances	REACH Regulation (EC 1907/2006) article 59 - Candidate List of Substances of Very High Concern (SVHC)
Acetic acid, hydrazide	1068-57-1	-	-	-

Seveso III Directive (2012/18/EC)

Component	CAS No	Seveso III Directive (2012/18/EC) - Qualifying Quantities for Major Accident Notification	Seveso III Directive (2012/18/EC) - Qualifying Quantities for Safety Report Requirements
Acetic acid, hydrazide	1068-57-1	Not applicable	Not applicable

Regulation (EC) No 649/2012 of the European Parliament and of the Council of 4 July 2012 concerning the export and import of dangerous chemicals

Not applicable

Contains component(s) that meet a 'definition' of per & poly fluoroalkyl substance (PFAS)?

Not applicable

Take note of Directive 98/24/EC on the protection of the health and safety of workers from the risks related to chemical agents at work .

National Regulations

UK - Take note of Control of Substances Hazardous to Health Regulations (COSHH) 2002 and 2005 Amendment

WGK Classification

See table for values

Component	Germany - Water Classification (AwSV)	Germany - TA-Luft Class
Acetic acid, hydrazide	WGK1	

Swiss Regulations

Article 4 para. 4 of the Ordinance on the protection of young people in the workplace (SR 822.115) and Article 1 lit. f of the EAER

SAFETY DATA SHEET

Acethydrazide

Revision Date 22-Sep-2023

regulation on hazardous work and young people (SR 822.115.2).
Take note on Article 13 Maternity Ordinance (SR 822.111.52) with regards expectant and nursing mothers.

15.2. Chemical safety assessment

A Chemical Safety Assessment/Report (CSA/CSR) has not been conducted

SECTION 16: OTHER INFORMATION

Full text of H-Statements referred to under sections 2 and 3

H301 - Toxic if swallowed
H315 - Causes skin irritation
H319 - Causes serious eye irritation
H341 - Suspected of causing genetic defects
H351 - Suspected of causing cancer

Legend

CAS - Chemical Abstracts Service

EINECS/ELINCS - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

PICCS - Philippines Inventory of Chemicals and Chemical Substances

IECSC - Chinese Inventory of Existing Chemical Substances

KECL - Korean Existing and Evaluated Chemical Substances

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

ENCS - Japanese Existing and New Chemical Substances

AICS - Australian Inventory of Chemical Substances

NZIoC - New Zealand Inventory of Chemicals

WEL - Workplace Exposure Limit

ACGIH - American Conference of Governmental Industrial Hygienists

DNEL - Derived No Effect Level

RPE - Respiratory Protective Equipment

LC50 - Lethal Concentration 50%

NOEC - No Observed Effect Concentration

PBT - Persistent, Bioaccumulative, Toxic

TWA - Time Weighted Average

IARC - International Agency for Research on Cancer
Predicted No Effect Concentration (PNEC)

LD50 - Lethal Dose 50%

EC50 - Effective Concentration 50%

POW - Partition coefficient Octanol:Water

vPvB - very Persistent, very Bioaccumulative

ADR - European Agreement Concerning the International Carriage of Dangerous Goods by Road

IMO/IMDG - International Maritime Organization/International Maritime Dangerous Goods Code

OECD - Organisation for Economic Co-operation and Development

BCF - Bioconcentration factor

Key literature references and sources for data

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

ICAO/IATA - International Civil Aviation Organization/International Air Transport Association

MARPOL - International Convention for the Prevention of Pollution from Ships

ATE - Acute Toxicity Estimate

VOC - (volatile organic compound)

Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

Revision Date

22-Sep-2023

Revision Summary

SDS sections updated.

**This safety data sheet complies with the requirements of Regulation (EC) No. 1907/2006.
COMMISSION REGULATION (EU) 2020/878 amending Annex II to Regulation (EC) No
1907/2006 .**

For Switzerland - Compiled in accordance with the technical provisions referred to in Annex 2,

SAFETY DATA SHEET

Acethydrazide

Revision Date 22-Sep-2023

Number 3, ChemO (SR 813.11 - Ordinance on Protection against Dangerous Substances and Preparations).

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet