

Creation Date 29-Oct-2010

Revision Date 11-Dec-2020

Revision Number 6

## SECTION 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

### 1.1. Product identifier

Product Description: **Vanadyl(IV) acetylacetonate**  
Cat No. : **199590000; 199590500; 199592500**  
CAS-No **3153-26-2**  
EC-No. **221-590-8**  
Molecular Formula **C10 H14 O5 V**

### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Recommended Use Laboratory chemicals.  
Uses advised against No Information available

### 1.3. Details of the supplier of the safety data sheet

Company **UK entity/business name**  
Fisher Scientific UK  
Bishop Meadow Road, Loughborough,  
Leicestershire LE11 5RG, United Kingdom

**EU entity/business name**  
Acros Organics BVBA  
Janssen Pharmaceuticaaan 3a  
2440 Geel, Belgium

E-mail address [bege1.sdsdesk@thermofisher.com](mailto:bege1.sdsdesk@thermofisher.com)

### 1.4. Emergency telephone number

For information **US** call: 001-800-ACROS-01 / **Europe** call: +32 14 57 52 11  
Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99  
**CHEMTREC** Tel. No.**US**:001-800-424-9300 / **Europe**:001-703-527-3887

## SECTION 2: HAZARDS IDENTIFICATION

### 2.1. Classification of the substance or mixture

#### CLP Classification - Regulation (EC) No 1272/2008

#### Physical hazards

Based on available data, the classification criteria are not met

#### Health hazards

Acute oral toxicity

Category 4 (H302)

# SAFETY DATA SHEET

Vanadyl(IV) acetylacetonate

Revision Date 11-Dec-2020

Skin Corrosion/Irritation  
Serious Eye Damage/Eye Irritation  
Specific target organ toxicity - (single exposure)

Category 2 (H315)  
Category 2 (H319)  
Category 3 (H335)

## **Environmental hazards**

Based on available data, the classification criteria are not met

Full text of Hazard Statements: see section 16

## **2.2. Label elements**



**Signal Word**

**Warning**

## **Hazard Statements**

H302 - Harmful if swallowed  
H315 - Causes skin irritation  
H319 - Causes serious eye irritation  
H335 - May cause respiratory irritation

## **Precautionary Statements**

P301 + P330 + P331 - IF SWALLOWED: rinse mouth. Do NOT induce vomiting  
P312 - Call a POISON CENTER or doctor/physician if you feel unwell  
P302 + P352 - IF ON SKIN: Wash with plenty of soap and water  
P337 + P313 - If eye irritation persists: Get medical advice/attention  
P304 + P340 - IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing  
P280 - Wear protective gloves/protective clothing/eye protection/face protection

## **2.3. Other hazards**

No information available

## **SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS**

### **3.1. Substances**

Component	CAS-No	EC-No.	Weight %	CLP Classification - Regulation (EC) No 1272/2008
Vanadium, oxobis(2,4-pentanedionato-O,O')-, (SP-5-21)-	3153-26-2	EEC No. 221-590-8	>95	Acute Tox. 4 (H302) Skin Irrit. 2 (H315) Eye Irrit. 2 (H319) STOT SE 3 (H335)

Full text of Hazard Statements: see section 16

# SAFETY DATA SHEET

Vanadyl(IV) acetylacetonate

Revision Date 11-Dec-2020

## SECTION 4: FIRST AID MEASURES

### 4.1. Description of first aid measures

<b>General Advice</b>	If symptoms persist, call a physician.
<b>Eye Contact</b>	Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.
<b>Skin Contact</b>	Wash off immediately with plenty of water for at least 15 minutes. If skin irritation persists, call a physician.
<b>Ingestion</b>	Clean mouth with water and drink afterwards plenty of water. Get medical attention if symptoms occur.
<b>Inhalation</b>	Remove to fresh air. If not breathing, give artificial respiration. Get medical attention if symptoms occur.
<b>Self-Protection of the First Aider</b>	Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

### 4.2. Most important symptoms and effects, both acute and delayed

None reasonably foreseeable.

### 4.3. Indication of any immediate medical attention and special treatment needed

**Notes to Physician** Treat symptomatically.

## SECTION 5: FIREFIGHTING MEASURES

### 5.1. Extinguishing media

#### **Suitable Extinguishing Media**

Water spray, carbon dioxide (CO<sub>2</sub>), dry chemical, alcohol-resistant foam. Water mist may be used to cool closed containers.

#### **Extinguishing media which must not be used for safety reasons**

No information available.

### 5.2. Special hazards arising from the substance or mixture

Combustible material. Flammable. Containers may explode when heated.

#### **Hazardous Combustion Products**

Carbon monoxide (CO), Carbon dioxide (CO<sub>2</sub>).

### 5.3. Advice for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

## SECTION 6: ACCIDENTAL RELEASE MEASURES

### 6.1. Personal precautions, protective equipment and emergency procedures

Ensure adequate ventilation. Use personal protective equipment as required. Avoid dust formation. Remove all sources of ignition. Take precautionary measures against static discharges.

# SAFETY DATA SHEET

Vanadyl(IV) acetylacetonate

Revision Date 11-Dec-2020

## **6.2. Environmental precautions**

Should not be released into the environment.

## **6.3. Methods and material for containment and cleaning up**

Sweep up and shovel into suitable containers for disposal. Keep in suitable, closed containers for disposal. Remove all sources of ignition.

## **6.4. Reference to other sections**

Refer to protective measures listed in Sections 8 and 13.

## **SECTION 7: HANDLING AND STORAGE**

### **7.1. Precautions for safe handling**

Wear personal protective equipment/face protection. Ensure adequate ventilation. Do not get in eyes, on skin, or on clothing. Avoid ingestion and inhalation. Avoid dust formation. Keep away from open flames, hot surfaces and sources of ignition.

#### **Hygiene Measures**

Handle in accordance with good industrial hygiene and safety practice. Keep away from food, drink and animal feeding stuffs. Do not eat, drink or smoke when using this product. Remove and wash contaminated clothing and gloves, including the inside, before re-use. Wash hands before breaks and after work.

### **7.2. Conditions for safe storage, including any incompatibilities**

Keep in a dry, cool and well-ventilated place. Keep container tightly closed. Keep away from heat, sparks and flame. To maintain product quality. Keep under nitrogen. Do not allow contact with air.

**Technical Rules for Hazardous Substances (TRGS) 510 Storage Class (LGK)**  
**(Germany)**

Class 11

### **7.3. Specific end use(s)**

Use in laboratories

## **SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION**

### **8.1. Control parameters**

#### **Exposure limits**

List source(s):

#### **Biological limit values**

This product, as supplied, does not contain any hazardous materials with biological limits established by the region specific regulatory bodies

#### **Monitoring methods**

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents.

MDHS14/3 General methods for sampling and gravimetric analysis of respirable and inhalable dust

MDHS70 General methods for sampling airborne gases and vapours

**Derived No Effect Level (DNEL)** No information available

# SAFETY DATA SHEET

Vanadyl(IV) acetylacetonate

Revision Date 11-Dec-2020

Route of exposure	Acute effects (local)	Acute effects (systemic)	Chronic effects (local)	Chronic effects (systemic)
Oral Dermal Inhalation				

**Predicted No Effect Concentration (PNEC)** No information available.

## 8.2. Exposure controls

### Engineering Measures

Ensure adequate ventilation, especially in confined areas. Ensure that eyewash stations and safety showers are close to the workstation location.

Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source

### Personal protective equipment

**Eye Protection** Goggles (European standard - EN 166)

**Hand Protection** Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Nitrile rubber	> 480 minutes	0.11 mm	EN 374	(minimum requirement)
Neoprene				
Natural rubber				
PVC				

**Skin and body protection** Long sleeved clothing

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

**Respiratory Protection** When workers are facing concentrations above the exposure limit they must use appropriate certified respirators. To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly

**Large scale/emergency use** Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced  
**Recommended Filter type:** Particulates filter conforming to EN 143

**Small scale/Laboratory use** Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.  
**Recommended half mask:-** Particle filtering: EN149:2001  
When RPE is used a face piece Fit Test should be conducted

**Environmental exposure controls** No information available.

## SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

### 9.1. Information on basic physical and chemical properties

# SAFETY DATA SHEET

Vanadyl(IV) acetylacetonate

Revision Date 11-Dec-2020

<b>Physical State</b>	Powder Solid	
<b>Appearance</b>	Blue green	
<b>Odor</b>	Odorless	
<b>Odor Threshold</b>	No data available	
<b>Melting Point/Range</b>	256 - 259 °C / 492.8 - 498.2 °F	
<b>Softening Point</b>	No data available	
<b>Boiling Point/Range</b>	No information available	
<b>Flammability (liquid)</b>	Not applicable	Solid
<b>Flammability (solid,gas)</b>	No information available	
<b>Explosion Limits</b>	No data available	
<b>Flash Point</b>	79 °C / 174.2 °F	<b>Method -</b> No information available
<b>Autoignition Temperature</b>	No data available	
<b>Decomposition Temperature</b>	No data available	
<b>pH</b>	No information available	
<b>Viscosity</b>	Not applicable	Solid
<b>Water Solubility</b>	Insoluble	
<b>Solubility in other solvents</b>	No information available	
<b>Partition Coefficient (n-octanol/water)</b>		
<b>Vapor Pressure</b>	No data available	
<b>Density / Specific Gravity</b>	No data available	
<b>Bulk Density</b>	No data available	
<b>Vapor Density</b>	Not applicable	Solid
<b>Particle characteristics</b>	No data available	

## 9.2. Other information

<b>Molecular Formula</b>	C10 H14 O5 V
<b>Molecular Weight</b>	265.15
<b>Explosive Properties</b>	explosive air/vapour mixtures possible
<b>Evaporation Rate</b>	Not applicable - Solid

## SECTION 10: STABILITY AND REACTIVITY

### 10.1. Reactivity

None known, based on information available

### 10.2. Chemical stability

Air sensitive.

### 10.3. Possibility of hazardous reactions

<b>Hazardous Polymerization</b>	No information available.
<b>Hazardous Reactions</b>	None under normal processing.

### 10.4. Conditions to avoid

Exposure to air. Incompatible products. Keep away from open flames, hot surfaces and sources of ignition.

### 10.5. Incompatible materials

Strong oxidizing agents.

### 10.6. Hazardous decomposition products

Carbon monoxide (CO). Carbon dioxide (CO<sub>2</sub>).

## SECTION 11: TOXICOLOGICAL INFORMATION

# SAFETY DATA SHEET

Vanadyl(IV) acetylacetonate

Revision Date 11-Dec-2020

## 11.1. Information on hazard classes as defined in Regulation (EC) No 1272/2008

### Product Information

**(a) acute toxicity;**

Oral	Category 4
Dermal	No data available
Inhalation	No data available

**(b) skin corrosion/irritation;** Category 2

**(c) serious eye damage/irritation;** Category 2

**(d) respiratory or skin sensitization;**

Respiratory	No data available
Skin	No data available

**(e) germ cell mutagenicity;** No data available

**(f) carcinogenicity;** No data available

There are no known carcinogenic chemicals in this product

**(g) reproductive toxicity;** No data available

**(h) STOT-single exposure;** Category 3

**Results / Target organs** Respiratory system.

**(i) STOT-repeated exposure;** No data available

**Target Organs** No information available.

**(j) aspiration hazard;** Not applicable  
Solid

**Other Adverse Effects** The toxicological properties have not been fully investigated.

**Symptoms / effects, both acute and delayed** No information available.

## 11.2. Information on other hazards

**Endocrine Disrupting Properties** Assess endocrine disrupting properties for human health. This product does not contain any known or suspected endocrine disruptors.

## SECTION 12: ECOLOGICAL INFORMATION

### 12.1. Toxicity

**Ecotoxicity effects** Do not empty into drains. .

# SAFETY DATA SHEET

Vanadyl(IV) acetylacetonate

Revision Date 11-Dec-2020

## 12.2. Persistence and degradability

### **Persistence**

Insoluble in water.

## 12.3. Bioaccumulative potential

May have some potential to bioaccumulate

## 12.4. Mobility in soil

Spillage unlikely to penetrate soil Is not likely mobile in the environment due its low water solubility.

## 12.5. Results of PBT and vPvB assessment

No data available for assessment.

## 12.6. Endocrine disrupting properties

### **Endocrine Disruptor Information**

This product does not contain any known or suspected endocrine disruptors

## 12.7. Other adverse effects

### **Persistent Organic Pollutant Ozone Depletion Potential**

This product does not contain any known or suspected substance

This product does not contain any known or suspected substance

## SECTION 13: DISPOSAL CONSIDERATIONS

### 13.1. Waste treatment methods

#### **Waste from Residues/Unused Products**

Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.

#### **Contaminated Packaging**

Dispose of this container to hazardous or special waste collection point.

#### **European Waste Catalogue (EWC)**

According to the European Waste Catalog, Waste Codes are not product specific, but application specific.

#### **Other Information**

Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains.

## SECTION 14: TRANSPORT INFORMATION

### IMDG/IMO

#### 14.1. UN number

UN3285

#### 14.2. UN proper shipping name

Vanadium compound, n.o.s

#### **Technical Shipping Name**

Vanadium, oxobis(2,4-pentanedionato-O,O')-, (SP-5-21)-

#### 14.3. Transport hazard class(es)

6.1

#### 14.4. Packing group

III

### ADR

#### 14.1. UN number

UN3285

#### 14.2. UN proper shipping name

Vanadium compound, n.o.s

#### **Technical Shipping Name**

Vanadium, oxobis(2,4-pentanedionato-O,O')-, (SP-5-21)-

#### 14.3. Transport hazard class(es)

6.1

#### 14.4. Packing group

III



# SAFETY DATA SHEET

Vanadyl(IV) acetylacetonate

Revision Date 11-Dec-2020

## IATA

<b>14.1. UN number</b>	UN3285
<b>14.2. UN proper shipping name</b>	Vanadium compound, n.o.s
<b>Technical Shipping Name</b>	Vanadium, oxobis(2,4-pentanedionato-O,O')-, (SP-5-21)-
<b>14.3. Transport hazard class(es)</b>	6.1
<b>14.4. Packing group</b>	III

<b>14.5. Environmental hazards</b>	No hazards identified
<b>14.6. Special precautions for user</b>	No special precautions required
<b>14.7. Maritime transport in bulk according to IMO instruments</b>	Not applicable, packaged goods

## SECTION 15: REGULATORY INFORMATION

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

#### International Inventories

X = listed, Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), China (IECSC), Japan (ENCS), Australia (AICS), Korea (ECL).

Component	EINECS	ELINCS	NLP	TSCA	DSL	NDSL	PICCS	ENCS	IECSC	AICS	KECL
Vanadium, oxobis(2,4-pentanedionato-O,O')-, (SP-5-21)-	221-590-8	-		X	-	X	X	X	X	X	2008-1-581

#### Regulation (EC) No 649/2012 of the European Parliament and of the Council of 4 July 2012 concerning the export and import of dangerous chemicals

Not applicable

#### National Regulations

**WGK Classification** See table for values

Component	Germany - Water Classification (VwVwS)	Germany - TA-Luft Class
Vanadium, oxobis(2,4-pentanedionato-O,O')-, (SP-5-21)-	WGK3	

**UK** - Take note of Control of Substances Hazardous to Health Regulations (COSHH) 2002 and 2005 Amendment

### 15.2. Chemical safety assessment

A Chemical Safety Assessment/Report (CSA/CSR) has not been conducted

## SECTION 16: OTHER INFORMATION

#### Full text of H-Statements referred to under sections 2 and 3

H302 - Harmful if swallowed  
H315 - Causes skin irritation  
H319 - Causes serious eye irritation  
H335 - May cause respiratory irritation

# SAFETY DATA SHEET

Vanadyl(IV) acetylacetonate

Revision Date 11-Dec-2020

## Legend

**CAS** - Chemical Abstracts Service

**EINECS/ELINCS** - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

**PICCS** - Philippines Inventory of Chemicals and Chemical Substances

**IECSC** - Chinese Inventory of Existing Chemical Substances

**KECL** - Korean Existing and Evaluated Chemical Substances

**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory

**DSL/NDSL** - Canadian Domestic Substances List/Non-Domestic Substances List

**ENCS** - Japanese Existing and New Chemical Substances

**AICS** - Australian Inventory of Chemical Substances

**NZIoC** - New Zealand Inventory of Chemicals

**WEL** - Workplace Exposure Limit

**ACGIH** - American Conference of Governmental Industrial Hygienists

**DNEL** - Derived No Effect Level

**RPE** - Respiratory Protective Equipment

**LC50** - Lethal Concentration 50%

**NOEC** - No Observed Effect Concentration

**PBT** - Persistent, Bioaccumulative, Toxic

**TWA** - Time Weighted Average

**IARC** - International Agency for Research on Cancer

Predicted No Effect Concentration (PNEC)

**LD50** - Lethal Dose 50%

**EC50** - Effective Concentration 50%

**POW** - Partition coefficient Octanol:Water

**vPvB** - very Persistent, very Bioaccumulative

**ADR** - European Agreement Concerning the International Carriage of Dangerous Goods by Road

**IMO/IMDG** - International Maritime Organization/International Maritime Dangerous Goods Code

**OECD** - Organisation for Economic Co-operation and Development

**BCF** - Bioconcentration factor

**Key literature references and sources for data**

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

**ICAO/IATA** - International Civil Aviation Organization/International Air Transport Association

**MARPOL** - International Convention for the Prevention of Pollution from Ships

**ATE** - Acute Toxicity Estimate

VOC (volatile organic compound)

## Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

**Creation Date** 29-Oct-2010

**Revision Date** 11-Dec-2020

**Revision Summary** Update to CLP Format.

**This safety data sheet complies with the requirements of Regulation (EC) No. 1907/2006  
COMMISSION REGULATION (EU) 2020/878 amending Annex II to Regulation (EC) No  
1907/2006**

## Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

**End of Safety Data Sheet**