

Australian statement of hazardous nature : Classified as hazardous according to criteria of Safe Work Australia

Section 1 - Identification

Product Name Hydrochloric acid

Synonyms Muriatic acid

Product Code	124620000; 124620010; 124620011; 124620025; 124620026; 124620051; 124620100; 124620250
Address	ThermoFisher Scientific Australia Pty Ltd 5 Caribbean Drive, Scoresby VICTORIA 3179, Australia
Emergency Tel.	CHEMTREC® 03 9757 4559 or +613 9757 4559
Telephone / Fax Numbers	Tel: 1300 735 292 Fax: 1800 067 639
E-mail address	ANZinfo@thermofisher.com

Recommended Use Laboratory chemicals.

Uses advised against This product contains one or more substance(s) on the Illicit Drug Precursors/Reagents list. Verify requirements related to using, handling and storing these substances. This product does not contain any substance(s) subject to Prohibition, Authorization or Restriction. This product contains one or more substance(s) listed on the voluntary National Code of Practice for Chemicals of Security Concern.

Section 2 - Hazard(s) Identification

Classification under Safe Work Australia

Classified as hazardous according to criteria of Safe Work Australia

Physical hazards

Substances/mixtures corrosive to metal	Category 1
--	------------

Health hazards

Skin Corrosion/Irritation	Category 1 B
Serious Eye Damage/Eye Irritation	Category 1
Specific target organ toxicity - (single exposure)	Category 3

Environmental hazards

No hazards identified

Label Elements



Exclamation Mark



Corrosion

Signal Word**Danger****Hazard Statements**

H290 - May be corrosive to metals

H314 - Causes severe skin burns and eye damage

H335 - May cause respiratory irritation

Precautionary Statements

P234 - Keep only in original packaging

P264 - Wash face, hands and any exposed skin thoroughly after handling

P271 - Use only outdoors or in a well-ventilated area

P280 - Wear protective gloves/protective clothing/eye protection/face protection

P301 + P330 + P331 - IF SWALLOWED: rinse mouth. Do NOT induce vomiting

P303 + P361 + P353 - IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water or shower

P304 + P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing

P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing

P310 - Immediately call a POISON CENTER or doctor

P363 - Wash contaminated clothing before reuse

P390 - Absorb spillage to prevent material damage

P402 - Store in a dry place

P403 + P233 - Store in a well-ventilated place. Keep container tightly closed

P406 - Store in corrosion resistant polypropylene container with a resistant inliner

P501 - Dispose of contents/ container to an approved waste disposal plant

Other information

Toxic to terrestrial vertebrates

Section 3 - Composition and Information on Ingredients

Component	CAS No	Weight %
Hydrochloric acid	7647-01-0	35-38
Water	7732-18-5	62-65

Section 4 - First Aid Measures**Inhalation**

Remove to fresh air. If breathing is difficult, give oxygen. Do not use mouth-to-mouth method if victim ingested or inhaled the substance; give artificial respiration with the aid of a pocket mask equipped with a one-way valve or other proper respiratory medical device. Immediate medical attention is required.

Ingestion

Do NOT induce vomiting. Call a physician or poison control center immediately.

Skin Contact

Wash off immediately with plenty of water for at least 15 minutes. Immediate medical attention is required.

Eye Contact	Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Immediate medical attention is required.
Self-Protection of the First Aider	Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.
First Aid Facilities	Eyewash, safety shower and washroom.
Most important symptoms and effects	Causes burns by all exposure routes. Product is a corrosive material. Use of gastric lavage or emesis is contraindicated. Possible perforation of stomach or esophagus should be investigated: Ingestion causes severe swelling, severe damage to the delicate tissue and danger of perforation
Notes to Physician	Treat symptomatically.

Section 5 - Fire Fighting Measures

Suitable Extinguishing Media

Substance is nonflammable; use agent most appropriate to extinguish surrounding fire.

Extinguishing media which must not be used for safety reasons

No information available.

Hazardous Decomposition Products

Hydrogen chloride gas.

Specific Hazards Arising from the Chemical

Corrosive material. Causes burns by all exposure routes. Thermal decomposition can lead to release of irritating gases and vapors.

Special protective equipment and precautions for fire fighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

Section 6 - Accidental Release Measures

Emergency procedures

Use personal protective equipment as required. Ensure adequate ventilation. Evacuate personnel to safe areas. Keep people away from and upwind of spill/leak. Do not get in eyes, on skin, or on clothing.

Environmental Precautions

Should not be released into the environment. See Section 12 for additional Ecological Information.

Methods for Containment and Clean Up

Clean-up methods - small spillage

Soak up with inert absorbent material. Keep in suitable, closed containers for disposal.

Clean-up methods - large spillage

Typically only supplied in small quantities as packaged goods.

If extremely toxic or used in larger quantities ensure a spillage action plan is in place. Evacuate area. Control the source and/or contain the spill if safe and able to do so. Use temporary diking, sand bags, dry sand, earth or proprietary booms/absorbent pads if available. Obtain advice on containment, neutralisation and clean-up from local emergency responders.

Reference to Other Sections

Refer to protective measures listed in Sections 8 and 13.

Section 7 - Handling and Storage

Precautions for Safe Handling

Wear personal protective equipment/face protection. Do not breathe mist/vapors/spray. Do not get in eyes, on skin, or on clothing. Do not ingest. If swallowed then seek immediate medical assistance.

Conditions for Safe Storage, Including any Incompatibilities

Keep containers tightly closed in a dry, cool and well-ventilated place. Corrosives area.

AS/NZS 2243.10:2004, Safety in laboratories - Storage of chemicals

Section 8 - Exposure Controls and Personal Protection

Exposure limits

AUS - Exposure Standards for Atmospheric Contaminants in the Occupational Environment - Guidance Note on the Interpretation of Exposure Standards for Atmospheric Contaminants in the Occupational Environment [NOHSC:3008(1995)]

Adopted National Exposure Standards for Atmospheric Contaminants in the Occupational Environment [NOHSC:1003(1995)] updated in August, 2005. Safe Work Australia **ACGIH** - Threshold Limit Values - Ceiling (TLV-C) guidelines by the American Conference of Governmental Industrial Hygienists (ACGIH) for controlling worker exposure to airborne chemical concentrations in the workplace. **UK** - EH40/2005 Work Exposure Limits, Fourth edition. Published 2020. **DE** - MAK and BAT values of Hazardous Chemical Compounds in the Work Area. Published by German Research Foundation on July 1, 2011

Component	Australia	New Zealand WEL	ACGIH TLV	The United Kingdom	Germany
Hydrochloric acid	Ceiling: 5 ppm Ceiling: 7.5 mg/m ³	Ceiling: 5 ppm Ceiling: 7.5 mg/m ³	Ceiling: 2 ppm	STEL: 5 ppm 15 min STEL: 8 mg/m ³ 15 min TWA: 1 ppm 8 hr TWA: 2 mg/m ³ 8 hr	TWA: 2 ppm (8 Stunden). AGW - exposure factor 2 TWA: 3 mg/m ³ (8 Stunden). AGW - exposure factor 2 TWA: 2 ppm (8 Stunden). MAK TWA: 3.0 mg/m ³ (8 Stunden). MAK Höhepunkt: 4 ppm Höhepunkt: 6 mg/m ³

Biological limit values

This product, as supplied, does not contain any hazardous materials with biological limits established by the region specific regulatory bodies

Exposure Controls**Engineering Measures**

Ensure that eyewash stations and safety showers are close to the workstation location.

Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source

Personal protective equipment**Eye Protection**

Goggles (Australian/New Zealand Standard AS/NZS 1337 - Eye protectors for Industrial applications)

Hand Protection

Protective gloves

Glove material	Breakthrough time	Glove thickness	AUS/NZ Standard	Glove comments
Butyl rubber	> 480 minutes	0.5 mm	AS/NZS 2161	As tested under EN374-3 Determination of Resistance to Permeation by Chemicals
Nitrile rubber	> 480 minutes	0.35 mm		
Neoprene gloves	> 480 minutes	0.5 mm		
Viton (R)	> 480 minutes	0.4 mm		
PVC	> 480 minutes	0.5 mm		

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g.

sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

Skin and body protection	Long sleeved clothing
Respiratory Protection	Use an AS/NZS 1716 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced. To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained in line with AS/NZS 1715 on the use and maintenance of respiratory protective devices
Recommended Filter type:	Particulates filter conforming to EN 143 or Acid gases filter: Type E, Yellow. (or AUS/NZ equivalent)
Recommended half mask:-	Valve filtering: EN405 or Half mask: EN140 plus filter, EN 141 (or AUS/NZ equivalent) When RPE is used a face piece Fit Test should be conducted
Hygiene Measures	Handle in accordance with good industrial hygiene and safety practice.
Environmental exposure controls	No information available.

Section 9 - Physical and Chemical Properties

Information on basic physical and chemical properties

Appearance	Colorless	
Physical State	Liquid	
Odor	pungent	
Odor Threshold	No data available	
pH	< 1	
Melting Point/Range	-35 °C / -31 °F	
Softening Point	No data available	
Boiling Point/Range	57 °C / 135 °F	@ 760 mmHg
Flash Point	No information available	Method - No information available
Evaporation Rate	No data available	
Flammability (solid,gas)	Not applicable	Liquid
Explosion Limits	No data available	
Vapor Pressure	125 mbar @ 20 °C	
Vapor Density	1.27	(Air = 1.0)
Specific Gravity / Density	1.18	
Bulk Density	Not applicable	Liquid
Water Solubility	Miscible	
Solubility in other solvents	No information available	
Partition Coefficient (n-octanol/water)		
Autoignition Temperature	No data available	
Decomposition Temperature	No data available	
Viscosity	1.8 mPa.s @ 15°C	
Explosive Properties	No information available	
Oxidizing Properties	No information available	
Other information		
Molecular Formula	HCl	
Molecular Weight	36.46	

Section 10 - Stability and Reactivity

Reactivity	None known, based on information available
Stability	Stable under normal conditions.

Conditions to Avoid	Incompatible products, Excess heat.
Incompatible Materials	Metals, Strong oxidizing agents, Bases, sodium hypochlorite, Amines, Fluorine, Cyanides, Alkaline.
Hazardous Decomposition Products	Hydrogen chloride gas.
Hazardous Polymerization	Hazardous polymerization does not occur.

Section 11 - Toxicological Information

Information on Toxicological Effects

Product Information

(a) acute toxicity;	
Oral	Based on available data, the classification criteria are not met
Dermal	Based on available data, the classification criteria are not met
Inhalation	Based on available data, the classification criteria are not met

Toxicology data for the components

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
Hydrochloric acid	238 - 277 mg/kg (Rat)	> 5010 mg/kg (Rabbit)	1.68 mg/L (Rat) 1 h
Water	-	-	-

(b) skin corrosion/irritation; Category 1 B

(c) serious eye damage/irritation; Category 1

(d) respiratory or skin sensitization;	
Respiratory	No data available
Skin	No data available

(e) germ cell mutagenicity; No data available

(f) carcinogenicity; No data available
There are no known carcinogenic chemicals in this product

(g) reproductive toxicity; No data available

(h) STOT-single exposure; Category 3
Results / Target organs Respiratory system

(i) STOT-repeated exposure; No data available
Target Organs No information available.

(j) aspiration hazard; No data available

Symptoms / effects, both acute and delayed Product is a corrosive material. Use of gastric lavage or emesis is contraindicated. Possible perforation of stomach or esophagus should be investigated: Ingestion causes severe swelling, severe damage to the delicate tissue and danger of perforation

Section 12 - Ecological Information

Ecotoxicity effects

Do not empty into drains. Large amounts will affect pH and harm aquatic organisms.

Component	Freshwater Fish	Water Flea	Freshwater Algae	Microtox
Hydrochloric acid	282 mg/L LC50 96 h Gambusia affinis mg/L LC50 48 h Leuciscus idus	56mg/L EC50 72h Daphnia	-	-

Persistence and Degradability

Persistence

Persistence is unlikely, based on information available.

Bioaccumulative Potential

Bioaccumulation is unlikely

Mobility

Water. Soluble. Will likely be mobile in the environment due to its water solubility Highly mobile in soils

Endocrine Disruptor Information

This product does not contain any known or suspected endocrine disruptors

Persistent Organic Pollutant

This product does not contain any known or suspected substance

Ozone Depletion Potential

This product does not contain any known or suspected substance

Section 13 - Disposal Considerations

Waste from Residues/Unused Products

Do not allow into drains or watercourses or dispose of where ground or surface waters may be affected. Wastes, including emptied containers, are controlled wastes and should be disposed of in accordance with all federal, E.P.A., state and local regulations. Assure conformity with all applicable regulations.

Contaminated Packaging

Dispose of this container to hazardous or special waste collection point.

Other Information

Chemical wastes should be disposed through a licensed commercial waste collection service. Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains. Do not flush to sewer. Large amounts will affect pH and harm aquatic organisms. Solutions with low pH-value must be neutralized before discharge.

Section 14 - Transport Information

IMDG/IMO

UN-No	UN1789
Proper Shipping Name	Hydrochloric acid
Hazard Class	8
Packing Group	II

ADG

UN-No	UN1789
Proper Shipping Name	Hydrochloric acid
Hazard Class	8
Packing Group	II

Component	Hazchem Code
Hydrochloric acid	2RE
7647-01-0 (35-38)	2R

IATA

UN-No	UN1789
Proper Shipping Name	Hydrochloric acid
Hazard Class	8
Packing Group	II

Environmental hazards	No hazards identified
Special Precautions	No special precautions required
Additional information	None known

Section 15 - Regulatory Information

Safety, health and environmental regulations/legislation specific for the substance or mixture

National Regulations Australia

See section 8 for national exposure control parameters.

Standard for the Uniform Scheduling of Medicines and Poisons

Classified as a scheduled poison according to the Standard for Uniform Scheduling of Medicines and Poisons.

Component	Standard for the Uniform Scheduling of Medicines and Poisons
Hydrochloric acid - 7647-01-0	Schedule 5 listed - except its salts and derivatives; in preparations except: in preparations containing $\leq 0.5\%$ of Hydrochloric acid, or for therapeutic use Schedule 6 listed - except its salts and derivatives; except: when included in Schedule 5, in preparations for therapeutic use, or in preparations containing $\leq 0.5\%$ of Hydrochloric acid

Australian Industrial Chemicals Introduction Scheme (AICIS)

Component	Australian Industrial Chemicals Introduction Scheme (AICIS)	Additional information
Hydrochloric acid - 7647-01-0	Present	-
Water - 7732-18-5	Present	-

Australian - Illicit Drug Precursors/Reagents Substance List

This product contains one or more substance(s) on the Illicit Drug Precursors/Reagents list. Verify requirements related to using, handling and storing these substances.

Chemicals of Security Concern

This product contains one or more substance(s) listed on the voluntary National Code of Practice for Chemicals of Security Concern

Component	Australian - Illicit Drug Precursors/Reagents Substance List	Chemicals of Security Concern
Hydrochloric acid - 7647-01-0	Category 3	Listed in Appendix A

Legend

Category 3 - Chemicals and apparatus that may be used in the illicit production of drugs. Purchases from this list should alert companies or organizations to seek further indicators of any suspicious orders or enquiries. No official reporting is required for items on this list unless considered warranted

Chemicals of Security Concern - for further information see <http://www.chemicalsecurity.gov.au/securityconcerns>

National pollutant inventory Subject to reporting requirements

Component	National pollutant inventory
Hydrochloric acid - 7647-01-0	10 tonne/yr. Threshold category 1 400 tonne/yr. Threshold category 2a 1 tonne/h. Threshold category 2a 2000 tonne/yr. Threshold category 2b 60000 MWH. Threshold category 2b 20 MW. Threshold category 2b

Prohibition or notification/licensing requirements

Shown below are details of specific prohibition/notifications or licensing requirements when they apply.

This product does not contain any substance(s) subject to Prohibition, Authorization or Restriction.

International Inventories

Component	AICS	NZIoC	EINECS	ELINCS	TSCA	DSL	NDSL	PICCS	ENCS	ISHL	IECSC	KECL
Hydrochloric acid	X	X	231-595-7	-	X	X	-	X	X	X	X	KE-20189
Water	X	X	231-791-2	-	X	X	-	X	X		X	KE-35400

Legend: X - Listed. '-' - Not Listed. **KECL** - NIER number or KE number (<http://ncis.nier.go.kr/en/main.do>)

International Regulations

Ozone Depletion Potential This product does not contain any known or suspected substance

Persistent Organic Pollutant This product does not contain any known or suspected substance

Rotterdam Convention (PIC) Not applicable

Basel convention on the control of transboundary movements of hazardous wastes and their disposal

Take note that wastes may be subject to export, import, or transit controls pursuant to the Basel convention and/or local regulations implementing the Basel convention.

Component	Basel Convention (Hazardous Waste)	Australian Hazardous Waste Act - Categories of Wastes to Be Controlled
Hydrochloric acid - 7647-01-0	Annex I - Y34	Y34 solid or solution

Component	CAS No	OECD HPV	Restriction of Hazardous Substances (RoHS)	Seveso III Directive (2012/18/EC) - Qualifying Quantities for Major Accident Notification	Seveso III Directive (2012/18/EC) - Qualifying Quantities for Safety Report Requirements
Hydrochloric acid	7647-01-0	Listed	Not applicable	25 tonne	250 tonne
Water	7732-18-5	Listed	Not applicable	Not applicable	Not applicable

Authorisation/Restrictions according to EU REACH

Component	REACH (1907/2006) - Annex XIV - Substances Subject to Authorization	REACH (1907/2006) - Annex XVII - Restrictions on Certain Dangerous Substances	REACH Regulation (EC 1907/2006) article 59 - Candidate List of Substances of Very High Concern (SVHC)
Hydrochloric acid	-	Use restricted. See item 75. (see link for restriction details)	-

<https://echa.europa.eu/substances-restricted-under-reach>

Section 16 - Other Information**Legend**

AICS - Australian Inventory of Chemical Substances
TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDL - Canadian Domestic Substances List/Non-Domestic Substances List

IECSC - Chinese Inventory of Existing Chemical Substances

PICCS - Philippines Inventory of Chemicals and Chemical Substances

TWA - Time Weighted Average

IARC - International Agency for Research on Cancer

ICAO/IATA - International Civil Aviation Organization/International Air Transport Association

MARPOL - International Convention for the Prevention of Pollution from Ships

NZS 5433:2012 - Transport of Dangerous Goods on Land

LD50 - Lethal Dose 50%

EC50 - Effective Concentration 50%

WEL - Workplace Exposure Limit

DNEL - Derived No Effect Level

POW - Partition coefficient Octanol:Water

vPvB - very Persistent, very Bioaccumulative

VOC - (Volatile Organic Compound)

NZIoC - New Zealand Inventory of Chemicals

EINECS/ELINCS - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

ENCS - Japanese Existing and New Chemical Substances

KECL - Korean Existing and Evaluated Chemical Substances

CAS - Chemical Abstracts Service

ACGIH - American Conference of Governmental Industrial Hygienists
Predicted No Effect Concentration (PNEC)

IMO/IMDG - International Maritime Organization/International Maritime Dangerous Goods Code

ADG Australian Code for the Transport of Dangerous Goods by Road and Rail

OECD - Organisation for Economic Co-operation and Development

LC50 - Lethal Concentration 50%

ATE - Acute Toxicity Estimate

RPE - Respiratory Protective Equipment

NOEC - No Observed Effect Concentration

BCF - Bioconcentration factor

PBT - Persistent, Bioaccumulative, Toxic

Key literature references and sources for data

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

Classification and procedure used to derive the classification for mixtures according to Regulation (EC) 1272/2008 [CLP]: Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

Chemical incident response training.

Revision Date 17-Nov-2022
Revision Summary Not applicable.

**This Safety Data Sheet (SDS) is prepared in accordance to and complies with the requirements of
Safe Work Australia - Work Health and Safety Regulations (WHS Regulations).**

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet