

Australian statement of hazardous nature : Classified as hazardous according to criteria of Safe Work Australia

## Section 1 - Identification

**Product Name** 1,2,4-1H-Triazole

**CAS No** 288-88-0

**Product Code** 139280000; 139280050; 139280250; 139281000; 139285000

**Address** ThermoFisher Scientific Australia Pty Ltd  
 5 Caribbean Drive, Scoresby  
 VICTORIA 3179, Australia

**Emergency Tel.** **CHEMTREC®**  
**03 9757 4559 or +613 9757 4559**

**Telephone / Fax Numbers** Tel: 1300 735 292  
 Fax: 1800 067 639

**E-mail address** ANZinfo@thermofisher.com

**Recommended Use** Laboratory chemicals.

**Uses advised against** This product does not contain any substance(s) on the Illicit Drug Precursors/Reagents list.  
 This product does not contain any substance(s) subject to Prohibition, Authorization or Restriction. This product does not contain any substance(s) listed on the voluntary National Code of Practice for Chemicals of Security Concern.

## Section 2 - Hazard(s) Identification

### Classification under Safe Work Australia

Classified as hazardous according to criteria of Safe Work Australia

**Physical hazards**  
 No hazards identified

### **Health hazards**

Acute Oral Toxicity  
 Serious Eye Damage/Eye Irritation  
 Reproductive Toxicity

Category 4  
 Category 2  
 Category 1B

**Environmental hazards**  
 No hazards identified

### Label Elements



Exclamation Mark



Health Hazard

**Signal Word****Danger****Hazard Statements**

H302 - Harmful if swallowed

H319 - Causes serious eye irritation

H360 - May damage fertility or the unborn child

**Precautionary Statements**

P201 - Obtain special instructions before use

P202 - Do not handle until all safety precautions have been read and understood

P264 - Wash face, hands and any exposed skin thoroughly after handling

P270 - Do not eat, drink or smoke when using this product

P280 - Wear eye protection/ face protection

P280 - Wear protective gloves/protective clothing/eye protection/face protection

P301 + P312 - IF SWALLOWED: Call a POISON CENTER or doctor if you feel unwell

P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing

P308 + P313 - IF exposed or concerned: Get medical advice/attention

P330 - Rinse mouth

P403 - Store in a well-ventilated place

P501 - Dispose of contents/ container to an approved waste disposal plant

**Other information****Section 3 - Composition and Information on Ingredients**

Component	CAS No	Weight %
1H-1,2,4-Triazole	288-88-0	<=100

**Section 4 - First Aid Measures**

<b>Inhalation</b>	Remove to fresh air. If not breathing, give artificial respiration. Get medical attention if symptoms occur.
<b>Ingestion</b>	Clean mouth with water and drink afterwards plenty of water. Get medical attention if symptoms occur.
<b>Skin Contact</b>	Wash off immediately with plenty of water for at least 15 minutes. If skin irritation persists, call a physician.
<b>Eye Contact</b>	Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.
<b>General Advice</b>	If symptoms persist, call a physician.
<b>Self-Protection of the First Aider</b>	Use personal protective equipment as required.
<b>First Aid Facilities</b>	Eyewash, safety shower and washroom.
<b>Most important symptoms and effects</b>	None reasonably foreseeable.
<b>Notes to Physician</b>	Treat symptomatically.

## Section 5 - Fire Fighting Measures

### Suitable Extinguishing Media

Water spray, carbon dioxide (CO<sub>2</sub>), dry chemical, alcohol-resistant foam.

### Extinguishing media which must not be used for safety reasons

No information available.

### Hazardous Decomposition Products

Nitrogen oxides (NO<sub>x</sub>), Carbon monoxide (CO), Carbon dioxide (CO<sub>2</sub>), Hydrogen cyanide (hydrocyanic acid), Ammonia.

### Decomposition Temperature

430 °C

### Specific Hazards Arising from the Chemical

Thermal decomposition can lead to release of irritating gases and vapors.

### Special protective equipment and precautions for fire fighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

## Section 6 - Accidental Release Measures

### Emergency procedures

Use personal protective equipment as required. Ensure adequate ventilation. Avoid dust formation.

### Environmental Precautions

Should not be released into the environment.

### Methods for Containment and Clean Up

#### Clean-up methods - small spillage

Sweep up and shovel into suitable containers for disposal. Keep in suitable, closed containers for disposal.

#### Clean-up methods - large spillage

Typically only supplied in small quantities as packaged goods.

If extremely toxic or used in larger quantities ensure a spillage action plan is in place. Evacuate area. Control the source and/or contain the spill if safe and able to do so. Use temporary diking, sand bags, dry sand, earth or proprietary booms/absorbent pads if available. Obtain advice on containment, neutralisation and clean-up from local emergency responders.

### Reference to Other Sections

Refer to protective measures listed in Sections 8 and 13.

## Section 7 - Handling and Storage

### Precautions for Safe Handling

Wear personal protective equipment/face protection. Ensure adequate ventilation. Do not get in eyes, on skin, or on clothing. Avoid ingestion and inhalation. Avoid dust formation.

### Conditions for Safe Storage, Including any Incompatibilities

Keep containers tightly closed in a dry, cool and well-ventilated place.

AS/NZS 2243.10:2004, Safety in laboratories - Storage of chemicals

## Section 8 - Exposure Controls and Personal Protection

**Exposure limits**

The product does not contain any hazardous materials with occupational exposure limits established.

**Biological limit values**

This product, as supplied, does not contain any hazardous materials with biological limits established by the region specific regulatory bodies

**Exposure Controls****Engineering Measures**

Ensure adequate ventilation, especially in confined areas. Ensure that eyewash stations and safety showers are close to the workstation location.

Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source

**Personal protective equipment****Eye Protection**

Goggles (Australian/New Zealand Standard AS/NZS 1337 - Eye protectors for Industrial applications)

**Hand Protection**

Protective gloves

Glove material	Breakthrough time	Glove thickness	AUS/NZ Standard	Glove comments
Natural rubber	See manufacturers	-	AS/NZS 2161	(minimum requirement)
Nitrile rubber	recommendations			
Neoprene				
PVC				

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatability, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

**Skin and body protection**

Long sleeved clothing

**Respiratory Protection**

Use an AS/NZS 1716 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced. To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained in line with AS/NZS 1715 on the use and maintenance of respiratory protective devices

**Recommended Filter type:**

Particulates filter conforming to EN 143 (or AUS/NZ equivalent)

**Recommended half mask:-**

Particle filtering: EN149:2001 (or AUS/NZ equivalent)

When RPE is used a face piece Fit Test should be conducted

**Hygiene Measures**

Handle in accordance with good industrial hygiene and safety practice.

**Environmental exposure controls**

No information available.

## Section 9 - Physical and Chemical Properties

**Information on basic physical and chemical properties****Appearance**

White

**Physical State**

Solid

**Odor**

No information available

**Odor Threshold**

No data available

**pH**

No information available

<b>Melting Point/Range</b>	119 - 122 °C / 246.2 - 251.6 °F	
<b>Softening Point</b>	No data available	
<b>Boiling Point/Range</b>	260 °C / 500 °F	@ 760 mmHg
<b>Flash Point</b>	140 °C / 284 °F	<b>Method -</b> No information available
<b>Evaporation Rate</b>	Not applicable	Solid
<b>Flammability (solid,gas)</b>	No information available	
<b>Explosion Limits</b>	No data available	
<b>Vapor Pressure</b>	No data available	
<b>Vapor Density</b>	Not applicable	Solid
<b>Specific Gravity / Density</b>	No data available	
<b>Bulk Density</b>	No data available	
<b>Water Solubility</b>	1250 g/L (20°C)	
<b>Solubility in other solvents</b>	No information available	
<b>Partition Coefficient (n-octanol/water)</b>		
<b>Component</b>	<b>log Pow</b>	
1H-1,2,4-Triazole	-0.72	
<b>Autoignition Temperature</b>	490 °C / 914 °F	
<b>Decomposition Temperature</b>	430 °C	
<b>Viscosity</b>	Not applicable	Solid
<b>Explosive Properties</b>	No information available	
<b>Oxidizing Properties</b>	No information available	
<b>Other information</b>		
<b>Molecular Formula</b>	C2 H3 N3	
<b>Molecular Weight</b>	69.06	

## Section 10 - Stability and Reactivity

<b>Reactivity</b>	None known, based on information available
<b>Stability</b>	Stable under normal conditions.
<b>Conditions to Avoid</b>	Incompatible products, Excess heat, Avoid dust formation.
<b>Incompatible Materials</b>	Strong oxidizing agents, Strong acids, Oxidizing agent.
<b>Hazardous Decomposition Products</b>	Nitrogen oxides (NOx). Carbon monoxide (CO). Carbon dioxide (CO <sub>2</sub> ). Hydrogen cyanide (hydrocyanic acid). Ammonia.
<b>Hazardous Polymerization</b>	Hazardous polymerization does not occur.

## Section 11 - Toxicological Information

### Information on Toxicological Effects

#### Product Information

##### (a) acute toxicity;

<b>Oral</b>	Category 4
<b>Dermal</b>	Based on available data, the classification criteria are not met
<b>Inhalation</b>	Based on available data, the classification criteria are not met

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
1H-1,2,4-Triazole	1750 mg/kg (Rat) 1375 mg/kg (Rat)	3129 mg/kg (Rabbit)	

(b) skin corrosion/irritation; No data available

(c) serious eye damage/irritation;	Category 2
(d) respiratory or skin sensitization;	
Respiratory	No data available
Skin	No data available
(e) germ cell mutagenicity;	No data available
(f) carcinogenicity;	No data available
	There are no known carcinogenic chemicals in this product
(g) reproductive toxicity;	Category 1B
(h) STOT-single exposure;	No data available
(i) STOT-repeated exposure;	No data available
Target Organs	None known.
(j) aspiration hazard;	Not applicable
	Solid
Symptoms / effects, both acute and delayed	No information available

## Section 12 - Ecological Information

### Ecotoxicity effects

Component	Freshwater Fish	Water Flea	Freshwater Algae	Microtox
1H-1,2,4-Triazole	LC50 >1000 mg/kg/48h (Leuciscus idus)			EC50 = 5200 mg/L 30 min

Persistence and Degradability	Not readily biodegradable
Persistence	Persistence is unlikely.
Bioaccumulative Potential	Bioaccumulation is unlikely

Component	log Pow	Bioconcentration factor (BCF)
1H-1,2,4-Triazole	-0.72	No data available

Mobility	The product is water soluble, and may spread in water systems. : Will likely be mobile in the environment due to its water solubility Highly mobile in soils
Endocrine Disruptor Information	This product does not contain any known or suspected endocrine disruptors
Persistent Organic Pollutant	This product does not contain any known or suspected substance
Ozone Depletion Potential	This product does not contain any known or suspected substance

## Section 13 - Disposal Considerations

Waste from Residues/Unused Products	Do not allow into drains or watercourses or dispose of where ground or surface waters may be affected. Wastes, including emptied containers, are controlled wastes and should be disposed of in accordance with all federal, E.P.A., state and local regulations. Assure conformity with all applicable regulations.
Contaminated Packaging	Dispose of this container to hazardous or special waste collection point.
Other Information	Chemical wastes should be disposed through a licensed commercial waste collection service. Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains.

## Section 14 - Transport Information

<b>IMDG/IMO</b>	Not regulated
<b>ADG</b>	Not regulated
<b>IATA</b>	Not regulated
<b>Environmental hazards</b>	No hazards identified
<b>Special Precautions</b>	No special precautions required
<b>Additional information</b>	None known

## Section 15 - Regulatory Information

### Safety, health and environmental regulations/legislation specific for the substance or mixture

#### National Regulations                      **Australia**

See section 8 for national exposure control parameters.

#### **Standard for the Uniform Scheduling of Medicines and Poisons**

No poison schedule number allocated.

#### **Australian Industrial Chemicals Introduction Scheme (AICIS)**

Component	Australian Industrial Chemicals Introduction Scheme (AICIS)	Additional information
1H-1,2,4-Triazole - 288-88-0	Present	-

#### **Australian - Illicit Drug Precursors/Reagents Substance List**

This product does not contain any substance(s) on the Illicit Drug Precursors/Reagents list.

#### **Chemicals of Security Concern**

This product does not contain any substance(s) listed on the voluntary National Code of Practice for Chemicals of Security Concern

#### **National pollutant inventory**                      Not applicable

#### **Prohibition or notification/licensing requirements**

Shown below are details of specific prohibition/notifications or licensing requirements when they apply.

This product does not contain any substance(s) subject to Prohibition, Authorization or Restriction.

#### **International Inventories**

Component	AICS	NZIoC	EINECS	ELINCS	TSCA	DSL	NDSL	PICCS	ENCS	ISHL	IECSC	KECL
1H-1,2,4-Triazole	X	X	206-022-9	-	X	X	-	X	X	X	X	KE-34007

**Legend:** X - Listed. '-' - Not Listed. **KECL** - NIER number or KE number (<http://ncis.nier.go.kr/en/main.do>)

### International Regulations

**Ozone Depletion Potential** This product does not contain any known or suspected substance

**Persistent Organic Pollutant** This product does not contain any known or suspected substance

**Rotterdam Convention (PIC)** Not applicable

**Basel convention on the control of transboundary movements of hazardous wastes and their disposal**  
Not applicable.

Component	CAS No	OECD HPV	Restriction of Hazardous Substances (RoHS)	Seveso III Directive (2012/18/EC) - Qualifying Quantities for Major Accident Notification	Seveso III Directive (2012/18/EC) - Qualifying Quantities for Safety Report Requirements
1H-1,2,4-Triazole	288-88-0	Listed	Not applicable	Not applicable	Not applicable

### Authorisation/Restrictions according to EU REACH

Component	REACH (1907/2006) - Annex XIV - Substances Subject to Authorization	REACH (1907/2006) - Annex XVII - Restrictions on Certain Dangerous Substances	REACH Regulation (EC 1907/2006) article 59 - Candidate List of Substances of Very High Concern (SVHC)
1H-1,2,4-Triazole	-	Use restricted. See item 75. (see link for restriction details) Use restricted. See item 30. (see link for restriction details)	-

<https://echa.europa.eu/substances-restricted-under-reach>

## Section 16 - Other Information

### Legend

**AICS** - Australian Inventory of Chemical Substances  
**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory  
**DSL/NDSL** - Canadian Domestic Substances List/Non-Domestic Substances List  
**IECSC** - Chinese Inventory of Existing Chemical Substances  
**PICCS** - Philippines Inventory of Chemicals and Chemical Substances  
**TWA** - Time Weighted Average  
**IARC** - International Agency for Research on Cancer  
**ICAO/IATA** - International Civil Aviation Organization/International Air Transport Association  
**MARPOL** - International Convention for the Prevention of Pollution from Ships  
**NZS 5433:2012** - Transport of Dangerous Goods on Land  
**LD50** - Lethal Dose 50%

**NZIoC** - New Zealand Inventory of Chemicals  
**EINECS/ELINCS** - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances  
**ENCS** - Japanese Existing and New Chemical Substances  
**KECL** - Korean Existing and Evaluated Chemical Substances  
**CAS** - Chemical Abstracts Service  
**ACGIH** - American Conference of Governmental Industrial Hygienists  
**PNEC** - Predicted No Effect Concentration (PNEC)  
**IMO/IMDG** - International Maritime Organization/International Maritime Dangerous Goods Code  
**ADG** - Australian Code for the Transport of Dangerous Goods by Road and Rail  
**OECD** - Organisation for Economic Co-operation and Development  
**LC50** - Lethal Concentration 50%



**EC50** - Effective Concentration 50%  
**WEL** - Workplace Exposure Limit  
**DNEL** - Derived No Effect Level  
**POW** - Partition coefficient Octanol:Water  
**vPvB** - very Persistent, very Bioaccumulative  
**VOC** - (Volatile Organic Compound)

**ATE** - Acute Toxicity Estimate  
**RPE** - Respiratory Protective Equipment  
**NOEC** - No Observed Effect Concentration  
**BCF** - Bioconcentration factor  
**PBT** - Persistent, Bioaccumulative, Toxic

**Key literature references and sources for data**

<https://echa.europa.eu/information-on-chemicals>  
Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

**Training Advice**

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

**Revision Date** 17-Nov-2022  
**Revision Summary** SDS sections updated.

**This Safety Data Sheet (SDS) is prepared in accordance to and complies with the requirements of Safe Work Australia - Work Health and Safety Regulations (WHS Regulations).**

**Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

## End of Safety Data Sheet