

SECTION 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

1.1. Product identifier

Product Description:	4-Nitroimidazole
Cat No. :	161600000; 161600250; 161601000
Synonyms	4-Nitro-1H-Imidazole.
CAS No	3034-38-6
Molecular Formula	C3 H3 N3 O2

1.2. Relevant identified uses of the substance or mixture and uses advised against

Recommended Use	Laboratory chemicals.
Uses advised against	No Information available

1.3. Details of the supplier of the safety data sheet

Company

EU entity/business name
Thermo Fisher Scientific
Janssen Pharmaceuticaaan 3a, 2440 Geel, Belgium

UK entity/business name
Fisher Scientific UK
Bishop Meadow Road,
Loughborough, Leicestershire LE11 5RG, United Kingdom

Swiss distributor - Fisher Scientific AG
Neuhofstrasse 11, CH 4153 Reinach
Tel: +41 (0) 56 618 41 11
e-mail - infoch@thermofisher.com

E-mail address begel.sdsdesk@thermofisher.com

1.4. Emergency telephone number

For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11
Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99
CHEMTREC Tel. No.**US**:001-800-424-9300 / **Europe**:001-703-527-3887

customers in Switzerland:
Tox Info Suisse Emergency Number: **145 (24hr)**
Tox Info Suisse: +41-44 251 51 51 (Emergency number from abroad)
Chemtrec (24h) Toll-Free: 0800 564 402
Chemtrec Local: +41-43 508 20 11 (Zurich)

SECTION 2: HAZARDS IDENTIFICATION

2.1. Classification of the substance or mixture

SAFETY DATA SHEET

4-Nitroimidazole

Revision Date 22-Sep-2023

CLP Classification - Regulation (EC) No 1272/2008

Physical hazards

Based on available data, the classification criteria are not met

Health hazards

Acute oral toxicity	Category 4 (H302)
Skin Corrosion/Irritation	Category 2 (H315)
Serious Eye Damage/Eye Irritation	Category 2 (H319)
Specific target organ toxicity - (single exposure)	Category 3 (H335)

Environmental hazards

Based on available data, the classification criteria are not met

Full text of Hazard Statements: see section 16

2.2. Label elements



Signal Word

Warning

Hazard Statements

H302 - Harmful if swallowed
H319 - Causes serious eye irritation
H315 - Causes skin irritation
H335 - May cause respiratory irritation

Precautionary Statements

P261 - Avoid breathing dust/fume/gas/mist/vapors/spray
P301 + P312 - IF SWALLOWED: Call a POISON CENTER or doctor/physician if you feel unwell
P302 + P352 - IF ON SKIN: Wash with plenty of soap and water
P280 - Wear protective gloves/protective clothing/eye protection/face protection
P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing

2.3. Other hazards

This product does not contain any known or suspected endocrine disruptors

SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS

3.1. Substances

Component	CAS No	EC No	Weight %	CLP Classification - Regulation (EC) No 1272/2008
-----------	--------	-------	----------	---

ACR16160

SAFETY DATA SHEET

4-Nitroimidazole

Revision Date 22-Sep-2023

1H-Imidazole, 4-nitro-	3034-38-6	EEC No. 221-224-7	98	STOT SE 3 (H335) Skin Irrit. 2 (H315) Eye Irrit. 2 (H319) Acute Tox. 4 (H302)
------------------------	-----------	-------------------	----	--

Full text of Hazard Statements: see section 16

SECTION 4: FIRST AID MEASURES

4.1. Description of first aid measures

Eye Contact	Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.
Skin Contact	Wash off immediately with soap and plenty of water while removing all contaminated clothes and shoes. Get medical attention.
Ingestion	Clean mouth with water. Get medical attention.
Inhalation	Remove from exposure, lie down. Remove to fresh air. If not breathing, give artificial respiration. Get medical attention.
Self-Protection of the First Aider	Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

4.2. Most important symptoms and effects, both acute and delayed

No information available.

4.3. Indication of any immediate medical attention and special treatment needed

Notes to Physician Treat symptomatically.

SECTION 5: FIREFIGHTING MEASURES

5.1. Extinguishing media

Suitable Extinguishing Media

Water spray. Carbon dioxide (CO₂). Dry chemical. Chemical foam.

Extinguishing media which must not be used for safety reasons

No information available.

5.2. Special hazards arising from the substance or mixture

Thermal decomposition can lead to release of irritating gases and vapors.

Hazardous Combustion Products

Nitrogen oxides (NO_x), Carbon monoxide (CO), Carbon dioxide (CO₂).

5.3. Advice for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

SAFETY DATA SHEET

4-Nitroimidazole

Revision Date 22-Sep-2023

SECTION 6: ACCIDENTAL RELEASE MEASURES

6.1. Personal precautions, protective equipment and emergency procedures

Ensure adequate ventilation.

6.2. Environmental precautions

See Section 12 for additional Ecological Information.

6.3. Methods and material for containment and cleaning up

Sweep up and shovel into suitable containers for disposal.

6.4. Reference to other sections

Refer to protective measures listed in Sections 8 and 13.

SECTION 7: HANDLING AND STORAGE

7.1. Precautions for safe handling

Avoid contact with skin and eyes. Do not breathe dust.

Hygiene Measures

Handle in accordance with good industrial hygiene and safety practice. Keep away from food, drink and animal feeding stuffs. Do not eat, drink or smoke when using this product. Remove and wash contaminated clothing and gloves, including the inside, before re-use. Wash hands before breaks and after work.

7.2. Conditions for safe storage, including any incompatibilities

Keep in a dry, cool and well-ventilated place. Keep container tightly closed.

Technical Rules for Hazardous Substances (TRGS) 510
Storage Class (LGK) (Germany)

Storage Class/LGK 11

Switzerland - Storage of hazardous substances

Storage class - SC 11/13
<https://www.kvu.ch/de/themen/stoffe-und-produkte>
<https://www.kvu.ch/fr/themes/substances-et-produits>
<https://www.kvu.ch/it/temi/sostanze-e-prodotti>

7.3. Specific end use(s)

Use in laboratories

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1. Control parameters

Exposure limits

This product, as supplied, does not contain any hazardous materials with occupational exposure limits established by the region specific regulatory bodies

SAFETY DATA SHEET

4-Nitroimidazole

Revision Date 22-Sep-2023

Biological limit values

This product, as supplied, does not contain any hazardous materials with biological limits established by the region specific regulatory bodies

Monitoring methods

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents.

MDHS14/3 General methods for sampling and gravimetric analysis of respirable and inhalable dust

Derived No Effect Level (DNEL) / Derived Minimum Effect Level (DMEL)

No information available

Predicted No Effect Concentration (PNEC)

No information available.

8.2. Exposure controls

Engineering Measures

Ensure adequate ventilation, especially in confined areas. Ensure that eyewash stations and safety showers are close to the workstation location.

Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source

Personal protective equipment

Eye Protection

Goggles (European standard - EN 166)

Hand Protection

Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Nitrile rubber Neoprene Natural rubber PVC	See manufacturers recommendations	-	EN 374	(minimum requirement)

Skin and body protection

Wear appropriate protective gloves and clothing to prevent skin exposure.

Inspect gloves before use. observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information) gloves are suitable for the task: Chemical compatability, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion. gloves with care avoiding skin contamination.

Respiratory Protection

No protective equipment is needed under normal use conditions.

Large scale/emergency use

Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced

SAFETY DATA SHEET

4-Nitroimidazole

Revision Date 22-Sep-2023

Small scale/Laboratory use Maintain adequate ventilation

Environmental exposure controls No information available.

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

9.1. Information on basic physical and chemical properties

Physical State	Powder Solid	
Appearance	Off-white	
Odor	Odorless	
Odor Threshold	No data available	
Melting Point/Range	303 °C / 577.4 °F	
Softening Point	No data available	
Boiling Point/Range	No information available	
Flammability (liquid)	Not applicable	Solid
Flammability (solid,gas)	No information available	
Explosion Limits	No data available	
Flash Point	> 200 °C / > 392 °F	Method - No information available
Autoignition Temperature	Not applicable	
Decomposition Temperature	303 °C	
pH	No information available	
Viscosity	Not applicable	Solid
Water Solubility	slightly soluble in water	
Solubility in other solvents	No information available	
Partition Coefficient (n-octanol/water)		
Vapor Pressure	No data available	
Density / Specific Gravity	No data available	
Bulk Density	No data available	
Vapor Density	Not applicable	Solid
Particle characteristics	No data available	

9.2. Other information

Molecular Formula	C3 H3 N3 O2
Molecular Weight	113.08
Evaporation Rate	Not applicable - Solid

SECTION 10: STABILITY AND REACTIVITY

10.1. Reactivity
None known, based on information available

10.2. Chemical stability
Stable under normal conditions.

10.3. Possibility of hazardous reactions

Hazardous Polymerization No information available.
Hazardous Reactions No information available.

10.4. Conditions to avoid
Incompatible products.

SAFETY DATA SHEET

4-Nitroimidazole

Revision Date 22-Sep-2023

10.5. Incompatible materials

Strong oxidizing agents.

10.6. Hazardous decomposition products

Nitrogen oxides (NOx). Carbon monoxide (CO). Carbon dioxide (CO₂).

SECTION 11: TOXICOLOGICAL INFORMATION

11.1. Information on hazard classes as defined in Regulation (EC) No 1272/2008

Product Information

(a) acute toxicity;

Oral

Category 4

Dermal

No data available

Inhalation

No data available

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
1H-Imidazole, 4-nitro-	LD50 = 600 mg/kg (Rat)	-	-

(b) skin corrosion/irritation;

Category 2

(c) serious eye damage/irritation;

Category 2

(d) respiratory or skin sensitization;

Respiratory

No data available

Skin

No data available

(e) germ cell mutagenicity;

No data available

(f) carcinogenicity;

No data available

There are no known carcinogenic chemicals in this product

(g) reproductive toxicity;

No data available

(h) STOT-single exposure;

Category 3

Results / Target organs

Respiratory system.

(i) STOT-repeated exposure;

No data available

Target Organs

No information available.

(j) aspiration hazard;

Not applicable

Solid

Other Adverse Effects

The toxicological properties have not been fully investigated.

Symptoms / effects, both acute and delayed

No information available.

SAFETY DATA SHEET

4-Nitroimidazole

Revision Date 22-Sep-2023

11.2. Information on other hazards

Endocrine Disrupting Properties Assess endocrine disrupting properties for human health. This product does not contain any known or suspected endocrine disruptors.

SECTION 12: ECOLOGICAL INFORMATION

12.1. Toxicity

Ecotoxicity effects Contains no substances known to be hazardous to the environment or that are not degradable in waste water treatment plants.

12.2. Persistence and degradability

Persistence Soluble in water, Persistence is unlikely, based on information available.

12.3. Bioaccumulative potential

Bioaccumulation is unlikely

12.4. Mobility in soil

The product is water soluble, and may spread in water systems Will likely be mobile in the environment due to its water solubility. Highly mobile in soils

12.5. Results of PBT and vPvB assessment

No data available for assessment.

12.6. Endocrine disrupting properties

Endocrine Disruptor Information This product does not contain any known or suspected endocrine disruptors

12.7. Other adverse effects

Persistent Organic Pollutant This product does not contain any known or suspected substance
Ozone Depletion Potential This product does not contain any known or suspected substance

SECTION 13: DISPOSAL CONSIDERATIONS

13.1. Waste treatment methods

Waste from Residues/Unused Products Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.

Contaminated Packaging Dispose of this container to hazardous or special waste collection point.

European Waste Catalogue (EWC) According to the European Waste Catalog, Waste Codes are not product specific, but application specific.

Other Information Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains.

Switzerland - Waste Ordinance Disposal should be in accordance with applicable regional, national and local laws and regulations. Ordinance on the Avoidance and the Disposal of Waste (Waste Ordinance, ADWO) SR 814.600
<https://www.fedlex.admin.ch/eli/cc/2015/891/en>

SAFETY DATA SHEET

4-Nitroimidazole

Revision Date 22-Sep-2023

SECTION 14: TRANSPORT INFORMATION

IMDG/IMO Not regulated

14.1. UN number
14.2. UN proper shipping name
14.3. Transport hazard class(es)
14.4. Packing group

ADR Not regulated

14.1. UN number
14.2. UN proper shipping name
14.3. Transport hazard class(es)
14.4. Packing group

IATA Not regulated

14.1. UN number
14.2. UN proper shipping name
14.3. Transport hazard class(es)
14.4. Packing group

14.5. Environmental hazards No hazards identified

14.6. Special precautions for user No special precautions required.

14.7. Maritime transport in bulk according to IMO instruments Not applicable, packaged goods

SECTION 15: REGULATORY INFORMATION

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

International Inventories

Europe (EINECS/ELINCS/NLP), China (IECSC), Taiwan (TCSI), Korea (KECL), Japan (ENCS), Japan (ISHL), Canada (DSL/NDSL), Australia (AICS), New Zealand (NZIoC), Philippines (PICCS). US EPA (TSCA) - Toxic Substances Control Act, (40 CFR Part 710)

Component	CAS No	EINECS	ELINCS	NLP	IECSC	TCSI	KECL	ENCS	ISHL
1H-Imidazole, 4-nitro-	3034-38-6	221-224-7	-	-	-	X	-	-	X

Component	CAS No	TSCA	TSCA Inventory notification - Active-Inactive	DSL	NDSL	AICS	NZIoC	PICCS
1H-Imidazole, 4-nitro-	3034-38-6	X	ACTIVE	-	X	-	-	X

Legend: X - Listed '-' - Not Listed

KECL - NIER number or KE number (<http://ncis.nier.go.kr/en/main.do>)

Authorisation/Restrictions according to EU REACH Not applicable

Component	CAS No	REACH (1907/2006) - Annex XIV - Substances Subject to Authorization	REACH (1907/2006) - Annex XVII - Restrictions on Certain Dangerous Substances	REACH Regulation (EC 1907/2006) article 59 - Candidate List of Substances of Very High Concern (SVHC)
1H-Imidazole, 4-nitro-	3034-38-6	-	-	-

SAFETY DATA SHEET

4-Nitroimidazole

Revision Date 22-Sep-2023

Seveso III Directive (2012/18/EC)

Component	CAS No	Seveso III Directive (2012/18/EC) - Qualifying Quantities for Major Accident Notification	Seveso III Directive (2012/18/EC) - Qualifying Quantities for Safety Report Requirements
1H-Imidazole, 4-nitro-	3034-38-6	Not applicable	Not applicable

Regulation (EC) No 649/2012 of the European Parliament and of the Council of 4 July 2012 concerning the export and import of dangerous chemicals

Not applicable

Contains component(s) that meet a 'definition' of per & poly fluoroalkyl substance (PFAS)?

Not applicable

Take note of Directive 98/24/EC on the protection of the health and safety of workers from the risks related to chemical agents at work .

National Regulations

UK - Take note of Control of Substances Hazardous to Health Regulations (COSHH) 2002 and 2005 Amendment

WGK Classification Water endangering class = 3 (self classification)

Swiss Regulations

Article 4 para. 4 of the Ordinance on the protection of young people in the workplace (SR 822.115) and Article 1 lit. f of the EAER regulation on hazardous work and young people (SR 822.115.2).

Take note on Article 13 Maternity Ordinance (SR 822.111.52) with regards expectant and nursing mothers.

15.2. Chemical safety assessment

A Chemical Safety Assessment/Report (CSA/CSR) has not been conducted

SECTION 16: OTHER INFORMATION

Full text of H-Statements referred to under sections 2 and 3

H302 - Harmful if swallowed

H315 - Causes skin irritation

H319 - Causes serious eye irritation

H335 - May cause respiratory irritation

Legend

CAS - Chemical Abstracts Service

EINECS/ELINCS - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

PICCS - Philippines Inventory of Chemicals and Chemical Substances

IECSC - Chinese Inventory of Existing Chemical Substances

KECL - Korean Existing and Evaluated Chemical Substances

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDL - Canadian Domestic Substances List/Non-Domestic Substances List

ENCS - Japanese Existing and New Chemical Substances

AICS - Australian Inventory of Chemical Substances

NZIoC - New Zealand Inventory of Chemicals

WEL - Workplace Exposure Limit

ACGIH - American Conference of Governmental Industrial Hygienists

TWA - Time Weighted Average

IARC - International Agency for Research on Cancer

SAFETY DATA SHEET

4-Nitroimidazole

Revision Date 22-Sep-2023

DNEL - Derived No Effect Level
RPE - Respiratory Protective Equipment
LC50 - Lethal Concentration 50%
NOEC - No Observed Effect Concentration
PBT - Persistent, Bioaccumulative, Toxic

Predicted No Effect Concentration (PNEC)
LD50 - Lethal Dose 50%
EC50 - Effective Concentration 50%
POW - Partition coefficient Octanol:Water
vPvB - very Persistent, very Bioaccumulative

ADR - European Agreement Concerning the International Carriage of Dangerous Goods by Road
IMO/IMDG - International Maritime Organization/International Maritime Dangerous Goods Code
OECD - Organisation for Economic Co-operation and Development
BCF - Bioconcentration factor

ICAO/IATA - International Civil Aviation Organization/International Air Transport Association
MARPOL - International Convention for the Prevention of Pollution from Ships
ATE - Acute Toxicity Estimate
VOC - (volatile organic compound)

Key literature references and sources for data

<https://echa.europa.eu/information-on-chemicals>
Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

Revision Date 22-Sep-2023
Revision Summary Not applicable.

This safety data sheet complies with the requirements of Regulation (EC) No. 1907/2006. COMMISSION REGULATION (EU) 2020/878 amending Annex II to Regulation (EC) No 1907/2006 .

For Switzerland - Compiled in accordance with the technical provisions referred to in Annex 2, Number 3, ChemO (SR 813.11 - Ordinance on Protection against Dangerous Substances and Preparations).

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet