

Creation Date 22-Oct-2009

Revision Date 11-Dec-2020

Revision Number 5

SECTION 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

1.1. Product identifier

Product Description: Methyl cellulose, viscosity 15 cP (2% solution in water)
Cat No. : 182310000; 182310010; 182311000; 182312500
CAS-No 9004-67-5

1.2. Relevant identified uses of the substance or mixture and uses advised against

Recommended Use Laboratory chemicals.
Uses advised against No Information available

1.3. Details of the supplier of the safety data sheet

Company **UK entity/business name**
Fisher Scientific UK
Bishop Meadow Road, Loughborough,
Leicestershire LE11 5RG, United Kingdom

EU entity/business name
Acros Organics BVBA
Janssen Pharmaceuticaaan 3a
2440 Geel, Belgium

E-mail address begel.sdsdesk@thermofisher.com

1.4. Emergency telephone number

For information **US** call: 001-800-ACROS-01 / **Europe** call: +32 14 57 52 11
Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99
CHEMTREC Tel. No.**US**:001-800-424-9300 / **Europe**:001-703-527-3887

SECTION 2: HAZARDS IDENTIFICATION

2.1. Classification of the substance or mixture

CLP Classification - Regulation (EC) No 1272/2008

Not hazardous

Physical hazards

Based on available data, the classification criteria are not met

Health hazards

Based on available data, the classification criteria are not met

Environmental hazards

SAFETY DATA SHEET

Methyl cellulose, viscosity 15 cP (2% solution in water)

Revision Date 11-Dec-2020

Based on available data, the classification criteria are not met

Full text of Hazard Statements: see section 16

2.2. Label elements

None required

2.3. Other hazards

SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS

3.1. Substances

Component	CAS-No	EC-No.	Weight %	CLP Classification - Regulation (EC) No 1272/2008
Methylcellulose	9004-67-5		>95	-

Full text of Hazard Statements: see section 16

SECTION 4: FIRST AID MEASURES

4.1. Description of first aid measures

Eye Contact	Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.
Skin Contact	Wash off immediately with plenty of water for at least 15 minutes. Get medical attention immediately if symptoms occur.
Ingestion	Clean mouth with water and drink afterwards plenty of water. Get medical attention if symptoms occur.
Inhalation	Remove to fresh air. Get medical attention immediately if symptoms occur.
Self-Protection of the First Aider	No special precautions required.

4.2. Most important symptoms and effects, both acute and delayed

None reasonably foreseeable.

4.3. Indication of any immediate medical attention and special treatment needed

Notes to Physician Treat symptomatically.

SAFETY DATA SHEET

Methyl cellulose, viscosity 15 cP (2% solution in water)

Revision Date 11-Dec-2020

SECTION 5: FIREFIGHTING MEASURES

5.1. Extinguishing media

Suitable Extinguishing Media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment. Water spray, carbon dioxide (CO₂), dry chemical, alcohol-resistant foam.

Extinguishing media which must not be used for safety reasons

No information available.

5.2. Special hazards arising from the substance or mixture

Thermal decomposition can lead to release of irritating gases and vapors.

Hazardous Combustion Products

None under normal use conditions.

5.3. Advice for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

SECTION 6: ACCIDENTAL RELEASE MEASURES

6.1. Personal precautions, protective equipment and emergency procedures

Ensure adequate ventilation. Use personal protective equipment as required. Avoid dust formation.

6.2. Environmental precautions

Should not be released into the environment.

6.3. Methods and material for containment and cleaning up

Sweep up and shovel into suitable containers for disposal. Avoid dust formation.

6.4. Reference to other sections

Refer to protective measures listed in Sections 8 and 13.

SECTION 7: HANDLING AND STORAGE

7.1. Precautions for safe handling

Wear personal protective equipment/face protection. Ensure adequate ventilation. Avoid contact with skin, eyes or clothing. Avoid ingestion and inhalation. Avoid dust formation.

Hygiene Measures

Handle in accordance with good industrial hygiene and safety practice. Keep away from food, drink and animal feeding stuffs. Do not eat, drink or smoke when using this product. Remove and wash contaminated clothing and gloves, including the inside, before re-use. Wash hands before breaks and after work.

7.2. Conditions for safe storage, including any incompatibilities

Keep containers tightly closed in a dry, cool and well-ventilated place. Protect from moisture.

SAFETY DATA SHEET

Methyl cellulose, viscosity 15 cP (2% solution in water)

Revision Date 11-Dec-2020

Technical Rules for Hazardous Substances (TRGS) 510 Storage Class (LGK)
(Germany)

Class 11

7.3. Specific end use(s)

Use in laboratories

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1. Control parameters

Exposure limits

List source(s):

Biological limit values

This product, as supplied, does not contain any hazardous materials with biological limits established by the region specific regulatory bodies

Monitoring methods

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents.

MDHS14/3 General methods for sampling and gravimetric analysis of respirable and inhalable dust

Derived No Effect Level (DNEL) No information available

<u>Route of exposure</u>	Acute effects (local)	Acute effects (systemic)	Chronic effects (local)	Chronic effects (systemic)
Oral Dermal Inhalation				

Predicted No Effect Concentration (PNEC) No information available.

8.2. Exposure controls

Engineering Measures

None under normal use conditions.

Personal protective equipment

Eye Protection

Wear safety glasses with side shields (or goggles) (European standard - EN 166)

Hand Protection

Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Natural rubber	See manufacturers	-	EN 374	(minimum requirement)
Nitrile rubber	recommendations			
Neoprene				
PVC				

Skin and body protection

Wear appropriate protective gloves and clothing to prevent skin exposure

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

SAFETY DATA SHEET

Methyl cellulose, viscosity 15 cP (2% solution in water)

Revision Date 11-Dec-2020

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

Respiratory Protection

No protective equipment is needed under normal use conditions.

Large scale/emergency use

Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced

Recommended Filter type: Particle filter 2

Small scale/Laboratory use

Maintain adequate ventilation

Environmental exposure controls

No information available.

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

9.1. Information on basic physical and chemical properties

Physical State	Solid	
Appearance		
Odor	Odorless	
Odor Threshold	No data available	
Melting Point/Range	No data available	
Softening Point	No data available	
Boiling Point/Range	No information available	
Flammability (liquid)	Not applicable	Solid
Flammability (solid,gas)	No information available	
Explosion Limits	No data available	
Flash Point	No information available	Method - No information available
Autoignition Temperature	No data available	
Decomposition Temperature	No data available	
pH	5.5-8.0	1% aq.sol
Viscosity	Not applicable	Solid
Water Solubility	Soluble	
Solubility in other solvents	No information available	
Partition Coefficient (n-octanol/water)		
Vapor Pressure	No data available	
Density / Specific Gravity	No data available	
Bulk Density	No data available	
Vapor Density	Not applicable	Solid
Particle characteristics	No data available	

9.2. Other information

Evaporation Rate Not applicable - Solid

SECTION 10: STABILITY AND REACTIVITY

10.1. Reactivity

None known, based on information available

10.2. Chemical stability

SAFETY DATA SHEET

Methyl cellulose, viscosity 15 cP (2% solution in water)

Revision Date 11-Dec-2020

Hygroscopic.

10.3. Possibility of hazardous reactions

Hazardous Polymerization Hazardous polymerization does not occur.
Hazardous Reactions None under normal processing.

10.4. Conditions to avoid

Incompatible products. Excess heat. Avoid dust formation. Exposure to moist air or water.

10.5. Incompatible materials

Strong oxidizing agents.

10.6. Hazardous decomposition products

None under normal use conditions.

SECTION 11: TOXICOLOGICAL INFORMATION

11.1. Information on hazard classes as defined in Regulation (EC) No 1272/2008

Product Information See actual entry in RTECS for complete information.

(a) acute toxicity;
Oral No data available
Dermal No data available
Inhalation No data available

Toxicology data for the components

(b) skin corrosion/irritation; No data available

(c) serious eye damage/irritation; No data available

(d) respiratory or skin sensitization;
Respiratory No data available
Skin No data available

(e) germ cell mutagenicity; No data available

(f) carcinogenicity; No data available
There are no known carcinogenic chemicals in this product

(g) reproductive toxicity; No data available

(h) STOT-single exposure; No data available

(i) STOT-repeated exposure; No data available
Target Organs No information available.

(j) aspiration hazard; Not applicable

SAFETY DATA SHEET

Methyl cellulose, viscosity 15 cP (2% solution in water)

Revision Date 11-Dec-2020

Solid

Other Adverse Effects The toxicological properties have not been fully investigated.

Symptoms / effects, both acute and delayed No information available.

11.2. Information on other hazards

Endocrine Disrupting Properties Assess endocrine disrupting properties for human health. This product does not contain any known or suspected endocrine disruptors.

SECTION 12: ECOLOGICAL INFORMATION

12.1. Toxicity

Ecotoxicity effects Do not empty into drains. .

Component	Freshwater Fish	Water Flea	Freshwater Algae
Methylcellulose	Oryzias latipes: LC50: >1000 mg/L/48h		

12.2. Persistence and degradability

Persistence Soluble in water, Persistence is unlikely, based on information available.

12.3. Bioaccumulative potential Bioaccumulation is unlikely

12.4. Mobility in soil

The product is water soluble, and may spread in water systems. Will likely be mobile in the environment due to its water solubility. Highly mobile in soils

12.5. Results of PBT and vPvB assessment

No data available for assessment.

12.6. Endocrine disrupting properties

Endocrine Disruptor Information This product does not contain any known or suspected endocrine disruptors

12.7. Other adverse effects

Persistent Organic Pollutant This product does not contain any known or suspected substance
Ozone Depletion Potential This product does not contain any known or suspected substance

SECTION 13: DISPOSAL CONSIDERATIONS

13.1. Waste treatment methods

Waste from Residues/Unused Products Chemical waste generators must determine whether a discarded chemical is classified as a hazardous waste. Consult local, regional, and national hazardous waste regulations to ensure complete and accurate classification.

Contaminated Packaging Empty remaining contents. Dispose of in accordance with local regulations. Do not re-use empty containers.

European Waste Catalogue (EWC) According to the European Waste Catalog, Waste Codes are not product specific, but

SAFETY DATA SHEET

Methyl cellulose, viscosity 15 cP (2% solution in water)

Revision Date 11-Dec-2020

Other Information application specific.
Waste codes should be assigned by the user based on the application for which the product was used.

SECTION 14: TRANSPORT INFORMATION

IMDG/IMO Not regulated

- 14.1. UN number**
- 14.2. UN proper shipping name**
- 14.3. Transport hazard class(es)**
- 14.4. Packing group**

ADR Not regulated

- 14.1. UN number**
- 14.2. UN proper shipping name**
- 14.3. Transport hazard class(es)**
- 14.4. Packing group**

IATA Not regulated

- 14.1. UN number**
- 14.2. UN proper shipping name**
- 14.3. Transport hazard class(es)**
- 14.4. Packing group**

14.5. Environmental hazards No hazards identified

14.6. Special precautions for user No special precautions required

14.7. Maritime transport in bulk according to IMO instruments Not applicable, packaged goods

SECTION 15: REGULATORY INFORMATION

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

International Inventories

X = listed, Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), China (IECSC), Japan (ENCS), Australia (AICS), Korea (ECL).

Component	EINECS	ELINCS	NLP	TSCA	DSL	NDSL	PICCS	ENCS	IECSC	AICS	KECL
Methylcellulose	-	-		X	X	-	X	X	X	X	KE-0536 9

Regulation (EC) No 649/2012 of the European Parliament and of the Council of 4 July 2012 concerning the export and import of dangerous chemicals
Not applicable

National Regulations

WGK Classification See table for values

Component	Germany - Water Classification (VwVwS)	Germany - TA-Luft Class
Methylcellulose	WGK1	

SAFETY DATA SHEET

Methyl cellulose, viscosity 15 cP (2% solution in water)

Revision Date 11-Dec-2020

UK - Take note of Control of Substances Hazardous to Health Regulations (COSHH) 2002 and 2005 Amendment

15.2. Chemical safety assessment

Chemical Safety Assessment/Reports (CSA/CSR) are not required for mixtures

SECTION 16: OTHER INFORMATION

Full text of H-Statements referred to under sections 2 and 3

Legend

CAS - Chemical Abstracts Service

EINECS/ELINCS - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

PICCS - Philippines Inventory of Chemicals and Chemical Substances

IECSC - Chinese Inventory of Existing Chemical Substances

KECL - Korean Existing and Evaluated Chemical Substances

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDL - Canadian Domestic Substances List/Non-Domestic Substances List

ENCS - Japanese Existing and New Chemical Substances

AICS - Australian Inventory of Chemical Substances

NZIoC - New Zealand Inventory of Chemicals

WEL - Workplace Exposure Limit

ACGIH - American Conference of Governmental Industrial Hygienists

DNEL - Derived No Effect Level

RPE - Respiratory Protective Equipment

LC50 - Lethal Concentration 50%

NOEC - No Observed Effect Concentration

PBT - Persistent, Bioaccumulative, Toxic

TWA - Time Weighted Average

IARC - International Agency for Research on Cancer Predicted No Effect Concentration (PNEC)

LD50 - Lethal Dose 50%

EC50 - Effective Concentration 50%

POW - Partition coefficient Octanol:Water

vPvB - very Persistent, very Bioaccumulative

ADR - European Agreement Concerning the International Carriage of Dangerous Goods by Road

IMO/IMDG - International Maritime Organization/International Maritime Dangerous Goods Code

OECD - Organisation for Economic Co-operation and Development

BCF - Bioconcentration factor

Key literature references and sources for data

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

ICAO/IATA - International Civil Aviation Organization/International Air Transport Association

MARPOL - International Convention for the Prevention of Pollution from Ships

ATE - Acute Toxicity Estimate

VOC (volatile organic compound)

Classification and procedure used to derive the classification for mixtures according to Regulation (EC) 1272/2008 [CLP]:

Physical hazards On basis of test data

Health Hazards Calculation method

Environmental hazards Calculation method

Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Creation Date 22-Oct-2009

Revision Date 11-Dec-2020

Revision Summary Update to CLP Format.

**This safety data sheet complies with the requirements of Regulation (EC) No. 1907/2006
COMMISSION REGULATION (EU) 2020/878 amending Annex II to Regulation (EC) No
1907/2006**

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the

SAFETY DATA SHEET

Methyl cellulose, viscosity 15 cP (2% solution in water)

Revision Date 11-Dec-2020

date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet