

Creation Date 27-Jul-2010

Revision Date 06-Oct-2023

Revision Number 8

SECTION 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

1.1. Product identifier

Product Description:	<u>Magnesium sulfate, anhydrous</u>
Cat No. :	413480000; 413480025; 413480050; 413480250; 413485000
Synonyms	Epsom salts.; Magnesium sulfate
CAS No	7487-88-9
EC No	231-298-2
Molecular Formula	Mg O4 S

1.2. Relevant identified uses of the substance or mixture and uses advised against

Recommended Use	Laboratory chemicals.
Uses advised against	No Information available

1.3. Details of the supplier of the safety data sheet

Company

EU entity/business name
Thermo Fisher Scientific
Janssen Pharmaceuticaaan 3a, 2440 Geel, Belgium

UK entity/business name
Fisher Scientific UK
Bishop Meadow Road,
Loughborough, Leicestershire LE11 5RG, United Kingdom

Swiss distributor - Fisher Scientific AG
Neuhofstrasse 11, CH 4153 Reinach
Tel: +41 (0) 56 618 41 11
e-mail - infoch@thermofisher.com

E-mail address begel.sdsdesk@thermofisher.com

1.4. Emergency telephone number

For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11
Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99
CHEMTREC Tel. No.**US**:001-800-424-9300 / **Europe**:001-703-527-3887

customers in Switzerland:
Tox Info Suisse Emergency Number: **145 (24hr)**
Tox Info Suisse: +41-44 251 51 51 (Emergency number from abroad)
Chemtrec (24h) Toll-Free: 0800 564 402
Chemtrec Local: +41-43 508 20 11 (Zurich)

SECTION 2: HAZARDS IDENTIFICATION

2.1. Classification of the substance or mixture

SAFETY DATA SHEET

Magnesium sulfate, anhydrous

Revision Date 06-Oct-2023

CLP Classification - Regulation (EC) No 1272/2008

Physical hazards

Based on available data, the classification criteria are not met

Health hazards

Based on available data, the classification criteria are not met

Environmental hazards

Based on available data, the classification criteria are not met

Full text of Hazard Statements: see section 16

2.2. Label elements

None required

2.3. Other hazards

In accordance with Annex XIII of the REACH Regulation, inorganic substances do not require assessment

This product does not contain any known or suspected endocrine disruptors

SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS

3.1. Substances

Component	CAS No	EC No	Weight %	CLP Classification - Regulation (EC) No 1272/2008
Magnesium sulfate	7487-88-9	EEC No. 231-298-2	>95	-

Full text of Hazard Statements: see section 16

SECTION 4: FIRST AID MEASURES

4.1. Description of first aid measures

Eye Contact Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.

Skin Contact Wash off immediately with plenty of water for at least 15 minutes. Get medical attention immediately if symptoms occur.

SAFETY DATA SHEET

Magnesium sulfate, anhydrous

Revision Date 06-Oct-2023

Ingestion	Do NOT induce vomiting. Get medical attention.
Inhalation	Remove to fresh air. Get medical attention immediately if symptoms occur. If not breathing, give artificial respiration.
Self-Protection of the First Aider	No special precautions required.

4.2. Most important symptoms and effects, both acute and delayed

No information available.

4.3. Indication of any immediate medical attention and special treatment needed

Notes to Physician Treat symptomatically.

SECTION 5: FIREFIGHTING MEASURES

5.1. Extinguishing media

Suitable Extinguishing Media

Substance is nonflammable; use agent most appropriate to extinguish surrounding fire.

Extinguishing media which must not be used for safety reasons

No information available.

5.2. Special hazards arising from the substance or mixture

Thermal decomposition can lead to release of irritating gases and vapors.

Hazardous Combustion Products

Sulfur oxides, Magnesium oxides.

5.3. Advice for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

SECTION 6: ACCIDENTAL RELEASE MEASURES

6.1. Personal precautions, protective equipment and emergency procedures

Use personal protective equipment as required. Ensure adequate ventilation. Avoid dust formation.

6.2. Environmental precautions

See Section 12 for additional Ecological Information.

6.3. Methods and material for containment and cleaning up

Avoid dust formation. Sweep up and shovel into suitable containers for disposal.

6.4. Reference to other sections

Refer to protective measures listed in Sections 8 and 13.

SECTION 7: HANDLING AND STORAGE

SAFETY DATA SHEET

Magnesium sulfate, anhydrous

Revision Date 06-Oct-2023

7.1. Precautions for safe handling

Wear personal protective equipment/face protection. Ensure adequate ventilation. Avoid dust formation. Do not breathe dust. Avoid contact with skin, eyes or clothing.

Hygiene Measures

Handle in accordance with good industrial hygiene and safety practice. Keep away from food, drink and animal feeding stuffs. Do not eat, drink or smoke when using this product. Remove and wash contaminated clothing and gloves, including the inside, before re-use. Wash hands before breaks and after work.

7.2. Conditions for safe storage, including any incompatibilities

Keep containers tightly closed in a dry, cool and well-ventilated place.

Technical Rules for Hazardous Substances (TRGS) 510
Storage Class (LGK) (Germany)

Storage Class/LGK 13

Switzerland - Storage of hazardous substances

Storage class - SC 11/13
<https://www.kvu.ch/de/themen/stoffe-und-produkte>
<https://www.kvu.ch/fr/themes/substances-et-produits>
<https://www.kvu.ch/it/temi/sostanze-e-prodotti>

7.3. Specific end use(s)

Use in laboratories

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1. Control parameters

Exposure limits

List source(s):

Component	Russia	Slovak Republic	Slovenia	Sweden	Turkey
Magnesium sulfate	MAC: 2 mg/m ³				

Biological limit values

This product, as supplied, does not contain any hazardous materials with biological limits established by the region specific regulatory bodies

Monitoring methods

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents.

MDHS14/3 General methods for sampling and gravimetric analysis of respirable and inhalable dust

Derived No Effect Level (DNEL) / Derived Minimum Effect Level (DMEL)

See table for values

SAFETY DATA SHEET

Magnesium sulfate, anhydrous

Revision Date 06-Oct-2023

Component	Acute effects local (Dermal)	Acute effects systemic (Dermal)	Chronic effects local (Dermal)	Chronic effects systemic (Dermal)
Magnesium sulfate 7487-88-9 (>95)				DNEL = 21.3mg/kg bw/day

Component	Acute effects local (Inhalation)	Acute effects systemic (Inhalation)	Chronic effects local (Inhalation)	Chronic effects systemic (Inhalation)
Magnesium sulfate 7487-88-9 (>95)				DNEL = 37.6mg/m ³

Predicted No Effect Concentration (PNEC)

See values below.

Component	Fresh water	Fresh water sediment	Water Intermittent	Microorganisms in sewage treatment	Soil (Agriculture)
Magnesium sulfate 7487-88-9 (>95)	PNEC = 0.68mg/L		PNEC = 6.8mg/L	PNEC = 10mg/L	

Component	Marine water	Marine water sediment	Marine water Intermittent	Food chain	Air
Magnesium sulfate 7487-88-9 (>95)	PNEC = 0.068mg/L				

8.2. Exposure controls

Engineering Measures

None under normal use conditions.

Personal protective equipment

Eye Protection

Wear safety glasses with side shields (or goggles) (European standard - EN 166)

Hand Protection

Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Natural rubber	See manufacturers	-	EN 374	(minimum requirement)
Nitrile rubber	recommendations			
Neoprene				
PVC				

Skin and body protection

Wear appropriate protective gloves and clothing to prevent skin exposure.

Inspect gloves before use. observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information) gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion. gloves with care avoiding skin contamination.

Respiratory Protection

No protective equipment is needed under normal use conditions.

Large scale/emergency use

Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced

Recommended Filter type: Particle filter

Small scale/Laboratory use

Maintain adequate ventilation

Environmental exposure controls

No information available.

SAFETY DATA SHEET

Magnesium sulfate, anhydrous

Revision Date 06-Oct-2023

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

9.1. Information on basic physical and chemical properties

Physical State	Solid	
Appearance	Off-white	
Odor	Odorless	
Odor Threshold	No data available	
Melting Point/Range	1124 °C / 2055.2 °F	
Softening Point	No data available	
Boiling Point/Range	No information available	
Flammability (liquid)	Not applicable	Solid
Flammability (solid,gas)	No information available	
Explosion Limits	No data available	
Flash Point	No information available	Method - No information available
Autoignition Temperature	No data available	
Decomposition Temperature	> 700°C	
pH	7.9	5% aq.sol
Viscosity	Not applicable	Solid
Water Solubility	26g/100ml (0°C)	
Solubility in other solvents	No information available	
Partition Coefficient (n-octanol/water)		
Vapor Pressure	No information available	
Density / Specific Gravity	2.65	
Bulk Density	No data available	
Vapor Density	Not applicable	Solid
Particle characteristics	No data available	

9.2. Other information

Molecular Formula	Mg O4 S
Molecular Weight	120.37
Evaporation Rate	Not applicable - Solid

SECTION 10: STABILITY AND REACTIVITY

10.1. Reactivity

None known, based on information available

10.2. Chemical stability

Hygroscopic.

10.3. Possibility of hazardous reactions

Hazardous Polymerization	No information available.
Hazardous Reactions	No information available.

10.4. Conditions to avoid

Avoid dust formation. Incompatible products. Exposure to moist air or water.

10.5. Incompatible materials

Strong oxidizing agents.

10.6. Hazardous decomposition products

Sulfur oxides. Magnesium oxides.

SAFETY DATA SHEET

Magnesium sulfate, anhydrous

Revision Date 06-Oct-2023

SECTION 11: TOXICOLOGICAL INFORMATION

11.1. Information on hazard classes as defined in Regulation (EC) No 1272/2008

Product Information	No acute toxicity information is available for this product
(a) acute toxicity;	
Oral	No data available
Dermal	No data available
Inhalation	No data available
(b) skin corrosion/irritation;	No data available
(c) serious eye damage/irritation;	No data available
(d) respiratory or skin sensitization;	
Respiratory	No data available
Skin	No data available
(e) germ cell mutagenicity;	No data available
(f) carcinogenicity;	No data available
	There are no known carcinogenic chemicals in this product
(g) reproductive toxicity;	No data available
(h) STOT-single exposure;	No data available
(i) STOT-repeated exposure;	No data available
Target Organs	No information available.
(j) aspiration hazard;	Not applicable
	Solid
Other Adverse Effects	The toxicological properties have not been fully investigated.
Symptoms / effects, both acute and delayed	No information available.

11.2. Information on other hazards

Endocrine Disrupting Properties	Assess endocrine disrupting properties for human health. This product does not contain any known or suspected endocrine disruptors.
--	---

SECTION 12: ECOLOGICAL INFORMATION

12.1. Toxicity

SAFETY DATA SHEET

Magnesium sulfate, anhydrous

Revision Date 06-Oct-2023

Ecotoxicity effects . Do not empty into drains.

Component	Freshwater Fish	Water Flea	Freshwater Algae
Magnesium sulfate	LC50: 2610 - 3080 mg/L, 96h static (Pimephales promelas)	EC50: 266.4 - 417.3 mg/L, 48h Static (Daphnia magna)	EC50: = 2700 mg/L, 72h (Desmodesmus subspicatus)

Component	Microtox	M-Factor
Magnesium sulfate	= 84000 mg/L EC50 Photobacterium phosphoreum 30 min	

12.2. Persistence and degradability Not readily biodegradable
Persistence Soluble in water, Persistence is unlikely, based on information available.
Degradability Not relevant for inorganic substances.

12.3. Bioaccumulative potential Bioaccumulation is unlikely

12.4. Mobility in soil The product is water soluble, and may spread in water systems Will likely be mobile in the environment due to its water solubility. Highly mobile in soils

12.5. Results of PBT and vPvB assessment In accordance with Annex XIII of the REACH Regulation, inorganic substances do not require assessment.

12.6. Endocrine disrupting properties
Endocrine Disruptor Information This product does not contain any known or suspected endocrine disruptors

12.7. Other adverse effects
Persistent Organic Pollutant This product does not contain any known or suspected substance
Ozone Depletion Potential This product does not contain any known or suspected substance

SECTION 13: DISPOSAL CONSIDERATIONS

13.1. Waste treatment methods

Waste from Residues/Unused Products Chemical waste generators must determine whether a discarded chemical is classified as a hazardous waste. Consult local, regional, and national hazardous waste regulations to ensure complete and accurate classification.

Contaminated Packaging Empty remaining contents. Dispose of in accordance with local regulations. Do not re-use empty containers.

European Waste Catalogue (EWC) According to the European Waste Catalog, Waste Codes are not product specific, but application specific.

Other Information Waste codes should be assigned by the user based on the application for which the product was used.

Switzerland - Waste Ordinance Disposal should be in accordance with applicable regional, national and local laws and regulations. Ordinance on the Avoidance and the Disposal of Waste (Waste Ordinance, ADWO) SR 814.600
<https://www.fedlex.admin.ch/eli/cc/2015/891/en>

SAFETY DATA SHEET

Magnesium sulfate, anhydrous

Revision Date 06-Oct-2023

SECTION 14: TRANSPORT INFORMATION

IMDG/IMO Not regulated

14.1. UN number
14.2. UN proper shipping name
14.3. Transport hazard class(es)
14.4. Packing group

ADR Not regulated

14.1. UN number
14.2. UN proper shipping name
14.3. Transport hazard class(es)
14.4. Packing group

IATA Not regulated

14.1. UN number
14.2. UN proper shipping name
14.3. Transport hazard class(es)
14.4. Packing group

14.5. Environmental hazards No hazards identified

14.6. Special precautions for user No special precautions required.

14.7. Maritime transport in bulk according to IMO instruments Not applicable, packaged goods

SECTION 15: REGULATORY INFORMATION

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

International Inventories

Europe (EINECS/ELINCS/NLP), China (IECSC), Taiwan (TCSI), Korea (KECL), Japan (ENCS), Japan (ISHL), Canada (DSL/NDSL), Australia (AICS), New Zealand (NZIoC), Philippines (PICCS). US EPA (TSCA) - Toxic Substances Control Act, (40 CFR Part 710)

Component	CAS No	EINECS	ELINCS	NLP	IECSC	TCSI	KECL	ENCS	ISHL
Magnesium sulfate	7487-88-9	231-298-2	-	-	X	X	KE-22752	X	X

Component	CAS No	TSCA	TSCA Inventory notification - Active-Inactive	DSL	NDSL	AICS	NZIoC	PICCS
Magnesium sulfate	7487-88-9	X	ACTIVE	X	-	X	X	X

Legend: X - Listed '-' - Not Listed

KECL - NIER number or KE number (<http://ncis.nier.go.kr/en/main.do>)

Authorisation/Restrictions according to EU REACH Not applicable

Component	CAS No	REACH (1907/2006) - Annex XIV - Substances Subject to Authorization	REACH (1907/2006) - Annex XVII - Restrictions on Certain Dangerous Substances	REACH Regulation (EC 1907/2006) article 59 - Candidate List of Substances of Very High Concern (SVHC)
Magnesium sulfate	7487-88-9	-	-	-

SAFETY DATA SHEET

Magnesium sulfate, anhydrous

Revision Date 06-Oct-2023

Seveso III Directive (2012/18/EC)

Component	CAS No	Seveso III Directive (2012/18/EC) - Qualifying Quantities for Major Accident Notification	Seveso III Directive (2012/18/EC) - Qualifying Quantities for Safety Report Requirements
Magnesium sulfate	7487-88-9	Not applicable	Not applicable

Regulation (EC) No 649/2012 of the European Parliament and of the Council of 4 July 2012 concerning the export and import of dangerous chemicals

Not applicable

Contains component(s) that meet a 'definition' of per & poly fluoroalkyl substance (PFAS)?

Not applicable

Take note of Directive 98/24/EC on the protection of the health and safety of workers from the risks related to chemical agents at work .

National Regulations

UK - Take note of Control of Substances Hazardous to Health Regulations (COSHH) 2002 and 2005 Amendment

WGK Classification

See table for values

Component	Germany - Water Classification (AwSV)	Germany - TA-Luft Class
Magnesium sulfate	WGK1	

Swiss Regulations

Article 4 para. 4 of the Ordinance on the protection of young people in the workplace (SR 822.115) and Article 1 lit. f of the EAER regulation on hazardous work and young people (SR 822.115.2).

Take note on Article 13 Maternity Ordinance (SR 822.111.52) with regards expectant and nursing mothers.

Component	Switzerland - Ordinance on the Reduction of Risk from handling of hazardous substances preparation (SR 814.81)	Switzerland - Ordinance on Incentive Taxes on Volatile Organic Compounds (OVOC)	Switzerland - Ordinance of the Rotterdam Convention on the Prior Informed Consent Procedure
Magnesium sulfate 7487-88-9 (>95)	Prohibited and Restricted Substances		

15.2. Chemical safety assessment

A Chemical Safety Assessment/Report (CSA/CSR) has not been conducted

SECTION 16: OTHER INFORMATION

Full text of H-Statements referred to under sections 2 and 3

Legend

CAS - Chemical Abstracts Service

EINECS/ELINCS - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

PICCS - Philippines Inventory of Chemicals and Chemical Substances

IECSC - Chinese Inventory of Existing Chemical Substances

KECL - Korean Existing and Evaluated Chemical Substances

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDL - Canadian Domestic Substances List/Non-Domestic Substances List

ENCS - Japanese Existing and New Chemical Substances

AICS - Australian Inventory of Chemical Substances

NZIoC - New Zealand Inventory of Chemicals

SAFETY DATA SHEET

Magnesium sulfate, anhydrous

Revision Date 06-Oct-2023

WEL - Workplace Exposure Limit

ACGIH - American Conference of Governmental Industrial Hygienists

DNEL - Derived No Effect Level

RPE - Respiratory Protective Equipment

LC50 - Lethal Concentration 50%

NOEC - No Observed Effect Concentration

PBT - Persistent, Bioaccumulative, Toxic

TWA - Time Weighted Average

IARC - International Agency for Research on Cancer
Predicted No Effect Concentration (PNEC)

LD50 - Lethal Dose 50%

EC50 - Effective Concentration 50%

POW - Partition coefficient Octanol:Water

vPvB - very Persistent, very Bioaccumulative

ADR - European Agreement Concerning the International Carriage of Dangerous Goods by Road

IMO/IMDG - International Maritime Organization/International Maritime Dangerous Goods Code

OECD - Organisation for Economic Co-operation and Development

BCF - Bioconcentration factor

Key literature references and sources for data

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

ICAO/IATA - International Civil Aviation Organization/International Air Transport Association

MARPOL - International Convention for the Prevention of Pollution from Ships

ATE - Acute Toxicity Estimate

VOC - (volatile organic compound)

Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Creation Date 27-Jul-2010

Revision Date 06-Oct-2023

Revision Summary Not applicable.

**This safety data sheet complies with the requirements of Regulation (EC) No. 1907/2006.
COMMISSION REGULATION (EU) 2020/878 amending Annex II to Regulation (EC) No
1907/2006 .**

**For Switzerland - Compiled in accordance with the technical provisions referred to in Annex 2,
Number 3, ChemO (SR 813.11 - Ordinance on Protection against Dangerous Substances and
Preparations).**

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet