

ALFAA14524

## Yttrium(III) isopropoxide, 20-25% w/w in toluene

### SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

<b>产品说明:</b> Product Description:	异丙醇钇(III), 20-25% w/w 甲苯溶液 Yttrium(III) isopropoxide, 20-25% w/w in toluene
<b>Cat No. :</b> Molecular Formula	14524 C9 H21 O3 Y
<b>Supplier</b>	Avocado Research Chemicals Ltd. (Part of Thermo Fisher Scientific) Shore Road, Heysham Lancashire, LA3 2XY, United Kingdom Office Tel: +44 (0) 1524 850506 Office Fax: +44 (0) 1524 850608
<b>Emergency Telephone Number</b>	For information <b>US</b> call: 001-800-227-6701 / <b>Europe</b> call: +32 14 57 52 11 Emergency Number <b>US</b> :001-201-796-7100 / <b>Europe</b> : +32 14 57 52 99 <b>CHEMTREC</b> Tel. No. <b>US</b> :001-800-424-9300 / <b>Europe</b> :001-703-527-3887
<b>E-mail address</b>	begel.sdsdesk@thermofisher.com
<b>Recommended Use</b> <b>Uses advised against</b>	Laboratory chemicals. No Information available

### SECTION 2. HAZARD IDENTIFICATION

Physical State	Appearance	Odor
Liquid	No information available	No information available
<b>Emergency Overview</b>		
Highly flammable liquid and vapor. May be fatal if swallowed and enters airways. Suspected of damaging fertility or the unborn child. May cause drowsiness and dizziness. Toxic to aquatic life. Harmful to aquatic life with long lasting effects. Causes severe skin burns and eye damage. May cause damage to organs through prolonged or repeated exposure. Moisture sensitive. Air sensitive.		

#### Classification of the substance or mixture

Flammable liquids.	Category 2
Aspiration Toxicity	Category 1
Skin Corrosion/Irritation	Category 1 C
Serious Eye Damage/Eye Irritation	Category 1
Reproductive Toxicity	Category 2
Specific target organ toxicity - (single exposure)	Category 3
Specific target organ toxicity - (repeated exposure)	Category 2
Acute aquatic toxicity	Category 2
Chronic aquatic toxicity	Category 3

#### Label Elements

# SAFETY DATA SHEET

## Yttrium(III) isopropoxide, 20-25% w/w in toluene

**Signal Word****Danger****Hazard Statements**

H225 - Highly flammable liquid and vapor  
 H304 - May be fatal if swallowed and enters airways  
 H336 - May cause drowsiness or dizziness  
 H401 - Toxic to aquatic life  
 H412 - Harmful to aquatic life with long lasting effects  
 H314 - Causes severe skin burns and eye damage  
 H373 - May cause damage to organs through prolonged or repeated exposure  
 H361 - Suspected of damaging fertility or the unborn child

**Precautionary Statements****Prevention**

P240 - Ground and bond container and receiving equipment  
 P242 - Use non-sparking tools  
 P243 - Take action to prevent static discharges  
 P201 - Obtain special instructions before use  
 P202 - Do not handle until all safety precautions have been read and understood  
 P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking  
 P260 - Do not breathe dust/fume/gas/mist/vapors/spray  
 P264 - Wash face, hands and any exposed skin thoroughly after handling  
 P271 - Use only outdoors or in a well-ventilated area  
 P280 - Wear protective gloves/protective clothing/eye protection/face protection

**Response**

P310 - Immediately call a POISON CENTER or doctor  
 P330 - Rinse mouth  
 P303 + P361 + P353 - IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water or shower  
 P304 + P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing  
 P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing  
 P370 + P378 - In case of fire: Use dry sand, dry chemical or alcohol-resistant foam to extinguish  
 P331 - Do NOT induce vomiting  
 P362 + P364 - Take off contaminated clothing and wash it before reuse

**Storage**

P403 + P233 - Store in a well-ventilated place. Keep container tightly closed

**Disposal**

P501 - Dispose of contents/ container to an approved waste disposal plant

**Physical and Chemical Hazards**

Vapors may cause flash fire or explosion. Highly flammable.

**Health Hazards**

Aspiration hazard if swallowed - can enter lungs and cause damage. Suspected of damaging fertility or the unborn child. May cause drowsiness or dizziness. Corrosive. Causes skin and eye burns. May cause damage to organs through prolonged or repeated exposure.

**Environmental hazards**

Toxic to aquatic life. Harmful to aquatic life with long lasting effects. Is not likely mobile in the environment due its low water solubility. Spillage unlikely to penetrate soil.

Toxic to terrestrial vertebrates. This product does not contain any known or suspected endocrine disruptors.

**SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS**

Component	CAS No	Weight %
-----------	--------	----------

# SAFETY DATA SHEET

## Yttrium(III) isopropoxide, 20-25% w/w in toluene

Toluene	108-88-3	75.00
Yttrium(III) isopropoxide	2172-12-5	25.00

### SECTION 4. FIRST AID MEASURES

#### General Advice

Show this safety data sheet to the doctor in attendance. Immediate medical attention is required.

#### Eye Contact

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Immediate medical attention is required.

#### Skin Contact

Wash off immediately with plenty of water for at least 15 minutes. Remove and wash contaminated clothing and gloves, including the inside, before re-use. Call a physician immediately.

#### Inhalation

If not breathing, give artificial respiration. Remove from exposure, lie down. Do not use mouth-to-mouth method if victim ingested or inhaled the substance; give artificial respiration with the aid of a pocket mask equipped with a one-way valve or other proper respiratory medical device. Call a physician immediately. Risk of serious damage to the lungs (by aspiration).

#### Ingestion

Do NOT induce vomiting. Clean mouth with water. Never give anything by mouth to an unconscious person. Call a physician immediately. Call a physician or poison control center immediately. If vomiting occurs naturally, have victim lean forward.

#### Most important symptoms and effects

Causes burns by all exposure routes. Difficulty in breathing. Product is a corrosive material. Use of gastric lavage or emesis is contraindicated. Possible perforation of stomach or esophagus should be investigated: Ingestion causes severe swelling, severe damage to the delicate tissue and danger of perforation: Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting: Inhalation of high vapor concentrations may cause symptoms like headache, dizziness, tiredness, nausea and vomiting

#### Self-Protection of the First Aider

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

#### Notes to Physician

Treat symptomatically. Symptoms may be delayed.

### SECTION 5. FIRE-FIGHTING MEASURES

#### Suitable Extinguishing Media

CO<sub>2</sub>, dry chemical, dry sand, alcohol-resistant foam.

#### Extinguishing media which must not be used for safety reasons

No information available.

#### Specific Hazards Arising from the Chemical

Thermal decomposition can lead to release of irritating gases and vapors. The product causes burns of eyes, skin and mucous membranes.

#### Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear. Thermal decomposition can lead to release of irritating gases and vapors.

### SECTION 6. ACCIDENTAL RELEASE MEASURES

#### Personal Precautions

# SAFETY DATA SHEET

## Yttrium(III) isopropoxide, 20-25% w/w in toluene

Ensure adequate ventilation. Use personal protective equipment as required. Evacuate personnel to safe areas. Keep people away from and upwind of spill/leak.

### Environmental Precautions

Do not flush into surface water or sanitary sewer system. Should not be released into the environment. Do not allow material to contaminate ground water system. See Section 12 for additional Ecological Information.

### Methods for Containment and Clean Up

Soak up with inert absorbent material. Keep in suitable, closed containers for disposal.

Refer to protective measures listed in Sections 8 and 13.

## SECTION 7. HANDLING AND STORAGE

### Handling

Wear personal protective equipment/face protection. Do not get in eyes, on skin, or on clothing. Use only under a chemical fume hood. Do not breathe mist/vapors/spray. Do not ingest. If swallowed then seek immediate medical assistance.

### Storage

Corrosives area. Keep containers tightly closed in a dry, cool and well-ventilated place.

### Specific Use(s)

Use in laboratories

## SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

### Control Parameters

Component	China	Taiwan	Thailand	Hong Kong
Toluene	TWA: 50 mg/m <sup>3</sup> STEL: 100 mg/m <sup>3</sup> Skin	TWA: 100 ppm TWA: 376 mg/m <sup>3</sup>	Ceiling: 300 ppm STEL: 500 ppm TWA: 200 ppm	TWA: 50 ppm TWA: 188 mg/m <sup>3</sup>

Component	ACGIH TLV	OSHA PEL	NIOSH	The United Kingdom	European Union
Toluene	TWA: 20 ppm	(Vacated) TWA: 100 ppm (Vacated) TWA: 375 mg/m <sup>3</sup> Ceiling: 300 ppm (Vacated) STEL: 150 ppm (Vacated) STEL: 560 mg/m <sup>3</sup> TWA: 200 ppm	IDLH: 500 ppm TWA: 100 ppm TWA: 375 mg/m <sup>3</sup> STEL: 150 ppm STEL: 560 mg/m <sup>3</sup>	STEL: 100 ppm 15 min STEL: 384 mg/m <sup>3</sup> 15 min TWA: 50 ppm 8 hr TWA: 191 mg/m <sup>3</sup> 8 hr Skin	TWA: 50 ppm (8hr) TWA: 192 mg/m <sup>3</sup> (8hr) STEL: 100 ppm (15min) STEL: 384 mg/m <sup>3</sup> (15min) Skin

### Legend

ACGIH - American Conference of Governmental Industrial Hygienists

OSHA - Occupational Safety and Health Administration

NIOSH: NIOSH - National Institute for Occupational Safety and Health

### Monitoring methods

MDHS 91 Metals and metalloids in workplace air by X-ray fluorescence spectrometry MDHS 99 Metals in air by ICP-AES

### Exposure Controls

#### Engineering Measures

Ensure that eyewash stations and safety showers are close to the workstation location. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

### Personal protective equipment

## Yttrium(III) isopropoxide, 20-25% w/w in toluene

**Eye Protection** Goggles (European standard - EN 166)

**Hand Protection** Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Nitrile rubber Viton (R)	See manufacturers recommendations	-	EN 374	(minimum requirement)

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

**Skin and body protection** Long sleeved clothing

**Respiratory Protection** When workers are facing concentrations above the exposure limit they must use appropriate certified respirators. To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly

**Large scale/emergency use** Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced  
**Recommended Filter type:** Multi-purpose/ABEK conforming to EN14387 low boiling organic solvent Type AX Brown conforming to EN371 or Organic gases and vapours filter Type A Brown

**Small scale/Laboratory use** Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.  
**Recommended half mask:-** Valve filtering: EN405; or; Half mask: EN140; plus filter, EN 141  
When RPE is used a face piece Fit Test should be conducted

**Hygiene Measures** Handle in accordance with good industrial hygiene and safety practice.

**Environmental exposure controls** Prevent product from entering drains. Do not allow material to contaminate ground water system.

## SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

**Appearance**

**Physical State** Liquid

**Odor**

No information available

**Odor Threshold**

No data available

**pH**

Not applicable

**Melting Point/Range**

No data available

**Softening Point**

No data available

**Boiling Point/Range**

No information available

**Flash Point**

4 °C / 39.2 °F

**Method -** No information available

**Evaporation Rate**

No data available

**Flammability (solid,gas)**

Not applicable

Liquid

**Explosion Limits**

No data available

**Vapor Pressure**

No data available

**Vapor Density**

No data available

(Air = 1.0)

**Specific Gravity / Density**

No data available

**Bulk Density**

Not applicable

Liquid

**Water Solubility**

Immiscible

## Yttrium(III) isopropoxide, 20-25% w/w in toluene

<b>Solubility in other solvents</b>	No information available
<b>Partition Coefficient (n-octanol/water)</b>	
<b>Component</b>	<b>log Pow</b>
Toluene	2.73
<b>Autoignition Temperature</b>	No data available
<b>Decomposition Temperature</b>	No data available
<b>Viscosity</b>	No data available
<b>Explosive Properties</b>	No information available
<b>Oxidizing Properties</b>	No information available

<b>Molecular Formula</b>	C9 H21 O3 Y
<b>Molecular Weight</b>	266.17

## SECTION 10. STABILITY AND REACTIVITY

<b>Stability</b>	Air sensitive. Moisture sensitive.
<b>Hazardous Reactions</b>	None under normal processing.
<b>Hazardous Polymerization</b>	No information available.
<b>Conditions to Avoid</b>	None known.
<b>Materials to avoid</b>	No information available.

**Hazardous Decomposition Products** Carbon monoxide (CO). Carbon dioxide (CO<sub>2</sub>). Yttrium oxide.

## SECTION 11. TOXICOLOGICAL INFORMATION

## Product Information

(a) acute toxicity;  
Toxicology data for the components

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
Toluene	> 5000 mg/kg ( Rat )	LD50 = 12000 mg/kg ( Rabbit )	26700 ppm ( Rat ) 1 h

(b) skin corrosion/irritation; No data available

(c) serious eye damage/irritation; No data available

(d) respiratory or skin sensitization;  
Respiratory No data available  
Skin No data available

(e) germ cell mutagenicity; No data available

(f) carcinogenicity; No data available  
There are no known carcinogenic chemicals in this product

(g) reproductive toxicity; No data available

(h) STOT-single exposure; No data available

# SAFETY DATA SHEET

## Yttrium(III) isopropoxide, 20-25% w/w in toluene

**Results / Target organs** Central nervous system (CNS)

**(i) STOT-repeated exposure;** No data available

**Target Organs** Neuropsychological effects, Eyes, Ears.

**(j) aspiration hazard;** Category 1

**Symptoms / effects, both acute and delayed** Product is a corrosive material. Use of gastric lavage or emesis is contraindicated. Possible perforation of stomach or esophagus should be investigated: Ingestion causes severe swelling, severe damage to the delicate tissue and danger of perforation: Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting: Inhalation of high vapor concentrations may cause symptoms like headache, dizziness, tiredness, nausea and vomiting

### SECTION 12. ECOLOGICAL INFORMATION

**Ecotoxicity effects** The product contains following substances which are hazardous for the environment. Contains a substance which is: Toxic to aquatic organisms. May cause long-term adverse effects in the environment. Do not allow material to contaminate ground water system.

Component	Freshwater Fish	Water Flea	Freshwater Algae	Microtox
Toluene	50-70 mg/L LC50 96 h 5-7 mg/L LC50 96 h 15-19 mg/L LC50 96 h 28 mg/L LC50 96 h 12 mg/L LC50 96 h	EC50: = 11.5 mg/L, 48h (Daphnia magna) EC50: 5.46 - 9.83 mg/L, 48h Static (Daphnia magna)	EC50: = 12.5 mg/L, 72h static (Pseudokirchneriella subcapitata) EC50: > 433 mg/L, 96h (Pseudokirchneriella subcapitata)	EC50 = 19.7 mg/L 30 min

**Persistence and Degradability** Product contains heavy metals. Discharge into the environment must be avoided. Special pre-treatment is necessary  
**Persistence** Immiscible with water, May persist.

Component	Degradability
Toluene 108-88-3 ( 75.00 )	86% (20d)

**Degradation in sewage treatment plant** Contains substances known to be hazardous to the environment or not degradable in waste water treatment plants.

**Bioaccumulative Potential** May have some potential to bioaccumulate; Product has a high potential to bioconcentrate

Component	log Pow	Bioconcentration factor (BCF)
Toluene	2.73	90

**Mobility in soil** Spillage unlikely to penetrate soil Is not likely mobile in the environment due its low water solubility

**Endocrine Disruptor Information** This product does not contain any known or suspected endocrine disruptors  
**Persistent Organic Pollutant** This product does not contain any known or suspected substance  
**Ozone Depletion Potential** This product does not contain any known or suspected substance

### SECTION 13. DISPOSAL CONSIDERATIONS

**Waste from Residues/Unused Products** Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.

## Yttrium(III) isopropoxide, 20-25% w/w in toluene

<b>Contaminated Packaging</b>	Dispose of this container to hazardous or special waste collection point.
<b>Other Information</b>	Do not flush to sewer. Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains. Large amounts will affect pH and harm aquatic organisms.

## SECTION 14. TRANSPORT INFORMATION

Road and Rail Transport

<b>UN-No</b>	UN2924
<b>Proper Shipping Name</b>	Flammable liquid, corrosive, n.o.s.
<b>Technical Shipping Name</b>	(Yttrium(III) isopropoxide, TOLUENE)
<b>Hazard Class</b>	3
<b>Subsidiary Hazard Class</b>	8
<b>Packing Group</b>	II

IMDG/IMO

<b>UN-No</b>	UN2924
<b>Proper Shipping Name</b>	Flammable liquid, corrosive, n.o.s.
<b>Technical Shipping Name</b>	(Yttrium(III) isopropoxide, TOLUENE)
<b>Hazard Class</b>	3
<b>Subsidiary Hazard Class</b>	8
<b>Packing Group</b>	II

IATA

<b>UN-No</b>	UN2924
<b>Proper Shipping Name</b>	Flammable liquid, corrosive, n.o.s.
<b>Technical Shipping Name</b>	(Yttrium(III) isopropoxide, TOLUENE)
<b>Hazard Class</b>	3
<b>Subsidiary Hazard Class</b>	8
<b>Packing Group</b>	II

**Special Precautions for User** No special precautions required

## SECTION 15. REGULATORY INFORMATION

**International Inventories**

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
Toluene	X	X	X	X	203-625-9	X	X	X	X	X	X	KE-33936
Yttrium(III) isopropoxide	-	-	X	-	-	-	-	-	-	-	-	-

**National Regulations**



## SECTION 16. OTHER INFORMATION

**Prepared By** Health, Safety and Environmental Department  
**Revision Date** 09-May-2024  
**Revision Summary** New emergency telephone response service provider.

### Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

Fire prevention and fighting, identifying hazards and risks, static electricity, explosive atmospheres posed by vapours and dusts.

Chemical incident response training.

### Legend

**CAS** - Chemical Abstracts Service

**EINECS/ELINCS** - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

**PICCS** - Philippines Inventory of Chemicals and Chemical Substances

**IECSC** - Chinese Inventory of Existing Chemical Substances

**KECL** - Korean Existing and Evaluated Chemical Substances

**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory

**DSL/NDSL** - Canadian Domestic Substances List/Non-Domestic Substances List

**ENCS** - Japanese Existing and New Chemical Substances

**AICS** - Australian Inventory of Chemical Substances

**NZIoC** - New Zealand Inventory of Chemicals

**WEL** - Workplace Exposure Limit

**ACGIH** - American Conference of Governmental Industrial Hygienists

**DNEL** - Derived No Effect Level

**RPE** - Respiratory Protective Equipment

**LC50** - Lethal Concentration 50%

**NOEC** - No Observed Effect Concentration

**PBT** - Persistent, Bioaccumulative, Toxic

**TWA** - Time Weighted Average

**IARC** - International Agency for Research on Cancer

**PNEC** - Predicted No Effect Concentration

**LD50** - Lethal Dose 50%

**EC50** - Effective Concentration 50%

**POW** - Partition coefficient Octanol:Water

**vPvB** - very Persistent, very Bioaccumulative

**ICAO/IATA** - International Civil Aviation Organization/International Air Transport Association

**ADR** - European Agreement Concerning the International Carriage of Dangerous Goods by Road

**OECD** - Organisation for Economic Co-operation and Development

**BCF** - Bioconcentration factor

**IMO/IMDG** - International Maritime Organization/International Maritime Dangerous Goods Code

**MARPOL** - International Convention for the Prevention of Pollution from Ships

**ATE** - Acute Toxicity Estimate

**VOC** - (Volatile Organic Compound)

### Key literature references and sources for data

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

**Physical hazards** On basis of test data  
**Health Hazards** Calculation method  
**Environmental hazards** Calculation method

### Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

**End of Safety Data Sheet**