

ALFAA21120

## Cerium(IV) oxide, hydrated

### SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

产品说明:  
Product Description: 二氧化铈水合物  
Cerium(IV) oxide, hydrated

Cat No. : 21120  
CAS No 12014-56-1  
Molecular Formula CeO<sub>2</sub>. xH<sub>2</sub>O

Supplier Avocado Research Chemicals Ltd.  
(Part of Thermo Fisher Scientific)  
Shore Road, Heysham  
Lancashire, LA3 2XY,  
United Kingdom  
Office Tel: +44 (0) 1524 850506  
Office Fax: +44 (0) 1524 850608

Emergency Telephone Number For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11  
Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99  
**CHEMTREC** Tel. No. **US**:001-800-424-9300 / **Europe**:001-703-527-3887

E-mail address begel.sdsdesk@thermofisher.com

Recommended Use Laboratory chemicals.  
Uses advised against No Information available

### SECTION 2. HAZARD IDENTIFICATION

**Physical State**  
Solid

**Appearance**  
Yellow - Pale brown

**Odor**  
Odorless

**Emergency Overview**  
Causes severe skin burns and eye damage.

#### Classification of the substance or mixture

Skin Corrosion/Irritation	Category 1 B
Serious Eye Damage/Eye Irritation	Category 1

#### Label Elements



Signal Word **Danger**

Hazard Statements  
H314 - Causes severe skin burns and eye damage

## Cerium(IV) oxide, hydrated

**Precautionary Statements****Prevention**

P264 - Wash face, hands and any exposed skin thoroughly after handling

P271 - Use only outdoors or in a well-ventilated area

P280 - Wear protective gloves/protective clothing/eye protection/face protection

**Response**

P301 + P330 + P331 - IF SWALLOWED: rinse mouth. Do NOT induce vomiting

P303 + P361 + P353 - IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water or shower

P304 + P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing

P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing

P310 - Immediately call a POISON CENTER or doctor

P362 + P364 - Take off contaminated clothing and wash it before reuse

**Storage**

P403 + P233 - Store in a well-ventilated place. Keep container tightly closed

**Disposal**

P501 - Dispose of contents/ container to an approved waste disposal plant

**Physical and Chemical Hazards**

None identified.

**Health Hazards**

Corrosive. Causes skin and eye burns.

**Environmental hazards**

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants. Is not likely mobile in the environment due its low water solubility. Spillage unlikely to penetrate soil.

This product does not contain any known or suspected endocrine disruptors.

**SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS**

Component	CAS No	Weight %
Cerium hydroxide (Ce(OH) <sub>4</sub> ), (T-4)-	12014-56-1	<=100

**SECTION 4. FIRST AID MEASURES****General Advice**

Show this safety data sheet to the doctor in attendance. Immediate medical attention is required.

**Eye Contact**

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Immediate medical attention is required.

Keep eye wide open while rinsing.

**Skin Contact**

Wash off immediately with soap and plenty of water while removing all contaminated clothes and shoes. Call a physician immediately.

**Inhalation**

Remove to fresh air. If not breathing, give artificial respiration. Call a physician or poison control center immediately. Do not use mouth-to-mouth method if victim ingested or inhaled the substance; give artificial respiration with the aid of a pocket mask equipped with a one-way valve or other proper respiratory medical device.

**Ingestion**

Immediate medical attention is required. Do NOT induce vomiting. Drink plenty of water. Never give anything by mouth to an unconscious person.

**Most important symptoms and effects**

Causes burns by all exposure routes. Product is a corrosive material. Use of gastric lavage or emesis is contraindicated. Possible perforation of stomach or esophagus should be investigated: Ingestion causes severe swelling, severe damage to the delicate tissue and danger of perforation

**Self-Protection of the First Aider**

No special precautions required.

**Notes to Physician**

Treat symptomatically.

**SECTION 5. FIRE-FIGHTING MEASURES****Suitable Extinguishing Media**

Not combustible. CO<sub>2</sub>, dry chemical, dry sand, alcohol-resistant foam.

**Extinguishing media which must not be used for safety reasons**

No information available.

**Specific Hazards Arising from the Chemical**

The product causes burns of eyes, skin and mucous membranes.

**Protective Equipment and Precautions for Firefighters**

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear. Thermal decomposition can lead to release of irritating gases and vapors.

**SECTION 6. ACCIDENTAL RELEASE MEASURES****Personal Precautions**

Use personal protective equipment as required. Evacuate personnel to safe areas. Avoid contact with skin, eyes or clothing.

**Environmental Precautions**

Should not be released into the environment. Do not allow material to contaminate ground water system. See Section 12 for additional Ecological Information. Do not flush into surface water or sanitary sewer system.

**Methods for Containment and Clean Up**

Sweep up and shovel into suitable containers for disposal. Avoid dust formation.

Refer to protective measures listed in Sections 8 and 13.

**SECTION 7. HANDLING AND STORAGE****Handling**

Wear personal protective equipment/face protection. Do not get in eyes, on skin, or on clothing. Use only under a chemical fume hood. Do not breathe dust. Do not ingest. If swallowed then seek immediate medical assistance.

**Storage**

Corrosives area. Keep containers tightly closed in a dry, cool and well-ventilated place.

**Specific Use(s)**

Use in laboratories

**SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION****Control Parameters****Monitoring methods**

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of

## Cerium(IV) oxide, hydrated

exposure to chemical and biological agents. MDHS14/3 General methods for sampling and gravimetric analysis of respirable and inhalable dust MDHS 91 Metals and metalloids in workplace air by X-ray fluorescence spectrometry MDHS 99 Metals in air by ICP-AES

**Exposure Controls****Engineering Measures**

None under normal use conditions. Ensure that eyewash stations and safety showers are close to the workstation location. .

**Personal protective equipment**

**Eye Protection** Goggles (European standard - EN 166)

**Hand Protection** Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Natural rubber	See manufacturers recommendations	-	EN 374	(minimum requirement)
Nitrile rubber				
Neoprene				
PVC				

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves.

(Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatability, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

**Skin and body protection** Long sleeved clothing

**Respiratory Protection** No protective equipment is needed under normal use conditions.

**Large scale/emergency use** Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced  
**Recommended Filter type:** Particle filter

**Small scale/Laboratory use** Maintain adequate ventilation

**Hygiene Measures** Handle in accordance with good industrial hygiene and safety practice.

**Environmental exposure controls** No information available.

## SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

<b>Appearance</b>	Yellow - Pale brown	
<b>Physical State</b>	Solid	
<b>Odor</b>	Odorless	
<b>Odor Threshold</b>	No data available	
<b>pH</b>	No information available	
<b>Melting Point/Range</b>	No data available	
<b>Softening Point</b>	No data available	
<b>Boiling Point/Range</b>	No information available	
<b>Flash Point</b>	No information available	<b>Method -</b> No information available
<b>Evaporation Rate</b>	Not applicable	Solid
<b>Flammability (solid,gas)</b>	No information available	
<b>Explosion Limits</b>	No data available	
<b>Vapor Pressure</b>	No data available	
<b>Vapor Density</b>	Not applicable	Solid

## Cerium(IV) oxide, hydrated

<b>Specific Gravity / Density</b>	No data available	
<b>Bulk Density</b>	No data available	
<b>Water Solubility</b>	Insoluble in water	
<b>Solubility in other solvents</b>	No information available	
<b>Partition Coefficient (n-octanol/water)</b>		
<b>Autoignition Temperature</b>	No data available	
<b>Decomposition Temperature</b>	No data available	
<b>Viscosity</b>	Not applicable	Solid
<b>Explosive Properties</b>	No information available	
<b>Oxidizing Properties</b>	No information available	
<b>Molecular Formula</b>	CeO <sub>2</sub> . xH <sub>2</sub> O	
<b>Molecular Weight</b>	172.12(anhy)	

## SECTION 10. STABILITY AND REACTIVITY

<b>Stability</b>	Stable under normal conditions.
<b>Hazardous Reactions</b>	None under normal processing.
<b>Hazardous Polymerization</b>	No information available.
<b>Conditions to Avoid</b>	None known.
<b>Materials to avoid</b>	Oxidizing agent.

**Hazardous Decomposition Products** Metal oxides.

## SECTION 11. TOXICOLOGICAL INFORMATION

## Product Information

<b>(a) acute toxicity;</b>	
<b>(b) skin corrosion/irritation;</b>	Category 1 B
<b>(c) serious eye damage/irritation;</b>	Category 1
<b>(d) respiratory or skin sensitization;</b>	
<b>Respiratory</b>	No data available
<b>Skin</b>	No data available
<b>(e) germ cell mutagenicity;</b>	No data available
<b>(f) carcinogenicity;</b>	No data available
	There are no known carcinogenic chemicals in this product
<b>(g) reproductive toxicity;</b>	No data available
<b>(h) STOT-single exposure;</b>	No data available
<b>(i) STOT-repeated exposure;</b>	No data available

**Cerium(IV) oxide, hydrated**

<b>Target Organs</b>	No information available.
<b>(j) aspiration hazard;</b>	Not applicable Solid
<b>Symptoms / effects,both acute and delayed</b>	Product is a corrosive material. Use of gastric lavage or emesis is contraindicated. Possible perforation of stomach or esophagus should be investigated: Ingestion causes severe swelling, severe damage to the delicate tissue and danger of perforation

**SECTION 12. ECOLOGICAL INFORMATION**

<b>Ecotoxicity effects</b>	May cause long-term adverse effects in the environment. Do not allow material to contaminate ground water system.
<b>Persistence and Degradability</b>	Product contains heavy metals. Discharge into the environment must be avoided. Special pre-treatment is necessary
<b>Persistence</b>	Insoluble in water, May persist.
<b>Degradability</b>	Not relevant for inorganic substances.
<b>Degradation in sewage treatment plant</b>	Contains substances known to be hazardous to the environment or not degradable in waste water treatment plants.
<b>Bioaccumulative Potential</b>	May have some potential to bioaccumulate; Product has a high potential to bioconcentrate
<b>Mobility in soil</b>	Spillage unlikely to penetrate soil Is not likely mobile in the environment due its low water solubility
<b>Endocrine Disruptor Information</b>	This product does not contain any known or suspected endocrine disruptors
<b>Persistent Organic Pollutant</b>	This product does not contain any known or suspected substance
<b>Ozone Depletion Potential</b>	This product does not contain any known or suspected substance

**SECTION 13. DISPOSAL CONSIDERATIONS**

<b>Waste from Residues/Unused Products</b>	Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.
<b>Contaminated Packaging</b>	Dispose of this container to hazardous or special waste collection point.
<b>Other Information</b>	Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains. Do not flush to sewer. Large amounts will affect pH and harm aquatic organisms.

**SECTION 14. TRANSPORT INFORMATION****Road and Rail Transport**

<b>UN-No</b>	UN3262
<b>Proper Shipping Name</b>	Corrosive solid, basic, inorganic, n.o.s.
<b>Technical Shipping Name</b>	(Cerium(IV) oxide, hydrated)
<b>Hazard Class</b>	8
<b>Packing Group</b>	III

**IMDG/IMO**

<b>UN-No</b>	UN3262
--------------	--------

**Cerium(IV) oxide, hydrated**

**Proper Shipping Name** Corrosive solid, basic, inorganic, n.o.s.  
**Technical Shipping Name** (Cerium(IV) oxide, hydrated)  
**Hazard Class** 8  
**Packing Group** III

**IATA**

**UN-No** UN3262  
**Proper Shipping Name** CORROSIVE SOLID, BASIC, INORGANIC, N.O.S.\*  
**Technical Shipping Name** (Cerium(IV) oxide, hydrated)  
**Hazard Class** 8  
**Packing Group** III

**Special Precautions for User** No special precautions required

**SECTION 15. REGULATORY INFORMATION****International Inventories**

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
Cerium hydroxide (Ce(OH) <sub>4</sub> ), (T-4)-	-	-	X	X	234-599-7	X	X	X	X	X	X	KE-05410

**National Regulations****SECTION 16. OTHER INFORMATION**

**Prepared By** Health, Safety and Environmental Department  
**Revision Date** 01-May-2024  
**Revision Summary** New emergency telephone response service provider.

**Training Advice**

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

**Legend**

**CAS** - Chemical Abstracts Service

**EINECS/ELINCS** - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

**PICCS** - Philippines Inventory of Chemicals and Chemical Substances

**IECSC** - Chinese Inventory of Existing Chemical Substances

**KECL** - Korean Existing and Evaluated Chemical Substances

**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory

**DSL/NDSL** - Canadian Domestic Substances List/Non-Domestic Substances List

**ENCS** - Japanese Existing and New Chemical Substances

**AICS** - Australian Inventory of Chemical Substances

**NZIoC** - New Zealand Inventory of Chemicals

**WEL** - Workplace Exposure Limit

**ACGIH** - American Conference of Governmental Industrial Hygienists

**DNEL** - Derived No Effect Level

**RPE** - Respiratory Protective Equipment

**LC50** - Lethal Concentration 50%

**TWA** - Time Weighted Average

**IARC** - International Agency for Research on Cancer

**PNEC** - Predicted No Effect Concentration

**LD50** - Lethal Dose 50%

**EC50** - Effective Concentration 50%

**Cerium(IV) oxide, hydrated****NOEC** - No Observed Effect Concentration**PBT** - Persistent, Bioaccumulative, Toxic**POW** - Partition coefficient Octanol:Water**vPvB** - very Persistent, very Bioaccumulative**ICAO/IATA** - International Civil Aviation Organization/International Air Transport Association**ADR** - European Agreement Concerning the International Carriage of Dangerous Goods by Road**OECD** - Organisation for Economic Co-operation and Development**BCF** - Bioconcentration factor**IMO/IMDG** - International Maritime Organization/International Maritime Dangerous Goods Code**MARPOL** - International Convention for the Prevention of Pollution from Ships**ATE** - Acute Toxicity Estimate**VOC** - (Volatile Organic Compound)**Key literature references and sources for data**<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

**Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

**End of Safety Data Sheet**