

ALFAA22585

## Ethanethiol

### SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

<b>产品说明:</b> <b>Product Description:</b>	<b>乙硫醇</b> <b>Ethanethiol</b>
<b>Cat No. :</b>	<b>22585</b>
<b>Synonyms</b>	Ethyl mercaptan
<b>CAS No</b>	75-08-1
<b>Molecular Formula</b>	C2 H6 S
<b>Supplier</b>	Avocado Research Chemicals Ltd. (Part of Thermo Fisher Scientific) Shore Road, Heysham Lancashire, LA3 2XY, United Kingdom Office Tel: +44 (0) 1524 850506 Office Fax: +44 (0) 1524 850608
<b>Emergency Telephone Number</b>	For information <b>US</b> call: 001-800-227-6701 / <b>Europe</b> call: +32 14 57 52 11 Emergency Number <b>US</b> :001-201-796-7100 / <b>Europe</b> : +32 14 57 52 99 <b>CHEMTREC</b> Tel. No. <b>US</b> :001-800-424-9300 / <b>Europe</b> :001-703-527-3887
<b>E-mail address</b>	begel.sdsdesk@thermofisher.com
<b>Recommended Use</b>	Laboratory chemicals.
<b>Uses advised against</b>	No Information available

### SECTION 2. HAZARD IDENTIFICATION

Physical State	Appearance	Odor
Liquid	Colorless	Stench
<b>Emergency Overview</b>		
Highly flammable liquid and vapor. Harmful to aquatic life. Very toxic to aquatic life with long lasting effects. Harmful if swallowed. May cause an allergic skin reaction. Harmful if inhaled. Stench.		

#### Classification of the substance or mixture

Flammable liquids.	Category 2
Acute Oral Toxicity	Category 4
Acute Inhalation Toxicity - Vapors	Category 4
Skin Sensitization	Category 1
Acute aquatic toxicity	Category 1 Category 3
Chronic aquatic toxicity	Category 1

#### Label Elements

## Ethanethiol



Signal Word

Danger

**Hazard Statements**

H225 - Highly flammable liquid and vapor  
 H410 - Very toxic to aquatic life with long lasting effects  
 H317 - May cause an allergic skin reaction  
 H302 + H332 - Harmful if swallowed or if inhaled

**Precautionary Statements****Prevention**

P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking  
 P233 - Keep container tightly closed  
 P240 - Ground and bond container and receiving equipment  
 P241 - Use explosion-proof electrical/ ventilating/ lighting equipment  
 P242 - Use non-sparking tools  
 P243 - Take action to prevent static discharges  
 P261 - Avoid breathing dust/fume/gas/mist/vapors/spray  
 P264 - Wash face, hands and any exposed skin thoroughly after handling  
 P270 - Do not eat, drink or smoke when using this product  
 P271 - Use only outdoors or in a well-ventilated area  
 P272 - Contaminated work clothing should not be allowed out of the workplace  
 P280 - Wear protective gloves/protective clothing/eye protection/face protection

**Response**

P303 + P361 + P353 - IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water or shower  
 P304 + P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing  
 P312 - Call a POISON CENTER or doctor if you feel unwell  
 P330 - Rinse mouth  
 P370 + P378 - In case of fire: Use dry sand, dry chemical or alcohol-resistant foam to extinguish  
 P362 + P364 - Take off contaminated clothing and wash it before reuse

**Storage**

P403 + P235 - Store in a well-ventilated place. Keep cool

**Disposal**

P501 - Dispose of contents/ container to an approved waste disposal plant

**Physical and Chemical Hazards**

Vapors may cause flash fire or explosion. Highly flammable.

**Health Hazards**

Harmful if swallowed. May cause an allergic skin reaction. Harmful if inhaled.

**Environmental hazards**

Harmful to aquatic life. Very toxic to aquatic life with long lasting effects. Will likely be mobile in the environment due to its volatility. The product contains volatile organic compounds (VOC) which will evaporate easily from all surfaces.

**Other Hazards**

Stench. Toxic to terrestrial vertebrates. This product does not contain any known or suspected endocrine disruptors.

**SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS**

Component	CAS No	Weight %
Ethyl mercaptan	75-08-1	>95

**SECTION 4. FIRST AID MEASURES**

## Ethanethiol

**Eye Contact**

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.

**Skin Contact**

Wash off immediately with soap and plenty of water while removing all contaminated clothes and shoes. Get medical attention.

**Inhalation**

Remove from exposure, lie down. Remove to fresh air. If not breathing, give artificial respiration. Get medical attention.

**Ingestion**

Clean mouth with water. Get medical attention.

**Most important symptoms and effects**

Difficulty in breathing. May cause allergic skin reaction. Inhalation of high vapor concentrations may cause symptoms like headache, dizziness, tiredness, nausea and vomiting: Symptoms of allergic reaction may include rash, itching, swelling, trouble breathing, tingling of the hands and feet, dizziness, lightheadedness, chest pain, muscle pain or flushing

**Self-Protection of the First Aider**

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

**Notes to Physician**

Treat symptomatically.

**SECTION 5. FIRE-FIGHTING MEASURES****Suitable Extinguishing Media**

Carbon dioxide (CO<sub>2</sub>). Dry chemical. Water mist may be used to cool closed containers. Chemical foam. Water mist may be used to cool closed containers.

**Extinguishing media which must not be used for safety reasons**

Water may be ineffective.

**Specific Hazards Arising from the Chemical**

Vapors may travel to source of ignition and flash back. Extremely flammable. Containers may explode when heated. Vapors may form explosive mixtures with air. Do not allow run-off from fire-fighting to enter drains or water courses.

**Protective Equipment and Precautions for Firefighters**

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

**SECTION 6. ACCIDENTAL RELEASE MEASURES****Personal Precautions**

Remove all sources of ignition. Take precautionary measures against static discharges.

**Environmental Precautions**

Do not flush into surface water or sanitary sewer system. Do not allow material to contaminate ground water system. Prevent product from entering drains. Local authorities should be advised if significant spillages cannot be contained.

**Methods for Containment and Clean Up**

Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust). Keep in suitable, closed containers for disposal. Remove all sources of ignition. Use spark-proof tools and explosion-proof equipment. Do not let this chemical enter the environment.

Refer to protective measures listed in Sections 8 and 13.

## Ethanethiol

## SECTION 7. HANDLING AND STORAGE

**Handling**

Avoid contact with skin and eyes. Avoid contact with skin and clothing. Avoid breathing vapors or mists. Do not ingest. If swallowed then seek immediate medical assistance. Handle product only in closed system or provide appropriate exhaust ventilation. Use spark-proof tools and explosion-proof equipment. Use only non-sparking tools. Contents may develop pressure upon prolonged storage. Keep away from open flames, hot surfaces and sources of ignition. To avoid ignition of vapors by static electricity discharge, all metal parts of the equipment must be grounded. Take precautionary measures against static discharges.

**Storage**

Keep in a dry, cool and well-ventilated place. Keep container tightly closed. Keep away from heat, sparks and flame. Flammables area. Keep container tightly closed in a dry and well-ventilated place.

**Specific Use(s)**

Use in laboratories

## SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

**Control Parameters**

Component	China	Taiwan	Thailand	Hong Kong
Ethyl mercaptan	TWA: 1 mg/m <sup>3</sup> STEL: 2.5 mg/m <sup>3</sup>	-	Ceiling: 10 ppm	TWA: 0.5 ppm TWA: 1.3 mg/m <sup>3</sup>

Component	ACGIH TLV	OSHA PEL	NIOSH	The United Kingdom	European Union
Ethyl mercaptan	TWA: 0.5 ppm	(Vacated) TWA: 0.5 ppm (Vacated) TWA: 1 mg/m <sup>3</sup> Ceiling: 10 ppm Ceiling: 25 mg/m <sup>3</sup>	IDLH: 500 ppm Ceiling: 0.5 ppm Ceiling: 1.3 mg/m <sup>3</sup>	STEL: 2 ppm 15 min STEL: 5.2 mg/m <sup>3</sup> 15 min TWA: 0.5 ppm 8 hr TWA: 1.3 mg/m <sup>3</sup> 8 hr	

Legend

ACGIH - American Conference of Governmental Industrial Hygienists

OSHA - Occupational Safety and Health Administration

NIOSH: NIOSH - National Institute for Occupational Safety and Health

**Monitoring methods**

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS70 General methods for sampling airborne gases and vapours MDHS 88 Volatile organic compounds in air. Laboratory method using diffusive samplers, solvent desorption and gas chromatography MDHS 96 Volatile organic compounds in air - Laboratory method using pumped solid sorbent tubes, solvent desorption and gas chromatography

**Exposure Controls****Engineering Measures**

Use explosion-proof electrical/ventilating/lighting equipment. Ensure adequate ventilation, especially in confined areas. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

**Personal protective equipment**

**Eye Protection** Wear safety glasses with side shields (or goggles) (European standard - EN 166)

**Hand Protection** Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Natural rubber	See manufacturers	-		(minimum requirement)

## Ethanethiol

Nitrile rubber Neoprene PVC	recommendations	EN 374
-----------------------------------	-----------------	--------

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatability, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

<b>Skin and body protection</b>	Wear appropriate protective gloves and clothing to prevent skin exposure
<b>Respiratory Protection</b>	When workers are facing concentrations above the exposure limit they must use appropriate certified respirators.
<b>Large scale/emergency use</b>	Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced <b>Recommended Filter type:</b> Organic gases and vapours filter Type A Brown conforming to EN14387
<b>Small scale/Laboratory use</b>	Maintain adequate ventilation Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced. <b>Recommended half mask:-</b> Valve filtering: EN405; or; Half mask: EN140; plus filter, EN 141
<b>Hygiene Measures</b>	Handle in accordance with good industrial hygiene and safety practice.
<b>Environmental exposure controls</b>	Prevent product from entering drains. Do not allow material to contaminate ground water system. Local authorities should be advised if significant spillages cannot be contained.

## SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

<b>Appearance</b>	Colorless
<b>Physical State</b>	Liquid
<b>Odor</b>	Stench
<b>Odor Threshold</b>	No data available
<b>pH</b>	No information available
<b>Melting Point/Range</b>	-148 °C / -234.4 °F
<b>Softening Point</b>	No data available
<b>Boiling Point/Range</b>	35 °C / 95 °F @ 760 mmHg
<b>Flash Point</b>	-45 °C / -49 °F <b>Method -</b> No information available
<b>Evaporation Rate</b>	No data available
<b>Flammability (solid,gas)</b>	Not applicable Liquid
<b>Explosion Limits</b>	<b>Lower</b> 2.8 Vol% <b>Upper</b> 18.2 Vol%
<b>Vapor Pressure</b>	440 mmHg @ 20 °C
<b>Vapor Density</b>	2.14 (Air = 1.0) (Air = 1.0)
<b>Specific Gravity / Density</b>	0.830
<b>Bulk Density</b>	Not applicable Liquid
<b>Water Solubility</b>	Soluble in water
<b>Solubility in other solvents</b>	No information available
<b>Partition Coefficient (n-octanol/water)</b>	
<b>Component</b>	<b>log Pow</b>
Ethyl mercaptan	1.5

## Ethanethiol

<b>Autoignition Temperature</b>	298 °C / 568.4 °F	
<b>Decomposition Temperature</b>	No data available	
<b>Viscosity</b>	No data available	
<b>Explosive Properties</b>		Vapors may form explosive mixtures with air
<b>Oxidizing Properties</b>	No information available	
<b>Molecular Formula</b>	C <sub>2</sub> H <sub>6</sub> S	
<b>Molecular Weight</b>	62.13	

## SECTION 10. STABILITY AND REACTIVITY

<b>Stability</b>	Stable under normal conditions.
<b>Hazardous Reactions</b>	No information available.
<b>Hazardous Polymerization</b>	No information available.
<b>Conditions to Avoid</b>	Keep away from open flames, hot surfaces and sources of ignition. Incompatible products.
<b>Materials to avoid</b>	Bases. Strong oxidizing agents. Metals.
<b>Hazardous Decomposition Products</b>	Carbon monoxide (CO). Carbon dioxide (CO <sub>2</sub> ). Sulfur oxides.

## SECTION 11. TOXICOLOGICAL INFORMATION

## Product Information

## (a) acute toxicity;

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
Ethyl mercaptan	682 mg/kg (Rat)	LD50 > 2000 mg/kg ( Rat )	LC50 = 4420 ppm ( Rat ) 4 h

<b>(b) skin corrosion/irritation;</b>	Based on available data, the classification criteria are not met
<b>(c) serious eye damage/irritation;</b>	Based on available data, the classification criteria are not met
<b>(d) respiratory or skin sensitization;</b>	
<b>Respiratory</b>	Based on available data, the classification criteria are not met
<b>Skin</b>	Category 1 May cause sensitization by skin contact
<b>(e) germ cell mutagenicity;</b>	Based on available data, the classification criteria are not met Not mutagenic in AMES Test
<b>(f) carcinogenicity;</b>	Based on available data, the classification criteria are not met There are no known carcinogenic chemicals in this product
<b>(g) reproductive toxicity;</b>	Based on available data, the classification criteria are not met
<b>(h) STOT-single exposure;</b>	Based on available data, the classification criteria are not met
<b>(i) STOT-repeated exposure;</b>	Based on available data, the classification criteria are not met

## Ethanethiol

**Target Organs** None known.

**(j) aspiration hazard;** Based on available data, the classification criteria are not met

**Symptoms / effects, both acute and delayed** Inhalation of high vapor concentrations may cause symptoms like headache, dizziness, tiredness, nausea and vomiting: Symptoms of allergic reaction may include rash, itching, swelling, trouble breathing, tingling of the hands and feet, dizziness, lightheadedness, chest pain, muscle pain or flushing

## SECTION 12. ECOLOGICAL INFORMATION

**Ecotoxicity effects** Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment. The product contains following substances which are hazardous for the environment.

Component	Freshwater Fish	Water Flea	Freshwater Algae	Microtox
Ethyl mercaptan	LC50: = 2.4 mg/L, 96h (Oncorhynchus mykiss)	0.09 - 0.28 mg/L EC50 48 h 90 - 280 mg/L EC50 48 h		

**Persistence and Degradability** Not readily biodegradable  
**Persistence** Persistence is unlikely, based on information available.  
**Degradation in sewage treatment plant** Contains substances known to be hazardous to the environment or not degradable in waste water treatment plants.

**Bioaccumulative Potential** Bioaccumulation is unlikely

Component	log Pow	Bioconcentration factor (BCF)
Ethyl mercaptan	1.5	No data available

**Mobility in soil** The product contains volatile organic compounds (VOC) which will evaporate easily from all surfaces. Will likely be mobile in the environment due to its volatility. Disperses rapidly in air

**Endocrine Disruptor Information** This product does not contain any known or suspected endocrine disruptors  
**Persistent Organic Pollutant** This product does not contain any known or suspected substance  
**Ozone Depletion Potential** This product does not contain any known or suspected substance

## SECTION 13. DISPOSAL CONSIDERATIONS

**Waste from Residues/Unused Products** Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.

**Contaminated Packaging** Dispose of this container to hazardous or special waste collection point. Empty containers retain product residue, (liquid and/or vapor), and can be dangerous. Keep product and empty container away from heat and sources of ignition.

**Other Information** Do not flush to sewer. Waste codes should be assigned by the user based on the application for which the product was used. Can be landfilled or incinerated, when in compliance with local regulations. Do not let this chemical enter the environment. Do not empty into drains.

## SECTION 14. TRANSPORT INFORMATION

Road and Rail Transport

**UN-No** UN2363

## Ethanethiol

Proper Shipping Name ETHYL MERCAPTAN  
 Hazard Class 3  
 Packing Group I

**IMDG/IMO**

UN-No UN2363  
 Proper Shipping Name ETHYL MERCAPTAN  
 Hazard Class 3  
 Packing Group I

**IATA**

UN-No UN2363  
 Proper Shipping Name ETHYL MERCAPTAN  
 Hazard Class 3  
 Packing Group I

Special Precautions for User No special precautions required

**SECTION 15. REGULATORY INFORMATION****International Inventories**

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
Ethyl mercaptan	X	X	X	X	200-837-3	X	X	X	X	X	X	X

**National Regulations****SECTION 16. OTHER INFORMATION**

Prepared By Health, Safety and Environmental Department  
 Revision Date 26-Apr-2024  
 Revision Summary New emergency telephone response service provider.

**Training Advice**

Chemical incident response training.

**Legend**

**CAS** - Chemical Abstracts Service

**EINECS/ELINCS** - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

**PICCS** - Philippines Inventory of Chemicals and Chemical Substances

**IECSC** - Chinese Inventory of Existing Chemical Substances

**KECL** - Korean Existing and Evaluated Chemical Substances

**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory

**DSL/NDL** - Canadian Domestic Substances List/Non-Domestic Substances List

**ENCS** - Japanese Existing and New Chemical Substances

**AICS** - Australian Inventory of Chemical Substances

**NZIoC** - New Zealand Inventory of Chemicals



**Ethanethiol****WEL** - Workplace Exposure Limit**ACGIH** - American Conference of Governmental Industrial Hygienists**DNEL** - Derived No Effect Level**RPE** - Respiratory Protective Equipment**LC50** - Lethal Concentration 50%**NOEC** - No Observed Effect Concentration**PBT** - Persistent, Bioaccumulative, Toxic**TWA** - Time Weighted Average**IARC** - International Agency for Research on Cancer**PNEC** - Predicted No Effect Concentration**LD50** - Lethal Dose 50%**EC50** - Effective Concentration 50%**POW** - Partition coefficient Octanol:Water**vPvB** - very Persistent, very Bioaccumulative**ICAO/IATA** - International Civil Aviation Organization/International Air Transport Association**ADR** - European Agreement Concerning the International Carriage of Dangerous Goods by Road**OECD** - Organisation for Economic Co-operation and Development**BCF** - Bioconcentration factor**IMO/IMDG** - International Maritime Organization/International Maritime Dangerous Goods Code**MARPOL** - International Convention for the Prevention of Pollution from Ships**ATE** - Acute Toxicity Estimate**VOC** - (Volatile Organic Compound)**Key literature references and sources for data**<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

**Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

**End of Safety Data Sheet**