

ALFAA35688

Cerium(III) chloride, anhydrous

SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

产品说明: 三氯化铈(III)
Product Description: Cerium(III) chloride, anhydrous

Cat No. : 35688
Synonyms Cerium trichloride.
CAS No 7790-86-5
Molecular Formula Ce Cl₃

Supplier Avocado Research Chemicals Ltd.
(Part of Thermo Fisher Scientific)
Shore Road, Heysham
Lancashire, LA3 2XY,
United Kingdom
Office Tel: +44 (0) 1524 850506
Office Fax: +44 (0) 1524 850608

Emergency Telephone Number For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11
Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99
CHEMTREC Tel. No. **US**:001-800-424-9300 / **Europe**:001-703-527-3887

E-mail address begel.sdsdesk@thermofisher.com

Recommended Use Laboratory chemicals.
Uses advised against No Information available

SECTION 2. HAZARD IDENTIFICATION

Physical State
Powder Solid

Appearance
Light grey

Odor
Odorless

Emergency Overview

May be harmful if swallowed. Causes severe skin burns and eye damage. Very toxic to aquatic life with long lasting effects.
Hygroscopic.

Classification of the substance or mixture

Acute Oral Toxicity	Category 5
Skin Corrosion/Irritation	C Category 1
Serious Eye Damage/Eye Irritation	Category 1
Acute aquatic toxicity	Category 1
Chronic aquatic toxicity	Category 1

Label Elements



Cerium(III) chloride, anhydrous

Signal Word**Danger****Hazard Statements**

H303 - May be harmful if swallowed
H314 - Causes severe skin burns and eye damage
H410 - Very toxic to aquatic life with long lasting effects

Precautionary Statements**Prevention**

P264 - Wash face, hands and any exposed skin thoroughly after handling
P270 - Do not eat, drink or smoke when using this product
P280 - Wear protective gloves/protective clothing/eye protection/face protection

Response

P303 + P361 + P353 - IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water or shower
P301 + P330 + P331 - IF SWALLOWED: rinse mouth. Do NOT induce vomiting
P304 + P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing
P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing
P310 - Immediately call a POISON CENTER or doctor
P362 + P364 - Take off contaminated clothing and wash it before reuse

Storage

P403 - Store in a well-ventilated place

Disposal

P501 - Dispose of contents/ container to an approved waste disposal plant

Physical and Chemical Hazards

Hygroscopic.

Health Hazards

May be harmful if swallowed. Corrosive. Causes skin and eye burns.

Environmental hazards

Very toxic to aquatic life with long lasting effects. Will likely be mobile in the environment due to its water solubility. The product is water soluble, and may spread in water systems.

This product does not contain any known or suspected endocrine disruptors.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Component	CAS No	Weight %
Cerium chloride (CeCl ₃)	7790-86-5	>95

SECTION 4. FIRST AID MEASURES**General Advice**

Immediate medical attention is required. Show this safety data sheet to the doctor in attendance.

Eye Contact

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Immediate medical attention is required. Keep eye wide open while rinsing.

Skin Contact

Wash off immediately with soap and plenty of water while removing all contaminated clothes and shoes. Call a physician immediately.

Inhalation

Remove to fresh air. Call a physician or poison control center immediately. Do not use mouth-to-mouth method if victim ingested or inhaled the substance; give artificial respiration with the aid of a pocket mask equipped with a one-way valve or other proper respiratory medical device. If not breathing, give artificial respiration.

Ingestion

Cerium(III) chloride, anhydrous

Immediate medical attention is required. Do NOT induce vomiting. Never give anything by mouth to an unconscious person. Drink plenty of water.

Most important symptoms and effects

Causes burns by all exposure routes. Product is a corrosive material. Use of gastric lavage or emesis is contraindicated. Possible perforation of stomach or esophagus should be investigated: Ingestion causes severe swelling, severe damage to the delicate tissue and danger of perforation

Self-Protection of the First Aider

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

Notes to Physician

Treat symptomatically.

SECTION 5. FIRE-FIGHTING MEASURES**Suitable Extinguishing Media**

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Extinguishing media which must not be used for safety reasons

No information available.

Specific Hazards Arising from the Chemical

The product causes burns of eyes, skin and mucous membranes. Do not allow run-off from fire-fighting to enter drains or water courses.

Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear. Thermal decomposition can lead to release of irritating gases and vapors.

SECTION 6. ACCIDENTAL RELEASE MEASURES**Personal Precautions**

Evacuate personnel to safe areas. Use personal protective equipment as required. Avoid contact with skin, eyes or clothing.

Environmental Precautions

Do not flush into surface water or sanitary sewer system. Do not allow material to contaminate ground water system. Prevent product from entering drains. Local authorities should be advised if significant spillages cannot be contained.

Methods for Containment and Clean Up

Avoid dust formation. Sweep up and shovel into suitable containers for disposal.

Refer to protective measures listed in Sections 8 and 13.

SECTION 7. HANDLING AND STORAGE**Handling**

Do not breathe dust. Do not ingest. If swallowed then seek immediate medical assistance. Do not get in eyes, on skin, or on clothing. Use only under a chemical fume hood. Wear personal protective equipment/face protection.

Storage

Keep containers tightly closed in a dry, cool and well-ventilated place. Corrosives area. Store under an inert atmosphere.

Specific Use(s)

Use in laboratories

Cerium(III) chloride, anhydrous

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control Parameters

Monitoring methods

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS14/3 General methods for sampling and gravimetric analysis of respirable and inhalable dust

Exposure Controls

Engineering Measures

Ensure adequate ventilation, especially in confined areas. Ensure that eyewash stations and safety showers are close to the workstation location. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

Personal protective equipment

Eye Protection Goggles (European standard - EN 166)

Hand Protection Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Natural rubber	See manufacturers	-	EN 374	(minimum requirement)
Nitrile rubber	recommendations			
Neoprene				
PVC				

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

Skin and body protection Long sleeved clothing

Respiratory Protection When workers are facing concentrations above the exposure limit they must use appropriate certified respirators. To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly

Large scale/emergency use Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced
Recommended Filter type: Particulates filter conforming to EN 143

Small scale/Laboratory use Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.
Recommended half mask:- Particle filtering: EN149:2001
When RPE is used a face piece Fit Test should be conducted

Hygiene Measures Handle in accordance with good industrial hygiene and safety practice.

Environmental exposure controls Prevent product from entering drains. Do not allow material to contaminate ground water system. Local authorities should be advised if significant spillages cannot be contained.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Cerium(III) chloride, anhydrous

Appearance	Light grey	
Physical State	Powder Solid	
Odor	Odorless	
Odor Threshold	No data available	
pH	No information available	
Melting Point/Range	848 °C / 1558.4 °F	
Softening Point	No data available	
Boiling Point/Range	1727 °C / 3140.6 °F	@ 760 mmHg
Flash Point	No information available	Method - No information available
Evaporation Rate	Not applicable	Solid
Flammability (solid,gas)	No information available	
Explosion Limits	No data available	
Vapor Pressure	No information available	
Vapor Density	Not applicable	Solid
Specific Gravity / Density	No data available	
Bulk Density	No data available	
Water Solubility	Soluble	
Solubility in other solvents	No information available	
Partition Coefficient (n-octanol/water)		
Autoignition Temperature	Not applicable	
Decomposition Temperature	No data available	
Viscosity	Not applicable	Solid
Explosive Properties	No information available	
Oxidizing Properties	No information available	
Molecular Formula	Ce Cl ₃	
Molecular Weight	246.48	

SECTION 10. STABILITY AND REACTIVITY

Stability	Hygroscopic.
Hazardous Reactions	None under normal processing.
Hazardous Polymerization	Hazardous polymerization does not occur.
Conditions to Avoid	Incompatible products. Excess heat. Exposure to moist air or water.
Materials to avoid	Bases. Strong oxidizing agents. Strong acids.
Hazardous Decomposition Products	Thermal decomposition can lead to release of irritating gases and vapors. Hydrogen chloride gas.

SECTION 11. TOXICOLOGICAL INFORMATION

Product Information

(a) acute toxicity;

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
Cerium chloride (CeCl ₃)	2800 mg/kg (Rat)		

(b) skin corrosion/irritation; Category 1 C

(c) serious eye damage/irritation; Category 1

(d) respiratory or skin sensitization;

Cerium(III) chloride, anhydrous

Respiratory Skin	Based on available data, the classification criteria are not met Based on available data, the classification criteria are not met
(e) germ cell mutagenicity;	Based on available data, the classification criteria are not met
(f) carcinogenicity;	Based on available data, the classification criteria are not met There are no known carcinogenic chemicals in this product
(g) reproductive toxicity;	Based on available data, the classification criteria are not met
(h) STOT-single exposure;	Based on available data, the classification criteria are not met
(i) STOT-repeated exposure;	Based on available data, the classification criteria are not met
Target Organs	None known.
(j) aspiration hazard;	Not applicable Solid
Other Adverse Effects	The toxicological properties have not been fully investigated.
Symptoms / effects, both acute and delayed	Product is a corrosive material. Use of gastric lavage or emesis is contraindicated. Possible perforation of stomach or esophagus should be investigated: Ingestion causes severe swelling, severe damage to the delicate tissue and danger of perforation

SECTION 12. ECOLOGICAL INFORMATION

Ecotoxicity effects Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment. The product contains following substances which are hazardous for the environment.

Component	Freshwater Fish	Water Flea	Freshwater Algae	Microtox
Cerium chloride (CeCl ₃)	LC50: 0.13 mg/L/96h (Oncorhynchus Mykiss)	EC50: 6.9 mg/L/48h		

Persistence and Degradability
Persistence Soluble in water, Persistence is unlikely, based on information available.
Degradability Not relevant for inorganic substances.
Degradation in sewage treatment plant Contains substances known to be hazardous to the environment or not degradable in waste water treatment plants.

Bioaccumulative Potential Bioaccumulation is unlikely

Bioconcentration factor (BCF)	89
--------------------------------------	----

Mobility in soil The product is water soluble, and may spread in water systems Will likely be mobile in the environment due to its water solubility Highly mobile in soils

Endocrine Disruptor Information This product does not contain any known or suspected endocrine disruptors
Persistent Organic Pollutant This product does not contain any known or suspected substance
Ozone Depletion Potential This product does not contain any known or suspected substance

Cerium(III) chloride, anhydrous

SECTION 13. DISPOSAL CONSIDERATIONS

Waste from Residues/Unused Products	Should not be released into the environment. Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.
Contaminated Packaging	Dispose of this container to hazardous or special waste collection point.
Other Information	Do not flush to sewer. Large amounts will affect pH and harm aquatic organisms. Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains. Do not let this chemical enter the environment.

SECTION 14. TRANSPORT INFORMATION

Road and Rail Transport

UN-No	UN1759
Proper Shipping Name	Corrosive solid, n.o.s.
Technical Shipping Name	Cerium chloride (CeCl ₃)
Hazard Class	8
Packing Group	II

IMDG/IMO

UN-No	UN1759
Proper Shipping Name	Corrosive solid, n.o.s.
Technical Shipping Name	Cerium chloride (CeCl ₃)
Hazard Class	8
Packing Group	II

IATA

UN-No	UN1759
Proper Shipping Name	Corrosive solid, n.o.s.
Technical Shipping Name	Cerium chloride (CeCl ₃)
Hazard Class	8
Packing Group	II

Special Precautions for User No special precautions required

SECTION 15. REGULATORY INFORMATION

International Inventories

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
Cerium chloride (CeCl ₃)	-	-	X	X	232-227-8	X	X	-	X	X	X	KE-05416

National Regulations

Cerium(III) chloride, anhydrous**SECTION 16. OTHER INFORMATION**

Prepared By Health, Safety and Environmental Department
Creation Date 19-Aug-2011
Revision Date 23-Apr-2024
Revision Summary New emergency telephone response service provider.

Training Advice
Chemical incident response training.

Legend

CAS - Chemical Abstracts Service	TSCA - United States Toxic Substances Control Act Section 8(b) Inventory
EINECS/ELINCS - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances	DSL/NDL - Canadian Domestic Substances List/Non-Domestic Substances List
PICCS - Philippines Inventory of Chemicals and Chemical Substances	ENCS - Japanese Existing and New Chemical Substances
IECSC - Chinese Inventory of Existing Chemical Substances	AICS - Australian Inventory of Chemical Substances
KECL - Korean Existing and Evaluated Chemical Substances	NZIoC - New Zealand Inventory of Chemicals
WEL - Workplace Exposure Limit	TWA - Time Weighted Average
ACGIH - American Conference of Governmental Industrial Hygienists	IARC - International Agency for Research on Cancer
DNEL - Derived No Effect Level	PNEC - Predicted No Effect Concentration
RPE - Respiratory Protective Equipment	LD50 - Lethal Dose 50%
LC50 - Lethal Concentration 50%	EC50 - Effective Concentration 50%
NOEC - No Observed Effect Concentration	POW - Partition coefficient Octanol:Water
PBT - Persistent, Bioaccumulative, Toxic	vPvB - very Persistent, very Bioaccumulative
ICAO/IATA - International Civil Aviation Organization/International Air Transport Association	IMO/IMDG - International Maritime Organization/International Maritime Dangerous Goods Code
ADR - European Agreement Concerning the International Carriage of Dangerous Goods by Road	MARPOL - International Convention for the Prevention of Pollution from Ships
OECD - Organisation for Economic Co-operation and Development 89	ATE - Acute Toxicity Estimate
	VOC - (Volatile Organic Compound)

Key literature references and sources for data
<https://echa.europa.eu/information-on-chemicals>
Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet