

ALFAA41385

Chlorhexidine digluconate, 20% w/v aqueous solution, non-sterile

SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

产品说明: 葡萄糖酸氯己定
Product Description: Chlorhexidine digluconate, 20% w/v aqueous solution, non-sterile

Cat No. : 41385
Molecular Formula C₂₂ H₃₀ Cl₂ N₁₀ . 2 C₆ H₁₂ O₇

Supplier Avocado Research Chemicals Ltd.
(Part of Thermo Fisher Scientific)
Shore Road, Heysham
Lancashire, LA3 2XY,
United Kingdom
Office Tel: +44 (0) 1524 850506
Office Fax: +44 (0) 1524 850608

Emergency Telephone Number For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11
Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99
CHEMTREC Tel. No. **US**:001-800-424-9300 / **Europe**:001-703-527-3887

E-mail address begel.sdsdesk@thermofisher.com

Recommended Use Laboratory chemicals.
Uses advised against No Information available

SECTION 2. HAZARD IDENTIFICATION

Physical State
Liquid

Appearance
No information available

Odor
No information available

Emergency Overview
Causes serious eye damage. Very toxic to aquatic life.

Classification of the substance or mixture

Serious Eye Damage/Eye Irritation	Category 1
Acute aquatic toxicity	Category 1

Label Elements



Signal Word

Danger

Hazard Statements

H318 - Causes serious eye damage
H400 - Very toxic to aquatic life

Chlorhexidine digluconate, 20% w/v aqueous solution, non-sterile

Precautionary Statements**Prevention**

P280 - Wear protective gloves/protective clothing/eye protection/face protection

Response

P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing

P310 - Immediately call a POISON CENTER or doctor

Storage

P403 - Store in a well-ventilated place

Disposal

P501 - Dispose of contents/ container to an approved waste disposal plant

Physical and Chemical Hazards

None identified.

Health Hazards

The product contains no substances which at their given concentration are considered to be hazardous to health.

Environmental hazards

Very toxic to aquatic life. .

This product does not contain any known or suspected endocrine disruptors. Toxic to terrestrial vertebrates.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Component	CAS No	Weight %
Water	7732-18-5	80
Chlorhexidine digluconate	18472-51-0	20

SECTION 4. FIRST AID MEASURES**General Advice**

If symptoms persist, call a physician.

Eye Contact

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.

Skin Contact

Wash off immediately with plenty of water for at least 15 minutes. If skin irritation persists, call a physician.

Inhalation

Remove to fresh air. If not breathing, give artificial respiration. Get medical attention if symptoms occur.

Ingestion

Clean mouth with water and drink afterwards plenty of water.

Most important symptoms and effects

None reasonably foreseeable. Causes severe eye damage.

Self-Protection of the First Aider

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

Notes to Physician

Treat symptomatically.

SECTION 5. FIRE-FIGHTING MEASURES**Suitable Extinguishing Media**

Chlorhexidine digluconate, 20% w/v aqueous solution, non-sterile

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Extinguishing media which must not be used for safety reasons

No information available.

Specific Hazards Arising from the Chemical

Do not allow run-off from fire-fighting to enter drains or water courses.

Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

SECTION 6. ACCIDENTAL RELEASE MEASURES**Personal Precautions**

Ensure adequate ventilation. Use personal protective equipment as required.

Environmental Precautions

Do not flush into surface water or sanitary sewer system. Do not allow material to contaminate ground water system. Prevent product from entering drains. Local authorities should be advised if significant spillages cannot be contained.

Methods for Containment and Clean Up

Soak up with inert absorbent material. Keep in suitable, closed containers for disposal.

Refer to protective measures listed in Sections 8 and 13.

SECTION 7. HANDLING AND STORAGE**Handling**

Wear personal protective equipment/face protection. Ensure adequate ventilation. Do not get in eyes, on skin, or on clothing. Avoid ingestion and inhalation.

Storage

Keep containers tightly closed in a dry, cool and well-ventilated place.

Specific Use(s)

Use in laboratories

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION**Control Parameters****Exposure Controls****Engineering Measures**

Ensure that eyewash stations and safety showers are close to the workstation location. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

Personal protective equipment**Eye Protection**

Goggles (European standard - EN 166)

Hand Protection

Protective gloves

Chlorhexidine digluconate, 20% w/v aqueous solution, non-sterile

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Natural rubber	See manufacturers recommendations	-	EN 374	(minimum requirement)
Nitrile rubber				
Neoprene				
PVC				

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

Skin and body protection	Long sleeved clothing
Respiratory Protection	When workers are facing concentrations above the exposure limit they must use appropriate certified respirators. To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly
Large scale/emergency use	Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced Recommended Filter type: Particulates filter conforming to EN 143
Small scale/Laboratory use	Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced. Recommended half mask:- Particle filtering: EN149:2001 When RPE is used a face piece Fit Test should be conducted

Hygiene Measures Handle in accordance with good industrial hygiene and safety practice.

Environmental exposure controls Prevent product from entering drains. Do not allow material to contaminate ground water system. Local authorities should be advised if significant spillages cannot be contained.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance		
Physical State	Liquid	
Odor	No information available	
Odor Threshold	No data available	
pH	No information available	
Melting Point/Range	No data available	
Softening Point	No data available	
Boiling Point/Range	No information available	
Flash Point	No information available	Method - No information available
Evaporation Rate	No data available	
Flammability (solid,gas)	Not applicable	Liquid
Explosion Limits	No data available	
Vapor Pressure	No data available	
Vapor Density	No data available	(Air = 1.0)
Specific Gravity / Density	1.06	
Bulk Density	Not applicable	Liquid
Water Solubility	No information available	
Solubility in other solvents	No information available	
Partition Coefficient (n-octanol/water)		
Component	log Pow	
Chlorohexidine digluconate	-1.81	
Autoignition Temperature	No data available	
Decomposition Temperature	No data available	

Chlorhexidine digluconate, 20% w/v aqueous solution, non-sterile

Viscosity No data available
Explosive Properties No information available
Oxidizing Properties No information available

Molecular Formula C₂₂ H₃₀ Cl₂ N₁₀ . 2 C₆ H₁₂ O₇
Molecular Weight 897.77

SECTION 10. STABILITY AND REACTIVITY

Stability Stable under normal conditions.
Hazardous Reactions None under normal processing.
Hazardous Polymerization Hazardous polymerization does not occur.
Conditions to Avoid Incompatible products. Excess heat.
Materials to avoid Strong oxidizing agents.

Hazardous Decomposition Products None under normal use conditions.

SECTION 11. TOXICOLOGICAL INFORMATION

Product Information

(a) acute toxicity;
Toxicology data for the components

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
Water	-	-	-
Chlorhexidine digluconate	2 g/kg (Rat) 1260 mg/kg (Mouse)	LD50 > 5000 mg/kg (Rabbit)	-

(b) skin corrosion/irritation; No data available
(c) serious eye damage/irritation; Category 1
(d) respiratory or skin sensitization;
Respiratory No data available
Skin No data available
(e) germ cell mutagenicity; No data available
(f) carcinogenicity; No data available
There are no known carcinogenic chemicals in this product
(g) reproductive toxicity; No data available
(h) STOT-single exposure; No data available
(i) STOT-repeated exposure; No data available
Target Organs None known.

Chlorhexidine digluconate, 20% w/v aqueous solution, non-sterile

(j) aspiration hazard; No data available

Symptoms / effects, both acute and delayed No information available

SECTION 12. ECOLOGICAL INFORMATION

Ecotoxicity effects Very toxic to aquatic organisms. The product contains following substances which are hazardous for the environment.

Persistence and Degradability
Degradation in sewage treatment plant No information available
Contains substances known to be hazardous to the environment or not degradable in waste water treatment plants.

Bioaccumulative Potential No information available

Component	log Pow	Bioconcentration factor (BCF)
Chlorhexidine digluconate	-1.81	No data available

Mobility in soil No information available

Endocrine Disruptor Information This product does not contain any known or suspected endocrine disruptors
Persistent Organic Pollutant This product does not contain any known or suspected substance
Ozone Depletion Potential This product does not contain any known or suspected substance**SECTION 13. DISPOSAL CONSIDERATIONS**

Waste from Residues/Unused Products Should not be released into the environment. Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.

Contaminated Packaging Dispose of this container to hazardous or special waste collection point.

Other Information Do not flush to sewer. Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains. Do not let this chemical enter the environment.

SECTION 14. TRANSPORT INFORMATION**Road and Rail Transport**UN-No UN3082
Proper Shipping Name Environmentally hazardous substances, liquid, n.o.s.
Technical Shipping Name Chlorhexidine digluconate
Hazard Class 9
Packing Group III**IMDG/IMO**UN-No UN3082
Proper Shipping Name Environmentally hazardous substances, liquid, n.o.s.
Technical Shipping Name Chlorhexidine digluconate
Hazard Class 9
Packing Group III

Chlorhexidine digluconate, 20% w/v aqueous solution, non-sterile

IATA

UN-No UN3082
Proper Shipping Name Environmentally hazardous substances, liquid, n.o.s.
Technical Shipping Name Chlorohexidine digluconate
Hazard Class 9
Packing Group III

Special Precautions for User No special precautions required

SECTION 15. REGULATORY INFORMATION**International Inventories**

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
Water	-	-	X	X	231-791-2	X	X	X	X		X	KE-35400
Chlorohexidine digluconate	-	-	X	X	242-354-0	X	X	-	X		X	KE-17668

National Regulations**SECTION 16. OTHER INFORMATION**

Prepared By Health, Safety and Environmental Department
Creation Date 23-Nov-2012
Revision Date 07-Aug-2024
Revision Summary New emergency telephone response service provider.

Training Advice

Chemical incident response training.

Legend

CAS - Chemical Abstracts Service

EINECS/ELINCS - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

PICCS - Philippines Inventory of Chemicals and Chemical Substances

IECSC - Chinese Inventory of Existing Chemical Substances

KECL - Korean Existing and Evaluated Chemical Substances

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

ENCS - Japanese Existing and New Chemical Substances

AICS - Australian Inventory of Chemical Substances

NZIoC - New Zealand Inventory of Chemicals

WEL - Workplace Exposure Limit

ACGIH - American Conference of Governmental Industrial Hygienists

DNEL - Derived No Effect Level

RPE - Respiratory Protective Equipment

LC50 - Lethal Concentration 50%

NOEC - No Observed Effect Concentration

PBT - Persistent, Bioaccumulative, Toxic

TWA - Time Weighted Average

IARC - International Agency for Research on Cancer

PNEC - Predicted No Effect Concentration

LD50 - Lethal Dose 50%

EC50 - Effective Concentration 50%

POW - Partition coefficient Octanol:Water

vPvB - very Persistent, very Bioaccumulative

Chlorhexidine digluconate, 20% w/v aqueous solution, non-sterile

ICAO/IATA - International Civil Aviation Organization/International Air Transport Association

ADR - European Agreement Concerning the International Carriage of Dangerous Goods by Road

OECD - Organisation for Economic Co-operation and Development

BCF - Bioconcentration factor

IMO/IMDG - International Maritime Organization/International Maritime Dangerous Goods Code

MARPOL - International Convention for the Prevention of Pollution from Ships

ATE - Acute Toxicity Estimate

VOC - (Volatile Organic Compound)

Key literature references and sources for data

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

Physical hazards

On basis of test data

Health Hazards

Calculation method

Environmental hazards

Calculation method

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet