

## SAFETY DATA SHEET

Creation Date 25-Jun-2010

Revision Date 25-Feb-2020

Revision Number 2

### 1. Identification

**Product Name** Ethylenediaminetetraacetic acid disodium salt, 0.200N (0.1M)  
Standardized solution

**Cat No. :** 39783

**Synonyms** EDTA disodium salt

**Recommended Use** Laboratory chemicals.

**Uses advised against** Food, drug, pesticide or biocidal product use.

**Details of the supplier of the safety data sheet**

**Company**

Alfa Aesar  
Thermo Fisher Scientific Chemicals, Inc.  
30 Bond Street  
Ward Hill, MA 01835-8099  
Tel: 800-343-0660  
Fax: 800-322-4757  
**Email:** tech@alfa.com  
www.alfa.com

**Emergency Telephone Number**

During normal business hours (Monday-Friday, 8am-7pm EST), call (800) 343-0660.  
After normal business hours, call Carechem 24 at (866) 928-0789.

### 2. Hazard(s) identification

**Classification**

Classification under 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Based on available data, the classification criteria are not met

**Label Elements**

None required

**Hazards not otherwise classified (HNOC)**

None identified

### 3. Composition/Information on Ingredients

Component	CAS-No	Weight %
-----------	--------	----------

Water	7732-18-5	>95
Disodium EDTA	139-33-3	<5

#### 4. First-aid measures

<b>Eye Contact</b>	Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.
<b>Skin Contact</b>	Wash off immediately with plenty of water for at least 15 minutes. Get medical attention immediately if symptoms occur.
<b>Inhalation</b>	Remove to fresh air. Get medical attention immediately if symptoms occur.
<b>Ingestion</b>	Clean mouth with water and drink afterwards plenty of water. Get medical attention if symptoms occur.
<b>Most important symptoms and effects</b>	None reasonably foreseeable.
<b>Notes to Physician</b>	Treat symptomatically

#### 5. Fire-fighting measures

<b>Unsuitable Extinguishing Media</b>	No information available
<b>Flash Point</b>	Not applicable
<b>Method -</b>	No information available
<b>Autoignition Temperature</b>	No information available
<b>Explosion Limits</b>	
<b>Upper</b>	No data available
<b>Lower</b>	No data available
<b>Sensitivity to Mechanical Impact</b>	No information available
<b>Sensitivity to Static Discharge</b>	No information available

#### Specific Hazards Arising from the Chemical

Keep product and empty container away from heat and sources of ignition.

#### Hazardous Combustion Products

Sodium oxides.

#### Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

#### NFPA

**Health**  
0

**Flammability**  
0

**Instability**  
0

**Physical hazards**  
N/A

#### 6. Accidental release measures

<b>Personal Precautions</b>	Ensure adequate ventilation. Use personal protective equipment as required. Avoid dust formation.
<b>Environmental Precautions</b>	Should not be released into the environment.
<b>Methods for Containment and Clean Up</b>	Sweep up and shovel into suitable containers for disposal. Avoid dust formation.

#### 7. Handling and storage

Handling	Wear personal protective equipment/face protection. Ensure adequate ventilation. Avoid contact with skin, eyes or clothing. Avoid ingestion and inhalation. Avoid dust formation.
Storage	Keep containers tightly closed in a dry, cool and well-ventilated place.

## 8. Exposure controls / personal protection

<u>Exposure Guidelines</u>	This product does not contain any hazardous materials with occupational exposure limits established by the region specific regulatory bodies.
----------------------------	---

Engineering Measures	None under normal use conditions.
----------------------	-----------------------------------

### Personal Protective Equipment

Eye/face Protection	Wear appropriate protective eyeglasses or chemical safety goggles as described by OSHA's eye and face protection regulations in 29 CFR 1910.133 or European Standard EN166.
Skin and body protection	Wear appropriate protective gloves and clothing to prevent skin exposure.
Respiratory Protection	No protective equipment is needed under normal use conditions.
Hygiene Measures	Handle in accordance with good industrial hygiene and safety practice.

## 9. Physical and chemical properties

Physical State	Liquid
Appearance	Colorless
Odor	No information available
Odor Threshold	No information available
pH	No information available
Melting Point/Range	No data available
Boiling Point/Range	No information available
Flash Point	Not applicable
Evaporation Rate	No information available
Flammability (solid,gas)	Not applicable
Flammability or explosive limits	
Upper	No data available
Lower	No data available
Vapor Pressure	No information available
Vapor Density	No information available
Specific Gravity	No information available
Solubility	miscible
Partition coefficient; n-octanol/water	No data available
Autoignition Temperature	No information available
Decomposition Temperature	No information available
Viscosity	No information available

## 10. Stability and reactivity

Reactive Hazard	None known, based on information available
Stability	Stable under normal conditions.
Conditions to Avoid	Incompatible products. Excess heat.
Incompatible Materials	Strong oxidizing agents

**Hazardous Decomposition Products** Sodium oxides

**Hazardous Polymerization** Hazardous polymerization does not occur.

**Hazardous Reactions** None under normal processing.

## 11. Toxicological information

### Acute Toxicity

#### Product Information

**Oral LD50**

Based on ATE data, the classification criteria are not met. ATE > 2000 mg/kg.

**Dermal LD50**

Based on ATE data, the classification criteria are not met. ATE > 2000 mg/kg.

**Vapor LC50**

Based on ATE data, the classification criteria are not met. ATE > 20 mg/l.

#### Component Information

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
Water	-	-	-
Disodium EDTA	LD50 > 2 g/kg ( Rat )	Not listed	Not listed

**Toxicologically Synergistic Products** No information available

### Delayed and immediate effects as well as chronic effects from short and long-term exposure

**Irritation** No information available

**Sensitization** No information available

**Carcinogenicity** The table below indicates whether each agency has listed any ingredient as a carcinogen.

Component	CAS-No	IARC	NTP	ACGIH	OSHA	Mexico
Water	7732-18-5	Not listed	Not listed	Not listed	Not listed	Not listed
Disodium EDTA	139-33-3	Not listed	Not listed	Not listed	Not listed	Not listed

**Mutagenic Effects** No information available

**Reproductive Effects** No information available.

**Developmental Effects** No information available.

**Teratogenicity** No information available.

**STOT - single exposure** None known

**STOT - repeated exposure** None known

**Aspiration hazard** No information available

**Symptoms / effects, both acute and delayed** No information available

**Endocrine Disruptor Information** No information available

**Other Adverse Effects** The toxicological properties have not been fully investigated.

## 12. Ecological information

### Ecotoxicity

Component	Freshwater Algae	Freshwater Fish	Microtox	Water Flea
Disodium EDTA	Not listed	Leuciscus idus: LC50 > 500 mg/L 96h	EC50 = 56 mg/L 8 h	> 100 mg/L 24h

**Persistence and Degradability** Miscible with water Persistence is unlikely based on information available.

**Bioaccumulation/ Accumulation** No information available.

**Mobility** . Will likely be mobile in the environment due to its water solubility.

### 13. Disposal considerations

**Waste Disposal Methods** Chemical waste generators must determine whether a discarded chemical is classified as a hazardous waste. Chemical waste generators must also consult local, regional, and national hazardous waste regulations to ensure complete and accurate classification.

### 14. Transport information

**DOT** Not regulated

**TDG** Not regulated

**IATA** Not regulated

**IMDG/IMO** Not regulated

### 15. Regulatory information

#### United States of America Inventory

Component	CAS-No	TSCA	TSCA Inventory notification - Active/Inactive	TSCA - EPA Regulatory Flags
Water	7732-18-5	X	ACTIVE	-
Disodium EDTA	139-33-3	X	ACTIVE	-

**Legend:**

**TSCA** - Toxic Substances Control Act, (40 CFR Part 710)

X - Listed

- - Not Listed

**TSCA 12(b)** - Notices of Export Not applicable

#### International Inventories

Canada (DSL/NDSL), Europe (EINECS/ELINCS/NLP), Philippines (PICCS), Japan (ENCS), Australia (AICS), China (IECSC), Korea (ECL).

Component	CAS-No	DSL	NDSL	EINECS	PICCS	ENCS	AICS	IECSC	KECL
Water	7732-18-5	X	-	231-791-2	X	X	X	X	KE-35400
Disodium EDTA	139-33-3	X	-	205-358-3	X	X	X	X	KE-13651

#### U.S. Federal Regulations

**SARA 313** Not applicable

**SARA 311/312 Hazard Categories** See section 2 for more information

**CWA (Clean Water Act)** Not applicable

**Clean Air Act** Not applicable

**OSHA** - Occupational Safety and Health Administration Not applicable

**CERCLA** Not applicable

**California Proposition 65** This product does not contain any Proposition 65 chemicals.

**U.S. State Right-to-Know**

**Regulations**

Component	Massachusetts	New Jersey	Pennsylvania	Illinois	Rhode Island
Water	-	-	X	-	-

**U.S. Department of Transportation**

Reportable Quantity (RQ): N  
DOT Marine Pollutant N  
DOT Severe Marine Pollutant N

**U.S. Department of Homeland Security**

This product does not contain any DHS chemicals.

**Other International Regulations**

**Mexico - Grade** No information available

**16. Other information**

**Prepared By** Health, Safety and Environmental Department  
Email: tech@alfa.com  
www.alfa.com

**Creation Date** 25-Jun-2010  
**Revision Date** 25-Feb-2020  
**Print Date** 25-Feb-2020  
**Revision Summary** SDS authoring systems update, replaces ChemGes SDS No. 1,134.

**Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

**End of SDS**