

ALFAA43324

Lithium tri-tert-butoxyaluminum hydride, nominally 1M in THF

SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

产品说明: 氢化三叔丁醇铝锂
Product Description: Lithium tri-tert-butoxyaluminum hydride, nominally 1M in THF

Cat No. : 43324
Synonyms LAH; Lithium tetrahydridoaluminate; Lithiumalanate
Molecular Formula Al H4 Li

Supplier Avocado Research Chemicals Ltd.
(Part of Thermo Fisher Scientific)
Shore Road, Heysham
Lancashire, LA3 2XY,
United Kingdom
Office Tel: +44 (0) 1524 850506
Office Fax: +44 (0) 1524 850608

Emergency Telephone Number For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11
Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99
CHEMTREC Tel. No. **US**:001-800-424-9300 / **Europe**:001-703-527-3887

E-mail address begel.sdsdesk@thermofisher.com

Recommended Use Laboratory chemicals.
Uses advised against No Information available

SECTION 2. HAZARD IDENTIFICATION

Physical State
Liquid

Appearance
Grey

Odor
Irritating

Emergency Overview

Highly flammable liquid and vapor. In contact with water releases flammable gases which may ignite spontaneously. Causes serious eye damage. Causes skin irritation. Suspected of causing cancer. May cause respiratory irritation. Harmful if swallowed. May cause drowsiness and dizziness. May form explosive peroxides. Moisture sensitive.

Classification of the substance or mixture

Flammable liquids.	Category 2
Substances/mixtures which, in contact with water, emit flammable gases	Category 1
Acute Oral Toxicity	Category 4
Skin Corrosion/Irritation	Category 2
Serious Eye Damage/Eye Irritation	Category 1
Carcinogenicity	Category 2
Specific target organ toxicity - (single exposure)	Category 3

Label Elements

Lithium tri-tert-butoxyaluminum hydride, nominally 1M in THF

**Signal Word****Danger****Hazard Statements**

H225 - Highly flammable liquid and vapor
 H260 - In contact with water releases flammable gases which may ignite spontaneously
 H318 - Causes serious eye damage
 H315 - Causes skin irritation
 H351 - Suspected of causing cancer
 H335 - May cause respiratory irritation
 H302 - Harmful if swallowed
 H336 - May cause drowsiness or dizziness

Precautionary Statements**Prevention**

P201 - Obtain special instructions before use
 P202 - Do not handle until all safety precautions have been read and understood
 P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking
 P231 + P232 - Handle and store contents under inert gas. Protect from moisture
 P240 - Ground and bond container and receiving equipment
 P242 - Use non-sparking tools
 P243 - Take action to prevent static discharges
 P261 - Avoid breathing dust/fume/gas/mist/vapors/spray
 P264 - Wash face, hands and any exposed skin thoroughly after handling
 P270 - Do not eat, drink or smoke when using this product
 P271 - Use only outdoors or in a well-ventilated area
 P280 - Wear protective gloves/protective clothing/eye protection/face protection

Response

P303 + P361 + P353 - IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water or shower
 P304 + P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing
 P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing
 P310 - Immediately call a POISON CENTER or doctor
 P330 - Rinse mouth
 P370 + P378 - In case of fire: Use dry sand, dry chemical or alcohol-resistant foam to extinguish
 P302 + P335 + P334 - IF ON SKIN: Brush off loose particles from skin. Immerse in cool water
 P362 + P364 - Take off contaminated clothing and wash it before reuse

Storage

P402 + P404 - Store in a dry place. Store in a closed container

Disposal

P501 - Dispose of contents/ container to an approved waste disposal plant

Physical and Chemical Hazards

Vapors may cause flash fire or explosion. Highly flammable. Reacts violently with water, liberating extremely flammable gases. May form explosive peroxides.

Health Hazards

Corrosive. Causes eye burns. Causes skin irritation. Causes serious eye damage. Suspected of causing cancer. May cause respiratory irritation. Harmful if swallowed. May cause drowsiness or dizziness.

Environmental hazards

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants. . Will likely be mobile in the environment due to its water solubility. Is not likely mobile in the environment. The product is water soluble, and may spread in water systems. Reacts violently with water.

Toxic to terrestrial vertebrates. This product does not contain any known or suspected endocrine disruptors.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Lithium tri-tert-butoxyaluminum hydride, nominally 1M in THF

Component	CAS No	Weight %
Tetrahydrofuran	109-99-9	96
Lithium aluminum hydride	16853-85-3	4

SECTION 4. FIRST AID MEASURES

General Advice

If symptoms persist, call a physician.

Eye Contact

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.

Skin Contact

Wash off immediately with plenty of water for at least 15 minutes. If skin irritation persists, call a physician.

Inhalation

Remove to fresh air. If not breathing, give artificial respiration. Get medical attention if symptoms occur.

Ingestion

Clean mouth with water and drink afterwards plenty of water.

Most important symptoms and effects

Causes severe eye damage. Inhalation of high vapor concentrations may cause symptoms like headache, dizziness, tiredness, nausea and vomiting: Causes central nervous system depression

Self-Protection of the First Aider

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

Notes to Physician

Treat symptomatically. Symptoms may be delayed.

SECTION 5. FIRE-FIGHTING MEASURES

Suitable Extinguishing Media

Water spray, carbon dioxide (CO₂), dry chemical, alcohol-resistant foam. Water mist may be used to cool closed containers.

Extinguishing media which must not be used for safety reasons

Water. Carbon dioxide (CO₂). Foam.

Specific Hazards Arising from the Chemical

Flammable. Contact with water liberates toxic gas. Water reactive. Produce flammable gases on contact with water. Containers may explode when heated. Vapors may form explosive mixtures with air. Vapors may travel to source of ignition and flash back.

Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

SECTION 6. ACCIDENTAL RELEASE MEASURES

Personal Precautions

Ensure adequate ventilation. Use personal protective equipment as required. Remove all sources of ignition. Take precautionary measures against static discharges.

Environmental Precautions

Lithium tri-tert-butoxyaluminum hydride, nominally 1M in THF

Should not be released into the environment.

Methods for Containment and Clean Up

Keep in suitable, closed containers for disposal. Soak up with inert absorbent material. Remove all sources of ignition. Use spark-proof tools and explosion-proof equipment.

Refer to protective measures listed in Sections 8 and 13.

SECTION 7. HANDLING AND STORAGE**Handling**

Wear personal protective equipment/face protection. Do not get in eyes, on skin, or on clothing. Ensure adequate ventilation. Avoid ingestion and inhalation. If peroxide formation is suspected, do not open or move container. Keep away from open flames, hot surfaces and sources of ignition. Use only non-sparking tools. To avoid ignition of vapors by static electricity discharge, all metal parts of the equipment must be grounded. Take precautionary measures against static discharges.

Storage

Keep away from heat, sparks and flame. Protect from direct sunlight. Keep from any possible contact with water. Flammables area. Keep under nitrogen. Shelf life 12 months. May form explosive peroxides on prolonged storage. Keep container tightly closed in a dry and well-ventilated place. Containers should be dated when opened and tested periodically for the presence of peroxides. Should crystals form in a peroxidizable liquid, peroxidation may have occurred and the product should be considered extremely dangerous. In this instance, the container should only be opened remotely by professionals.

Specific Use(s)

Use in laboratories

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION**Control Parameters**

Component	China	Taiwan	Thailand	Hong Kong
Tetrahydrofuran	TWA: 300 mg/m ³	TWA: 200 ppm TWA: 590 mg/m ³	TWA: 200 ppm	TWA: 200 ppm TWA: 590 mg/m ³ STEL: 250 ppm STEL: 737 mg/m ³

Component	ACGIH TLV	OSHA PEL	NIOSH	The United Kingdom	European Union
Tetrahydrofuran	TWA: 50 ppm STEL: 100 ppm Skin	(Vacated) TWA: 200 ppm (Vacated) TWA: 590 mg/m ³ (Vacated) STEL: 250 ppm (Vacated) STEL: 735 mg/m ³ TWA: 200 ppm TWA: 590 mg/m ³	IDLH: 2000 ppm TWA: 200 ppm TWA: 590 mg/m ³ STEL: 250 ppm STEL: 735 mg/m ³	STEL: 100 ppm 15 min STEL: 300 mg/m ³ 15 min TWA: 50 ppm 8 hr TWA: 150 mg/m ³ 8 hr Skin	TWA: 50 ppm (8h) TWA: 150 mg/m ³ (8h) STEL: 100 ppm (15min) STEL: 300 mg/m ³ (15min) Skin

Legend

ACGIH - American Conference of Governmental Industrial Hygienists

OSHA - Occupational Safety and Health Administration

NIOSH: NIOSH - National Institute for Occupational Safety and Health

Monitoring methods

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS70 General methods for sampling airborne gases and vapours MDHS 88 Volatile organic compounds in air. Laboratory method using diffusive samplers, solvent desorption and gas chromatography MDHS 96 Volatile organic compounds in air - Laboratory method using pumped solid sorbent tubes, solvent desorption and gas chromatography

Exposure Controls

Lithium tri-tert-butoxyaluminum hydride, nominally 1M in THF

Engineering Measures

Use explosion-proof electrical/ventilating/lighting equipment. Ensure that eyewash stations and safety showers are close to the workstation location. Ensure adequate ventilation, especially in confined areas. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

Personal protective equipment

Eye Protection Goggles (European standard - EN 166)

Hand Protection Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Butyl rubber	See manufacturers recommendations	-	EN 374	(minimum requirement)
Neoprene gloves				

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves.

(Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

Skin and body protection Long sleeved clothing

Respiratory Protection When workers are facing concentrations above the exposure limit they must use appropriate certified respirators.
To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly

Large scale/emergency use Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced
Recommended Filter type: low boiling organic solvent Type AX Brown conforming to EN371 or Organic gases and vapours filter Type A Brown conforming to EN14387

Small scale/Laboratory use Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.
Recommended half mask:- Valve filtering: EN405; or; Half mask: EN140; plus filter, EN 141
When RPE is used a face piece Fit Test should be conducted

Hygiene Measures Handle in accordance with good industrial hygiene and safety practice.

Environmental exposure controls No information available.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance	Grey	
Physical State	Liquid	
Odor	Irritating	
Odor Threshold	No data available	
pH	7	
Melting Point/Range	No data available	
Softening Point	No data available	
Boiling Point/Range	No information available	
Flash Point	-17 °C / 1.4 °F	Method - No information available
Evaporation Rate	No data available	
Flammability (solid,gas)	Not applicable	Liquid
Explosion Limits	No data available	

Lithium tri-tert-butoxyaluminum hydride, nominally 1M in THF

Vapor Pressure	No data available	
Vapor Density	No data available	(Air = 1.0)
Specific Gravity / Density	0.900	
Bulk Density	Not applicable	Liquid
Water Solubility	Reacts violently with water	
Solubility in other solvents	No information available	
Partition Coefficient (n-octanol/water)		
Component	log Pow	
Tetrahydrofuran	0.45	
Autoignition Temperature	No data available	
Decomposition Temperature	No data available	
Viscosity	No data available	
Explosive Properties		Vapors may form explosive mixtures with air
Oxidizing Properties	No information available	
Molecular Formula	Al H4 Li	
Molecular Weight	37.95	

SECTION 10. STABILITY AND REACTIVITY

Stability	Decomposes in contact with water. Moisture sensitive. heat sensitive. May form explosive peroxides.
Hazardous Reactions	None under normal processing.
Hazardous Polymerization	Hazardous polymerization does not occur.
Conditions to Avoid	Keep away from open flames, hot surfaces and sources of ignition. Excess heat. Exposure to light. Incompatible products. Exposure to moist air or water.
Materials to avoid	Acids. Water. Alcohols. Carbon dioxide (CO ₂). Oxidizing agent.
Hazardous Decomposition Products	Carbon monoxide (CO). Carbon dioxide (CO ₂). Hydrogen.

SECTION 11. TOXICOLOGICAL INFORMATION

Product Information

(a) acute toxicity;
Toxicology data for the components

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
Tetrahydrofuran	1650 mg/kg (Rat)	> 2000 mg/kg (Rabbit)	180 mg/L (Rat) 1 h 53.9 mg/L (Rat) 4 h

(b) skin corrosion/irritation; Category 2

(c) serious eye damage/irritation; Category 1

(d) respiratory or skin sensitization;

Respiratory Based on available data, the classification criteria are not met
Skin Based on available data, the classification criteria are not met

Component	Test method	Test species	Study result
Tetrahydrofuran 109-99-9 (96)	Local Lymph Node Assay OECD Test Guideline 429	mouse	non-sensitising

Lithium tri-tert-butoxyaluminum hydride, nominally 1M in THF

(e) germ cell mutagenicity; Based on available data, the classification criteria are not met

Component	Test method	Test species	Study result
Tetrahydrofuran 109-99-9 (96)	OECD Test Guideline 476 Gene cell mutation	in vivo Mammalian	negative
	OECD Test Guideline 473 Chromosomal aberration assay	in vitro Mammalian	negative

(f) carcinogenicity; Category 2The table below indicates whether each agency has listed any ingredient as a carcinogen
Limited evidence of a carcinogenic effect

Component	EU	UK	Germany	IARC
Tetrahydrofuran				Group 2B

(g) reproductive toxicity; Based on available data, the classification criteria are not met

Component	Test method	Test species / Duration	Study result
Tetrahydrofuran 109-99-9 (96)	OECD Test Guideline 416	Rat 2 Generation	NOAEL = 3,000 ppm

(h) STOT-single exposure; Category 3**Results / Target organs** Respiratory system
Central nervous system (CNS)**(i) STOT-repeated exposure;** Based on available data, the classification criteria are not met**Target Organs** None known.**(j) aspiration hazard;** Based on available data, the classification criteria are not met**Symptoms / effects, both acute and delayed** Inhalation of high vapor concentrations may cause symptoms like headache, dizziness, tiredness, nausea and vomiting: Causes central nervous system depression**SECTION 12. ECOLOGICAL INFORMATION****Ecotoxicity effects** Reacts with water so no ecotoxicity data for the substance is available.

Component	Freshwater Fish	Water Flea	Freshwater Algae	Microtox
Tetrahydrofuran	2160 mg/l LC50 = 96 h Pimephales promelas Leuciscus idus: LC50: 2820 mg/L/48h	EC50 48 h 3485 mg/l EC50: >10000 mg/L/24h		

Persistence and Degradability**Persistence** Persistence is unlikely, based on information available.
Degradability Reacts with water.
Degradation in sewage treatment plant Reacts violently with water.**Bioaccumulative Potential** Bioaccumulation is unlikely; Product does not bioaccumulate due to reaction with water

Component	log Pow	Bioconcentration factor (BCF)
Tetrahydrofuran	0.45	No data available

Lithium tri-tert-butoxyaluminum hydride, nominally 1M in THF

Mobility in soil The product is water soluble, and may spread in water systems Reacts violently with water Will likely be mobile in the environment due to its water solubility Is not likely mobile in the environment Highly mobile in soils

Endocrine Disruptor Information

Component	EU - Endocrine Disruptors Candidate List	EU - Endocrine Disruptors - Evaluated Substances	Japan - Endocrine Disruptor Information
Tetrahydrofuran	Group III Chemical		

Persistent Organic Pollutant This product does not contain any known or suspected substance

Ozone Depletion Potential This product does not contain any known or suspected substance

SECTION 13. DISPOSAL CONSIDERATIONS

Waste from Residues/Unused Products Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.

Contaminated Packaging Dispose of this container to hazardous or special waste collection point. Empty containers retain product residue, (liquid and/or vapor), and can be dangerous. Keep product and empty container away from heat and sources of ignition.

Other Information Do not flush to sewer. Waste codes should be assigned by the user based on the application for which the product was used. Can be landfilled or incinerated, when in compliance with local regulations. Do not empty into drains.

SECTION 14. TRANSPORT INFORMATION**Road and Rail Transport**

UN-No UN1411
Proper Shipping Name LITHIUM ALUMINIUM HYDRIDE, ETHEREAL
Hazard Class 4.3
Subsidiary Hazard Class 3
Packing Group I

IMDG/IMO

UN-No UN1411
Proper Shipping Name LITHIUM ALUMINIUM HYDRIDE, ETHEREAL
Hazard Class 4.3
Subsidiary Hazard Class 3
Packing Group I

IATA

UN-No UN1411
Proper Shipping Name LITHIUM ALUMINIUM HYDRIDE, ETHEREAL
Hazard Class 4.3
Subsidiary Hazard Class 3
Packing Group I

Special Precautions for User No special precautions required

SECTION 15. REGULATORY INFORMATION**International Inventories**

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

Lithium tri-tert-butoxyaluminum hydride, nominally 1M in THF

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
Tetrahydrofuran	X	X	X	X	203-726-8	X	X	X	X	X	X	KE-33454
Lithium aluminum hydride	X	X	X	X	240-877-9	X	-	X	X	X	X	KE-00990

National Regulations

SECTION 16. OTHER INFORMATION

Prepared By Health, Safety and Environmental Department
Creation Date 24-Nov-2010
Revision Date 08-May-2024
Revision Summary New emergency telephone response service provider.

Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

Fire prevention and fighting, identifying hazards and risks, static electricity, explosive atmospheres posed by vapours and dusts.

Chemical incident response training.

Legend

CAS - Chemical Abstracts Service

EINECS/ELINCS - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

PICCS - Philippines Inventory of Chemicals and Chemical Substances

IECSC - Chinese Inventory of Existing Chemical Substances

KECL - Korean Existing and Evaluated Chemical Substances

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

ENCS - Japanese Existing and New Chemical Substances

AICS - Australian Inventory of Chemical Substances

NZIoC - New Zealand Inventory of Chemicals

WEL - Workplace Exposure Limit

ACGIH - American Conference of Governmental Industrial Hygienists

DNEL - Derived No Effect Level

RPE - Respiratory Protective Equipment

LC50 - Lethal Concentration 50%

NOEC - No Observed Effect Concentration

PBT - Persistent, Bioaccumulative, Toxic

TWA - Time Weighted Average

IARC - International Agency for Research on Cancer

PNEC - Predicted No Effect Concentration

LD50 - Lethal Dose 50%

EC50 - Effective Concentration 50%

POW - Partition coefficient Octanol:Water

vPvB - very Persistent, very Bioaccumulative

ICAO/IATA - International Civil Aviation Organization/International Air Transport Association

ADR - European Agreement Concerning the International Carriage of Dangerous Goods by Road

OECD - Organisation for Economic Co-operation and Development

BCF - Bioconcentration factor

IMO/IMDG - International Maritime Organization/International Maritime Dangerous Goods Code

MARPOL - International Convention for the Prevention of Pollution from Ships

ATE - Acute Toxicity Estimate

VOC - (Volatile Organic Compound)

Key literature references and sources for data

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

Physical hazards

On basis of test data

Health Hazards

Calculation method

Lithium tri-tert-butoxyaluminum hydride, nominally 1M in THF

Environmental hazards

Calculation method

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet