

ALFAA41529

## Sodium DL-lactate, 60% w/w aqueous solution

### SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

<b>产品说明:</b> <b>Product Description:</b>	<b>DL-乳酸钠, 60% w/w 水溶液</b> <b>Sodium DL-lactate, 60% w/w aqueous solution</b>
<b>Cat No. :</b> <b>Synonyms</b>	<b>41529</b> Sodium DL-lactate; DL-Lactic acid sodium salt; Propanoic acid, 2-hydroxy-, monosodium salt
<b>Molecular Formula</b>	C3H5NaO3
<b>Supplier</b>	Avocado Research Chemicals Ltd. (Part of Thermo Fisher Scientific) Shore Road, Heysham Lancashire, LA3 2XY, United Kingdom Office Tel: +44 (0) 1524 850506 Office Fax: +44 (0) 1524 850608
<b>Emergency Telephone Number</b>	For information <b>US</b> call: 001-800-227-6701 / <b>Europe</b> call: +32 14 57 52 11 Emergency Number <b>US</b> :001-201-796-7100 / <b>Europe</b> : +32 14 57 52 99 <b>CHEMTREC</b> Tel. No. <b>US</b> :001-800-424-9300 / <b>Europe</b> :001-703-527-3887
<b>E-mail address</b>	begel.sdsdesk@thermofisher.com
<b>Recommended Use</b> <b>Uses advised against</b>	Laboratory chemicals. No Information available

### SECTION 2. HAZARD IDENTIFICATION

<b>Physical State</b> Viscous liquid Liquid	<b>Appearance</b> Light yellow	<b>Odor</b> No information available
<b>Emergency Overview</b>		
The product contains no substances which at their given concentration are considered to be hazardous to health.		

#### Classification of the substance or mixture

Based on available data, the classification criteria are not met

#### Label Elements

None required

#### **Storage**

P403 - Store in a well-ventilated place

#### **Disposal**

P501 - Dispose of contents/ container to an approved waste disposal plant

#### **Physical and Chemical Hazards**

None identified.

#### **Health Hazards**

# SAFETY DATA SHEET

## Sodium DL-lactate, 60% w/w aqueous solution

The product contains no substances which at their given concentration are considered to be hazardous to health.

### Environmental hazards

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants. . Will likely be mobile in the environment due to its water solubility. The product is water soluble, and may spread in water systems.

### Other Hazards

None known

Toxic to terrestrial vertebrates. This product does not contain any known or suspected endocrine disruptors.

## SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Component	CAS No	Weight %
Propanoic acid, 2-hydroxy-, monosodium salt	72-17-3	60
Water	7732-18-5	40

## SECTION 4. FIRST AID MEASURES

### Eye Contact

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.

### Skin Contact

Wash off immediately with plenty of water for at least 15 minutes. Get medical attention immediately if symptoms occur.

### Inhalation

Remove to fresh air. Get medical attention immediately if symptoms occur.

### Ingestion

Clean mouth with water and drink afterwards plenty of water. Get medical attention if symptoms occur.

### Most important symptoms and effects

None reasonably foreseeable.

### Self-Protection of the First Aider

No special precautions required.

### Notes to Physician

Treat symptomatically.

## SECTION 5. FIRE-FIGHTING MEASURES

### Suitable Extinguishing Media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

### Extinguishing media which must not be used for safety reasons

No information available.

### Specific Hazards Arising from the Chemical

Keep product and empty container away from heat and sources of ignition. Thermal decomposition can lead to release of irritating gases and vapors.

### Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

## SECTION 6. ACCIDENTAL RELEASE MEASURES

### Personal Precautions

# SAFETY DATA SHEET

## Sodium DL-lactate, 60% w/w aqueous solution

Ensure adequate ventilation. Use personal protective equipment as required.

### Environmental Precautions

Should not be released into the environment. See Section 12 for additional Ecological Information.

### Methods for Containment and Clean Up

Sweep up and shovel into suitable containers for disposal.

Refer to protective measures listed in Sections 8 and 13.

## SECTION 7. HANDLING AND STORAGE

### Handling

Wear personal protective equipment/face protection. Ensure adequate ventilation. Avoid contact with skin, eyes or clothing. Avoid ingestion and inhalation.

### Storage

Keep refrigerated. Keep container tightly closed.

### Specific Use(s)

Use in laboratories

## SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

### Control Parameters

### Exposure Controls

### Engineering Measures

Ensure that eyewash stations and safety showers are close to the workstation location. .

### Personal protective equipment

**Eye Protection**                      Wear safety glasses with side shields (or goggles) (European standard - EN 166)

**Hand Protection**                      Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Natural rubber	See manufacturers	-	EN 374	(minimum requirement)
Nitrile rubber	recommendations			
Neoprene				
PVC				

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatability, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

**Skin and body protection**              Wear appropriate protective gloves and clothing to prevent skin exposure

**Respiratory Protection**              When workers are facing concentrations above the exposure limit they must use appropriate certified respirators.

**Large scale/emergency use**            Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced

# SAFETY DATA SHEET

## Sodium DL-lactate, 60% w/w aqueous solution

**Recommended Filter type:** Particle filter

**Small scale/Laboratory use** Maintain adequate ventilation

**Hygiene Measures** Handle in accordance with good industrial hygiene and safety practice.

**Environmental exposure controls** No information available.

### SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

<b>Appearance</b>	Light yellow	
<b>Physical State</b>	Viscous liquid	Liquid
<b>Odor</b>	No information available	
<b>Odor Threshold</b>	No data available	
<b>pH</b>	7	
<b>Melting Point/Range</b>	17.2 °C / 63 °F	
<b>Softening Point</b>	No data available	
<b>Boiling Point/Range</b>	140 °C / 284 °F	
<b>Flash Point</b>	Not applicable	<b>Method -</b> No information available
<b>Evaporation Rate</b>	> 1 (Ether = 1.0)	
<b>Flammability (solid,gas)</b>	Not applicable	Liquid
<b>Explosion Limits</b>	No data available	
<b>Vapor Pressure</b>	14 mmHg @ 20 °C	
<b>Vapor Density</b>	0.7	(Air = 1.0)
<b>Specific Gravity / Density</b>	1.33	
<b>Bulk Density</b>	Not applicable	Liquid
<b>Water Solubility</b>	Miscible	
<b>Solubility in other solvents</b>	No information available	
<b>Partition Coefficient (n-octanol/water)</b>		
<b>Autoignition Temperature</b>	No data available	
<b>Decomposition Temperature</b>	No data available	
<b>Viscosity</b>	No data available	
<b>Explosive Properties</b>	No information available	
<b>Oxidizing Properties</b>	No information available	
<b>Molecular Formula</b>	C3H5NaO3	
<b>Molecular Weight</b>	112.06	

### SECTION 10. STABILITY AND REACTIVITY

<b>Stability</b>	Stable under normal conditions.
<b>Hazardous Reactions</b>	None under normal processing.
<b>Hazardous Polymerization</b>	Hazardous polymerization does not occur.
<b>Conditions to Avoid</b>	Incompatible products. Excess heat.
<b>Materials to avoid</b>	Strong oxidizing agents.

**Hazardous Decomposition Products** Sodium oxides. Carbon monoxide (CO). Carbon dioxide (CO<sub>2</sub>).

### SECTION 11. TOXICOLOGICAL INFORMATION

**Product Information**

# SAFETY DATA SHEET

## Sodium DL-lactate, 60% w/w aqueous solution

**(a) acute toxicity;**  
**Toxicology data for the components**

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
Propanoic acid, 2-hydroxy-, monosodium salt		LD50 > 2000 mg/kg ( Rabbit )	LC50 > 7.94 mg/L ( Rat ) 4 h
Water	-	-	-

**(b) skin corrosion/irritation;** No data available

**(c) serious eye damage/irritation;** No data available

**(d) respiratory or skin sensitization;**  
**Respiratory** No data available  
**Skin** No data available

**(e) germ cell mutagenicity;** No data available

**(f) carcinogenicity;** No data available  
 There are no known carcinogenic chemicals in this product

**(g) reproductive toxicity;** No data available

**(h) STOT-single exposure;** No data available

**(i) STOT-repeated exposure;** No data available  
**Target Organs** No information available.

**(j) aspiration hazard;** No data available

**Symptoms / effects, both acute and delayed** No information available

### SECTION 12. ECOLOGICAL INFORMATION

**Ecotoxicity effects** Contains no substances known to be hazardous to the environment or that are not degradable in waste water treatment plants.

**Persistence and Degradability**  
**Persistence** Miscible with water, Persistence is unlikely, based on information available.

**Bioaccumulative Potential** Bioaccumulation is unlikely

**Mobility in soil** The product is water soluble, and may spread in water systems Will likely be mobile in the environment due to its water solubility Highly mobile in soils

**Endocrine Disruptor Information** This product does not contain any known or suspected endocrine disruptors

## Sodium DL-lactate, 60% w/w aqueous solution

**Persistent Organic Pollutant  
Ozone Depletion Potential**

This product does not contain any known or suspected substance  
This product does not contain any known or suspected substance

**SECTION 13. DISPOSAL CONSIDERATIONS****Waste from Residues/Unused  
Products**

Chemical waste generators must determine whether a discarded chemical is classified as a hazardous waste. Consult local, regional, and national hazardous waste regulations to ensure complete and accurate classification.

**Contaminated Packaging**

Empty remaining contents. Dispose of in accordance with local regulations. Do not re-use empty containers.

**Other Information**

Waste codes should be assigned by the user based on the application for which the product was used.

**SECTION 14. TRANSPORT INFORMATION****Road and Rail Transport**

Not Regulated

**IMDG/IMO**

Not regulated

**IATA**

Not regulated

**Special Precautions for User**

No special precautions required

**SECTION 15. REGULATORY INFORMATION****International Inventories**

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
Propanoic acid, 2-hydroxy-, monosodium salt	-	-	X	X	200-772-0	X	X	X	X	X	X	KE-20862
Water	-	-	X	X	231-791-2	X	X	X	X		X	KE-35400

**National Regulations****SECTION 16. OTHER INFORMATION****Prepared By**

Health, Safety and Environmental Department

**Creation Date**

12-May-2011

**Revision Date**

08-May-2024

**Revision Summary**

New emergency telephone response service provider.

# SAFETY DATA SHEET

## Sodium DL-lactate, 60% w/w aqueous solution

### Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

### Legend

**CAS** - Chemical Abstracts Service

**EINECS/ELINCS** - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

**PICCS** - Philippines Inventory of Chemicals and Chemical Substances

**IECSC** - Chinese Inventory of Existing Chemical Substances

**KECL** - Korean Existing and Evaluated Chemical Substances

**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory

**DSL/NDL** - Canadian Domestic Substances List/Non-Domestic Substances List

**ENCS** - Japanese Existing and New Chemical Substances

**AICS** - Australian Inventory of Chemical Substances

**NZIoC** - New Zealand Inventory of Chemicals

**WEL** - Workplace Exposure Limit

**ACGIH** - American Conference of Governmental Industrial Hygienists

**DNEL** - Derived No Effect Level

**RPE** - Respiratory Protective Equipment

**LC50** - Lethal Concentration 50%

**NOEC** - No Observed Effect Concentration

**PBT** - Persistent, Bioaccumulative, Toxic

**TWA** - Time Weighted Average

**IARC** - International Agency for Research on Cancer

**PNEC** - Predicted No Effect Concentration

**LD50** - Lethal Dose 50%

**EC50** - Effective Concentration 50%

**POW** - Partition coefficient Octanol:Water

**vPvB** - very Persistent, very Bioaccumulative

**ICAO/IATA** - International Civil Aviation Organization/International Air Transport Association

**ADR** - European Agreement Concerning the International Carriage of Dangerous Goods by Road

**OECD** - Organisation for Economic Co-operation and Development

**BCF** - Bioconcentration factor

**IMO/IMDG** - International Maritime Organization/International Maritime Dangerous Goods Code

**MARPOL** - International Convention for the Prevention of Pollution from Ships

**ATE** - Acute Toxicity Estimate

**VOC** - (Volatile Organic Compound)

### Key literature references and sources for data

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

**Physical hazards**

On basis of test data

**Health Hazards**

Calculation method

**Environmental hazards**

Calculation method

### Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

## End of Safety Data Sheet