

ALFAA87257

Barium cyclohexanebutyrate

SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

产品说明: 环己烷丁酸钡, AAS, Ba 28.9%
Product Description: Barium cyclohexanebutyrate

Cat No. : 87257
CAS No 62669-65-2
Molecular Formula C20 H34 Ba O4

Supplier Avocado Research Chemicals Ltd.
(Part of Thermo Fisher Scientific)
Shore Road, Heysham
Lancashire, LA3 2XY,
United Kingdom
Office Tel: +44 (0) 1524 850506
Office Fax: +44 (0) 1524 850608

Emergency Telephone Number For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11
Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99
CHEMTREC Tel. No. **US**:001-800-424-9300 / **Europe**:001-703-527-3887

E-mail address begel.sdsdesk@thermofisher.com

Recommended Use Laboratory chemicals.
Uses advised against No Information available

SECTION 2. HAZARD IDENTIFICATION

Physical State
Powder Solid

Appearance
Beige

Odor
Odorless

Emergency Overview
Harmful if swallowed. Harmful if inhaled.

Classification of the substance or mixture

Acute Oral Toxicity	Category 4
Acute Inhalation Toxicity - Dusts and Mists	Category 4

Label Elements



Signal Word

Warning

Hazard Statements

H302 + H332 - Harmful if swallowed or if inhaled

Barium cyclohexanebutyrate

Precautionary Statements**Prevention**

P261 - Avoid breathing dust/fume/gas/mist/vapors/spray
P264 - Wash face, hands and any exposed skin thoroughly after handling
P270 - Do not eat, drink or smoke when using this product
P271 - Use only outdoors or in a well-ventilated area

Response

P304 + P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing
P312 - Call a POISON CENTER or doctor if you feel unwell
P330 - Rinse mouth

Storage

P403 - Store in a well-ventilated place

Disposal

P501 - Disposal of contents/ container to an approved waste disposal plant

Physical and Chemical Hazards

None identified.

Health Hazards

Harmful if swallowed. Harmful if inhaled.

Environmental hazards

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants.

Toxic to terrestrial vertebrates. This product does not contain any known or suspected endocrine disruptors.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Component	CAS No	Weight %
Cyclohexanebutanoic acid, barium salt	62669-65-2	99

Note

Note 1: The concentration stated or, in the absence of such concentrations, the generic concentrations of this Regulation (Table 3.1) or the generic concentrations of Directive 1999/45/EC (Table 3.2), are the percentages by weight of the metallic element calculated with reference to the total weight of the mixture

SECTION 4. FIRST AID MEASURES**Eye Contact**

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.

Skin Contact

Wash off immediately with soap and plenty of water while removing all contaminated clothes and shoes. Get medical attention.

Inhalation

Remove from exposure, lie down. Remove to fresh air. If not breathing, give artificial respiration. Get medical attention.

Ingestion

Clean mouth with water. Get medical attention.

Most important symptoms and effects

Difficulty in breathing. Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting

Self-Protection of the First Aider

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

Notes to Physician

Treat symptomatically. Symptoms may be delayed.

SECTION 5. FIRE-FIGHTING MEASURES

Barium cyclohexanebutyrate

Suitable Extinguishing Media

Water spray. Carbon dioxide (CO₂). Dry chemical. Chemical foam.

Extinguishing media which must not be used for safety reasons

No information available.

Specific Hazards Arising from the Chemical

Thermal decomposition can lead to release of irritating gases and vapors.

Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

SECTION 6. ACCIDENTAL RELEASE MEASURES**Personal Precautions**

Ensure adequate ventilation.

Environmental Precautions

See Section 12 for additional Ecological Information.

Methods for Containment and Clean Up

Sweep up and shovel into suitable containers for disposal.

Refer to protective measures listed in Sections 8 and 13.

SECTION 7. HANDLING AND STORAGE**Handling**

Avoid contact with skin and eyes. Do not breathe dust.

Storage

Keep in a dry, cool and well-ventilated place. Keep container tightly closed.

Specific Use(s)

Use in laboratories

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION**Control Parameters**

Component	China	Taiwan	Thailand	Hong Kong
Cyclohexanebutanoic acid, barium salt	-	TWA: 0.5 mg/m ³	TWA: 0.5 mg/m ³	-

Component	ACGIH TLV	OSHA PEL	NIOSH	The United Kingdom	European Union
Cyclohexanebutanoic acid, barium salt	TWA: 0.5 mg/m ³	(Vacated) TWA: 0.5 mg/m ³	IDLH: 50 mg/m ³ TWA: 0.5 mg/m ³	STEL: 1.5 mg/m ³ 15 min TWA: 0.5 mg/m ³ 8 hr	TWA: 0.5 mg/m ³ (8hr)

Legend

ACGIH - American Conference of Governmental Industrial Hygienists

OSHA - Occupational Safety and Health Administration

NIOSH: NIOSH - National Institute for Occupational Safety and Health

Monitoring methods

Barium cyclohexanebutyrate

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS14/3 General methods for sampling and gravimetric analysis of respirable and inhalable dust

Exposure Controls**Engineering Measures**

Ensure adequate ventilation, especially in confined areas. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

Personal protective equipment

Eye Protection Wear safety glasses with side shields (or goggles) (European standard - EN 166)

Hand Protection Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Nitrile rubber	See manufacturers	-	EN 374	(minimum requirement)
Viton (R)	recommendations			

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves.

(Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

Skin and body protection Wear appropriate protective gloves and clothing to prevent skin exposure

Respiratory Protection No protective equipment is needed under normal use conditions.

Large scale/emergency use Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced

Small scale/Laboratory use Maintain adequate ventilation

Hygiene Measures Handle in accordance with good industrial hygiene and safety practice.

Environmental exposure controls No information available.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance	Beige	
Physical State	Powder Solid	
Odor	Odorless	
Odor Threshold	No data available	
pH	No information available	
Melting Point/Range	No data available	
Softening Point	No data available	
Boiling Point/Range	No information available	
Flash Point	No information available	Method - No information available
Evaporation Rate	Not applicable	Solid
Flammability (solid,gas)	No information available	
Explosion Limits	No data available	
Vapor Pressure	No data available	
Vapor Density	Not applicable	Solid
Specific Gravity / Density	No data available	

Barium cyclohexanebutyrate

Bulk Density	No data available	
Water Solubility	No information available	
Solubility in other solvents	No information available	
Partition Coefficient (n-octanol/water)		
Autoignition Temperature	No data available	
Decomposition Temperature	No data available	
Viscosity	Not applicable	Solid
Explosive Properties	No information available	
Oxidizing Properties	No information available	

Molecular Formula	C20 H34 Ba O4
Molecular Weight	475.8

SECTION 10. STABILITY AND REACTIVITY

Stability	Stable under normal conditions.
Hazardous Reactions	No information available.
Hazardous Polymerization	No information available.
Conditions to Avoid	Incompatible products.
Materials to avoid	Strong oxidizing agents. Strong acids.

Hazardous Decomposition Products Carbon monoxide (CO). Carbon dioxide (CO₂).

SECTION 11. TOXICOLOGICAL INFORMATION

Product Information

(a) acute toxicity;	
(b) skin corrosion/irritation;	No data available
(c) serious eye damage/irritation;	No data available
(d) respiratory or skin sensitization;	
Respiratory	No data available
Skin	No data available
(e) germ cell mutagenicity;	No data available
(f) carcinogenicity;	No data available
	There are no known carcinogenic chemicals in this product
(g) reproductive toxicity;	No data available
(h) STOT-single exposure;	No data available
(i) STOT-repeated exposure;	No data available
Target Organs	No information available.

Barium cyclohexanebutyrate

(j) aspiration hazard; Not applicable
Solid

Other Adverse Effects The toxicological properties have not been fully investigated.

Symptoms / effects, both acute and delayed Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting

SECTION 12. ECOLOGICAL INFORMATION

Ecotoxicity effects Contains no substances known to be hazardous to the environment or that are not degradable in waste water treatment plants.

Persistence and Degradability No information available

Bioaccumulative Potential No information available

Mobility in soil No information available

Endocrine Disruptor Information This product does not contain any known or suspected endocrine disruptors
Persistent Organic Pollutant This product does not contain any known or suspected substance
Ozone Depletion Potential This product does not contain any known or suspected substance

SECTION 13. DISPOSAL CONSIDERATIONS

Waste from Residues/Unused Products Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.

Contaminated Packaging Dispose of this container to hazardous or special waste collection point.

Other Information Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains.

SECTION 14. TRANSPORT INFORMATION**Road and Rail Transport**

UN-No UN1564
Proper Shipping Name Barium compound, n.o.s.
Hazard Class 6.1
Packing Group III

IMDG/IMO

UN-No UN1564
Proper Shipping Name Barium compound, n.o.s.
Hazard Class 6.1
Packing Group III

IATA

UN-No UN1564

Barium cyclohexanebutyrate

Proper Shipping Name Barium compound, n.o.s.
Hazard Class 6.1
Packing Group III

Special Precautions for User No special precautions required

SECTION 15. REGULATORY INFORMATION

International Inventories

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
Cyclohexanebutanoic acid, barium salt	-	X	X	X	263-685-7	X	X	-	-		-	-

Note

Note 1: The concentration stated or, in the absence of such concentrations, the generic concentrations of this Regulation (Table 3.1) or the generic concentrations of Directive 1999/45/EC (Table 3.2), are the percentages by weight of the metallic element calculated with reference to the total weight of the mixture

National Regulations

SECTION 16. OTHER INFORMATION

Prepared By Health, Safety and Environmental Department
Revision Date 23-Apr-2024
Revision Summary New emergency telephone response service provider.

Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

Fire prevention and fighting, identifying hazards and risks, static electricity, explosive atmospheres posed by vapours and dusts.

Chemical incident response training.

Legend

CAS - Chemical Abstracts Service

EINECS/ELINCS - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

PICCS - Philippines Inventory of Chemicals and Chemical Substances

IECSC - Chinese Inventory of Existing Chemical Substances

KECL - Korean Existing and Evaluated Chemical Substances

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

ENCS - Japanese Existing and New Chemical Substances

AICS - Australian Inventory of Chemical Substances

NZIoC - New Zealand Inventory of Chemicals

WEL - Workplace Exposure Limit

ACGIH - American Conference of Governmental Industrial Hygienists

DNEL - Derived No Effect Level

RPE - Respiratory Protective Equipment

LC50 - Lethal Concentration 50%

TWA - Time Weighted Average

IARC - International Agency for Research on Cancer

PNEC - Predicted No Effect Concentration

LD50 - Lethal Dose 50%

EC50 - Effective Concentration 50%

Barium cyclohexanebutyrate**NOEC** - No Observed Effect Concentration**PBT** - Persistent, Bioaccumulative, Toxic**POW** - Partition coefficient Octanol:Water**vPvB** - very Persistent, very Bioaccumulative**ICAO/IATA** - International Civil Aviation Organization/International Air Transport Association**ADR** - European Agreement Concerning the International Carriage of Dangerous Goods by Road**OECD** - Organisation for Economic Co-operation and Development**BCF** - Bioconcentration factor**IMO/IMDG** - International Maritime Organization/International Maritime Dangerous Goods Code**MARPOL** - International Convention for the Prevention of Pollution from Ships**ATE** - Acute Toxicity Estimate**VOC** - (Volatile Organic Compound)**Key literature references and sources for data**<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet