ALFAA43696

Dihydrogen hexachloroplatinate(IV) hydrate

SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

产品说明:	**水合六氯铂(Ⅳ)酸**
Product Description:	**Dihydrogen hexachloroplatinate(IV) hydrate**
Cat No. :	**43696**
Synonyms	Hexachloroplatinic acid hydrate; Platinic chloride hydrate
CAS No	26023-84-7
Molecular Formula	H2 Cl6 Pt . x H2 O

Supplier

Avocado Research Chemicals Ltd.
(Part of Thermo Fisher Scientific)
Shore Road, Heysham
Lancashire, LA3 2XY,
United Kingdom
Office Tel: +44 (0) 1524 850506
Office Fax: +44 (0) 1524 850608

Emergency Telephone Number

For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11
Emergency Number **US:**001-201-796-7100 / **Europe:** +32 14 57 52 99
CHEMTREC Tel. No. **US:**001-800-424-9300 / **Europe:**001-703-527-3887

E-mail address begel.sdsdesk@thermofisher.com

Recommended Use Laboratory chemicals.
Uses advised against No Information available

SECTION 2. HAZARD IDENTIFICATION

Physical State	**Appearance**	**Odor**
Solid Powder	Amber	Odorless

Emergency Overview

May be corrosive to metals. Fatal if swallowed. Causes severe skin burns and eye damage. May cause an allergic skin reaction. May cause allergy or asthma symptoms or breathing difficulties if inhaled. Causes damage to organs through prolonged or repeated exposure. Very toxic to aquatic life with long lasting effects. Corrosive to the respiratory tract. Sensitivity to light. Moisture sensitive.

Classification of the substance or mixture

Substances/mixtures corrosive to metal	Category 1
Acute Oral Toxicity	Category 2
Skin Corrosion/Irritation	Category 1 B
Serious Eye Damage/Eye Irritation	Category 1
Respiratory Sensitization	Category 1A
Skin Sensitization	Category 1B
Specific target organ toxicity - (repeated exposure)	Category 1
Acute aquatic toxicity	Category 1
Chronic aquatic toxicity	Category 1

Label Elements

Signal Word **Danger**

Hazard Statements
H290 - May be corrosive to metals
H300 - Fatal if swallowed
H314 - Causes severe skin burns and eye damage
H317 - May cause an allergic skin reaction
H334 - May cause allergy or asthma symptoms or breathing difficulties if inhaled
H372 - Causes damage to organs through prolonged or repeated exposure
H410 - Very toxic to aquatic life with long lasting effects

Precautionary Statements
Prevention
P234 - Keep only in original packaging
P264 - Wash face, hands and any exposed skin thoroughly after handling
P270 - Do not eat, drink or smoke when using this product
P271 - Use only outdoors or in a well-ventilated area
P272 - Contaminated work clothing should not be allowed out of the workplace
P280 - Wear protective gloves/protective clothing/eye protection/face protection
P284 - In case of inadequate ventilation wear respiratory protection
Response
P303 + P361 + P353 - IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water or shower
P304 + P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing
P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing
P310 - Immediately call a POISON CENTER or doctor
P330 - Rinse mouth
P331 - Do NOT induce vomiting
P363 - Wash contaminated clothing before reuse
P390 - Absorb spillage to prevent material damage
Storage
P402 - Store in a dry place
P403 + P233 - Store in a well-ventilated place. Keep container tightly closed
P406 - Store in corrosion resistant polypropylene container with a resistant inliner
P405 - Store locked up
Disposal
P501 - Dispose of contents/ container to an approved waste disposal plant

Physical and Chemical Hazards
May be corrosive to metals.
Health Hazards
Very toxic if swallowed. Corrosive. Causes skin and eye burns. May cause an allergic skin reaction. May cause allergy or asthma symptoms or breathing difficulties if inhaled. Causes damage to organs through prolonged or repeated exposure.
Environmental hazards
Very toxic to aquatic life with long lasting effects. Will likely be mobile in the environment due to its water solubility. The product is water soluble, and may spread in water systems.

Other Hazards
No information available
This product does not contain any known or suspected endocrine disruptors.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Component	CAS No	Weight %

Hydrogen hexachloroplatinate(IV) hydrate	26023-84-7	>95
Chloroplatinic acid	16941-12-1	-

SECTION 4. FIRST AID MEASURES

General Advice
Show this safety data sheet to the doctor in attendance. Immediate medical attention is required.

Eye Contact
In the case of contact with eyes, rinse immediately with plenty of water and seek medical advice.

Skin Contact
Wash off immediately with plenty of water for at least 15 minutes. Immediate medical attention is required.

Inhalation
Remove to fresh air. If not breathing, give artificial respiration. Do not use mouth-to-mouth method if victim ingested or inhaled the substance; give artificial respiration with the aid of a pocket mask equipped with a one-way valve or other proper respiratory medical device. Immediate medical attention is required.

Ingestion
Do NOT induce vomiting. Call a physician or poison control center immediately.

Most important symptoms and effects
Causes burns by all exposure routes. May cause allergy or asthma symptoms or breathing difficulties if inhaled. May cause allergic skin reaction. Product is a corrosive material. Use of gastric lavage or emesis is contraindicated. Possible perforation of stomach or esophagus should be investigated: Ingestion causes severe swelling, severe damage to the delicate tissue and danger of perforation: Symptoms of allergic reaction may include rash, itching, swelling, trouble breathing, tingling of the hands and feet, dizziness, lightheadedness, chest pain, muscle pain or flushing

Self-Protection of the First Aider
Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

Notes to Physician
Treat symptomatically.

SECTION 5. FIRE-FIGHTING MEASURES

Suitable Extinguishing Media
CO_2, dry chemical, dry sand, alcohol-resistant foam.

Extinguishing media which must not be used for safety reasons
No information available.

Specific Hazards Arising from the Chemical
The product causes burns of eyes, skin and mucous membranes. Do not allow run-off from fire-fighting to enter drains or water courses.

Protective Equipment and Precautions for Firefighters
As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear. Thermal decomposition can lead to release of irritating gases and vapors.

SECTION 6. ACCIDENTAL RELEASE MEASURES

Personal Precautions
Use personal protective equipment as required. Evacuate personnel to safe areas. Ensure adequate ventilation. Keep people away from and upwind of spill/leak. Avoid dust formation.

Environmental Precautions
Do not flush into surface water or sanitary sewer system. Do not allow material to contaminate ground water system. Prevent product from entering drains. Local authorities should be advised if significant spillages cannot be contained. Should not be released into the environment.

Methods for Containment and Clean Up
Sweep up and shovel into suitable containers for disposal. Avoid dust formation.

Refer to protective measures listed in Sections 8 and 13.

SECTION 7. HANDLING AND STORAGE

Handling
Wear personal protective equipment/face protection. Do not get in eyes, on skin, or on clothing. Use only under a chemical fume hood. Do not ingest. If swallowed then seek immediate medical assistance. Do not breathe (dust, vapor, mist, gas). Avoid dust formation.

Storage
Corrosives area. Keep containers tightly closed in a dry, cool and well-ventilated place. Keep away from water or moist air. Protect from direct sunlight.

Specific Use(s)
Use in laboratories

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control Parameters

Component	China	ACGIH TLV	OSHA PEL	NIOSH
Hydrogen hexachloroplatinate(IV) hydrate	-	TWA: 0.002 mg/m³	(Vacated) TWA: 0.002 mg/m³	IDLH: 4 mg/m³ REL = 0.002 mg/m³ (TWA)
Chloroplatinic acid	-	TWA: 0.002 mg/m³	(Vacated) TWA: 0.002 mg/m³	IDLH: 4 mg/m³ REL = 0.002 mg/m³ (TWA)

Component	Hong Kong	Thailand	European Union	The United Kingdom
Hydrogen hexachloroplatinate(IV) hydrate	-			STEL: 0.006 mg/m³ 15 min TWA: 0.002 mg/m³ 8 hr
Chloroplatinic acid	-			STEL: 0.006 mg/m³ 15 min TWA: 0.002 mg/m³ 8 hr Resp. Sens.

Legend

ACGIH - American Conference of Governmental Industrial Hygienists
OSHA - Occupational Safety and Health Administration
NIOSH: NIOSH - National Institute for Occupational Safety and Health

Monitoring methods
BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS14/3 General methods for sampling and gravimetric analysis of respirable and inhalable dust

Exposure Controls

Engineering Measures
Use only under a chemical fume hood. Ensure that eyewash stations and safety showers are close to the workstation location. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

Personal protective equipment

Eye Protection Goggles (European standard - EN 166)

Hand Protection Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Natural rubber Nitrile rubber Neoprene PVC	See manufacturers recommendations	-	EN 374	(minimum requirement)

Inspect gloves before use.
Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)
Ensure gloves are suitable for the task: Chemical compatability, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.
Remove gloves with care avoiding skin contamination.

Skin and body protection Long sleeved clothing

Respiratory Protection When workers are facing concentrations above the exposure limit they must use appropriate certified respirators.
To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly

Large scale/emergency use Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced
Recommended Filter type: Particulates filter conforming to EN 143

Small scale/Laboratory use Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.
Recommended half mask:- Particle filtering: EN149:2001
When RPE is used a face piece Fit Test should be conducted

Hygiene Measures Handle in accordance with good industrial hygiene and safety practice.

Environmental exposure controls Prevent product from entering drains. Do not allow material to contaminate ground water system. Local authorities should be advised if significant spillages cannot be contained.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance	Amber	
Physical State	Solid Powder	
Odor	Odorless	
Odor Threshold	No data available	
pH	Not applicable	
Melting Point/Range	60 °C / 140 °F	
Softening Point	No data available	
Boiling Point/Range	No information available	
Flash Point	No information available	**Method -** No information available
Evaporation Rate	Not applicable	Solid
Flammability (solid,gas)	No information available	
Explosion Limits	No data available	
Vapor Pressure	No data available	
Vapor Density	Not applicable	Solid
Specific Gravity / Density	No data available	
Bulk Density	No data available	
Water Solubility	Soluble	

Solubility in other solvents	No information available	
Partition Coefficient (n-octanol/water)		
Autoignition Temperature	No data available	
Decomposition Temperature	No data available	
Viscosity	Not applicable	Solid
Explosive Properties	No information available	
Oxidizing Properties	No information available	

Molecular Formula	H2 Cl6 Pt . x H2 O
Molecular Weight	409.82

SECTION 10. STABILITY AND REACTIVITY

Stability Light sensitive. Moisture sensitive.

Hazardous Reactions None under normal processing.
Hazardous Polymerization Hazardous polymerization does not occur.

Conditions to Avoid Incompatible products. Excess heat. Exposure to light. Exposure to moisture.

Materials to avoid Strong oxidizing agents.

Hazardous Decomposition Products Platinum oxide. Carbon monoxide (CO). Carbon dioxide (CO_2). Hydrogen chloride gas.

SECTION 11. TOXICOLOGICAL INFORMATION

Product Information

(a) acute toxicity;

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
Hydrogen hexachloroplatinate(IV) hydrate	195 mg/kg (Rat)		
Chloroplatinic acid	25-200 mg/kg (Rat)		

(b) skin corrosion/irritation; Category 1 B

(c) serious eye damage/irritation; Category 1

(d) respiratory or skin sensitization;
Respiratory Sub-category 1A
Skin Sub-category 1B

May cause sensitization by skin contact

(e) germ cell mutagenicity; No data available

(f) carcinogenicity; No data available

There are no known carcinogenic chemicals in this product

(g) reproductive toxicity; No data available

(h) STOT-single exposure; No data available

(i) STOT-repeated exposure;	Category 1
Target Organs	None known.
(j) aspiration hazard;	Not applicable Solid
Symptoms / effects,both acute and delayed	Product is a corrosive material. Use of gastric lavage or emesis is contraindicated. Possible perforation of stomach or esophagus should be investigated: Ingestion causes severe swelling, severe damage to the delicate tissue and danger of perforation: Symptoms of allergic reaction may include rash, itching, swelling, trouble breathing, tingling of the hands and feet, dizziness, lightheadedness, chest pain, muscle pain or flushing

SECTION 12. ECOLOGICAL INFORMATION

Ecotoxicity effects	Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment. The product contains following substances which are hazardous for the environment. May cause long-term adverse effects in the environment. Do not allow material to contaminate ground water system.
Persistence and Degradability	Product contains heavy metals. Discharge into the environment must be avoided. Special pre-treatment is necessary
Persistence	based on information available, May persist.
Degradability	Not relevant for inorganic substances.
Degradation in sewage treatment plant	Contains substances known to be hazardous to the environment or not degradable in waste water treatment plants.
Bioaccumulative Potential	May have some potential to bioaccumulate
Mobility in soil	The product is water soluble, and may spread in water systems Will likely be mobile in the environment due to its water solubility Highly mobile in soils
Endocrine Disruptor Information	This product does not contain any known or suspected endocrine disruptors
Persistent Organic Pollutant	This product does not contain any known or suspected substance
Ozone Depletion Potential	This product does not contain any known or suspected substance

SECTION 13. DISPOSAL CONSIDERATIONS

Waste from Residues/Unused Products	Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations. Should not be released into the environment.
Contaminated Packaging	Dispose of this container to hazardous or special waste collection point.
Other Information	Do not flush to sewer. Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains. Large amounts will affect pH and harm aquatic organisms. Do not let this chemical enter the environment.

SECTION 14. TRANSPORT INFORMATION

Road and Rail Transport

UN-No	UN2507
Proper Shipping Name	Chloroplatinic acid, solid

Hazard Class 8
Packing Group III

IMDG/IMO

UN-No UN2507
Proper Shipping Name CHLOROPLATINIC ACID, SOLID
Hazard Class 8
Packing Group III

IATA

UN-No UN2507
Proper Shipping Name CHLOROPLATINIC ACID, SOLID
Hazard Class 8
Packing Group III

Special Precautions for User No special precautions required

SECTION 15. REGULATORY INFORMATION

International Inventories
China, X = listed, U.S.A. (TSCA), Canada (DSL/NDSL), Europe (EINECS/ELINCS/NLP), Australia (AICS), Korea (KECL), China (IECSC), Japan (ENCS), Philippines (PICCS), Taiwan (TCSI), Japan (ISHL), New Zealand (NZIoC), Japan (ISHL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
Hydrogen hexachloroplatinate(IV) hydrate	-	-	X	-	-	-	-	-		-	-
Chloroplatinic acid	X	X	X	241-010-7	X	X	X	X	X	X	KE-18416

National Regulations

SECTION 16. OTHER INFORMATION

Prepared By Health, Safety and Environmental Department
Creation Date 06-Apr-2010
Revision Date 25-Jul-2026
Revision Summary SDS sections updated.

Training Advice
Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.
Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.
First aid for chemical exposure, including the use of eye wash and safety showers.
Chemical incident response training.

Legend

CAS - Chemical Abstracts Service
EINECS/ELINCS - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances
PICCS - Philippines Inventory of Chemicals and Chemical Substances
IECSC - Chinese Inventory of Existing Chemical Substances
KECL - Korean Existing and Evaluated Chemical Substances
TSCA - United States Toxic Substances Control Act Section 8(b) Inventory
DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List
ENCS - Japanese Existing and New Chemical Substances
AICS - Australian Inventory of Chemical Substances
NZIoC - New Zealand Inventory of Chemicals

WEL - Workplace Exposure Limit
ACGIH - American Conference of Governmental Industrial Hygienists
DNEL - Derived No Effect Level
RPE - Respiratory Protective Equipment
LC50 - Lethal Concentration 50%
NOEC - No Observed Effect Concentration
PBT - Persistent, Bioaccumulative, Toxic
TWA - Time Weighted Average
IARC - International Agency for Research on Cancer
PNEC - Predicted No Effect Concentration
LD50 - Lethal Dose 50%
EC50 - Effective Concentration 50%
POW - Partition coefficient Octanol:Water
vPvB - very Persistent, very Bioaccumulative

ICAO/IATA - International Civil Aviation Organization/International Air Transport Association
ADR - European Agreement Concerning the International Carriage of Dangerous Goods by Road
OECD - Organisation for Economic Co-operation and Development
BCF - Bioconcentration factor
IMO/IMDG - International Maritime Organization/International Maritime Dangerous Goods Code
MARPOL - International Convention for the Prevention of Pollution from Ships
ATE - Acute Toxicity Estimate
VOC - (Volatile Organic Compound)

Key literature references and sources for data
https://echa.europa.eu/information-on-chemicals
Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet