

SAFETY DATA SHEET

Revision Date 14-Feb-2020 Revision Number 2

1. Identification

Product Name Pyridine-3-methanol

Cat No. : A10381

CAS-No 100-55-0

Synonyms 3-Pyridinemethanol; 3-Pyridylcarbinol; Nicotinyl alcohol

Recommended Use Laboratory chemicals.

Uses advised against Food, drug, pesticide or biocidal product use.

Details of the supplier of the safety data sheet

Company

Alfa Aesar

Thermo Fisher Scientific Chemicals, Inc.

30 Bond Street

Ward Hill, MA 01835-8099

Tel: 800-343-0660 Fax: 800-322-4757 **Email:** tech@alfa.com

www.alfa.com

Emergency Telephone Number

During normal business hours (Monday-Friday, 8am-7pm EST), call (800) 343-0660.

After normal business hours, call Carechem 24 at (866) 928-0789.

2. Hazard(s) identification

Classification

This chemical is considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Acute oral toxicityCategory 4Skin Corrosion/IrritationCategory 2Serious Eye Damage/Eye IrritationCategory 2Specific target organ toxicity (single exposure)Category 3

Target Organs - Respiratory system.

Label Elements

Signal Word

Warning

Hazard Statements

Harmful if swallowed Causes skin irritation

Causes serious eye irritation

May cause respiratory irritation



Precautionary Statements

Prevention

Wash face, hands and any exposed skin thoroughly after handling

Do not eat, drink or smoke when using this product

Wear protective gloves/protective clothing/eye protection/face protection

Avoid breathing dust/fume/gas/mist/vapors/spray

Use only outdoors or in a well-ventilated area

Inhalation

IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing

Call a POISON CENTER or doctor/physician if you feel unwell

Skin

IF ON SKIN: Wash with plenty of soap and water

If skin irritation occurs: Get medical advice/attention

Take off contaminated clothing and wash before reuse

Eyes

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing If eye irritation persists: Get medical advice/attention

Ingestion

IF SWALLOWED: Call a POISON CENTER or doctor/physician if you feel unwell

Rinse mouth

Storage

Store in a well-ventilated place. Keep container tightly closed

Store locked up

Disposal

Dispose of contents/container to an approved waste disposal plant

Hazards not otherwise classified (HNOC)

None identified

3. Composition/Information on Ingredients

| Component | CAS-No | Weight % | | |
|--------------------|----------|----------|--|--|
| 3-Pyridinemethanol | 100-55-0 | 98 | | |

4. First-aid measures

Eye Contact Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get

medical attention.

Skin Contact Wash off immediately with soap and plenty of water while removing all contaminated

clothes and shoes. Get medical attention.

Inhalation Remove from exposure, lie down. Remove to fresh air. If not breathing, give artificial

respiration. Get medical attention.

Ingestion Clean mouth with water. Get medical attention.

Most important symptoms and

effects

No information available.

Revision Date 14-Feb-2020 Pyridine-3-methanol

Notes to Physician Treat symptomatically

Fire-fighting measures

Suitable Extinguishing Media Water spray. Carbon dioxide (CO₂). Dry chemical. Chemical foam.

Unsuitable Extinguishing Media No information available

149 °C / 300.2 °F **Flash Point**

No information available Method -

Autoignition Temperature

Explosion Limits

No information available

Upper No data available Lower No data available Sensitivity to Mechanical Impact No information available Sensitivity to Static Discharge No information available

Specific Hazards Arising from the Chemical

Keep product and empty container away from heat and sources of ignition.

Hazardous Combustion Products

Nitrogen oxides (NOx). Carbon monoxide (CO). Carbon dioxide (CO₂).

Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

NFPA

| Health | Flammability | Instability | Physical hazards |
|--------|--------------|-------------|------------------|
| 2 | 1 | 0 | N/A |

6. Accidental release measures

Personal Precautions Ensure adequate ventilation. Use personal protective equipment as required.

Environmental Precautions See Section 12 for additional Ecological Information.

Up

Methods for Containment and Clean Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust). Keep in suitable, closed containers for disposal. Do not let this chemical enter the

environment.

Handling and storage

Handling Avoid contact with skin and eyes. Do not breathe mist/vapors/spray. Do not ingest. If

swallowed then seek immediate medical assistance.

Keep in a dry, cool and well-ventilated place. Refer product specification and/or product Storage

label for specific storage temperature requirement. Keep container tightly closed.

8. Exposure controls / personal protection

Exposure Guidelines

This product does not contain any hazardous materials with occupational exposure

limitsestablished by the region specific regulatory bodies.

Ensure adequate ventilation, especially in confined areas. Ensure that eyewash stations **Engineering Measures**

and safety showers are close to the workstation location.

Personal Protective Equipment

Eye/face ProtectionWear appropriate protective eyeglasses or chemical safety goggles as described by

OSHA's eye and face protection regulations in 29 CFR 1910.133 or European Standard

EN166.

Skin and body protectionWear appropriate protective gloves and clothing to prevent skin exposure.

Respiratory ProtectionNo protective equipment is needed under normal use conditions.

Hygiene Measures Handle in accordance with good industrial hygiene and safety practice.

9. Physical and chemical properties

Physical StateLiquidAppearanceLight yellowOdorOdorless

Odor Threshold
pHNo information available
No information available

Melting Point/Range -7 °C / 19.4 °F

Boiling Point/Range 259 °C / 498.2 °F @ 760 mmHg

Flash Point 149 °C / 300.2 °F
Evaporation Rate No information available

Flammability (solid,gas) Not applicable

Flammability or explosive limits

UpperNo data availableLowerNo data availableVapor PressureNo information available

Vapor Density 3.8 Specific Gravity 1.124

Solubility No information available

Partition coefficient; n-octanol/water
Autoignition Temperature

No data available
No information available

Decomposition Temperature

No information available
Viscosity

No information available

Molecular Formula C6 H7 N O Molecular Weight 109.13

10. Stability and reactivity

Reactive Hazard None known, based on information available

Stability Stable under normal conditions. Hygroscopic.

Conditions to Avoid Incompatible products. Exposure to moist air or water.

Incompatible Materials Acids, Strong oxidizing agents, Acid chlorides

Hazardous Decomposition Products Nitrogen oxides (NOx), Carbon monoxide (CO), Carbon dioxide (CO2)

Hazardous Polymerization No information available.

Hazardous Reactions None under normal processing.

11. Toxicological information

Acute Toxicity

Product Information Component Information

Toxicologically Synergistic No information available

Products

Revision Date 14-Feb-2020 Pyridine-3-methanol

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Irritation No information available

Sensitization No information available

The table below indicates whether each agency has listed any ingredient as a carcinogen. Carcinogenicity

| Component | CAS-No | IARC | NTP | ACGIH | OSHA | Mexico | |
|--------------------|----------|------------|------------|------------|------------|------------|--|
| 3-Pyridinemethanol | 100-55-0 | Not listed | |

Mutagenic Effects No information available

Reproductive Effects No information available.

No information available. **Teratogenicity**

STOT - single exposure Respiratory system STOT - repeated exposure None known

Aspiration hazard No information available

Symptoms / effects,both acute and No information available

delayed

No information available.

Endocrine Disruptor Information No information available

Other Adverse Effects The toxicological properties have not been fully investigated.

12. Ecological information

Ecotoxicity

Do not empty into drains. .

Developmental Effects

Persistence and Degradability Soluble in water Persistence is unlikely based on information available.

Bioaccumulation/ Accumulation No information available.

Mobility Will likely be mobile in the environment due to its water solubility.

13. Disposal considerations

Chemical waste generators must determine whether a discarded chemical is classified as a **Waste Disposal Methods**

hazardous waste. Chemical waste generators must also consult local, regional, and national hazardous waste regulations to ensure complete and accurate classification.

| | 14. Transport information | |
|------------|---------------------------|--|
| DOT TDG | Not regulated | |
| TDG | Not regulated | |

IATA Not regulated Not regulated IMDG/IMO

15. Regulatory information

United States of America Inventory

| Component | CAS-No | o TSCA TSCA Inventory notific Active/Inactive | | TSCA - EPA Regulatory Flags |
|--------------------|----------|---|--------|--------------------------------|
| 3-Pvridinemethanol | 100-55-0 | X | ACTIVE | - |

Legend:

TSCA - Toxic Substances Control Act, (40 CFR Part 710)

X - Listed '-' - Not Listed

TSCA 12(b) - Notices of Export Not applicable

International Inventories

Canada (DSL/NDSL), Europe (EINECS/ELINCS/NLP), Philippines (PICCS), Japan (ENCS), Australia (AICS), China (IECSC), Korea (ECL).

| Component | CAS-No | DSL | NDSL | EINECS | PICCS | ENCS | AICS | IECSC | KECL |
|--------------------|----------|-----|------|-----------|-------|------|------|-------|----------|
| 3-Pyridinemethanol | 100-55-0 | - | X | 202-864-6 | X | X | - | Χ | KE-29943 |

U.S. Federal Regulations

SARA 313 Not applicable

SARA 311/312 Hazard Categories See section 2 for more information

CWA (Clean Water Act) Not applicable

Clean Air Act Not applicable

OSHA - Occupational Safety and

Health Administration

Not applicable

CERCLA Not applicable

California Proposition 65 This product does not contain any Proposition 65 chemicals.

U.S. State Right-to-Know

Regulations

Not applicable

U.S. Department of Transportation

Reportable Quantity (RQ): N
DOT Marine Pollutant N
DOT Severe Marine Pollutant N

U.S. Department of Homeland

Security

This product does not contain any DHS chemicals.

Other International Regulations

Mexico - Grade No information available

16. Other information

Prepared By Health, Safety and Environmental Department

Email: tech@alfa.com

www.alfa.com

Revision Date 14-Feb-2020 Print Date 14-Feb-2020

Revision Summary SDS authoring systems update, replaces ChemGes SDS No. 100-55-0/2.

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage,

transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of SDS