

ALFAAA11136

Dopamine hydrochloride

SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

产品说明: Product Description:	多巴胺盐酸盐 Dopamine hydrochloride
Cat No. :	A11136
Synonyms	3,4-Dihydroxyphenethylamine hydrochloride; Dopamine hydrochloride
CAS No	62-31-7
Molecular Formula	C8 H11 N O2 . H Cl
Supplier	Avocado Research Chemicals Ltd. (Part of Thermo Fisher Scientific) Shore Road, Heysham Lancashire, LA3 2XY, United Kingdom Office Tel: +44 (0) 1524 850506 Office Fax: +44 (0) 1524 850608
Emergency Telephone Number	For information US call: 001-800-227-6701 / Europe call: +32 14 57 52 11 Emergency Number US :001-201-796-7100 / Europe : +32 14 57 52 99 CHEMTREC Tel. No. US :001-800-424-9300 / Europe :001-703-527-3887
E-mail address	begel.sdsdesk@thermofisher.com
Recommended Use	Laboratory chemicals.
Uses advised against	No Information available

SECTION 2. HAZARD IDENTIFICATION

Physical State Powder Solid	Appearance Off-white	Odor Odorless
Emergency Overview May be harmful if swallowed. Sensitivity to light.		

Classification of the substance or mixture

Acute Oral Toxicity	Category 5
---------------------	------------

Label Elements

None required

Signal Word **Warning**

Hazard Statements

H303 - May be harmful if swallowed

Precautionary Statements

Prevention

P270 - Do not eat, drink or smoke when using this product

Response

Dopamine hydrochloride

P301 + P312 - IF SWALLOWED: Call a POISON CENTER or doctor if you feel unwell

Storage

P403 - Store in a well-ventilated place

Disposal

P501 - Dispose of contents/ container to an approved waste disposal plant

Physical and Chemical Hazards

None identified.

Health Hazards

May be harmful if swallowed.

Environmental hazards

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants.

This product does not contain any known or suspected endocrine disruptors.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Component	CAS No	Weight %
1,2-Benzenediol, 4-(2-aminoethyl)-, hydrochloride	62-31-7	99

SECTION 4. FIRST AID MEASURES**Eye Contact**

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes.

Skin Contact

Wash off immediately with soap and plenty of water while removing all contaminated clothes and shoes.

Inhalation

Remove from exposure, lie down. Remove to fresh air.

Ingestion

Do NOT induce vomiting. Never give anything by mouth to an unconscious person. Drink plenty of water. If possible drink milk afterwards.

Most important symptoms and effects

No information available.

Self-Protection of the First Aider

No special precautions required.

Notes to Physician

Treat symptomatically.

SECTION 5. FIRE-FIGHTING MEASURES**Suitable Extinguishing Media**

Water spray. Carbon dioxide (CO₂). Dry chemical. Alcohol resistant foam.

Extinguishing media which must not be used for safety reasons

No information available.

Specific Hazards Arising from the Chemical

Thermal decomposition can lead to release of irritating gases and vapors.

Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear. Thermal decomposition can lead to release of irritating gases and vapors.

SECTION 6. ACCIDENTAL RELEASE MEASURES**Personal Precautions**

Ensure adequate ventilation.

Environmental Precautions

See Section 12 for additional Ecological Information.

Methods for Containment and Clean Up

Sweep up and shovel into suitable containers for disposal.

Refer to protective measures listed in Sections 8 and 13.

SECTION 7. HANDLING AND STORAGE**Handling**

Avoid contact with skin and eyes. Avoid contact with skin and clothing. Remove and wash contaminated clothing and gloves, including the inside, before re-use. Avoid breathing vapors or mists. Do not ingest. If swallowed then seek immediate medical assistance. Wash thoroughly after handling.

Storage

Keep in a dry, cool and well-ventilated place. Keep container tightly closed.

Specific Use(s)

Use in laboratories

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION**Control Parameters****Monitoring methods**

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS14/3 General methods for sampling and gravimetric analysis of respirable and inhalable dust

Exposure Controls**Engineering Measures**

None under normal use conditions.

Personal protective equipment

Eye Protection Wear safety glasses with side shields (or goggles) (European standard - EN 166)

Hand Protection Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Nitrile rubber	See manufacturers recommendations	-	EN 374	(minimum requirement)
Neoprene				
Natural rubber				
PVC				

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger

Dopamine hydrochloride

of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

Skin and body protection	Long sleeved clothing
Respiratory Protection	No protective equipment is needed under normal use conditions.
Large scale/emergency use	Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced Recommended Filter type: Particle filter
Small scale/Laboratory use	Maintain adequate ventilation

Hygiene Measures Handle in accordance with good industrial hygiene and safety practice.

Environmental exposure controls No information available.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance	Off-white	
Physical State	Powder Solid	
Odor	Odorless	
Odor Threshold	No data available	
pH	No information available	
Melting Point/Range	241 - 243 °C / 465.8 - 469.4 °F	
Softening Point	No data available	
Boiling Point/Range	No information available	
Flash Point	No information available	Method - No information available
Evaporation Rate	Not applicable	Solid
Flammability (solid,gas)	No information available	
Explosion Limits	No data available	
Vapor Pressure	No data available	
Vapor Density	Not applicable	Solid
Specific Gravity / Density	No data available	
Bulk Density	No data available	
Water Solubility	Very soluble	
Solubility in other solvents	No information available	
Partition Coefficient (n-octanol/water)		
Autoignition Temperature	No data available	
Decomposition Temperature	No data available	
Viscosity	Not applicable	Solid
Explosive Properties	No information available	
Oxidizing Properties	No information available	
Molecular Formula	C8 H11 N O2 . H Cl	
Molecular Weight	189.64	

SECTION 10. STABILITY AND REACTIVITY

Stability Stable under normal conditions. Light sensitive.

Hazardous Reactions No information available.

Hazardous Polymerization No information available.

Dopamine hydrochloride

Conditions to Avoid Incompatible products.

Materials to avoid Strong oxidizing agents. Oxidizing agent.

Hazardous Decomposition Products Nitrogen oxides (NOx). Thermal decomposition can lead to release of irritating gases and vapors. Carbon monoxide (CO). Carbon dioxide (CO₂). Hydrogen chloride gas.

SECTION 11. TOXICOLOGICAL INFORMATION

Product Information

(a) acute toxicity;

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
1,2-Benzenediol, 4-(2-aminoethyl)-, hydrochloride	LD50 = 2859 mg/kg (Rat)		

(b) skin corrosion/irritation; No data available

(c) serious eye damage/irritation; No data available

(d) respiratory or skin sensitization;

Respiratory No data available
Skin No data available

(e) germ cell mutagenicity; No data available

(f) carcinogenicity; No data available

There are no known carcinogenic chemicals in this product

(g) reproductive toxicity; No data available

(h) STOT-single exposure; No data available

(i) STOT-repeated exposure; No data available

Target Organs No information available.

(j) aspiration hazard; Not applicable
Solid

Other Adverse Effects The toxicological properties have not been fully investigated.

Symptoms / effects, both acute and delayed No information available

SECTION 12. ECOLOGICAL INFORMATION

Ecotoxicity effects Contains no substances known to be hazardous to the environment or that are not degradable in waste water treatment plants.

Persistence and Degradability No information available

Bioaccumulative Potential No information available

Mobility in soil No information available

Endocrine Disruptor Information This product does not contain any known or suspected endocrine disruptors

Persistent Organic Pollutant This product does not contain any known or suspected substance

Ozone Depletion Potential This product does not contain any known or suspected substance

SECTION 13. DISPOSAL CONSIDERATIONS

Waste from Residues/Unused Products Chemical waste generators must determine whether a discarded chemical is classified as a hazardous waste. Consult local, regional, and national hazardous waste regulations to ensure complete and accurate classification.

Contaminated Packaging Empty remaining contents. Dispose of in accordance with local regulations. Do not re-use empty containers.

Other Information Waste codes should be assigned by the user based on the application for which the product was used.

SECTION 14. TRANSPORT INFORMATION

Road and Rail Transport Not Regulated

IMDG/IMO Not regulated

IATA Not regulated

Special Precautions for User No special precautions required

SECTION 15. REGULATORY INFORMATION

International Inventories

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
1,2-Benzenediol, 4-(2-aminoethyl)-, hydrochloride	-	-	X	-	200-527-8	X	-	X	-		-	KE-01355

National Regulations

Dopamine hydrochloride**SECTION 16. OTHER INFORMATION**

Prepared By Health, Safety and Environmental Department
Creation Date 14-May-2010
Revision Date 25-Apr-2024
Revision Summary New emergency telephone response service provider.

Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Legend

CAS - Chemical Abstracts Service	TSCA - United States Toxic Substances Control Act Section 8(b) Inventory
EINECS/ELINCS - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances	DSL/NDL - Canadian Domestic Substances List/Non-Domestic Substances List
PICCS - Philippines Inventory of Chemicals and Chemical Substances	ENCS - Japanese Existing and New Chemical Substances
IECSC - Chinese Inventory of Existing Chemical Substances	AICS - Australian Inventory of Chemical Substances
KECL - Korean Existing and Evaluated Chemical Substances	NZIoC - New Zealand Inventory of Chemicals
WEL - Workplace Exposure Limit	TWA - Time Weighted Average
ACGIH - American Conference of Governmental Industrial Hygienists	IARC - International Agency for Research on Cancer
DNEL - Derived No Effect Level	PNEC - Predicted No Effect Concentration
RPE - Respiratory Protective Equipment	LD50 - Lethal Dose 50%
LC50 - Lethal Concentration 50%	EC50 - Effective Concentration 50%
NOEC - No Observed Effect Concentration	POW - Partition coefficient Octanol:Water
PBT - Persistent, Bioaccumulative, Toxic	vpvB - very Persistent, very Bioaccumulative
ICAO/IATA - International Civil Aviation Organization/International Air Transport Association	IMO/IMDG - International Maritime Organization/International Maritime Dangerous Goods Code
ADR - European Agreement Concerning the International Carriage of Dangerous Goods by Road	MARPOL - International Convention for the Prevention of Pollution from Ships
OECD - Organisation for Economic Co-operation and Development	ATE - Acute Toxicity Estimate
BCF - Bioconcentration factor	VOC - (Volatile Organic Compound)

Key literature references and sources for data

<https://echa.europa.eu/information-on-chemicals>
 Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet