

ALFAAA11545

Quinoline

SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

产品说明: Product Description:	喹啉 Quinoline
Cat No. :	A11545
Synonyms	Benzo[b]pyridine
CAS No	91-22-5
Molecular Formula	C9 H7 N
Supplier	Avocado Research Chemicals Ltd. (Part of Thermo Fisher Scientific) Shore Road, Heysham Lancashire, LA3 2XY, United Kingdom Office Tel: +44 (0) 1524 850506 Office Fax: +44 (0) 1524 850608
Emergency Telephone Number	For information US call: 001-800-227-6701 / Europe call: +32 14 57 52 11 Emergency Number US :001-201-796-7100 / Europe : +32 14 57 52 99 CHEMTREC Tel. No. US :001-800-424-9300 / Europe :001-703-527-3887
E-mail address	begel.sdsdesk@thermofisher.com
Recommended Use	Laboratory chemicals.
Uses advised against	No Information available

SECTION 2. HAZARD IDENTIFICATION

Physical State	Appearance	Odor
Liquid	Brown	pungent
Emergency Overview		
Toxic if swallowed. Harmful in contact with skin. Causes skin irritation. Causes serious eye irritation. Suspected of causing genetic defects. May cause cancer. Toxic to aquatic life with long lasting effects. Sensitivity to light. Hygroscopic.		

Classification of the substance or mixture

Acute Oral Toxicity	Category 3
Acute Dermal Toxicity	Category 4
Skin Corrosion/Irritation	Category 2
Serious Eye Damage/Eye Irritation	Category 2
Germ Cell Mutagenicity	Category 2
Carcinogenicity	Category 1B
Chronic aquatic toxicity	Category 2

Label Elements

Quinoline



Signal Word

Danger

Hazard Statements

H301 - Toxic if swallowed
 H312 - Harmful in contact with skin
 H315 - Causes skin irritation
 H319 - Causes serious eye irritation
 H341 - Suspected of causing genetic defects
 H350 - May cause cancer
 H411 - Toxic to aquatic life with long lasting effects

Precautionary Statements**Prevention**

P201 - Obtain special instructions before use
 P202 - Do not handle until all safety precautions have been read and understood
 P264 - Wash face, hands and any exposed skin thoroughly after handling
 P270 - Do not eat, drink or smoke when using this product
 P280 - Wear eye protection/ face protection

Response

P301 + P310 - IF SWALLOWED: Immediately call a POISON CENTER or doctor
 P302 + P352 - IF ON SKIN: Wash with plenty of soap and water
 P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing
 P312 - Call a POISON CENTER or doctor if you feel unwell
 P330 - Rinse mouth
 P362 + P364 - Take off contaminated clothing and wash it before reuse

Storage

P405 - Store locked up

Disposal

P501 - Dispose of contents/ container to an approved waste disposal plant

Physical and Chemical Hazards

Hygroscopic.

Health Hazards

Toxic if swallowed. Harmful in contact with skin. Causes skin irritation. Causes serious eye irritation. Suspected of causing genetic defects. May cause cancer.

Environmental hazards

Toxic to aquatic life with long lasting effects. . Is not likely mobile in the environment due its low water solubility. .

This product does not contain any known or suspected endocrine disruptors.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Component	CAS No	Weight %
Quinoline	91-22-5	>95

SECTION 4. FIRST AID MEASURES

General Advice

Show this safety data sheet to the doctor in attendance. Immediate medical attention is required.

Eye Contact

Quinoline

In the case of contact with eyes, rinse immediately with plenty of water and seek medical advice.

Skin Contact

Immediate medical attention is required. Wash off immediately with plenty of water for at least 15 minutes.

Inhalation

Remove to fresh air. If breathing is difficult, give oxygen. Do not use mouth-to-mouth method if victim ingested or inhaled the substance; give artificial respiration with the aid of a pocket mask equipped with a one-way valve or other proper respiratory medical device. Immediate medical attention is required.

Ingestion

Do NOT induce vomiting. Call a physician or poison control center immediately.

Most important symptoms and effects

No information available.

Self-Protection of the First Aider

Use personal protective equipment as required.

Notes to Physician

Treat symptomatically.

SECTION 5. FIRE-FIGHTING MEASURES**Suitable Extinguishing Media**

Water spray, carbon dioxide (CO₂), dry chemical, alcohol-resistant foam.

Extinguishing media which must not be used for safety reasons

No information available.

Specific Hazards Arising from the Chemical

Containers may explode when heated. Keep product and empty container away from heat and sources of ignition. Thermal decomposition can lead to release of irritating gases and vapors.

Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear. Thermal decomposition can lead to release of irritating gases and vapors.

SECTION 6. ACCIDENTAL RELEASE MEASURES**Personal Precautions**

Use personal protective equipment as required. Ensure adequate ventilation. Evacuate personnel to safe areas. Keep people away from and upwind of spill/leak.

Environmental Precautions

Do not flush into surface water or sanitary sewer system. See Section 12 for additional Ecological Information. Avoid release to the environment. Collect spillage.

Methods for Containment and Clean Up

Soak up with inert absorbent material. Keep in suitable, closed containers for disposal.

Refer to protective measures listed in Sections 8 and 13.

SECTION 7. HANDLING AND STORAGE**Handling**

Use only under a chemical fume hood. Wear personal protective equipment/face protection. Do not get in eyes, on skin, or on

Quinoline

clothing. Do not breathe mist/vapors/spray. Do not ingest. If swallowed then seek immediate medical assistance.

Storage

Keep containers tightly closed in a dry, cool and well-ventilated place. Protect from direct sunlight.

Specific Use(s)

Use in laboratories

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control Parameters**Exposure Controls****Engineering Measures**

Use only under a chemical fume hood. Ensure adequate ventilation, especially in confined areas. Ensure that eyewash stations and safety showers are close to the workstation location. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

Personal protective equipment

Eye Protection Goggles (European standard - EN 166)

Hand Protection Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Natural rubber	See manufacturers recommendations	-	EN 374	(minimum requirement)
Nitrile rubber				
Neoprene				
PVC				

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

Skin and body protection Long sleeved clothing

Respiratory Protection When workers are facing concentrations above the exposure limit they must use appropriate certified respirators. To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly

Large scale/emergency use Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced
Recommended Filter type: Organic gases and vapours filter Type A Brown conforming to EN14387

Small scale/Laboratory use Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.
Recommended half mask:- Valve filtering: EN405; or; Half mask: EN140; plus filter, EN 141
When RPE is used a face piece Fit Test should be conducted

Hygiene Measures Handle in accordance with good industrial hygiene and safety practice.

Environmental exposure controls Prevent product from entering drains. Do not allow material to contaminate ground water

Quinoline

system.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance	Brown	
Physical State	Liquid	
Odor	pungent	
Odor Threshold	No data available	
pH	7.3	5 g/L aq.solution
Melting Point/Range	-15 °C / 5 °F	
Softening Point	No data available	
Boiling Point/Range	237 °C / 458.6 °F	
Flash Point	101 °C / 213.8 °F	Method - CC (closed cup)
Evaporation Rate	No data available	
Flammability (solid,gas)	Not applicable	Liquid
Explosion Limits	Lower 1.2 vol% Upper 7 vol%	
Vapor Pressure	<0.1 mbar @ 20 °C	
Vapor Density	4.45	(Air = 1.0)
Specific Gravity / Density	1.095 1.088	
Bulk Density	Not applicable	Liquid
Water Solubility	Slightly soluble	
Solubility in other solvents	No information available	
Partition Coefficient (n-octanol/water)		
Component	log Pow	
Quinoline	2.06	
Autoignition Temperature	480 °C / 896 °F	
Decomposition Temperature	No data available	
Viscosity	No data available	
Explosive Properties	Not explosive	
Oxidizing Properties	Not oxidising (based on the chemical structure of the substance and oxidation states of the constituent elements)	
Molecular Formula	C9 H7 N	
Molecular Weight	129.16	

SECTION 10. STABILITY AND REACTIVITY

Stability	Stable under normal conditions. Hygroscopic. Light sensitive.
Hazardous Reactions	None under normal processing.
Hazardous Polymerization	Hazardous polymerization does not occur.
Conditions to Avoid	Incompatible products. Excess heat. Exposure to moist air or water. Protect from light.
Materials to avoid	Strong oxidizing agents. Strong acids. nitrogen oxides (NOx). Peroxides.
Hazardous Decomposition Products	Nitrogen oxides (NOx). Carbon monoxide (CO). Carbon dioxide (CO ₂).

SECTION 11. TOXICOLOGICAL INFORMATION

Product Information

(a) acute toxicity;

Quinoline

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
Quinoline	270 mg/kg (Rat)	1370 mg/kg (Rat)	

(b) skin corrosion/irritation; Category 2

(c) serious eye damage/irritation; Category 2

(d) respiratory or skin sensitization;

Respiratory

Based on available data, the classification criteria are not met

Skin

Based on available data, the classification criteria are not met

(e) germ cell mutagenicity;

Category 2

Ames test:: positive

(f) carcinogenicity;

Category 1B

The European Union classifies this product as a carcinogen The table below indicates whether each agency has listed any ingredient as a carcinogen

Component	EU	UK	Germany	IARC
Quinoline	Carc Cat. 1B			Group 2B

(g) reproductive toxicity; Based on available data, the classification criteria are not met

(h) STOT-single exposure; Based on available data, the classification criteria are not met

(i) STOT-repeated exposure; Based on available data, the classification criteria are not met

Target Organs

None known.

(j) aspiration hazard;

Based on available data, the classification criteria are not met

Other Adverse Effects

See actual entry in RTECS for complete information

Symptoms / effects, both acute and delayed No information available

SECTION 12. ECOLOGICAL INFORMATION

Ecotoxicity effects

The product contains following substances which are hazardous for the environment. Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

Component	Freshwater Fish	Water Flea	Freshwater Algae	Microtox
Quinoline	40 mg/L LC50 96 h 46 mg/L LC50 96 h 77.8 mg/L LC50 96 h	45.9 - 57.3 mg/L EC50 48 h 28.5 mg/L EC50 = 48 h	51 mg/L EC50 = 4 h 84 mg/L EC50 = 72 h 90 mg/L EC50 = 96 h	EC50 34.34 - 130.29 mg/L 60 h

Persistence and Degradability

Persistence

May persist, based on information available.

Degradation in sewage treatment plant

Contains substances known to be hazardous to the environment or not degradable in waste water treatment plants.

Bioaccumulative Potential

May have some potential to bioaccumulate

Quinoline

Component	log Pow	Bioconcentration factor (BCF)
Quinoline	2.06	7.78 - 150 dimensionless

Mobility in soil Is not likely mobile in the environment due its low water solubility

Endocrine Disruptor Information This product does not contain any known or suspected endocrine disruptors

Persistent Organic Pollutant This product does not contain any known or suspected substance

Ozone Depletion Potential This product does not contain any known or suspected substance

SECTION 13. DISPOSAL CONSIDERATIONS

Waste from Residues/Unused Products Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.

Contaminated Packaging Dispose of this container to hazardous or special waste collection point.

Other Information Do not flush to sewer. Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains. Do not let this chemical enter the environment.

SECTION 14. TRANSPORT INFORMATION

Road and Rail Transport

UN-No UN2656
Proper Shipping Name QUINOLINE
Hazard Class 6.1
Packing Group III

IMDG/IMO

UN-No UN2656
Proper Shipping Name QUINOLINE
Hazard Class 6.1
Packing Group III

IATA

UN-No UN2656
Proper Shipping Name QUINOLINE
Hazard Class 6.1
Packing Group III

Special Precautions for User No special precautions required

SECTION 15. REGULATORY INFORMATION

International Inventories

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
Quinoline	X	X	X	X	202-051-6	X	X	X	X	X	X	X

Quinoline

National Regulations

SECTION 16. OTHER INFORMATION

Prepared By Health, Safety and Environmental Department
Creation Date 19-Apr-2012
Revision Date 07-Mar-2024
Revision Summary New emergency telephone response service provider.

Training Advice
Chemical incident response training.

Legend

CAS - Chemical Abstracts Service
EINECS/ELINCS - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances
PICCS - Philippines Inventory of Chemicals and Chemical Substances
IECSC - Chinese Inventory of Existing Chemical Substances
KECL - Korean Existing and Evaluated Chemical Substances
WEL - Workplace Exposure Limit
ACGIH - American Conference of Governmental Industrial Hygienists
DNEL - Derived No Effect Level
RPE - Respiratory Protective Equipment
LC50 - Lethal Concentration 50%
NOEC - No Observed Effect Concentration
PBT - Persistent, Bioaccumulative, Toxic
ICAO/IATA - International Civil Aviation Organization/International Air Transport Association
ADR - European Agreement Concerning the International Carriage of Dangerous Goods by Road
OECD - Organisation for Economic Co-operation and Development
BCF - Bioconcentration factor
TSCA - United States Toxic Substances Control Act Section 8(b) Inventory
DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List
ENCS - Japanese Existing and New Chemical Substances
AICS - Australian Inventory of Chemical Substances
NZIoC - New Zealand Inventory of Chemicals
TWA - Time Weighted Average
IARC - International Agency for Research on Cancer
PNEC - Predicted No Effect Concentration
LD50 - Lethal Dose 50%
EC50 - Effective Concentration 50%
POW - Partition coefficient Octanol:Water
vPvB - very Persistent, very Bioaccumulative
IMO/IMDG - International Maritime Organization/International Maritime Dangerous Goods Code
MARPOL - International Convention for the Prevention of Pollution from Ships
ATE - Acute Toxicity Estimate
VOC - (Volatile Organic Compound)

Key literature references and sources for data

<https://echa.europa.eu/information-on-chemicals>
Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet