

ALFAAA11801

## N-Ethyldiisopropylamine

### SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

<b>产品说明:</b> <b>Product Description:</b>	<b>N-乙基二异丙基胺</b> <b>N-Ethyldiisopropylamine</b>
<b>Cat No. :</b>	<b>A11801</b>
<b>Synonyms</b>	Huenig's base; N-Ethyldiisopropylamine
<b>CAS No</b>	7087-68-5
<b>Molecular Formula</b>	C8 H19 N
<b>Supplier</b>	Avocado Research Chemicals Ltd. (Part of Thermo Fisher Scientific) Shore Road, Heysham Lancashire, LA3 2XY, United Kingdom Office Tel: +44 (0) 1524 850506 Office Fax: +44 (0) 1524 850608
<b>Emergency Telephone Number</b>	For information <b>US</b> call: 001-800-227-6701 / <b>Europe</b> call: +32 14 57 52 11 Emergency Number <b>US</b> :001-201-796-7100 / <b>Europe</b> : +32 14 57 52 99 <b>CHEMTREC</b> Tel. No. <b>US</b> :001-800-424-9300 / <b>Europe</b> :001-703-527-3887
<b>E-mail address</b>	begel.sdsdesk@thermofisher.com
<b>Recommended Use</b>	Laboratory chemicals.
<b>Uses advised against</b>	No Information available

### SECTION 2. HAZARD IDENTIFICATION

<b>Physical State</b> Liquid	<b>Appearance</b> Light yellow	<b>Odor</b> No information available
<b>Emergency Overview</b>		
Highly flammable liquid and vapor. Causes severe skin burns and eye damage. Harmful if swallowed. Toxic if inhaled. May cause respiratory irritation.		

#### Classification of the substance or mixture

Flammable liquids.	Category 2
Acute Oral Toxicity	Category 4
Acute Inhalation Toxicity - Vapors	Category 3
Skin Corrosion/Irritation	Category 1
Serious Eye Damage/Eye Irritation	Category 1
Specific target organ toxicity - (single exposure)	Category 3

#### Label Elements

# SAFETY DATA SHEET

## N-Ethyl-diisopropylamine

**Signal Word****Danger****Hazard Statements**

H225 - Highly flammable liquid and vapor  
H314 - Causes severe skin burns and eye damage  
H302 - Harmful if swallowed  
H331 - Toxic if inhaled  
H335 - May cause respiratory irritation

**Precautionary Statements****Prevention**

P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking  
P234 - Keep only in original packaging  
P240 - Ground and bond container and receiving equipment  
P241 - Use explosion-proof electrical/ ventilating/ lighting equipment  
P242 - Use non-sparking tools  
P243 - Take action to prevent static discharges  
P261 - Avoid breathing dust/fume/gas/mist/vapors/spray  
P264 - Wash face, hands and any exposed skin thoroughly after handling  
P270 - Do not eat, drink or smoke when using this product  
P271 - Use only outdoors or in a well-ventilated area  
P280 - Wear protective gloves/protective clothing/eye protection/face protection

**Response**

P303 + P361 + P353 - IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water or shower  
P304 + P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing  
P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing  
P310 - Immediately call a POISON CENTER or doctor  
P330 - Rinse mouth  
P370 + P378 - In case of fire: Use dry sand, dry chemical or alcohol-resistant foam to extinguish  
P390 - Absorb spillage to prevent material damage

**Storage**

P402 - Store in a dry place  
P403 + P233 - Store in a well-ventilated place. Keep container tightly closed  
P406 - Store in corrosion resistant polypropylene container with a resistant inliner  
P405 - Store locked up

**Disposal**

P501 - Dispose of contents/ container to an approved waste disposal plant

**Physical and Chemical Hazards**

Vapors may cause flash fire or explosion. Highly flammable.

**Health Hazards**

Corrosive. Causes skin and eye burns. Causes serious eye damage. Harmful if swallowed. Toxic if inhaled. May cause respiratory irritation.

**Environmental hazards**

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants. Will likely be mobile in the environment due to its water solubility. The product is water soluble, and may spread in water systems.

**Other Hazards**

Toxic to terrestrial vertebrates. This product does not contain any known or suspected endocrine disruptors.

**SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS**

# SAFETY DATA SHEET

## N-Ethyldiisopropylamine

Component	CAS No	Weight %
2-Propanamine, N-ethyl-N-(1-methylethyl)-	7087-68-5	>95

### SECTION 4. FIRST AID MEASURES

#### General Advice

Show this safety data sheet to the doctor in attendance. Immediate medical attention is required.

#### Eye Contact

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Immediate medical attention is required.

#### Skin Contact

Wash off immediately with plenty of water for at least 15 minutes. Immediate medical attention is required.

#### Inhalation

Remove to fresh air. Do not use mouth-to-mouth method if victim ingested or inhaled the substance; give artificial respiration with the aid of a pocket mask equipped with a one-way valve or other proper respiratory medical device. Immediate medical attention is required. If not breathing, give artificial respiration.

#### Ingestion

Do NOT induce vomiting. Call a physician or poison control center immediately.

#### Most important symptoms and effects

Difficulty in breathing. Causes eye burns. Causes severe eye damage. Inhalation of high vapor concentrations may cause symptoms like headache, dizziness, tiredness, nausea and vomiting

#### Self-Protection of the First Aider

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

#### Notes to Physician

Treat symptomatically.

### SECTION 5. FIRE-FIGHTING MEASURES

#### Suitable Extinguishing Media

Water spray, carbon dioxide (CO<sub>2</sub>), dry chemical, alcohol-resistant foam. Water mist may be used to cool closed containers.

#### Extinguishing media which must not be used for safety reasons

Water may be ineffective.

#### Specific Hazards Arising from the Chemical

Flammable. Risk of ignition. Vapors may form explosive mixtures with air. Vapors may travel to source of ignition and flash back. Containers may explode when heated. Thermal decomposition can lead to release of irritating gases and vapors. Keep product and empty container away from heat and sources of ignition. In the event of fire and/or explosion do not breathe fumes.

#### Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear. Thermal decomposition can lead to release of irritating gases and vapors.

### SECTION 6. ACCIDENTAL RELEASE MEASURES

#### Personal Precautions

Use personal protective equipment as required. Ensure adequate ventilation. Keep people away from and upwind of spill/leak. Evacuate personnel to safe areas. Remove all sources of ignition. Take precautionary measures against static discharges.

#### Environmental Precautions

Should not be released into the environment. See Section 12 for additional Ecological Information.

### Methods for Containment and Clean Up

Soak up with inert absorbent material. Keep in suitable, closed containers for disposal. Remove all sources of ignition. Use spark-proof tools and explosion-proof equipment.

Refer to protective measures listed in Sections 8 and 13.

## SECTION 7. HANDLING AND STORAGE

### Handling

Wear personal protective equipment/face protection. Do not get in eyes, on skin, or on clothing. Use only under a chemical fume hood. Do not breathe mist/vapors/spray. Do not ingest. If swallowed then seek immediate medical assistance. Keep away from open flames, hot surfaces and sources of ignition. Use only non-sparking tools. To avoid ignition of vapors by static electricity discharge, all metal parts of the equipment must be grounded. Take precautionary measures against static discharges.

### Storage

Keep containers tightly closed in a dry, cool and well-ventilated place. Keep away from heat, sparks and flame. Flammables area.

### Specific Use(s)

Use in laboratories

## SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

### Control Parameters

### Monitoring methods

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS70 General methods for sampling airborne gases and vapours MDHS 88 Volatile organic compounds in air. Laboratory method using diffusive samplers, solvent desorption and gas chromatography MDHS 96 Volatile organic compounds in air - Laboratory method using pumped solid sorbent tubes, solvent desorption and gas chromatography

### Exposure Controls

### Engineering Measures

Use only under a chemical fume hood. Use explosion-proof electrical/ventilating/lighting equipment. Ensure that eyewash stations and safety showers are close to the workstation location. Ensure adequate ventilation, especially in confined areas. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

### Personal protective equipment

**Eye Protection** Goggles (European standard - EN 166)

**Hand Protection** Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Natural rubber	See manufacturers	-	EN 374	(minimum requirement)
Nitrile rubber	recommendations			
Neoprene				
PVC				

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger

## N-Ethyl-diisopropylamine

of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

<b>Skin and body protection</b>	Long sleeved clothing
<b>Respiratory Protection</b>	When workers are facing concentrations above the exposure limit they must use appropriate certified respirators. To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly
<b>Large scale/emergency use</b>	Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced <b>Recommended Filter type:</b> Particulates filter conforming to EN 143 Ammonia and organic ammonia derivatives filter Type K Green conforming to EN14387
<b>Small scale/Laboratory use</b>	Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced. <b>Recommended half mask:-</b> Valve filtering: EN405; or; Half mask: EN140; plus filter, EN 141 When RPE is used a face piece Fit Test should be conducted
<b>Hygiene Measures</b>	Handle in accordance with good industrial hygiene and safety practice.
<b>Environmental exposure controls</b>	No information available.

## SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

<b>Appearance</b>	Light yellow	
<b>Physical State</b>	Liquid	
<b>Odor</b>	No information available	
<b>Odor Threshold</b>	No data available	
<b>pH</b>	No information available	
<b>Melting Point/Range</b>	-46 °C / -50.8 °F	
<b>Softening Point</b>	No data available	
<b>Boiling Point/Range</b>	127 °C / 260.6 °F	@ 760 mmHg
<b>Flash Point</b>	6 °C / 42.8 °F	<b>Method -</b> No information available
<b>Evaporation Rate</b>	No data available	
<b>Flammability (solid,gas)</b>	Not applicable	Liquid
<b>Explosion Limits</b>	<b>Lower</b> 3 vol% <b>Upper</b> 17 vol%	
<b>Vapor Pressure</b>	14hPa @ 20°C	
<b>Vapor Density</b>	No data available	(Air = 1.0)
<b>Specific Gravity / Density</b>	0.7560	
<b>Bulk Density</b>	Not applicable	Liquid
<b>Water Solubility</b>	3.9 g/L (20°C)	
<b>Solubility in other solvents</b>	No information available	
<b>Partition Coefficient (n-octanol/water)</b>		
<b>Component</b>	<b>log Pow</b>	
2-Propanamine, N-ethyl-N-(1-methylethyl)-	-1.8	
<b>Autoignition Temperature</b>	260 °C / 500 °F	
<b>Decomposition Temperature</b>	No data available	
<b>Viscosity</b>	0.88 cSt @ 20°C	Kinematic
<b>Explosive Properties</b>		Vapors may form explosive mixtures with air
<b>Oxidizing Properties</b>	No information available	
<b>Molecular Formula</b>	C8 H19 N	
<b>Molecular Weight</b>	129.24	

### SECTION 10. STABILITY AND REACTIVITY

<b>Stability</b>	Stable under recommended storage conditions.
<b>Hazardous Reactions</b>	None under normal processing.
<b>Hazardous Polymerization</b>	Hazardous polymerization does not occur.
<b>Conditions to Avoid</b>	Incompatible products. Excess heat. Keep away from open flames, hot surfaces and sources of ignition.
<b>Materials to avoid</b>	Acids. Strong oxidizing agents. Metals. copper. Carbon dioxide (CO <sub>2</sub> ). Butyl rubber.
<b>Hazardous Decomposition Products</b>	Nitrogen oxides (NO <sub>x</sub> ). Carbon monoxide (CO). Carbon dioxide (CO <sub>2</sub> ). Thermal decomposition can lead to release of irritating gases and vapors.

### SECTION 11. TOXICOLOGICAL INFORMATION

#### Product Information

##### (a) acute toxicity;

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
2-Propanamine, N-ethyl-N-(1-methylethyl)-	317 mg/kg (Rat)		2.63 mg/L 4h ( Rat )

**(b) skin corrosion/irritation;** Based on available data, the classification criteria are not met

**(c) serious eye damage/irritation;** Category 1

##### (d) respiratory or skin sensitization;

**Respiratory**  
**Skin**

Based on available data, the classification criteria are not met  
Based on available data, the classification criteria are not met

**(e) germ cell mutagenicity;** Based on available data, the classification criteria are not met

**(f) carcinogenicity;** Based on available data, the classification criteria are not met  
There are no known carcinogenic chemicals in this product

**(g) reproductive toxicity;** Based on available data, the classification criteria are not met

**(h) STOT-single exposure;** Category 3

**Results / Target organs**

Respiratory system

**(i) STOT-repeated exposure;** Based on available data, the classification criteria are not met

**Target Organs**

None known.

**(j) aspiration hazard;** Based on available data, the classification criteria are not met

**Other Adverse Effects** The toxicological properties have not been fully investigated.

**Symptoms / effects, both acute and delayed** Inhalation of high vapor concentrations may cause symptoms like headache, dizziness, tiredness, nausea and vomiting

**N-Ethyl-diisopropylamine****SECTION 12. ECOLOGICAL INFORMATION**

**Ecotoxicity effects** Contains no substances known to be hazardous to the environment or that are not degradable in waste water treatment plants.

Component	Freshwater Fish	Water Flea	Freshwater Algae	Microtox
2-Propanamine, N-ethyl-N-(1-methylethyl)-	LC50: = 69.7 mg/L, 96h flow-through (Danio rerio)	>100 mg/L 48h		

**Persistence and Degradability** Not readily biodegradable  
**Persistence** Soluble in water, Persistence is unlikely, based on information available.

**Bioaccumulative Potential** Bioaccumulation is unlikely

Component	log Pow	Bioconcentration factor (BCF)
2-Propanamine, N-ethyl-N-(1-methylethyl)-	-1.8	No data available

**Mobility in soil** The product is water soluble, and may spread in water systems Will likely be mobile in the environment due to its water solubility Highly mobile in soils

**Endocrine Disruptor Information** This product does not contain any known or suspected endocrine disruptors  
**Persistent Organic Pollutant** This product does not contain any known or suspected substance  
**Ozone Depletion Potential** This product does not contain any known or suspected substance

**SECTION 13. DISPOSAL CONSIDERATIONS**

**Waste from Residues/Unused Products** Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.

**Contaminated Packaging** Dispose of this container to hazardous or special waste collection point. Empty containers retain product residue, (liquid and/or vapor), and can be dangerous. Keep product and empty container away from heat and sources of ignition.

**Other Information** Waste codes should be assigned by the user based on the application for which the product was used. Do not flush to sewer. Can be landfilled or incinerated, when in compliance with local regulations. Do not empty into drains.

**SECTION 14. TRANSPORT INFORMATION****Road and Rail Transport**

**UN-No** UN3384  
**Proper Shipping Name** TOXIC BY INHALATION LIQUID, FLAMMABLE, N.O.S.  
**Technical Shipping Name** N,N-Diisopropylethylamine  
**Hazard Class** 6.1  
**Subsidiary Hazard Class** 3  
**Packing Group** I

**IMDG/IMO**

**UN-No** UN3384  
**Proper Shipping Name** TOXIC BY INHALATION LIQUID, FLAMMABLE, N.O.S.  
**Technical Shipping Name** N,N-Diisopropylethylamine  
**Hazard Class** 6.1  
**Subsidiary Hazard Class** 3

# SAFETY DATA SHEET

## N-Ethyldiisopropylamine

<b>Packing Group</b>	
<b>IATA</b>	FORBIDDEN FOR IATA TRANSPORT
<b>UN-No</b>	UN3384
<b>Proper Shipping Name</b>	TOXIC BY INHALATION LIQUID, FLAMMABLE, N.O.S.* FORBIDDEN FOR IATA TRANSPORT
<b>Technical Shipping Name</b>	N,N-Diisopropylethylamine
<b>Hazard Class</b>	6.1
<b>Subsidiary Hazard Class</b>	3
<b>Packing Group</b>	I
<b>Special Precautions for User</b>	No special precautions required

### SECTION 15. REGULATORY INFORMATION

#### International Inventories

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
2-Propanamine, N-ethyl-N-(1-methylethyl)-	X	-	X	X	230-392-0	X	X	-	X	X	X	KE-10950

#### National Regulations

### SECTION 16. OTHER INFORMATION

<b>Prepared By</b>	Health, Safety and Environmental Department
<b>Creation Date</b>	09-Nov-2010
<b>Revision Date</b>	27-Apr-2024
<b>Revision Summary</b>	New emergency telephone response service provider.

#### Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

#### Legend

**CAS** - Chemical Abstracts Service

**EINECS/ELINCS** - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

**PICCS** - Philippines Inventory of Chemicals and Chemical Substances

**IECSC** - Chinese Inventory of Existing Chemical Substances

**KECL** - Korean Existing and Evaluated Chemical Substances

**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory

**DSL/NDSL** - Canadian Domestic Substances List/Non-Domestic Substances List

**ENCS** - Japanese Existing and New Chemical Substances

**AICS** - Australian Inventory of Chemical Substances

**NZIoC** - New Zealand Inventory of Chemicals



**N-Ethyldiisopropylamine**

**WEL** - Workplace Exposure Limit

**ACGIH** - American Conference of Governmental Industrial Hygienists

**DNEL** - Derived No Effect Level

**RPE** - Respiratory Protective Equipment

**LC50** - Lethal Concentration 50%

**NOEC** - No Observed Effect Concentration

**PBT** - Persistent, Bioaccumulative, Toxic

**TWA** - Time Weighted Average

**IARC** - International Agency for Research on Cancer

**PNEC** - Predicted No Effect Concentration

**LD50** - Lethal Dose 50%

**EC50** - Effective Concentration 50%

**POW** - Partition coefficient Octanol:Water

**vPvB** - very Persistent, very Bioaccumulative

**ICAO/IATA** - International Civil Aviation Organization/International Air Transport Association

**ADR** - European Agreement Concerning the International Carriage of Dangerous Goods by Road

**OECD** - Organisation for Economic Co-operation and Development

**BCF** - Bioconcentration factor

**IMO/IMDG** - International Maritime Organization/International Maritime Dangerous Goods Code

**MARPOL** - International Convention for the Prevention of Pollution from Ships

**ATE** - Acute Toxicity Estimate

**VOC** - (Volatile Organic Compound)

**Key literature references and sources for data**

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

**Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

**End of Safety Data Sheet**