

ALFAAA13135

Maleimide

SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

产品说明: Product Description:	马来酰亚胺 Maleimide
Cat No. :	A13135
Synonyms	2,5-Pyrroledione
CAS No	541-59-3
Molecular Formula	C4 H3 N O2
Supplier	Avocado Research Chemicals Ltd. (Part of Thermo Fisher Scientific) Shore Road, Heysham Lancashire, LA3 2XY, United Kingdom Office Tel: +44 (0) 1524 850506 Office Fax: +44 (0) 1524 850608
Emergency Telephone Number	For information US call: 001-800-227-6701 / Europe call: +32 14 57 52 11 Emergency Number US :001-201-796-7100 / Europe : +32 14 57 52 99 CHEMTREC Tel. No. US :001-800-424-9300 / Europe :001-703-527-3887
E-mail address	begel.sdsdesk@thermofisher.com
Recommended Use	Laboratory chemicals.
Uses advised against	No Information available

SECTION 2. HAZARD IDENTIFICATION

Physical State
Powder Solid

Appearance
Off-white

Odor
No information available

Emergency Overview

Causes severe skin burns and eye damage. Toxic if swallowed. Harmful in contact with skin. May cause an allergic skin reaction. Harmful if inhaled. Lachrymator (substance which increases the flow of tears).

Classification of the substance or mixture

Acute Oral Toxicity	Category 3
Acute Dermal Toxicity	Category 4
Acute Inhalation Toxicity - Dusts and Mists	Category 4
Skin Corrosion/Irritation	Category 1 B
Serious Eye Damage/Eye Irritation	Category 1
Skin Sensitization	Category 1

Label Elements

Maleimide

**Signal Word****Danger****Hazard Statements**

H301 - Toxic if swallowed
 H314 - Causes severe skin burns and eye damage
 H317 - May cause an allergic skin reaction
 H312 + H332 - Harmful in contact with skin or if inhaled

Precautionary Statements**Prevention**

P264 - Wash face, hands and any exposed skin thoroughly after handling
 P270 - Do not eat, drink or smoke when using this product
 P271 - Use only outdoors or in a well-ventilated area
 P272 - Contaminated work clothing should not be allowed out of the workplace
 P280 - Wear protective gloves/protective clothing/eye protection/face protection

Response

P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing
 P303 + P361 + P353 - IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water or shower
 P304 + P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing
 P310 - Immediately call a POISON CENTER or doctor
 P330 - Rinse mouth
 P331 - Do NOT induce vomiting
 P362 + P364 - Take off contaminated clothing and wash it before reuse

Storage

P403 + P233 - Store in a well-ventilated place. Keep container tightly closed
 P405 - Store locked up

Disposal

P501 - Dispose of contents/ container to an approved waste disposal plant

Physical and Chemical Hazards

None identified.

Health Hazards

Toxic if swallowed. Corrosive. Causes skin and eye burns. Harmful in contact with skin. May cause an allergic skin reaction. Harmful if inhaled. Lachrymator (substance which increases the flow of tears).

Environmental hazards

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants. Will likely be mobile in the environment due to its water solubility. The product is water soluble, and may spread in water systems.

Other Hazards

Lachrymator (substance which increases the flow of tears)
 This product does not contain any known or suspected endocrine disruptors.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Component	CAS No	Weight %
1H-Pyrrole-2,5-dione	541-59-3	98

SECTION 4. FIRST AID MEASURES**General Advice**

Show this safety data sheet to the doctor in attendance. Immediate medical attention is required.

Maleimide

Eye Contact

In the case of contact with eyes, rinse immediately with plenty of water and seek medical advice.

Skin Contact

Wash off immediately with plenty of water for at least 15 minutes. Immediate medical attention is required.

Inhalation

Remove to fresh air. If not breathing, give artificial respiration. Do not use mouth-to-mouth method if victim ingested or inhaled the substance; give artificial respiration with the aid of a pocket mask equipped with a one-way valve or other proper respiratory medical device. Immediate medical attention is required.

Ingestion

Do NOT induce vomiting. Call a physician or poison control center immediately.

Most important symptoms and effects

Causes burns by all exposure routes. May cause allergic skin reaction. Product is a corrosive material. Use of gastric lavage or emesis is contraindicated. Possible perforation of stomach or esophagus should be investigated: Ingestion causes severe swelling, severe damage to the delicate tissue and danger of perforation: Symptoms of allergic reaction may include rash, itching, swelling, trouble breathing, tingling of the hands and feet, dizziness, lightheadedness, chest pain, muscle pain or flushing

Self-Protection of the First Aider

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

Notes to Physician

Treat symptomatically.

SECTION 5. FIRE-FIGHTING MEASURES**Suitable Extinguishing Media**

Carbon dioxide (CO₂). Dry chemical. Chemical foam. CO₂, dry chemical, dry sand, alcohol-resistant foam.

Extinguishing media which must not be used for safety reasons

No information available.

Specific Hazards Arising from the Chemical

The product causes burns of eyes, skin and mucous membranes.

Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear. Thermal decomposition can lead to release of irritating gases and vapors.

SECTION 6. ACCIDENTAL RELEASE MEASURES**Personal Precautions**

Use personal protective equipment as required. Evacuate personnel to safe areas. Keep people away from and upwind of spill/leak. Ensure adequate ventilation. Avoid dust formation.

Environmental Precautions

Should not be released into the environment. See Section 12 for additional Ecological Information.

Methods for Containment and Clean Up

Sweep up and shovel into suitable containers for disposal. Avoid dust formation.

Refer to protective measures listed in Sections 8 and 13.

Maleimide

SECTION 7. HANDLING AND STORAGE

Handling

Do not get in eyes, on skin, or on clothing. Wear personal protective equipment/face protection. Use only under a chemical fume hood. Do not ingest. If swallowed then seek immediate medical assistance. Do not breathe (dust, vapor, mist, gas). Avoid dust formation.

Storage

Keep in a dry, cool and well-ventilated place. Keep container tightly closed. Corrosives area. Keep containers tightly closed in a dry, cool and well-ventilated place.

Specific Use(s)

Use in laboratories

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control Parameters**Monitoring methods**

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS14/3 General methods for sampling and gravimetric analysis of respirable and inhalable dust

Exposure Controls**Engineering Measures**

Ensure adequate ventilation, especially in confined areas. Ensure that eyewash stations and safety showers are close to the workstation location. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

Personal protective equipment

Eye Protection Goggles (European standard - EN 166)

Hand Protection Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Nitrile rubber	See manufacturers recommendations	-	EN 374	(minimum requirement)
Neoprene				
Natural rubber				
PVC				

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

Skin and body protection Long sleeved clothing

Respiratory Protection When workers are facing concentrations above the exposure limit they must use appropriate certified respirators. To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly

Large scale/emergency use Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced
Recommended Filter type: Particulates filter conforming to EN 143

Maleimide

Small scale/Laboratory use Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.
Recommended half mask:- Particle filtering: EN149:2001
 When RPE is used a face piece Fit Test should be conducted

Hygiene Measures Handle in accordance with good industrial hygiene and safety practice.

Environmental exposure controls No information available.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance	Off-white	
Physical State	Powder Solid	
Odor	No information available	
Odor Threshold	No data available	
pH	No information available	
Melting Point/Range	90 - 94 °C / 194 - 201.2 °F	
Softening Point	No data available	
Boiling Point/Range	No information available	
Flash Point	No information available	Method - No information available
Evaporation Rate	Not applicable	Solid
Flammability (solid,gas)	No information available	
Explosion Limits	No data available	
Vapor Pressure	No information available	
Vapor Density	Not applicable	Solid
Specific Gravity / Density	No data available	
Bulk Density	No data available	
Water Solubility	Soluble	
Solubility in other solvents	No information available	
Partition Coefficient (n-octanol/water)		
Autoignition Temperature	Not applicable	
Decomposition Temperature	No data available	
Viscosity	Not applicable	Solid
Explosive Properties	No information available	
Oxidizing Properties	No information available	
Molecular Formula	C4 H3 N O2	
Molecular Weight	97.07	

SECTION 10. STABILITY AND REACTIVITY

Stability Stable under normal conditions.

Hazardous Reactions None under normal processing.

Hazardous Polymerization Hazardous polymerization does not occur.

Conditions to Avoid Incompatible products.

Materials to avoid Strong oxidizing agents.

Hazardous Decomposition Products Nitrogen oxides (NO_x). Carbon monoxide (CO). Carbon dioxide (CO₂).

SECTION 11. TOXICOLOGICAL INFORMATION

Maleimide

Product Information**(a) acute toxicity;****(b) skin corrosion/irritation;** Category 1 B**(c) serious eye damage/irritation;** Category 1**(d) respiratory or skin sensitization;**

Respiratory No data available

Skin Category 1

No information available

(e) germ cell mutagenicity; No data available**(f) carcinogenicity;** No data available

There are no known carcinogenic chemicals in this product

(g) reproductive toxicity; No data available**(h) STOT-single exposure;** No data available**(i) STOT-repeated exposure;** No data available

Target Organs No information available.

(j) aspiration hazard; Not applicable
Solid**Other Adverse Effects** The toxicological properties have not been fully investigated.**Symptoms / effects, both acute and delayed** Product is a corrosive material. Use of gastric lavage or emesis is contraindicated. Possible perforation of stomach or esophagus should be investigated: Ingestion causes severe swelling, severe damage to the delicate tissue and danger of perforation: Symptoms of allergic reaction may include rash, itching, swelling, trouble breathing, tingling of the hands and feet, dizziness, lightheadedness, chest pain, muscle pain or flushing**SECTION 12. ECOLOGICAL INFORMATION****Ecotoxicity effects** Do not empty into drains.**Persistence and Degradability****Persistence** Soluble in water, Persistence is unlikely, based on information available.**Bioaccumulative Potential** Bioaccumulation is unlikely**Mobility in soil**

The product is water soluble, and may spread in water systems Will likely be mobile in the environment due to its water solubility Highly mobile in soils

Maleimide

Endocrine Disruptor Information This product does not contain any known or suspected endocrine disruptors
Persistent Organic Pollutant This product does not contain any known or suspected substance
Ozone Depletion Potential This product does not contain any known or suspected substance

SECTION 13. DISPOSAL CONSIDERATIONS

Waste from Residues/Unused Products Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.

Contaminated Packaging Dispose of this container to hazardous or special waste collection point.

Other Information Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains. Do not flush to sewer. Large amounts will affect pH and harm aquatic organisms.

SECTION 14. TRANSPORT INFORMATION

Road and Rail Transport

UN-No UN2923
Proper Shipping Name Corrosive solid, toxic, n.o.s.
Hazard Class 8
Subsidiary Hazard Class 6.1
Packing Group III

IMDG/IMO

UN-No UN2923
Proper Shipping Name Corrosive solid, toxic, n.o.s.
Hazard Class 8
Subsidiary Hazard Class 6.1
Packing Group III

IATA

UN-No UN2923
Proper Shipping Name CORROSIVE SOLID, TOXIC, N.O.S.*
Hazard Class 8
Subsidiary Hazard Class 6.1
Packing Group III

Special Precautions for User No special precautions required

SECTION 15. REGULATORY INFORMATION

International Inventories

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
1H-Pyrrole-2,5-dione	-	-	X	-	208-787-4	X	X	X	X	X	-	2008-1-586

National Regulations

Maleimide

SECTION 16. OTHER INFORMATION

Prepared By Health, Safety and Environmental Department
Revision Date 12-May-2024
Revision Summary New emergency telephone response service provider.

Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

Legend

CAS - Chemical Abstracts Service

EINECS/ELINCS - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

PICCS - Philippines Inventory of Chemicals and Chemical Substances

IECSC - Chinese Inventory of Existing Chemical Substances

KECL - Korean Existing and Evaluated Chemical Substances

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

ENCS - Japanese Existing and New Chemical Substances

AICS - Australian Inventory of Chemical Substances

NZIoC - New Zealand Inventory of Chemicals

WEL - Workplace Exposure Limit

ACGIH - American Conference of Governmental Industrial Hygienists

DNEL - Derived No Effect Level

RPE - Respiratory Protective Equipment

LC50 - Lethal Concentration 50%

NOEC - No Observed Effect Concentration

PBT - Persistent, Bioaccumulative, Toxic

TWA - Time Weighted Average

IARC - International Agency for Research on Cancer

PNEC - Predicted No Effect Concentration

LD50 - Lethal Dose 50%

EC50 - Effective Concentration 50%

POW - Partition coefficient Octanol:Water

vPvB - very Persistent, very Bioaccumulative

ICAO/IATA - International Civil Aviation Organization/International Air Transport Association

ADR - European Agreement Concerning the International Carriage of Dangerous Goods by Road

OECD - Organisation for Economic Co-operation and Development

BCF - Bioconcentration factor

IMO/IMDG - International Maritime Organization/International Maritime Dangerous Goods Code

MARPOL - International Convention for the Prevention of Pollution from Ships

ATE - Acute Toxicity Estimate

VOC - (Volatile Organic Compound)

Key literature references and sources for data

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet