

ALFAAA13178

n-Dodecyltrichlorosilane

SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

产品说明:
Product Description: 正十二烷基三氯硅烷
n-Dodecyltrichlorosilane

Cat No. : A13178
CAS No 4484-72-4
Molecular Formula C12 H25 Cl3 Si

Supplier Avocado Research Chemicals Ltd.
(Part of Thermo Fisher Scientific)
Shore Road, Heysham
Lancashire, LA3 2XY,
United Kingdom
Office Tel: +44 (0) 1524 850506
Office Fax: +44 (0) 1524 850608

Emergency Telephone Number For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11
Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99
CHEMTREC Tel. No. **US**:001-800-424-9300 / **Europe**:001-703-527-3887

E-mail address begel.sdsdesk@thermofisher.com

Recommended Use Laboratory chemicals.
Uses advised against No Information available

SECTION 2. HAZARD IDENTIFICATION

Physical State
Liquid

Appearance
Light yellow

Odor
pungent

Emergency Overview

Causes severe skin burns and eye damage. Reacts violently with water. Contact with water liberates toxic gas. Moisture sensitive.

Classification of the substance or mixture

Skin Corrosion/Irritation	Category 1 B
Serious Eye Damage/Eye Irritation	Category 1

Label Elements



Signal Word **Danger**

Hazard Statements
H314 - Causes severe skin burns and eye damage

Precautionary Statements**Prevention**

P264 - Wash face, hands and any exposed skin thoroughly after handling

P280 - Wear protective gloves/protective clothing/eye protection/face protection

Response

P301 + P330 + P331 - IF SWALLOWED: rinse mouth. Do NOT induce vomiting

P303 + P361 + P353 - IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water or shower

P304 + P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing

P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing

P310 - Immediately call a POISON CENTER or doctor

P362 + P364 - Take off contaminated clothing and wash it before reuse

Storage

P403 - Store in a well-ventilated place

Disposal

P501 - Dispose of contents/ container to an approved waste disposal plant

Physical and Chemical Hazards

Reacts violently with water.

Health Hazards

Corrosive. Causes skin and eye burns. Causes serious eye damage.

Environmental hazards

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants. Reacts violently with water. Will likely be mobile in the environment due to its water solubility. The product is water soluble, and may spread in water systems.

This product does not contain any known or suspected endocrine disruptors.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Component	CAS No	Weight %
Dodecyl trichlorosilane	4484-72-4	95

SECTION 4. FIRST AID MEASURES**Eye Contact**

Immediate medical attention is required. Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes.

Skin Contact

Wash off immediately with soap and plenty of water while removing all contaminated clothes and shoes. Immediate medical attention is required.

Inhalation

Remove from exposure, lie down. Remove to fresh air. If not breathing, give artificial respiration. Immediate medical attention is required.

Ingestion

Do NOT induce vomiting. Never give anything by mouth to an unconscious person. Drink plenty of water. Call a physician immediately. If possible drink milk afterwards.

Most important symptoms and effects

Causes burns by all exposure routes. Difficulty in breathing. Product is a corrosive material. Use of gastric lavage or emesis is contraindicated. Possible perforation of stomach or esophagus should be investigated: Ingestion causes severe swelling, severe damage to the delicate tissue and danger of perforation: Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting

Self-Protection of the First Aider

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of

contamination.

Notes to Physician

Treat symptomatically. Symptoms may be delayed.

SECTION 5. FIRE-FIGHTING MEASURES**Suitable Extinguishing Media**

Carbon dioxide (CO₂). Dry chemical. Chemical foam.

Extinguishing media which must not be used for safety reasons

No information available.

Specific Hazards Arising from the Chemical

Contact with water liberates toxic gas. Water reactive. Produce flammable gases on contact with water.

Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

SECTION 6. ACCIDENTAL RELEASE MEASURES**Personal Precautions**

Ensure adequate ventilation.

Environmental Precautions

See Section 12 for additional Ecological Information.

Methods for Containment and Clean Up

Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust). Keep in suitable, closed containers for disposal. Do not let this chemical enter the environment.

Refer to protective measures listed in Sections 8 and 13.

SECTION 7. HANDLING AND STORAGE**Handling**

Do not breathe mist/vapors/spray. Do not get in eyes, on skin, or on clothing. Do not ingest. If swallowed then seek immediate medical assistance. Handle product only in closed system or provide appropriate exhaust ventilation. Handle under inert gas, protect from moisture. Keep under nitrogen.

Storage

Keep in a dry, cool and well-ventilated place. Keep container tightly closed. Keep away from heat, sparks and flame. Protect from moisture. Corrosives area. Keep under nitrogen. Keep containers tightly closed in a dry, cool and well-ventilated place.

Specific Use(s)

Use in laboratories

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION**Control Parameters****Exposure Controls****Engineering Measures**

n-Dodecyltrichlorosilane

Ensure adequate ventilation, especially in confined areas. Ensure that eyewash stations and safety showers are close to the workstation location. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

Personal protective equipment

Eye Protection Goggles (European standard - EN 166)

Hand Protection Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Nitrile rubber	See manufacturers	-	EN 374	(minimum requirement)
Viton (R)	recommendations			

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

Skin and body protection Wear appropriate protective gloves and clothing to prevent skin exposure

Respiratory Protection When workers are facing concentrations above the exposure limit they must use appropriate certified respirators. To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly

Large scale/emergency use Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced
Recommended Filter type: Organic gases and vapours filter Type A Brown conforming to EN14387

Small scale/Laboratory use Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.
Recommended half mask:- Valve filtering: EN405; or; Half mask: EN140; plus filter, EN 141
When RPE is used a face piece Fit Test should be conducted

Hygiene Measures Handle in accordance with good industrial hygiene and safety practice.

Environmental exposure controls No information available.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance	Light yellow	
Physical State	Liquid	
Odor	pungent	
Odor Threshold	No data available	
pH	No information available	
Melting Point/Range	No data available	
Softening Point	No data available	
Boiling Point/Range	294 °C / 561.2 °F	
Flash Point	165 °C / 329 °F	Method - No information available
Evaporation Rate	No data available	
Flammability (solid,gas)	Not applicable	Liquid
Explosion Limits	No data available	
Vapor Pressure	<1 mm @ 25 °C	
Vapor Density	No data available	(Air = 1.0)

n-Dodecyltrichlorosilane

Specific Gravity / Density	1.028	
Bulk Density	Not applicable	Liquid
Water Solubility	insoluble in water, reacts with water	
Solubility in other solvents	No information available	
Partition Coefficient (n-octanol/water)		
Autoignition Temperature	No data available	
Decomposition Temperature	No data available	
Viscosity	No data available	
Explosive Properties	No information available	
Oxidizing Properties	No information available	
Molecular Formula	C ₁₂ H ₂₅ Cl ₃ Si	
Molecular Weight	303.77	

SECTION 10. STABILITY AND REACTIVITY

Stability	Stable under normal conditions. Moisture sensitive.
Hazardous Reactions	No information available.
Hazardous Polymerization	No information available.
Conditions to Avoid	Incompatible products. Exposure to moist air or water.
Materials to avoid	Acids. Strong oxidizing agents. Strong acids. Strong bases. Alcohols.
Hazardous Decomposition Products	Carbon monoxide (CO). Carbon dioxide (CO ₂). Silicon dioxide. Hydrogen chloride gas.

SECTION 11. TOXICOLOGICAL INFORMATION

Product Information	No acute toxicity information is available for this product
(a) acute toxicity;	
(b) skin corrosion/irritation;	Category 1 B
(c) serious eye damage/irritation;	Category 1
(d) respiratory or skin sensitization;	
Respiratory	No data available
Skin	No data available
(e) germ cell mutagenicity;	No data available
(f) carcinogenicity;	No data available
	There are no known carcinogenic chemicals in this product
(g) reproductive toxicity;	No data available
(h) STOT-single exposure;	No data available
(i) STOT-repeated exposure;	No data available

SAFETY DATA SHEET

n-Dodecyltrichlorosilane

Target Organs	No information available.
(j) aspiration hazard;	No data available
Other Adverse Effects	The toxicological properties have not been fully investigated.
Symptoms / effects, both acute and delayed	Product is a corrosive material. Use of gastric lavage or emesis is contraindicated. Possible perforation of stomach or esophagus should be investigated: Ingestion causes severe swelling, severe damage to the delicate tissue and danger of perforation: Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting

SECTION 12. ECOLOGICAL INFORMATION

Ecotoxicity effects	Do not empty into drains. .
Persistence and Degradability Persistence	Soluble in water, Persistence is unlikely, based on information available.
Bioaccumulative Potential	Bioaccumulation is unlikely
Mobility in soil	The product is water soluble, and may spread in water systems Will likely be mobile in the environment due to its water solubility Highly mobile in soils
Endocrine Disruptor Information Persistent Organic Pollutant Ozone Depletion Potential	This product does not contain any known or suspected endocrine disruptors This product does not contain any known or suspected substance This product does not contain any known or suspected substance

SECTION 13. DISPOSAL CONSIDERATIONS

Waste from Residues/Unused Products	Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.
Contaminated Packaging	Dispose of this container to hazardous or special waste collection point.
Other Information	Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains. Do not flush to sewer. Large amounts will affect pH and harm aquatic organisms.

SECTION 14. TRANSPORT INFORMATION

Road and Rail Transport

UN-No	UN1771
Proper Shipping Name	DODECYLTRICHLORO-SILANE
Hazard Class	8
Packing Group	II

IMDG/IMO

UN-No	UN1771
Proper Shipping Name	DODECYLTRICHLOROSILANE
Hazard Class	8
Packing Group	II

SAFETY DATA SHEET

n-Dodecyltrichlorosilane

IATA

UN-No UN1771
Proper Shipping Name DODECYLTRICHLOROSILANE
Hazard Class 8
Packing Group II

Special Precautions for User No special precautions required

SECTION 15. REGULATORY INFORMATION
International Inventories

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
Dodecyl trichlorosilane	X	X	X	X	224-769-9	X	-	X	X	X	X	-

National Regulations
SECTION 16. OTHER INFORMATION

Prepared By Health, Safety and Environmental Department
Revision Date 26-Apr-2024
Revision Summary New emergency telephone response service provider.

Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

Fire prevention and fighting, identifying hazards and risks, static electricity, explosive atmospheres posed by vapours and dusts.

Chemical incident response training.

Legend

CAS - Chemical Abstracts Service

EINECS/ELINCS - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

PICCS - Philippines Inventory of Chemicals and Chemical Substances

IECSC - Chinese Inventory of Existing Chemical Substances

KECL - Korean Existing and Evaluated Chemical Substances

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

ENCS - Japanese Existing and New Chemical Substances

AICS - Australian Inventory of Chemical Substances

NZIoC - New Zealand Inventory of Chemicals

WEL - Workplace Exposure Limit

ACGIH - American Conference of Governmental Industrial Hygienists

DNEL - Derived No Effect Level

RPE - Respiratory Protective Equipment

LC50 - Lethal Concentration 50%

NOEC - No Observed Effect Concentration

PBT - Persistent, Bioaccumulative, Toxic

TWA - Time Weighted Average

IARC - International Agency for Research on Cancer

PNEC - Predicted No Effect Concentration

LD50 - Lethal Dose 50%

EC50 - Effective Concentration 50%

POW - Partition coefficient Octanol:Water

vPvB - very Persistent, very Bioaccumulative

SAFETY DATA SHEET

n-Dodecyltrichlorosilane

ICAO/IATA - International Civil Aviation Organization/International Air Transport Association

ADR - European Agreement Concerning the International Carriage of Dangerous Goods by Road

OECD - Organisation for Economic Co-operation and Development

BCF - Bioconcentration factor

IMO/IMDG - International Maritime Organization/International Maritime Dangerous Goods Code

MARPOL - International Convention for the Prevention of Pollution from Ships

ATE - Acute Toxicity Estimate

VOC - (Volatile Organic Compound)

Key literature references and sources for data

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet