

ALFAAA13581

## 4-Aminophenol

### SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

**产品说明:** 4-氨基苯酚  
**Product Description:** 4-Aminophenol

**Cat No. :** A13581  
**Synonyms** 4-Amino-1-hydroxybenzene; 4-Hydroxyaniline  
**CAS No** 123-30-8  
**Molecular Formula** C6 H7 N O

**Supplier** Avocado Research Chemicals Ltd.  
(Part of Thermo Fisher Scientific)  
Shore Road, Heysham  
Lancashire, LA3 2XY,  
United Kingdom  
Office Tel: +44 (0) 1524 850506  
Office Fax: +44 (0) 1524 850608

**Emergency Telephone Number** For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11  
Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99  
**CHEMTREC** Tel. No. **US**:001-800-424-9300 / **Europe**:001-703-527-3887

**E-mail address** begel.sdsdesk@thermofisher.com

**Recommended Use** Laboratory chemicals.  
**Uses advised against** No Information available

### SECTION 2. HAZARD IDENTIFICATION

**Physical State**  
Solid

**Appearance**  
Beige

**Odor**  
Rotten-egg like

#### Emergency Overview

Suspected of causing genetic defects. Harmful to aquatic life. Very toxic to aquatic life with long lasting effects. Harmful if swallowed. Harmful if inhaled. Sensitivity to light. Air sensitive.

#### Classification of the substance or mixture

Acute Oral Toxicity	Category 4
Acute Inhalation Toxicity - Dusts and Mists	Category 4
Germ Cell Mutagenicity	Category 2
Acute aquatic toxicity	Category 1 Category 3
Chronic aquatic toxicity	Category 1

#### Label Elements



## 4-Aminophenol

**Signal Word****Warning****Hazard Statements**

H341 - Suspected of causing genetic defects  
H410 - Very toxic to aquatic life with long lasting effects  
H302 + H332 - Harmful if swallowed or if inhaled

**Precautionary Statements****Prevention**

P201 - Obtain special instructions before use  
P202 - Do not handle until all safety precautions have been read and understood  
P261 - Avoid breathing dust/fume/gas/mist/vapors/spray  
P264 - Wash face, hands and any exposed skin thoroughly after handling  
P270 - Do not eat, drink or smoke when using this product  
P271 - Use only outdoors or in a well-ventilated area  
P280 - Wear protective gloves/protective clothing/eye protection/face protection

**Response**

P301 + P312 - IF SWALLOWED: Call a POISON CENTER or doctor if you feel unwell  
P304 + P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing  
P308 + P313 - IF exposed or concerned: Get medical advice/attention  
P330 - Rinse mouth

**Storage**

P403 - Store in a well-ventilated place

**Disposal**

P501 - Dispose of contents/ container to an approved waste disposal plant

**Physical and Chemical Hazards**

None identified.

**Health Hazards**

Suspected of causing genetic defects. Harmful if swallowed. Harmful if inhaled.

**Environmental hazards**

Harmful to aquatic life. Very toxic to aquatic life with long lasting effects. . Will likely be mobile in the environment due to its water solubility. The product is water soluble, and may spread in water systems.

This product does not contain any known or suspected endocrine disruptors.

**SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS**

Component	CAS No	Weight %
p-Aminophenol	123-30-8	>95

**SECTION 4. FIRST AID MEASURES****General Advice**

If symptoms persist, call a physician.

**Eye Contact**

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.

**Skin Contact**

Wash off immediately with plenty of water for at least 15 minutes. If skin irritation persists, call a physician.

**Inhalation**

Remove to fresh air. If not breathing, give artificial respiration. Get medical attention if symptoms occur.

**Ingestion**

Clean mouth with water and drink afterwards plenty of water. Get medical attention if symptoms occur.

**Most important symptoms and effects**

## 4-Aminophenol

None reasonably foreseeable.

**Self-Protection of the First Aider**

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

**Notes to Physician**

Treat symptomatically.

**SECTION 5. FIRE-FIGHTING MEASURES****Suitable Extinguishing Media**

Water spray, carbon dioxide (CO<sub>2</sub>), dry chemical, alcohol-resistant foam.

**Extinguishing media which must not be used for safety reasons**

No information available.

**Specific Hazards Arising from the Chemical**

Do not allow run-off from fire-fighting to enter drains or water courses.

**Protective Equipment and Precautions for Firefighters**

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

**SECTION 6. ACCIDENTAL RELEASE MEASURES****Personal Precautions**

Ensure adequate ventilation. Use personal protective equipment as required. Avoid dust formation.

**Environmental Precautions**

Do not flush into surface water or sanitary sewer system. Do not allow material to contaminate ground water system. Prevent product from entering drains. Local authorities should be advised if significant spillages cannot be contained.

**Methods for Containment and Clean Up**

Sweep up and shovel into suitable containers for disposal. Keep in suitable, closed containers for disposal.

Refer to protective measures listed in Sections 8 and 13.

**SECTION 7. HANDLING AND STORAGE****Handling**

Wear personal protective equipment/face protection. Do not get in eyes, on skin, or on clothing. Avoid ingestion and inhalation. Avoid dust formation. Ensure adequate ventilation.

**Storage**

Keep containers tightly closed in a dry, cool and well-ventilated place. Protect from direct sunlight. Store under an inert atmosphere.

**Specific Use(s)**

Use in laboratories

**SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION****Control Parameters**

## 4-Aminophenol

**Monitoring methods**

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS14/3 General methods for sampling and gravimetric analysis of respirable and inhalable dust

**Exposure Controls****Engineering Measures**

Use only under a chemical fume hood. Ensure that eyewash stations and safety showers are close to the workstation location. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

**Personal protective equipment**

**Eye Protection** Goggles (European standard - EN 166)

**Hand Protection** Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Natural rubber	See manufacturers recommendations	-	EN 374	(minimum requirement)
Nitrile rubber				
Neoprene				
PVC				

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

**Skin and body protection** Wear appropriate protective gloves and clothing to prevent skin exposure

**Respiratory Protection** When workers are facing concentrations above the exposure limit they must use appropriate certified respirators.  
To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly

**Large scale/emergency use** Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced  
**Recommended Filter type:** Particulates filter conforming to EN 143

**Small scale/Laboratory use** Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.  
**Recommended half mask:-** Valve filtering: EN405; or; Half mask: EN140; plus filter, EN 141  
When RPE is used a face piece Fit Test should be conducted

**Hygiene Measures** Handle in accordance with good industrial hygiene and safety practice.

**Environmental exposure controls** Prevent product from entering drains. Do not allow material to contaminate ground water system. Local authorities should be advised if significant spillages cannot be contained.

**SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES**

**Appearance** Beige  
**Physical State** Solid

**Odor** Rotten-egg like  
**Odor Threshold** No data available

## 4-Aminophenol

<b>pH</b>	No information available	
<b>Melting Point/Range</b>	187 - 191 °C / 368.6 - 375.8 °F	
<b>Softening Point</b>	No data available	
<b>Boiling Point/Range</b>	284 °C / 543.2 °F	@ 760 mmHg
<b>Flash Point</b>	189 °C / 372.2 °F	<b>Method</b> - No information available
<b>Evaporation Rate</b>	Not applicable	Solid
<b>Flammability (solid,gas)</b>	No information available	
<b>Explosion Limits</b>	No data available	
<b>Vapor Pressure</b>	0.4 hPa @ 110 °C	
<b>Vapor Density</b>	Not applicable	Solid
<b>Specific Gravity / Density</b>	No data available	
<b>Bulk Density</b>	No data available	
<b>Water Solubility</b>	15 g/L (20°C)	
<b>Solubility in other solvents</b>	No information available	
<b>Partition Coefficient (n-octanol/water)</b>		
<b>Component</b>	<b>log Pow</b>	
p-Aminophenol	-0.09	
<b>Autoignition Temperature</b>	250 °C / 482 °F	
<b>Decomposition Temperature</b>	> 284°C	
<b>Viscosity</b>	Not applicable	Solid
<b>Explosive Properties</b>	No information available	
<b>Oxidizing Properties</b>	No information available	
<b>Molecular Formula</b>	C6 H7 N O	
<b>Molecular Weight</b>	109.13	

## SECTION 10. STABILITY AND REACTIVITY

<b>Stability</b>	Sensitivity to light. Air sensitive.
<b>Hazardous Reactions</b>	None under normal processing.
<b>Hazardous Polymerization</b>	Hazardous polymerization does not occur.
<b>Conditions to Avoid</b>	Incompatible products. Excess heat. Avoid dust formation. Protect from light. Exposure to air.
<b>Materials to avoid</b>	Strong oxidizing agents.

**Hazardous Decomposition Products** Carbon monoxide (CO). Carbon dioxide (CO<sub>2</sub>). Nitrogen oxides (NO<sub>x</sub>).

## SECTION 11. TOXICOLOGICAL INFORMATION

## Product Information

## (a) acute toxicity;

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
p-Aminophenol	LD50 = 375 mg/kg ( Rat )	LD50 > 8000 mg/kg ( Rabbit )	LC50 > 5.91 mg/m <sup>3</sup> ( Rat ) 1 h

(b) skin corrosion/irritation; No data available

(c) serious eye damage/irritation; No data available

## (d) respiratory or skin sensitization;

<b>Respiratory</b>	No data available
<b>Skin</b>	No data available

## 4-Aminophenol

<b>(e) germ cell mutagenicity;</b>	Category 2 Substances which cause concern for man owing to possible mutagenic effects but for which the available information is not adequate for making a satisfactory assessment
<b>(f) carcinogenicity;</b>	No data available There are no known carcinogenic chemicals in this product
<b>(g) reproductive toxicity;</b>	No data available
<b>(h) STOT-single exposure;</b>	No data available
<b>(i) STOT-repeated exposure;</b>	No data available
<b>Target Organs</b>	None known.
<b>(j) aspiration hazard;</b>	Not applicable Solid
<b>Symptoms / effects, both acute and delayed</b>	No information available

## SECTION 12. ECOLOGICAL INFORMATION

**Ecotoxicity effects** Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment. The product contains following substances which are hazardous for the environment.

Component	Freshwater Fish	Water Flea	Freshwater Algae	Microtox
p-Aminophenol	Onchorhynchus mykiss: LC50 = 1.2 mg/L 96h	200-280 mg/L 48h		EC50 = 0.77 mg/L 30 min EC50 = 0.81 mg/L 15 min EC50 = 0.91 mg/L 5 min

**Persistence and Degradability** Not readily biodegradable  
**Persistence** Persistence is unlikely.  
**Degradation in sewage treatment plant** Contains substances known to be hazardous to the environment or not degradable in waste water treatment plants.

**Bioaccumulative Potential** Bioaccumulation is unlikely

Component	log Pow	Bioconcentration factor (BCF)
p-Aminophenol	-0.09	15 - 46 dimensionless

**Mobility in soil** The product is water soluble, and may spread in water systems Will likely be mobile in the environment due to its water solubility Highly mobile in soils

**Endocrine Disruptor Information** This product does not contain any known or suspected endocrine disruptors  
**Persistent Organic Pollutant** This product does not contain any known or suspected substance  
**Ozone Depletion Potential** This product does not contain any known or suspected substance

## SECTION 13. DISPOSAL CONSIDERATIONS

## 4-Aminophenol

<b>Waste from Residues/Unused Products</b>	Should not be released into the environment. Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.
<b>Contaminated Packaging</b>	Dispose of this container to hazardous or special waste collection point.
<b>Other Information</b>	Do not flush to sewer. Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains. Do not let this chemical enter the environment.

## SECTION 14. TRANSPORT INFORMATION

Road and Rail Transport

<b>UN-No</b>	UN2512
<b>Proper Shipping Name</b>	AMINOPHENOLS
<b>Hazard Class</b>	6.1
<b>Packing Group</b>	III

IMDG/IMO

<b>UN-No</b>	UN2512
<b>Proper Shipping Name</b>	AMINOPHENOLS
<b>Hazard Class</b>	6.1
<b>Packing Group</b>	III

IATA

<b>UN-No</b>	UN2512
<b>Proper Shipping Name</b>	AMINOPHENOLS
<b>Hazard Class</b>	6.1
<b>Packing Group</b>	III

**Special Precautions for User** No special precautions required

## SECTION 15. REGULATORY INFORMATION

**International Inventories**

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
p-Aminophenol	X	-	X	X	204-616-2	X	X	X	X	X	X	KE-01529

**National Regulations**

## SECTION 16. OTHER INFORMATION

**4-Aminophenol**

<b>Prepared By</b>	Health, Safety and Environmental Department
<b>Creation Date</b>	02-Sep-2010
<b>Revision Date</b>	30-Apr-2024
<b>Revision Summary</b>	New emergency telephone response service provider.

**Training Advice**

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

Chemical incident response training.

**Legend**

**CAS** - Chemical Abstracts Service

**EINECS/ELINCS** - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

**PICCS** - Philippines Inventory of Chemicals and Chemical Substances

**IECSC** - Chinese Inventory of Existing Chemical Substances

**KECL** - Korean Existing and Evaluated Chemical Substances

**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory

**DSL/NDSL** - Canadian Domestic Substances List/Non-Domestic Substances List

**ENCS** - Japanese Existing and New Chemical Substances

**AICS** - Australian Inventory of Chemical Substances

**NZIoC** - New Zealand Inventory of Chemicals

**WEL** - Workplace Exposure Limit

**ACGIH** - American Conference of Governmental Industrial Hygienists

**DNEL** - Derived No Effect Level

**RPE** - Respiratory Protective Equipment

**LC50** - Lethal Concentration 50%

**NOEC** - No Observed Effect Concentration

**PBT** - Persistent, Bioaccumulative, Toxic

**TWA** - Time Weighted Average

**IARC** - International Agency for Research on Cancer

**PNEC** - Predicted No Effect Concentration

**LD50** - Lethal Dose 50%

**EC50** - Effective Concentration 50%

**POW** - Partition coefficient Octanol:Water

**vPvB** - very Persistent, very Bioaccumulative

**ICAO/IATA** - International Civil Aviation Organization/International Air Transport Association

**ADR** - European Agreement Concerning the International Carriage of Dangerous Goods by Road

**OECD** - Organisation for Economic Co-operation and Development

**BCF** - Bioconcentration factor

**IMO/IMDG** - International Maritime Organization/International Maritime Dangerous Goods Code

**MARPOL** - International Convention for the Prevention of Pollution from Ships

**ATE** - Acute Toxicity Estimate

**VOC** - (Volatile Organic Compound)

**Key literature references and sources for data**

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

**Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

**End of Safety Data Sheet**