

ALFAAA14064

4-(4-Hydroxyphenyl)-2-butanone

SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

产品说明: 4-(4-羟基苯基)2-丁酮
Product Description: 4-(4-Hydroxyphenyl)-2-butanone

Cat No. : A14064
Synonyms Raspberry keton
CAS No 5471-51-2
Molecular Formula C10 H12 O2

Supplier Avocado Research Chemicals Ltd.
(Part of Thermo Fisher Scientific)
Shore Road, Heysham
Lancashire, LA3 2XY,
United Kingdom
Office Tel: +44 (0) 1524 850506
Office Fax: +44 (0) 1524 850608

Emergency Telephone Number For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11
Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99
CHEMTREC Tel. No. **US**:001-800-424-9300 / **Europe**:001-703-527-3887

E-mail address begel.sdsdesk@thermofisher.com

Recommended Use Laboratory chemicals.
Uses advised against No Information available

SECTION 2. HAZARD IDENTIFICATION

Physical State
Solid

Appearance
Off-white

Odor
sweet

Emergency Overview
Harmful if swallowed.

Classification of the substance or mixture

Acute Oral Toxicity

Category 4

Label Elements



Signal Word

Warning

Hazard Statements

H302 - Harmful if swallowed

SAFETY DATA SHEET

4-(4-Hydroxyphenyl)-2-butanone

Precautionary Statements

Prevention

P264 - Wash face, hands and any exposed skin thoroughly after handling

P270 - Do not eat, drink or smoke when using this product

Response

P301 + P312 - IF SWALLOWED: Call a POISON CENTER or doctor if you feel unwell

P330 - Rinse mouth

Storage

P403 - Store in a well-ventilated place

Disposal

P501 - Dispose of contents/ container to an approved waste disposal plant

Physical and Chemical Hazards

None identified.

Health Hazards

Harmful if swallowed.

Environmental hazards

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants.

This product does not contain any known or suspected endocrine disruptors.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

| Component | CAS No | Weight % |
|----------------------------------|-----------|----------|
| 2-Butanone, 4-(4-hydroxyphenyl)- | 5471-51-2 | > 99 |

SECTION 4. FIRST AID MEASURES

Eye Contact

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes.

Skin Contact

Wash off immediately with soap and plenty of water while removing all contaminated clothes and shoes.

Inhalation

Remove from exposure, lie down. Remove to fresh air.

Ingestion

Do NOT induce vomiting. Never give anything by mouth to an unconscious person. Drink plenty of water. If possible drink milk afterwards.

Most important symptoms and effects

No information available.

Self-Protection of the First Aider

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

Notes to Physician

Treat symptomatically.

SECTION 5. FIRE-FIGHTING MEASURES

Suitable Extinguishing Media

Water spray. Carbon dioxide (CO₂). Dry chemical. Alcohol resistant foam.

Extinguishing media which must not be used for safety reasons

No information available.

Specific Hazards Arising from the Chemical

Thermal decomposition can lead to release of irritating gases and vapors.

Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear. Thermal decomposition can lead to release of irritating gases and vapors.

SECTION 6. ACCIDENTAL RELEASE MEASURES**Personal Precautions**

Ensure adequate ventilation.

Environmental Precautions

See Section 12 for additional Ecological Information.

Methods for Containment and Clean Up

Sweep up and shovel into suitable containers for disposal.

Refer to protective measures listed in Sections 8 and 13.

SECTION 7. HANDLING AND STORAGE**Handling**

Avoid contact with skin and eyes. Avoid contact with skin and clothing. Remove and wash contaminated clothing and gloves, including the inside, before re-use. Avoid breathing vapors or mists. Do not ingest. If swallowed then seek immediate medical assistance. Wash thoroughly after handling.

Storage

Keep in a dry, cool and well-ventilated place. Keep container tightly closed.

Specific Use(s)

Use in laboratories

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION**Control Parameters****Monitoring methods**

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS14/3 General methods for sampling and gravimetric analysis of respirable and inhalable dust

Exposure Controls**Engineering Measures**

Ensure adequate ventilation, especially in confined areas. Ventilation systems. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

Personal protective equipment**Eye Protection**

Wear safety glasses with side shields (or goggles) (European standard - EN 166)

Hand Protection

Protective gloves

4-(4-Hydroxyphenyl)-2-butanone

| Glove material | Breakthrough time | Glove thickness | EU standard | Glove comments |
|----------------|-----------------------------------|-----------------|-------------|-----------------------|
| Nitrile rubber | See manufacturers recommendations | - | EN 374 | (minimum requirement) |
| Neoprene | | | | |
| Natural rubber | | | | |
| PVC | | | | |

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

| | |
|-----------------------------------|---|
| Skin and body protection | Long sleeved clothing |
| Respiratory Protection | No protective equipment is needed under normal use conditions. |
| Large scale/emergency use | Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced |
| Small scale/Laboratory use | Maintain adequate ventilation |

Hygiene Measures Handle in accordance with good industrial hygiene and safety practice.

Environmental exposure controls No information available.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

| | | |
|--|-------------------------------|--|
| Appearance | Off-white | |
| Physical State | Solid | |
| Odor | sweet | |
| Odor Threshold | No data available | |
| pH | No information available | |
| Melting Point/Range | 82 - 84 °C / 179.6 - 183.2 °F | |
| Softening Point | No data available | |
| Boiling Point/Range | No information available | |
| Flash Point | No information available | Method - No information available |
| Evaporation Rate | Not applicable | Solid |
| Flammability (solid,gas) | No information available | |
| Explosion Limits | No data available | |
| Vapor Pressure | No information available | |
| Vapor Density | Not applicable | Solid |
| Specific Gravity / Density | No data available | |
| Bulk Density | No data available | |
| Water Solubility | No information available | |
| Solubility in other solvents | No information available | |
| Partition Coefficient (n-octanol/water) | | |
| Component | log Pow | |
| 2-Butanone, 4-(4-hydroxyphenyl)- | 1.33 | |
| Autoignition Temperature | No data available | |
| Decomposition Temperature | No data available | |
| Viscosity | Not applicable | Solid |
| Explosive Properties | No information available | |
| Oxidizing Properties | No information available | |
| Molecular Formula | C10 H12 O2 | |

SAFETY DATA SHEET

4-(4-Hydroxyphenyl)-2-butanone

Molecular Weight 164.2

SECTION 10. STABILITY AND REACTIVITY

Stability Stable under normal conditions.

Hazardous Reactions No information available.
Hazardous Polymerization No information available.

Conditions to Avoid Incompatible products.

Materials to avoid Strong oxidizing agents. Oxidizing agent.

Hazardous Decomposition Products Thermal decomposition can lead to release of irritating gases and vapors. Carbon monoxide (CO). Carbon dioxide (CO₂).

SECTION 11. TOXICOLOGICAL INFORMATION

Product Information

(a) acute toxicity;

| Component | LD50 Oral | LD50 Dermal | LC50 Inhalation |
|----------------------------------|---------------------------|---------------------------|-----------------|
| 2-Butanone, 4-(4-hydroxyphenyl)- | LD50 = 1320 mg/kg (Rat) | LD50 > 2000 mg/kg (Rat) | |

(b) skin corrosion/irritation; No data available

(c) serious eye damage/irritation; No data available

(d) respiratory or skin sensitization;
Respiratory No data available
Skin No data available

(e) germ cell mutagenicity; No data available

(f) carcinogenicity; No data available
 There are no known carcinogenic chemicals in this product

(g) reproductive toxicity; No data available

(h) STOT-single exposure; No data available

(i) STOT-repeated exposure; No data available
Target Organs No information available.

(j) aspiration hazard; Not applicable
 Solid

Symptoms / effects, both acute and delayed No information available

4-(4-Hydroxyphenyl)-2-butanone

SECTION 12. ECOLOGICAL INFORMATION

Ecotoxicity effects

.

Persistence and Degradability No information available

Bioaccumulative Potential No information available

| Component | log Pow | Bioconcentration factor (BCF) |
|----------------------------------|---------|-------------------------------|
| 2-Butanone, 4-(4-hydroxyphenyl)- | 1.33 | No data available |

Mobility in soil No information available

Endocrine Disruptor Information This product does not contain any known or suspected endocrine disruptors

Persistent Organic Pollutant This product does not contain any known or suspected substance

Ozone Depletion Potential This product does not contain any known or suspected substance

SECTION 13. DISPOSAL CONSIDERATIONS

Waste from Residues/Unused Products Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.

Contaminated Packaging Dispose of this container to hazardous or special waste collection point.

Other Information Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains.

SECTION 14. TRANSPORT INFORMATION

Road and Rail Transport Not Regulated

IMDG/IMO Not regulated

IATA Not regulated

Special Precautions for User No special precautions required

SECTION 15. REGULATORY INFORMATION

International Inventories

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

| Component | The Inventory of Hazardous Chemicals (2015 Edition) | List of dangerous goods GB 12268 - 2012 | TCSI | IECSC | EINECS | TSCA | DSL | PICCS | ENCS | ISHL | AICS | KECL |
|----------------------------------|---|---|------|-------|-----------|------|-----|-------|------|------|------|----------|
| 2-Butanone, 4-(4-hydroxyphenyl)- | - | - | X | X | 226-806-4 | X | X | X | X | X | X | KE-20801 |

National Regulations**SECTION 16. OTHER INFORMATION**

Prepared By Health, Safety and Environmental Department
Revision Date 12-May-2024
Revision Summary New emergency telephone response service provider.

Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

Legend

CAS - Chemical Abstracts Service

EINECS/ELINCS - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

PICCS - Philippines Inventory of Chemicals and Chemical Substances

IECSC - Chinese Inventory of Existing Chemical Substances

KECL - Korean Existing and Evaluated Chemical Substances

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

ENCS - Japanese Existing and New Chemical Substances

AICS - Australian Inventory of Chemical Substances

NZIoC - New Zealand Inventory of Chemicals

WEL - Workplace Exposure Limit

ACGIH - American Conference of Governmental Industrial Hygienists

DNEL - Derived No Effect Level

RPE - Respiratory Protective Equipment

LC50 - Lethal Concentration 50%

NOEC - No Observed Effect Concentration

PBT - Persistent, Bioaccumulative, Toxic

TWA - Time Weighted Average

IARC - International Agency for Research on Cancer

PNEC - Predicted No Effect Concentration

LD50 - Lethal Dose 50%

EC50 - Effective Concentration 50%

POW - Partition coefficient Octanol:Water

vPvB - very Persistent, very Bioaccumulative

ICAO/IATA - International Civil Aviation Organization/International Air Transport Association

ADR - European Agreement Concerning the International Carriage of Dangerous Goods by Road

OECD - Organisation for Economic Co-operation and Development

BCF - Bioconcentration factor

IMO/IMDG - International Maritime Organization/International Maritime Dangerous Goods Code

MARPOL - International Convention for the Prevention of Pollution from Ships

ATE - Acute Toxicity Estimate

VOC - (Volatile Organic Compound)

Key literature references and sources for data

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet